

NOTES:



1. RESISTANCE @ 25°C : 10KΩ ± 1%
2. BETA VALUE (0/50°C) : 3892K ± 1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
4. THERMAL TIME CONSTANT : 15SEC IN WATER
5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
7. DISSIPATION FACTOR : 1mW/°C.
8. LASER MARKING "MOLEX-DATE CODE(MM/YY)" & "XXK(R25-value) XXXX(B-value)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex
	△/A = 0	mm	NTS		
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 727818		GLASS NTC PROBE A -10K±1%,B3892,L300
	△/E = 0	ANGULAR TOL ± °		DRWN: NANDAK 2022/11/09	
DIVISIONAL SYMBOLS	△/F = 0	4 PLACES	±	CHK'D: RBBHASKAR 2022/11/15	PRODUCT CUSTOMER DRAWING
		3 PLACES	±	APPR: RBBHASKAR 2022/11/15	
		2 PLACES	±	INITIAL REVISION:	DOCUMENT NUMBER
		1 PLACE	±	DRWN: RAVIKM 2022/01/28	2185353609
	0 PLACES	±	APPR: RBBHASKAR 2022/02/18	PSD	DOC PART
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SHEET NUMBER
		A3-SIZE		SERIES	1 OF 2
		218535		MATERIAL NUMBER	
		2185353609		CUSTOMER	
		GENERAL MARKET			

RESISTANCE VS TEMPERATURE CHARACTERISTICS

TEMP (°C)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)
-40	355.513	339.798	324.748
-35	254.681	244.229	234.182
-30	184.656	177.642	170.877
-25	135.412	130.669	126.080
-20	100.370	97.142	94.008
-15	75.154	72.945	70.795
-10	56.815	55.298	53.817
-05	43.344	42.298	41.276
00	33.352	32.634	31.928
05	25.876	25.383	24.896
10	20.233	19.896	19.562
15	15.939	15.720	15.483
20	12.645	12.492	12.340
25	10.100	10.000	9.900
30	8.154	8.056	7.959
35	6.624	6.531	6.438
40	5.412	5.325	5.239
45	4.446	4.366	4.287
50	3.672	3.600	3.528
55	3.049	2.983	2.917
60	2.5439	2.4839	2.4250
65	2.1325	2.0784	2.0256
70	1.7957	1.7472	1.6998
75	1.5188	1.4752	1.4328
80	1.2900	1.2510	1.2130
85	1.1002	1.0651	1.0311
90	0.9420	0.9106	0.8801
95	0.8096	0.7814	0.7541
100	0.6984	0.6730	0.6486
105	0.6046	0.5818	0.5598
110	0.5252	0.5047	0.4849
115	0.4577	0.4393	0.4215
120	0.4003	0.3836	0.3676
125	0.3511	0.3360	0.3216
130	0.3089	0.2953	0.2822
135	0.2726	0.2602	0.2484
140	0.2412	0.2300	0.2193
145	0.2141	0.2039	0.1941
150	0.1905	0.1812	0.1723

TEMP (°C)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)
155	0.1700	0.1615	0.1534
160	0.1521	0.1443	0.1369
165	0.1364	0.1293	0.1225
170	0.1226	0.1161	0.1099
175	0.1105	0.1045	0.0988
180	0.0998	0.0943	0.0891
185	0.0903	0.0853	0.0805
190	0.0820	0.0773	0.0729
195	0.0745	0.0702	0.0662
200	0.0679	0.0639	0.0602
205	0.0620	0.0583	0.0548
210	0.0567	0.0533	0.0501
215	0.0520	0.0488	0.0458
220	0.0478	0.0448	0.0420
225	0.0440	0.0412	0.0386
230	0.0406	0.0380	0.0356
235	0.0375	0.0351	0.0328
240	0.0347	0.0324	0.0303
245	0.0322	0.0300	0.0281
250	0.0299	0.0279	0.0260

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:				
	$\nabla_A = 0$ $\nabla_E = 0$ $\nabla_Z = 0$	DIMENSION UNITS mm					
DIVISIONAL SYMBOLS	4 PLACES ±	EC NO: 727818	2022/11/09	GLASS NTC PROBE A -10K±1%,B3892,L300			
	3 PLACES ±	DRWN: NANDAK	2022/11/15				
	2 PLACES ±	CHK'D: RBBHASKAR	2022/11/15	PRODUCT CUSTOMER DRAWING			
	1 PLACE ±	APPR: RBBHASKAR	2022/11/15				
0 PLACES ±	INITIAL REVISION:	DRWN: RAVIKM	2022/01/28	DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE	218535	2185353609	GENERAL MARKET	2 OF 2