


ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	5023800400	1.25 W/B Single Plg Hsg 4Ckt	2	PC
C	5023810000	1.25 W/B Single Plg Term W/Pit	8	PC
D	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	B1	1X26AWG DISC BK	BLACK
A2	B2	1X26AWG DISC BK	BLACK
A3	B3	1X26AWG DISC BK	BLACK
A4	B4	1X26AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240911042	CLIK-Mate 1.25 R-R 4ckt 150mm disc Sn	150±5	15
2240911043	CLIK-Mate 1.25 R-R 4ckt 300mm disc Sn	300±5	15
2240911044	CLIK-Mate 1.25 R-R 4ckt 600mm disc Sn	600±5	15

MOLEX P/N  
MOLEX  
BATCH WK/YR

**DETAIL A**

- NOTES**
1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
  2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
  3. LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
  4. LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	C	INITIAL RELEASE	THANUB

RELEASE STATUS	P1	RELEASE DATE	2023/05/05	16:46:44
----------------	----	--------------	------------	----------

<b>FUNCTIONAL SYMBOLS</b> $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		<b>molex</b>  SEE TABLE		
	DIMENSION UNITS	SCALE			
	mm	NTS	EC NO: 745876		
	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: THANUB 2023/04/11		
ANGULAR TOL ± °		CHK'D: BCAPPS 2023/05/05			
4 PLACES ±		APPR: BCAPPS 2023/05/05			
3 PLACES ±		INITIAL REVISION:			
2 PLACES ±		DRWN: THANUB 2023/01/15			
1 PLACE ±		APPR: SKUMAR07 2023/02/06			
0 PLACES ±		DOCUMENT NUMBER			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER
			A4-SIZE	224091	2240911040
					CUSTOMER
					GENERAL MARKET
					SHEET NUMBER
					1 OF 1