


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 52756	07/23	SEE PDM



COMPONENTS:

- CONNECTORS** SMPM FEMALE R/A (3222-40006)
 SMPM FEMALE (3221-40007)
- CABLE:** FLEXIBLE Ø.047 CABLE (200-70-479)
- SHRINK TUBING:** M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 40.0 GHz.

MATERIAL: SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1'0" X"X' ±15'	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		<div style="text-align: center;"></div> TITLE: SMPM FEMALE R/A TO SMPM FEMALE 12" CABLE ASSEMBLY FOR Ø.047 CABLE SIZE DWG. NO. B 7032-9725 SCALE: 4:1	
FINISH: SEE NOTES		DECIMAL: X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994				
SURFACE AREA: N/A		THIRD ANGLE PROJECTION	DRAWN: KRR 05/10/23 CHECKED: SEE PDM APPROVED: SEE PDM		SHEET 1 OF 1	
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.			SCALE: 4:1			