


Bi-Directional Digital/Analogue Audio Converter



The AU-D9 is a versatile audio converter allowing users to convert analogue audio into digital or digital audio into analogue. It can simultaneously output in all 3 audio formats without any signal loss.

Features

- Bi-directional Digital/Analogue Audio Converter.
- Three-way conversion: Coaxial to Optical & Analogue; Optical to Coaxial & Analogue; Analogue to Optical & Coaxial.
- Integrated digital interpolator filter and Digital-to-Analog Converter (DAC).
- Accepts uncompressed digital stereo audio input.
- Supports sample rates from 16 to 100kHz.
- Simultaneous digital & analogue audio outputs.
- Provides electromagnetic-noise-free transmission.



Specifications

Input:	1 x Coaxial (RCA) 1 x Optical (Toslink) 2 x RCA (Left/Right Audio)
Output:	1 x Coaxial (RCA) 1 x Optical (Toslink) 2 x RCA (Left/Right Audio)
Power:	5V/1A DC (US/EU standards, CE/FCC/UL certified)
Dimensions:	95m (W) x 85mm (D) x 35mm (H)
Gross Weight:	420g
Net. Weight:	200g
Packaging:	Boxed

