

---

**SECTION I - PRODUCT AND COMPANY IDENTIFICATION**

---

TRADE NAME: PA6 L BLK

CAS NUMBER: MIXTURE

EC NUMBER: MIXTURE

MANUFACTURER: Information Phone: 0086-21-5729-7268

NanShi Knobs Factory Emergency Phone: 0086-136-0169-0961

NanShi JinShan District

Shanghai China 201515

PREPARED BY: Bruce Zhang MSDS COORDINATOR

Tang LianSheng MSDS MANAGER

---

**SECTION II - COMPOSITION/INFORMATION ON INGREDIENTS**

---

PRODUCT CLASS: NYLON 6

CHEMICAL NAME AND SYNONYMS: Nylon 6, Polyamide 6,  
Polycaprolactam.

HAZARDOUS CAS WEIGHT EXPOSURE LIMITS VP

INGREDIENTS # % ACGIH/TLV OSHA/PEL mmHG

---

**SECTION III - HAZARDS IDENTIFICATION**

---

HAZARD RATINGS: Health: 0 Fire: 1 Reactivity: 0 PPI: A

PERMISSIBLE EXPOSURE LEVEL:

This is a polymeric compound. All ingredients are encapsulated by the polymer and present no likelihood of exposure under normal conditions of processing and handling.

EFFECTS OF OVEREXPOSURE:

ACUTE OR IMMEDIATE EFFECTS:

INGESTION: Not a probable route of exposure.

SKIN: Pellets are not likely to cause irritation.

Contact with molten material may cause thermal burns.

Processing fumes may cause irritation.

EYE: Solid/dust may cause irritation due to mechanical action.

Processing fumes may cause irritation.

(cont.)

---

**SECTION III - HAZARDS IDENTIFICATION (cont.)**

---

**EFFECTS OF OVEREXPOSURE: (cont.)**

**INHALATION:** Processing fumes may cause irritation to the respiratory tract.

**CHRONIC EFFECTS:** None known for this compound.

---

**SECTION IV - FIRST AID MEASURES**

---

**FIRST AID:**

**EYES:** Flush with water. Consult physician if symptoms persist.

**SKIN:** Wash with soap and water. For thermal burns, immediately flush with cold water. Do not attempt to remove polymer from skin. Obtain medical attention.

**INHALATION:** Leave exposed area and seek fresh air. If irritation persists seek medical attention.

---

**SECTION V - FIREFIGHTING MEASURES**

---

**FLAMMABILITY CLASS:** 1 **FLASH POINT:** None **LEL:** None **UEL:** None

**EXTINGUISHING MEDIA:**

Water spray and foam. Water spray is preferred.

Dry chemical and CO<sub>2</sub> are not generally recommended due to their lack of cooling capacity which may allow re-ignition.

**SPECIAL FIREFIGHTING PROCEDURES:**

Persons exposed to products of combustion should wear NIOSH approved self contained breathing apparatus and full protective equipment.

**UNUSUAL FIRE & EXPLOSION HAZARDS:**

This compound has no unusual fire or explosion hazards.

---

**SECTION VI - ACCIDENTAL RELEASE MEASURES**

---

**STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED:**

Spilled pellets may cause a slipping hazard. Sweep area as needed.

---

**SECTION VII - HANDLING AND STORAGE**

---

**PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING:**

Store in a dry, sprinkler equipped warehouse.

(cont.)

---

**SECTION VII - HANDLING AND STORAGE (cont.)**

---

**PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING: (cont.)**

Product as shipped is not a combustible dust. Mechanical handling can cause the formation of dusts. To reduce the risk for dust explosion do not permit dust to accumulate.

**OTHER PRECAUTIONS:**

Proper purging and shut down procedures should be followed to avoid overheating of this compound.

---

**SECTION VIII - EXPOSURE CONTROLS/PERSONAL PROTECTION**

---

**RESPIRATORY PROTECTION:**

A NIOSH approved respirator is recommended for protection against processing fumes, or from dust generated from grinding, sanding, or sawing operations.

**VENTILATION:**

Local exhaust is preferred.

**PROTECTIVE GLOVES:**

Canvas or cotton gloves are recommended.

**EYE PROTECTION:**

Safety glasses with side shields are recommended.

**OTHER PROTECTIVE EQUIPMENT:**

None.

---

**SECTION IX - PHYSICAL AND CHEMICAL PROPERTIES**

---

**BOILING RANGE:** None **VAPOR DENSITY:** Non Volatile

**EVAP. RATE:** Unavailable **SPECIFIC GRAVITY:** 1.13

**VOLATILES:** volume %: N/AP weight %: N/AP

**APPEARANCE:** Cylindrical Pellets No Odor

---

**SECTION X - STABILITY AND REACTIVITY**

---

**STABILITY:** [ ] Unstable [x] Stable

**HAZARDOUS POLYMERIZATION:** [ ] May Occur [x] Will Not Occur

**INCOMPATIBILITY:**

Strong acids, bases, and oxidizing agents.

**CONDITIONS TO AVOID:**

Avoid temperatures above 300 C (572 F).

---

SECTION X - STABILITY AND REACTIVITY (cont.)

---

HAZARDOUS DECOMPOSITION PRODUCTS:

Carbon monoxide, carbon dioxide, ammonia, and trace amounts of aldehydes and hydrogen cyanide.

---

SECTION XI - TOXICOLOGICAL INFORMATION

---

TOXICITY DATA:

No specific toxicological information is available.

---

SECTION XII - ECOLOGICAL INFORMATION

---

ECOTOXICITY:

No specific ecological information is available. This material is considered to be non-biodegradable.

---

SECTION XIII - DISPOSAL CONSIDERATIONS

---

WASTE DISPOSAL METHOD:

The pellets, regrind, and purge of this material are nonhazardous and may be discarded in accordance with state, federal, and local regulations.

---

SECTION XIV - TRANSPORT INFORMATION

---

D.O.T. SHIPPING INFORMATION:

Not regulated under US Department of Transportation.

---

SECTION XV - REGULATORY INFORMATION

---

SARA TITLE III SECTION 313:

This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right To Know Act of 1986 and of 40 CFR 372:

NONE

---

SECTION XVI - OTHER INFORMATION

---

MSDS DISCLAIMER

NanShi Company believes that the information contained herein is accurate as of the date hereof. HOWEVER, NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESSED OR IMPLIED, OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE ARE MADE HEREIN AS TO THE INFORMATION PROVIDED OR THE PRODUCT TO WHICH THE INFORMATION REFERS. The health and safety precautions contained herein may not be adequate for all individuals and/or situations. It is the user's obligation to evaluate and use this product safely and to comply with all applicable laws and regulations. Nothing contained herein shall be construed as a license for the use of any product in a manner that would infringe existing patents.