

FOMBLIN® GREASE YNX

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

- Product name : FOMBLIN® GREASE YNX

1.2. Relevant identified uses of the substance or mixture and uses advised against

- Identified uses : - Lubricant
- For industrial use only.

1.3. Details of the supplier of the safety data sheet

- Company : SOLVAY SPECIALTY POLYMERS ITALY S.p.A.
- Address : VIALE LOMBARDIA, 20
I- 20021 BOLLATE
- Telephone : +390238351
- Fax : +390238352614
- E-mail address : sds.solexis@solvay.com

1.4. Emergency telephone number

- Emergency telephone number +44(0)1235 239 670 [CareChem 24] (Europe)

SECTION 2. HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

2.1.1. European regulation (EC) 1272/2008, as amended

Not classified as hazardous according to the European regulation (EC) 1272/2008, as amended

2.1.2. European Directive 67/548/EEC or 1999/45/EC, as amended

Not classified as hazardous according to European Directive 67/548/EEC or 1999/45/EC, as amended

2.2. Label elements

No labelling

2.3. Other hazards

- Thermal decomposition can lead to release of toxic and corrosive gases.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Concentration

| Substance name: | Concentration |
|--|---------------|
| 1-Propene, 1,1,2,3,3,3-hexafluoro-, oxidized, polymd. | % |
| CAS-No.: 69991-67-9 / EC-No.: - / Index-No.: - | |
| Talc | % |
| CAS-No.: 14807-96-6 / EC-No.: 238-877-9 / Index-No.: - | |



SECTION 4. FIRST AID MEASURES

4.1. Description of first aid measures

4.1.1. If inhaled

- Move to fresh air in case of accidental inhalation of fumes from overheating or combustion.
- Oxygen or artificial respiration if needed.

4.1.2. In case of eye contact

- Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
- If eye irritation persists, consult a specialist.

4.1.3. In case of skin contact

- Wash off with soap and water.

4.1.4. If swallowed

- Drink 1 or 2 glasses of water.
- Do NOT induce vomiting.
- If symptoms persist, call a physician.

4.2. Most important symptoms and effects, both acute and delayed

4.2.1. Inhalation

- No known effect.

4.2.2. Skin contact

- Redness

4.2.3. Eye contact

- Contact with eyes may cause irritation.
- Redness

4.2.4. Ingestion

- Ingestion may provoke the following symptoms:
- Symptoms: Nausea, Vomiting, Diarrhoea

4.3. Indication of any immediate medical attention and special treatment needed

- None.

SECTION 5. FIRE-FIGHTING MEASURES

5.1. Extinguishing media

5.1.1. Suitable extinguishing media

- Water
- powder
- Foam
- Dry chemical
- Carbon dioxide (CO₂)

5.1.2. Unsuitable extinguishing media

- None.

5.2. Special hazards arising from the substance or mixture

- The product is not flammable.
- Not explosive
- In case of fire hazardous decomposition products may be produced such as: Gaseous hydrogen fluoride (HF), Fluorophosgene

5.3. Advice for firefighters

- Wear self-contained breathing apparatus and protective suit.
- When intervention in close proximity wear acid resistant over suit.
- Evacuate personnel to safe areas.
- Approach from upwind.
- Protect intervention team with a water spray as they approach the fire.
- Keep containers and surroundings cool with water spray.
- Keep product and empty container away from heat and sources of ignition.



SECTION 6. ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. Advice for non-emergency personnel

- Prevent further leakage or spillage if safe to do so.

6.1.2. Advice for emergency responders

- Ensure adequate ventilation.
- Material can create slippery conditions.
- Sweep up to prevent slipping hazard.
- Keep away from open flames, hot surfaces and sources of ignition.

6.2. Environmental precautions

- Should not be released into the environment.
- Do not flush into surface water or sanitary sewer system.

6.3. Methods and materials for containment and cleaning up

- Soak up with inert absorbent material.
- Suitable material for picking up
- Dry sand
- Earth
- Shovel into suitable container for disposal.

6.4. Reference to other sections

- Refer to protective measures listed in sections 7 and 8.

SECTION 7. HANDLING AND STORAGE

7.1. Precautions for safe handling

- No special handling advice required.
- Ensure adequate ventilation.
- Use personal protective equipment.
- Keep away from heat and sources of ignition.
- To avoid thermal decomposition, do not overheat.
- Take measures to prevent the build up of electrostatic charge.
- Clean and dry piping circuits and equipment before any operations.
- Ensure all equipment is electrically grounded before beginning transfer operations.

7.2. Conditions for storage, including incompatibilities

7.2.1. Storage

- No special storage conditions required.
- Keep away from heat and sources of ignition.
- Keep in properly labelled containers.
- Keep away from combustible material.
- Keep away from incompatible products
- Provide tight electrical equipment well protected against corrosion.
- Refer to protective measures listed in sections 7 and 8.

7.2.2. Packaging material

7.2.2.1. *Suitable material*

- Plastic material

7.3. Specific end uses

- For further information, please contact: Supplier

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

8.1.1. Exposure Limit Values

Remarks:

- Threshold limit values of by-products from thermal decomposition

Hydrogen fluoride anhydrous

- UK. EH40 Workplace Exposure Limits (WELs) 2007
time weighted average = 1.8 ppm



- time weighted average = 1.5 mg/m³
Remarks: as F
- UK. EH40 Workplace Exposure Limits (WELs) 2007
Short term exposure limit = 3 ppm
Short term exposure limit = 2.5 mg/m³
Remarks: as F
 - US. ACGIH Threshold Limit Values 2009
time weighted average = 0.5 ppm
Remarks: as F
 - US. ACGIH Threshold Limit Values 2009
Ceiling Limit Value = 2 ppm
Remarks: as F
 - EU. Indicative Exposure and Directives relating to the protection of risks related to work exposure to chemical, physical, and biological agents. 12 2009
time weighted average = 1.8 ppm
time weighted average = 1.5 mg/m³
Remarks: Indicative
 - EU. Indicative Exposure and Directives relating to the protection of risks related to work exposure to chemical, physical, and biological agents. 12 2009
Short term exposure limit = 3 ppm
Short term exposure limit = 2.5 mg/m³
Remarks: Indicative
 - US. ACGIH Threshold Limit Values 2009
Remarks: as F, Can be absorbed through skin.

Carbonyl difluoride

- US. ACGIH Threshold Limit Values 2009
time weighted average = 2 ppm
- US. ACGIH Threshold Limit Values 2009
Short term exposure limit = 5 ppm
- UK. EH40 Workplace Exposure Limits (WELs) 2007
time weighted average = 2.5 mg/m³
Remarks: as F
- EU. Indicative Exposure and Directives relating to the protection of risks related to work exposure to chemical, physical, and biological agents. 12 2009
time weighted average = 2.5 mg/m³
Remarks: Indicative

8.2. Exposure controls

8.2.1. Appropriate engineering controls

- Provide local ventilation appropriate to the product decomposition risk (see section 10).
- Refer to protective measures listed in sections 7 and 8.
- Apply technical measures to comply with the occupational exposure limits.

8.2.2. Individual protection measures

8.2.2.1. *Respiratory protection*

- No personal respiratory protective equipment normally required.
- Use respirator when performing operations involving potential exposure to vapour of the product.
- Use only respiratory protection that conforms to international/ national standards.

8.2.2.2. *Hand protection*

- Rubber or plastic gloves
- Latex gloves
- Take note of the information given by the producer concerning permeability and break through times, and of special workplace conditions (mechanical strain, duration of contact).

8.2.2.3. *Eye protection*

- Tightly fitting safety goggles

8.2.2.4. *Skin and body protection*

- Long sleeved clothing
- Safety shoes

8.2.2.5. *Hygiene measures*

- Ensure that eyewash stations and safety showers are close to the workstation location.
- When using do not eat, drink or smoke.
- Wash hands before breaks and at the end of workday.
- Handle in accordance with good industrial hygiene and safety practice.



8.2.3. Environmental exposure controls

- Dispose of rinse water in accordance with local and national regulations.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**9.1. Information on basic physical and chemical properties**9.1.1. General Information

- | | |
|--------------------------|------------|
| ▪ Appearance | paste |
| ▪ Colour | colourless |
| ▪ Odour | odourless |
| ▪ Odour Threshold | No data |

9.1.2. Important health safety and environmental information

- | | |
|---|---|
| ▪ pH | No data |
| ▪ pKa | No data |
| ▪ Melting point/freezing point | not applicable |
| ▪ Boiling point/boiling range | no data available |
| ▪ Flash point | The product is not flammable. |
| ▪ Evaporation rate | No data |
| ▪ Flammability (solid, gas) | No data |
| ▪ Flammability | The product is not flammable. |
| ▪ Explosive properties | Not explosive |
| ▪ Vapour pressure | 0.0013 hPa, at 20 °C |
| ▪ Vapour density | No data |
| ▪ Density | 1.90 g/cm ³ Temperature: 20 °C |
| ▪ Relative density | No data |
| ▪ Bulk density | No data |
| ▪ Solubility(ies) | insoluble, Water soluble, fluorinated solvents |
| ▪ Solubility/qualitative | No data |
| ▪ Partition coefficient: n-octanol/water | No data |
| ▪ Autoignition temperature | No data |
| ▪ Decomposition temperature | > 290 °C |
| ▪ Viscosity | No data |
| ▪ Oxidizing properties | Non oxidizer |

9.2. Other information

| | |
|---------|---------|
| Remarks | No data |
|---------|---------|

SECTION 10. STABILITY AND REACTIVITY**10.1. Reactivity**

- No dangerous reaction known under conditions of normal use.

10.2. Chemical stability

- Stable under recommended storage conditions.



- Metals promote and lower decomposition temperature
- In presence of titanium and its alloys the decomposition temperature decreases to 260°C.

10.3. Possibility of hazardous reactions

- No dangerous reaction known under conditions of normal use.

10.4. Conditions to avoid

- To avoid thermal decomposition, do not overheat.
- Keep away from flames and sparks.

10.5. Incompatible materials

- Lewis acids (Friedel-Crafts) above 100°C, Aluminum and magnesium in powder form above 200°C

10.6. Hazardous decomposition products

- Gaseous hydrogen fluoride (HF)., Fluorophosgene

SECTION 11. TOXICOLOGICAL INFORMATION

11.1. Acute toxicity

11.1.1. Acute oral toxicity

- LD50, rat, > 5,000 mg/kg (Perfluorinated polyethers)

11.1.2. Acute inhalation toxicity

- no data available

11.1.3. Acute dermal toxicity

- LD50, rat, > 2,000 mg/kg (Perfluorinated polyethers)

11.2. Skin corrosion/irritation

- rabbit, No skin irritation (Perfluorinated polyethers)

11.3. Serious eye damage/eye irritation

- rabbit, No eye irritation (Perfluorinated polyethers)

11.4. Respiratory or skin sensitization

- guinea pig, Did not cause sensitization on laboratory animals. (Perfluorinated polyethers), Skin

11.5. Mutagenicity

- Not mutagenic in Ames Test. (Perfluorinated polyethers)

11.6. Carcinogenicity

- no data available

11.7. Toxicity for reproduction

- no data available

11.8. Repeated dose toxicity

- Dermal, 14 days , rabbit, No skin irritation, (Perfluorinated polyethers)
- 28-day , rat, > 1000 mg/kg/day, (Perfluorinated polyethers)

11.9. Other information

- Description of possible hazardous to health effects is based on experience and/or toxicological characteristics of several components.
- Thermal decomposition can lead to release of toxic and corrosive gases.
- Exposure to decomposition products
- Causes severe irritation of eyes, skin and mucous membranes.

SECTION 12. ECOLOGICAL INFORMATION

12.1. Toxicity

- Oncorhynchus mykiss (rainbow trout), LC50, 96 h, > 370 mg/l, static test, 200 ppm, saturated aqueous solution (Perfluorinated polyethers)
- Daphnia magna (Water flea), EC50, 48 h, > 370 mg/l, saturated aqueous solution (Perfluorinated polyethers)
- no data available

12.2. Persistence and degradability

12.2.1. Abiotic degradation

- Result: no data available



12.2.2. Biodegradation

- no data available

12.3. Bioaccumulative potential

- Result: no data available

12.4. Mobility

- no data available

12.5. PBT and vPvB assessment

- no data available

12.6. Other adverse effects

- Ecological injuries are not known or expected under normal use.

SECTION 13. DISPOSAL CONSIDERATIONS**13.1. Waste disposal methods**

- Can be incinerated, when in compliance with local regulations.
- The incinerator must be equipped with a system for the neutralisation or recovery of HF.
- In accordance with local and national regulations.

13.2. Contaminated packaging

- Empty containers can be landfilled, when in accordance with the local regulations.

SECTION 14. TRANSPORT INFORMATION**14.1. International transport regulations**

- Sea (IMO/IMDG)
- not regulated
- Air (ICAO/IATA)
- not regulated
- European Road/Rail (ADR/RID)
- not regulated
- Inland waterway transport
- not regulated

SECTION 15. REGULATORY INFORMATION**15.1. Applicable Laws or Regulations**

- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, as amended
- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), as amended
- European Waste Catalogue
- Waste codes should be assigned by the user based on the application for which the product was used.

15.2. Chemical Safety Assessment

- No data

SECTION 16. OTHER INFORMATION**16.1. Other information**

- New (MSDS)
- Distribute new edition to clients

This SDS is only intended for the indicated country to which it is applicable. The European SDS format compliant with the applicable European legislation is not intended for use nor distribution in countries outside the European Union with the exception of Norway and Switzerland. Safety datasheets applicable in other countries/regions are available upon request. The information given corresponds to the current state of our knowledge and experience of the product, and is not exhaustive. This applies to product which conforms to the specification, unless otherwise stated. In this case of combinations and mixtures one must make sure that no new dangers can arise. In any case, the user is not exempt from observing all legal, administrative and regulatory procedures relating to the product, personal hygiene, and protection of human welfare and the environment.



Print Date: 17.02.2012

