



**PORTABLE STAND-ALONE PA SYSTEM 15"/38CM WITH USB-MP3, REC, VOX, BLUETOOTH, 2 VHF MICS**

**PORT15VHF-BT**

In addition to its exceptional sound quality for this product category, this portable system offers important features such as an included rechargeable battery and dual power supply (12V & 220V), a retractable handle and wheels. It offers total freedom of movement in any application due to the 2 wireless VHF microphones (headset and hand-held mics, a remote control and various in- and outputs to suit all kinds of sources including USB/MP3, SD/MMC & iPod ports.

- USB MP3 / WMA / BLUETOOTH player
- 2 x VHF microphones (handheld 207.5MHz & headset 203.5MHz)
- 1x remote control
- REC function
- VOX function
- Bass & Treble controls
- Volume & ECHO controls for the microphone
- Music volume control
- MIC & LINE inputs
- MP3 & iPod inputs
- Built-in charger & RECHARGEABLE BATTERY
- Handle & wheels for ease of transport
- Transmission distance of the VHF mics: 25-30m outdoors at free sight, 10-15m indoors

**EAN  
CODE**

**5420047116192  
15-6022**

**SPECIFICATIONS TECHNIQUES**

Max. power	800W
RMS power	400W
Sensitivity :	99dB
Freq. range :	35Hz - 20kHz
Power supply:	220-240Vcc / 50-60Hz
Dimensions:	12W 7.2Ah (BAT-PORT7.2A)
Battery	482x442x730mm



**LOGISTICS VALUES**

Height	66 cm
Width	43 cm
Depth	38 cm
Volume	0.107844 m <sup>3</sup>
Net weight	17.14 kg
Packaging height	73.5 cm
Packaging width	48.5 cm
Packaging depth	45.5 cm
Packaging volume	0.162 m <sup>3</sup>
Packaging gross weight	19.49 kg
Master carton height	75.5 cm
Master carton width	45.5 cm
Master carton depth	49 cm
Master carton net weight	17.14 kg
Master carton gross weight	20.66 kg
Palette hauteur	1.985 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per master carton	1
nb uvc par palette	8
nb couches parpalette	4
nb cartons par couche	2
Customs code	85185000

