



## LIGHT STAND FITTED WITH 2x RGBW PAR CANS + 2x RED & GREEN LASERS

### DJLIGHT65

The set contains following items:

- 2 x PAR cans fitted with 12x 1W RGBW LEDs
- 2 x 130mW Red & Green Lasers
- Crossbar that powers the PAR cans
- 3/7/11-channel DMX, master-slave, auto & remote control
- Remote control
- Black stand with anti-slip feet
- Power cable 4m
- Pre-mounted DMX signal cable on all light effects

**EAN  
CODE**

**5420047131416  
15-1184**

### SPECIFICATIONS TECHNIQUES

Height	1.80m max.
Power supply	220-240V~ 50/60Hz
Consumption	60W
Laser	Red: 100mW; green 30mW
Laser class	3
Weight	6.7kg



### LOGISTICS VALUES

Height	90.5 cm
Width	24 cm
Depth	17 cm
Volume	6E-06 m <sup>3</sup>
Net weight	6.3 kg
Packaging height	92 cm
Packaging width	37.5 cm
Packaging depth	19 cm
Packaging volume	0.066 m <sup>3</sup>
Packaging gross weight	7.35 kg
Master carton height	92 cm
m carton largeur	37.5 cm
m carton profondeur	19 cm
m carton volume	0.06555 m <sup>3</sup>
m carton poids net	7.35 kg
m carton poids brut	7.35 kg
Palette hauteur	1.96 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per shipping box	1
nb uvc par palette	24
Customs code	94054099

