Regulation EC No 1907/2006 Art.31

Creationdate: 04.03.21 Version: 3.1 Productname: AMBERCLENS FG Ref.Nr.: BDS000316 3 20210304 (EN) Replaces: BDS000316 20180503

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERCLENS FG

Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd. Wylds Road **Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom**

Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail: hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosol, category 3

Pressurised container: May burst if heated.

Classification is based on test data.

Health: Serious eye damage, category 1

Causes serious eye damage.

Classification based on calculation method. **Environment:** Not classified Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008



Regulation EC No 1907/2006 Art.31

AMBERCLENS FG Creationdate: 04.03.21 Version: 3.1 Productname: Ref.Nr.: Replaces: BDS000316 20180503 BDS000316 3 20210304 (EN)

Product identifier: Contains:

Alcolhol C10, ethoxylated

Hazard pictogram(s):

Signal word: Danger

Hazard statement(s): H229: Pressurised container: May burst if heated.

H318: Causes serious eye damage.

Precautionary statement(s): P102: Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other

ignition sources. No smoking.

P251: Do not pierce or burn, even after use.

P305/351/338: IF IN EYES: Rinse cautiously with water for several minutes.

Remove contact lenses, if present and easy to do. Continue rinsing.

P313: Get medical advice/attention.

P410/412: Protect from sunlight. Do not expose to temperatures exceeding

50°C/122°F.

P501-2: Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information:

7 % by mass of the contents are flammable.

Regulation (EC) No 648/2004 on detergents:

aliphatic hydrocarbons< 5 %

anionic surfactants < 5 % non-ionic surfactants < 5 %

> benzisothiazolinone, methylchloroisothiazolinone, methylisothiazolinone, methylisothiazolinone,

methylchloroisothiazolinone

Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Alcolhol C10, ethoxylated	-	26183- 52-8	500- 046-6	1-5	Acute Tox. 4, Eye Dam. 1	H302,H318	F,X
(2-methoxymethylethoxy)propanol	01-2119450011- 60	34590- 94-8	252- 104-2	1-5	-	-	А
Hydrocarbons.C3-4-rich, petroleum distillate	01-2119485926-	68512-	270-	1-5	Press. Gas. Flam.	H280.H220	K.G



Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

Creationdate: 04.03.21 Version: 3.1 Productname: AMBERCLENS FG Ref.Nr.: BDS000316 20180503 BDS000316 3 20210304 (EN) Replaces:

Petroleumgas (1,3-butadiene < 0.1%)	20	91-4	990-9		Gas 1	
Explanation notes						
A : substance with Community workplace exposu	re limit					
F : not registered due to polymer status (no longer polymer list - directive 92/32/EEC)						
G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006						
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)						
X : SCL (specific concentration limit)in accordance with art 10 of CLP Regulation No 1272/2008						

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes: If substance has got into eyes, immediately wash out with water for at least 15

minutes

Seek immediate medical attention

Contact with skin: Remove contaminated clothing immediately and drench affected skin with

plenty of water. Then wash with soap and water

Seek medical attention if irritation persists

Inhalation: Fresh air, keep warm and at rest.

Seek medical attention if ill effects occur

If swallowed do not induce vomiting because of risk of aspiration into the Ingestion:

lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation: Excessive inhalation of solvent vapours may give rise to nausea, headaches

and dizziness

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents

may induce chemical pneumonia.

Symptoms: sore throat, abdominal pain, nausea, vomiting

Skin contact: May cause irritation.

Symptoms: redness and pain

Eye contact: Causes serious eye damage.

Symptoms: redness and pain, impaired vision

4.3. Indication of any immediate medical attention and special treatment needed

General Advice: If you feel unwell, seek medical advice (show the label where possible

If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture



Regulation EC No 1907/2006 Art.31

 Productname :
 AMBERCLENS FG
 Creationdate :
 04.03.21 Version : 3.1

 Ref.Nr.:
 BDS000316_3_20210304 (EN)
 Replaces:
 BDS000316_20180503

Aerosols may explode if heated above 50°C Forms hazardous decomposition products CO.CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material Place in appropriate container This material and/or its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition

Take precautionary measures against static discharges

Equipment should be earthed

Use explosion-proof electrical/ventilating/lighting/.../equipment.

Use only non-sparking tools.

Do not breathe aerosols or vapours.

Ensure adequate ventilation

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.

Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities



Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

AMBERCLENS FG Creationdate: 04.03.21 Version: 3.1 Productname: Ref.Nr.: BDS000316 3 20210304 (EN) Replaces: BDS000316 20180503

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:		-	-
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			•
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, Ireland			•
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
		STEL	-

8.2. Exposure controls

Control procedures: Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges Take precautions to avoid contact with skin and eyes when handling the Personal protection: product. Ensure adequate ventilation inhalation: In case of insufficient ventilation, wear suitable respiratory equipment. recommended respiratory protection: Air purifying respirator equiped with ABEK type cartridge hands and skin: When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Recommended gloves: Nitrile eyes: Wear safety eyewear according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : Propane/butane propelled liquid.

White. colour: odour : Neutral. pH: 11



Regulation EC No 1907/2006 Art.31

Creationdate: 04.03.21 Version: 3.1 Productname: AMBERCLENS FG Ref.Nr.: BDS000316 3 20210304 (EN) Replaces: BDS000316 20180503

100 °C Boiling point/range: Flash point: None

Evaporation rate: Not available. Explosion limits: upper limit: Not available. lower limit : Not available. Vapour pressure: Not available. Relative density: 1.01 g/cm3 (@ 20°C).

Solubility in water : Soluble in water Auto-ignition: > 200 °C Viscosity: Not applicable.

9.2. Other information

VOC = volatile organic 69 g/l compounds

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity: based on available data the classification criteria are not met skin corrosion/irritation: based on available data the classification criteria are not met

serious eye damage/irritation: Causes serious eye damage.



Regulation EC No 1907/2006 Art.31

Productname: 04.03.21 Version: 3.1 AMBERCLENS FG Creationdate: Ref.Nr.: BDS000316_3_20210304 (EN) Replaces: BDS000316_20180503

respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	based on available data the classification criteria are not met
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis
Eye contact :	Causes serious eye damage.

Toxicological data:

Hazardous ingredient	CAS-nr.	method	
Alcolhol C10, ethoxylated	26183-52-8	LD50 oral rat	1000 mg/kg
		LD50 derm.rat	> 2000 mg/kg
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Alcolhol C10, ethoxylated	26183-52-8	IC50 algae	< 47 mg/l
		LC50 fish	< 7 mg/l
		EC50 daphnia	5.3 mg/l
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l

12.2. Persistence and degradability

Readily biodegradable - OECD 301B



Regulation EC No 1907/2006 Art.31

AMBERCLENS FG Productname:

Ref.Nr.: BDS000316_3_20210304 (EN) Creationdate: Replaces:

04.03.21 Version: 3.1 BDS000316 20180503

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available GWP (global warming potential): 0

SECTION 13: Disposal considerations

13.1. Waste treatment methods

SECTION 14: Transport information

14.1. UN number

UN-number: 1950

14.2. UN proper shipping name

Proper shipping name: **AEROSOLS**

14.3. Transport hazard class(es)

2.2 Class: ADR/RID - Classification code: 5A

14.4. Packing group

hazardous:

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally No hazardous: IMDG - Marine pollutant: No IATA/ICAO - Environmentally No



Regulation EC No 1907/2006 Art.31

 Productname :
 AMBERCLENS FG
 Creationdate :
 04.03.21 Version : 3.1

 Ref.Nr.:
 BDS000316_3_20210304 (EN)
 Replaces:
 BDS000316_20180503

14.6. Special precautions for user

ADR/RID - Tunnelcode:	(E)
IMDG - Ems:	F-D, S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO	203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: -:-

H220: Extremely flammable gas.

H280 : Contains gas under pressure; may explode if heated.

H302: Harmful if swallowed.

H318: Causes serious eye damage.

acronyms and synonyms: TWA = time weight average

STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

