


Power Modules, Passivated Assembled Circuit Elements, 25 A



PACE-PAK (D-19)

FEATURES

- Glass passivated junctions for greater reliability
- Electrically isolated base plate
- Available up to 1200 V_{RRM}/V_{DRM}
- High dynamic characteristics
- Wide choice of circuit configurations
- Simplified mechanical design and assembly
- UL E78996 approved
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

DESCRIPTION

The VS-P100 series of integrated power circuits consists of power thyristors and power diodes configured in a single package. With its isolating base plate, mechanical designs are greatly simplified giving advantages of cost reduction and reduced size.

Applications include power supplies, control circuits and battery chargers.

PRIMARY CHARACTERISTICS	
I_o	25 A
Type	Modules - thyristor, standard
Package	PACE-PAK (D-19)

MAJOR RATINGS AND CHARACTERISTICS			
SYMBOL	CHARACTERISTICS	VALUES	UNITS
I_o	85 °C	25	A
I_{TSM}	50 Hz	357	A
	60 Hz	375	
I^2t	50 Hz	637	A ² s
	60 Hz	580	
$I^2\sqrt{t}$		6365	A ² √s
V_{DRM}, V_{RRM}		400 to 1200	V
V_{ISOL}		2500	V
T_J	Range	-40 to +125	°C
T_{Stg}		-40 to +125	°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS			
TYPE NUMBER	V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK REVERSE AND PEAK OFF-STATE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT T_J MAXIMUM mA
VS-P101, VS-P121, VS-P131	400	500	10
VS-P102, VS-P122, VS-P132	600	700	
VS-P103, VS-P123, VS-P133	800	900	
VS-P103, VS-P124, VS-P134	1000	1100	
VS-P105, VS-P125, VS-P135	1200	1300	



ON-STATE CONDUCTION					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum DC output current at case temperature	I _O	Full bridge		25	A
				85	°C
Maximum peak, one-cycle non-repetitive on-state or forward current	I _{TSM} , I _{FSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	A
		t = 8.3 ms			
		t = 10 ms	100 % V _{RRM} reapplied		
		t = 8.3 ms			
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		A ² s
		t = 8.3 ms			
		t = 10 ms	100 % V _{RRM} reapplied		
		t = 8.3 ms			
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied I ² t for time t _x = I ² √t · √t _x		6365	A ² √s
Maximum value of threshold voltage	V _{T(TO)}	T _J = 125 °C		0.82	V
Maximum level value of on-state slope resistance	r _{t1}	T _J = 125 °C, average power = V _{T(TO)} × I _{T(AV)} + r _t + (I _{T(RMS)}) ²		12	mΩ
Maximum on-state voltage drop	V _{TM}	I _{TM} = π × I _{T(AV)}	T _J = 25 °C	1.35	V
Maximum forward voltage drop	V _{FM}	I _{FM} = π × I _{F(AV)}	T _J = 25 °C	1.35	V
Maximum non-repetitive rate of rise of turned-on current	di/dt	T _J = 125 °C from 0.67 V _{DRM} I _{TM} = π × I _{T(AV)} , I _g = 500 mA, t _r < 0.5 μs, t _p > 6 μs		200	A/μs
Maximum holding current	I _H	T _J = 25 °C anode supply = 6 V, resistive load, gate open		130	mA
Maximum latching current	I _L	T _J = 25 °C anode supply = 6 V, resistive load		250	


BLOCKING					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum critical rate of rise of off-state voltage	dV/dt	T _J = 125 °C, exponential to 0.67 V _{DRM} gate open		200	V/μs
Maximum peak reverse and off-state leakage current at V _{RRM} , V _{DRM}	I _{RRM} , I _{DRM}	T _J = 125 °C, gate open circuit		10	mA
Maximum peak reverse leakage current	I _{RRM}	T _J = 25 °C		100	μA
RMS isolation voltage	V _{ISOL}	50 Hz, circuit to base, all terminals shorted, T _J = 25 °C, t = 1 s		2500	V

TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum peak gate power	P _{GM}			8	W
Maximum average gate power	P _{G(AV)}			2	
Maximum peak gate current	I _{GM}			2	A
Maximum peak negative gate voltage	-V _{GM}			10	V
Maximum gate voltage required to trigger	V _{GT}	T _J = -40 °C		3	V
		T _J = 25 °C		2	
		T _J = 125 °C		1	
Maximum gate current required to trigger	I _{GT}	T _J = -40 °C		90	mA
		T _J = 25 °C		60	
		T _J = 125 °C		35	
Maximum gate voltage that will not trigger	V _{GD}	T _J = 125 °C, rated V _{DRM} applied		0.2	V
Maximum gate current that will not trigger	I _{GD}			2	mA


THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating and storage temperature range	T_J, T_{Stg}		-40 to +125	°C
Maximum thermal resistance, junction to case per junction	R_{thJC}	DC operation	2.24	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth and greased	0.10	
Mounting torque, base to heatsink ⁽¹⁾			4	Nm
Approximate weight			58	g
			2.0	oz.
Case style			PACE-PAK (D-19)	

Note

⁽¹⁾ A mounting compound is recommended and the torque should be checked after a period of 3 hours to allow for the spread of the compound




93754_01a




93754_01b

Fig. 1 - Current Ratings Nomogram (1 Module Per Heatsink)




93754_02

Fig. 2 - On-State Power Loss Characteristics




93754_03

Fig. 3 - On-State Power Loss Characteristics




93754_04

Fig. 4 - Current Ratings Characteristics




93754_06

Fig. 6 - Maximum Non-Repetitive Surge Current




93754_05

Fig. 5 - On-State Voltage Drop Characteristics



93754_07

Fig. 7 - Maximum Non-Repetitive Surge Current



93754_08

Fig. 8 - Thermal Impedance Z_{thJC} Characteristics




Fig. 9 - Gate Characteristics

ORDERING INFORMATION TABLE

Device code	VS-	P	1	0	2	K	W
	(1)	(2)	(3)	(4)	(5)	(6)	(7)

- 1** - Vishay Semiconductors product
- 2** - Module type
- 3** - Current rating
 1 = 25 A DC (P100 series)
 4 = 40 A DC (P400 series)
- 4** - Circuit configuration
 0 = single phase, hybrid bridge common cathode
 2 = single phase, hybrid bridge doubler connection
 3 = single phase, all SCR Bridge
- 5** - Voltage code
 1 = 400 V
 2 = 600 V
 3 = 800 V
 4 = 1000 V
 5 = 1200 V
- 6** - K = optional voltage suppression
- 7** - W = optional freewheeling diode

CIRCUIT CONFIGURATION			
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	SCHEMATIC DIAGRAM	TERMINAL POSITIONS
Single phase, hybrid bridge common cathode	0		
Single phase, hybrid bridge doubler connection	2		
Single phase, all SCR bridge	3		

CODING (1)					
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	BASIC SERIES	WITH VOLTAGE SUPPRESSION	WITH FREEWHEELING DIODE	WITH BOTH VOLTAGE SUPPRESSION AND FREEWHEELING DIODE
Single phase, hybrid bridge common cathode	0	P10.	P10.K	P10.W	P10.KW
Single phase, hybrid bridge doubler connection	2	P12.	P12.K	-	-
Single phase, all SCR bridge	3	P13.	P13.K	-	-

Note

(1) To complete code refer to Voltage Ratings table, i.e.: for 600 V P10.W complete code is P102W

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95335

D-19 PACE-PAK

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.