Evo Drive



INTRODUCTION

The Integral USB Evo Flash Drive has a translucent blue casing with translucent edging. Its clever design allows you to store the cap on the end of the Flash Drive when in use.

FEATURES

- Entry-level product
- Stylish translucent blue casing
- Cap stores in base when Drive is in use
- Unique ID (optional) The USB Flash Drive can be personalised with a designated company identifying name or number. This will allow a Network Administrator to block access to unrecognised USBs for security purposes, whilst allowing the Integral USB Flash Drive to function as the 'official' company drive.

PRODUCT TYPE

USB Flash Drive

INTERFACE TYPE

Hi Speed USB

INTERFACE CONNECTIVITY

1x Hi-Speed USB - 4 Pin USB Type A

COMPATIBILITY

Windows XP, Vista, 7 and 8. Mac OS 9 and later. Linux v2.4.0 and above.

ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°c Max Operating Temperature 70°c

COMPLIANT STANDARD

Plug and Play

	LENGTH	WIDTH	DEPTH	WEIGHT
PRODUCT	76mm	20mm	9mm	10g
PACKED	170mm	105mm	14.3mm	25g

CAPACITY	PART CODE	BARCODE (EAN)	
2GB	INFD2GBEVOBL	5055288400832	
4GB	INFD4GBEVOBL	5055288400849	
8GB	INFD8GBEVOBL	5055288400856	
16GB	INFD16GBEVOBL	5055288400931	
32GB	INFD32GBEVOBL	5055288405530	
64GB	INFD64GBEVOBL	5055288418585	
128GB	INFD128GBEVOBL	5055288419988	

This device should not be used as your sole backup.

Product design and specification subject to change or modification without notice. E&OE. All trademarks acknowledged.

2 year warranty

For warranty information please visit www.integralmemory.com/warranty $% \left(1\right) =\left(1\right) \left(1$