







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1460045	2014-06-16	Fisher	Design Change the Pin Key
C	LEN1620289	2016-03-04	Fisher	Update print content of label
D	LEN1670288	2016-07-27	Fisher	Update the Label print content



Recommended PCB Layout
T = 1.60mm



Recommended Panel Cut-out

ALTW
CONFIDENTIAL
2016-07-27
R&D DEPT.

Pin 1	E26&E27 Screw
Pin 2	Rivet
Pin Out	



Note:

- * Ⓞ Important Dimension To Check.
- * Housing: Thermoplastic, UL94V-0, White.
- * Nut: Thermoplastic, UL94V-0, White.
- * Threaded Metal: Copper Alloy, Nickel Plated.
- * Terminal: Copper Alloy, Gold Plated.
- * Rivet: Copper Alloy, Nickel Plated.
- * Maximum Panel Thickness: 2.5mm.
- * Operating temperature: -40 ~ +105°C.
- * Current Rating: 3A maximum.
- * Voltage Rating: 500V AC/DC maximum.





UNIT: mm		TITLE SSL2.3 E26&E27 Adapter Conn.	
TOLERANCE		SCALE 3:2	SIZE A4
.X ±0.25		SHEET 1	OF 2
.XX ±0.1		REV. D	WC-REV. .0
.XXX ±0.05		QC: Inspection item	
ANGLES ±1°			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO. SSL23-D2S00-000001	DRAWN BY Fisher_Wang	DATE 2016-07-27
DWG NO. SSL23-D2S00-000001	CHECKED BY Victor_Hung	DATE 2016-07-27
CUSTOMER ALTW	APPROVED BY Kevin_Hu	DATE 2016-07-27



(50pcs per inner carton)



- QUANTITY
- * 50Pcs Per Inner Carton
 - * 10 Pcs inner Carton Per Carton (500Pcs/Carton)
 - * Net Weight: 6.0Kg/Carton.
 - * Gross Weight: 8.2Kg/Carton.

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		SSL2.3 PACKAGE		SSL23-D2S00-000001		Fisher_Wang		2016-07-27	
.X		SCALE	3:2	SIZE	A4	SHEET	2	OF	2
.XX		REV.	D	WC-REV.	.0	CHECKED BY		DATE	
.XXX		QC: Inspection item		SSL23-D2S00-000001		Victor_Hung		2016-07-27	
ANGLES				CUSTOMER		APPROVED BY		DATE	
				ALTW		Kevin_Hu		2016-07-27	

Amphenol LTW
安費諾亮泰企業股份有限公司