F<u>A</u>NE

THE **PROFESSIONAL** SERIES

COLOSSUS PRIME 18XS

18" / 457.2 mm

2400 W PROGRAM POWER **35 Hz - 500 Hz** FREQUENCY RESPONSE

12 mm Xmax

MAX. LINEAR EXCURSION

4" / 101.6 mm

100 dB SENSITIVITY (1W/ 1m)


- High grade Y35 ferrite magnet motor structure with Low interference flux path.
- Vented chassis and motor design provides efficient thermal management and extremely low power compression.
- + Aluminium demodulation ring.
- Dual silicone laminated suspension system combined with optimised software materials offers increased linearity for fast, accurate and undistorted bass reproduction at extreme SPL.
- + 12mm Xmax with 64 mm peak-to-peak travel.
- + Ideal for bass reflex and scoop enclosure designs from 125-400 Litres.
- + Also performs well in horn loaded systems.
- + 4-Inch Inside/ outside windings copper voice coil.


GENERAL SPECIFICATIONS

Nominal Chassis Diameter	18" / 457.2 mm
Nominal Impedance ⁽¹⁾	8 Ohm
Minimum Impedance Zmin	6.5 Ω
AES Power Handling ⁽²⁾	1200 W (A.E.S.)
Program Power	2400 W
Peak Power (6dB Crest Factor)	4800 W
Frequency Range (-6dB)	35 Hz - 500 Hz
Sensitivity (1W/ 1m)	100 dB
Magnet Material	Ferrite Y35
Magnet Weight	145 oz
Magnetic Gap Depth	0.43" / 11 mm
Flux Density	1.1 Tesla
Former Material	Glass Fibre
Voice Coil Material	Copper - Inside/ Outside
Coil Winding Height	1.18" / 30 mm
Voice Coil Diameter	4" / 101.6 mm
Cone/ Dust Dome Material	Straight Fibre Loaded Poly-cellulose Ribbed / Solid Paper (Inverted)
Surround / Edge Termination	Polyvinyl Damped Multi Roll. Poly Cotton

Fs	33 Hz
Re	5.2 Ω
Qms	8.2
Qes	0.404
Qts	0.385
Vas	257 Litres
Vd	1.45 Litres
Cms	0.124 mm/N
BI	22.4 T/m
Mms	188 g
Xmax	12 mm
Sd	1210 cm ²
Efficiency	2.2 %
Le (1k Hz)	1.5 mH
EBP	81.68 Hz
Effective Piston Diameter	15.43" / 391.92 mm
Rec. Enclosure Volume	4.41 - 14.12 ft3 / 125 - 400 Litres

TECHNICAL & THIELE SMALL PARAMETERS






MOUNTING / SHIPPING INFORMATION


Overall Diameter	19.1" / 485 mm
Width Across Flats	18" / 457 mm
Depth	8.50" / 216 mm
Flange Height	0.465" / 11.8 mm
Baffle Hole Diameter F/M	16.53" / 419.86 mm
Baffle Hole Diameter R/M	16.33" / 414.78 mm
Chassis Material	Die-cast Aluminium
Gasket Supplied	Front & Rear
Outer Fixing Holes	8x ø 0.275" on 18.425" PCD / 8x ø 7 mm on 468 mm PCD
Outer Fixing Holes	
	8x ø 7 mm on 468 mm PCD 8x ø 0.275" on 17.25" PCD / 8x
Inner Fixing Holes	8x Ø 7 mm on 468 mm PCD 8x Ø 0.275" on 17.25" PCD / 8x Ø 7 mm on 438.15 mm PCD Push-button Spring
Inner Fixing Holes Connectors (4)	8x Ø 7 mm on 468 mm PCD 8x Ø 0.275" on 17.25" PCD / 8x Ø 7 mm on 438.15 mm PCD Push-button Spring Terminals

COLOSSUS PRIME 18XS | SUB BASS DRIVER

FREQUENCY RESPONSE DATA (3)



IMPEDANCE



(1) Please enquire about alternative impedances.

(2) A.E.S. power handling test. Pink noise bandpass filtered at 12 dB per octave with cutoff frequencies of 30 Hz and 300 Hz. Driver mounted in free air, test signal applied at rated power for two hours. (3) Half space response measured in a 975 Litre sealed box. Blue line = fundamental 45° off-axis. Please note that the frequency response measurements are supplied for comparison only and are not a measure of the low frequency performance which may be achieved in a fully optimised system.

(4) Positive voltage at red terminal causes forward motion of cone.