

2351415-3 ✓ ACTIVE

TE Internal #: 2351415-3

Standard Circular Connectors, Wire-to-Wire, 8 Position, Sealable,
Wire & Cable, Signal, Nickel, Brass, A Polarization Code, Polyamide
66 GF30

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **8**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **2 A**

Features

Product Type Features

| | |
|-----------------------------------|----------------------|
| Prewired | No |
| Product Type | Connector |
| Accessory Color | Black |
| Assembly Type | Electrical Connector |
| Connector System | Wire-to-Wire |
| Sealable | Yes |
| Connector & Contact Terminates To | Wire & Cable |
| Circular Connector Type | Plug |
| Shell Type | Metal |

Configuration Features

| | |
|---------------------------------------|------|
| Keying & Polarized Position Locations | A |
| Factory Installed Backshell | With |
| Keying | A |
| Number of Positions | 8 |
| Number of Power Positions | 0 |



| | |
|----------------------------|---|
| Number of Signal Positions | 8 |
|----------------------------|---|

| | |
|--------------------|-----|
| Contacts Preloaded | Yes |
|--------------------|-----|

Electrical Characteristics

| | |
|-------------------|--------|
| Operating Voltage | 30 VAC |
|-------------------|--------|

| | |
|---------|----------|
| Voltage | 250 Vrms |
|---------|----------|

Body Features

| | |
|--------------------------|----------|
| Peripheral Seal Material | Silicone |
|--------------------------|----------|

| | |
|--------------------------|------|
| Environmental Protection | IP67 |
|--------------------------|------|

| | |
|-----------------|----------|
| O-Ring Material | Silicone |
|-----------------|----------|

| | |
|-------------------------------|------------------|
| Environmental Protection Type | Elastomer Sealed |
|-------------------------------|------------------|

| | |
|------------------------|--------|
| Shell Plating Material | Nickel |
|------------------------|--------|

| | |
|---------------------|-------|
| Shell Base Material | Brass |
|---------------------|-------|

| | |
|---------------------------------------------|-------------------|
| Circular Connector Insulation Material Type | Polyamide 66 GF30 |
|---------------------------------------------|-------------------|

Contact Features

| | |
|------------------------------|-----|
| Contact Current Rating (Max) | 2 A |
|------------------------------|-----|

| | |
|----------------|----|
| Reverse Gender | No |
|----------------|----|

| | |
|---------------------------------|-----|
| Circular Connector Contact Type | Pin |
|---------------------------------|-----|

Mechanical Attachment

| | |
|-----------------------|-------------------|
| Mating Retention Type | Threaded Coupling |
|-----------------------|-------------------|

| | |
|------------------|------|
| Mating Alignment | With |
|------------------|------|

| | |
|-------------------|---|
| Polarization Code | A |
|-------------------|---|

| | |
|-----------------------|-------|
| Mating Alignment Type | Keyed |
|-----------------------|-------|

Housing Features

| | |
|-------------------------------|----|
| Circular Connector Shell Size | 20 |
|-------------------------------|----|

Dimensions

| | |
|-----------|--------------------------|
| Wire Size | .75 – .5 mm ² |
|-----------|--------------------------|

Usage Conditions

| | |
|-----------------------|---|
| IP Dust Sealing Level | 6 |
|-----------------------|---|

| | |
|------------------------|------|
| IP Water Sealing Level | IP67 |
|------------------------|------|

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |
|-----------------------------|---------------------------|

Operation/Application



| | |
|---------------------|------------|
| Durability Rating | 100 Cycles |
| Circuit Application | Signal |
| Shielded | Yes |

Industry Standards

| | |
|------------------------|---------|
| UL Flammability Rating | UL 94V0 |
|------------------------|---------|

Other

| | |
|----------------------------|-----|
| Position Locations Omitted | 0 |
| Field Serviceable | Yes |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (1.9% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources. |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[M12 MALE,A8 CODE,STR CONNECTOR, PG7 SEAL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2351415-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2351415-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2351415-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

[PACKAGING SPECIFICATION FOR M12 RAIL CONNECTOR](#)

English

[Application Specification](#)

English