

Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adva



FXC-SFP-LX-1G-ADV

Features

- Operating Data Rate up to 1.25 Gbps
- Distance Range 10KM
- Single 3.3V Power Supply and TTL Logic Interface
- Pluggable SFP Duplex LC Connector
- Standard and Industrial Operating Temperature
- Compliant with Adva SFP Specification

Applications

- Telecom (Service Provider)
- Datacom
- Enterprise Networks
- Government
- Fiber to the home/business

Description

The L-com FXC-SFP-LX-1G-ADV is an SFP form-factor transceiver, supporting 1G Ethernet rates. The L-com FXC-SFP-LX-1G-ADV supports 10KM distance and it is Adva compliant transceiver. The L-com FXC-SFP-LX-1G-ADV features digital diagnostics for performance monitoring of the transceiver. The L-com FXC-SFP-LX-1G-ADV is one of thousands of fiber optic connectivity products available from L-com in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for your answers on fiber optic connectivity or other L-com products.

Configuration

Data Rate	1 Gbps
Form Factor	SFP
Connector	LC
Connector Mode	Duplex
Mode	Single Mode
Distance	10 km
Mfg Platform Compatibility	Adva

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Wattage			1.04	W
Power Supply Voltage Vcc	3.15	3.3	3.45	V
Power Supply Current Icc			300	mA

Optical Specifications

Description	Minimum	Typical	Maximum	Units
TX Center Wavelength	1260	1310	1360	nm
TX Data Rate		1.25		Gbps
TX Spectral Width			4	nm
TX Average Output Power	-9		-3	dBm
TX Extinction Ratio	9			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adva FXC-SFP-LX-1G-ADV](#)

Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adv



FXC-SFP-LX-1G-ADV

RX Center Wavelength	1260	1600	nm
RX Receiver Sensitivity	-21		dBm
RX Receiver Overload		-3	dBm

Environmental Specifications

Temperature

Operating Range

0 to +70 deg C

Storage Range

-40 to +85 deg C

Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adv



FXC-SFP-LX-1G-ADV

Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adva



FXC-SFP-LX-1G-ADV




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Fiber Optic Transceiver, SFP, 1310nm, LX SMF 10km, 1000Base DDM, Adva from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

