



KEY FEATURES

- COMFORTABLE RUBBER OVERMOULDED HANDLE
- EASY-OPEN LATCHES
- 2 PADLOCKABLE HASPS
- AUTOMATIC PRESSURE EQUALISATION VALVE
- NAMEPLATE (OPTIONAL PERSONALISATION AVAILABLE)

| 1400 | Length | Width | Depth | Lid | Base |
|-----------|--------|-------|-------|-----|------|
| INT. (mm) | 240 | 185 | 153 | 28 | 125 |
| EXT. (mm) | 270 | 246 | 174 | | |

WEIGHT (kg)

Empty: 1.80
With Foam: 2.00

SPECIFICATIONS

IP Rating: 67
No. of Latches: 2
Handles: Front Handle
Security: Stainless Steel Padlock Hasps
Foam Set Info: 1 x Base Foam, 1 x Pick 'N' Pluck™ Layer,
1 x Convoluted Lid Foam
Buoyancy: 9.10kg
Certificates: Def Stan 81-41/STANAG 4280
Protection: Waterproof, Crushproof, Dustproof,
Corrosion-proof

PACKAGING

Weight Empty (kg): 2.14
Weight with Foam (kg): 2.38
Packaging Dims (mm): 345 x 314 x 156
Units Per Master Pack: 4
Master Pack Dims (mm): 645 x 356 x 335
Units Per Pallet: 72

AVAILABLE COLOURS



PRODUCT ACCESSORIES

TrekPak Dividers
TSA Lock
Panel Frame
3 Piece Foam Set



LIFETIME GUARANTEE

All cases in the Peli™ Protector range are covered by the legendary Lifetime Guarantee. Simply put...“You break it, we replace it.”