

1. Chemical product and company identification

Product Description : The product is a 6P4C Modular Plug with gold plated copper alloy and a polycarbonate housing. This connector fits to flat RJ11 cables.

Intended use : Molding material for industry use

Supplier : Premier Farnell plc
150 Armley Road
Leeds
LS12 2QQ
+44 (0) 8701 202530

Emergency telephone : +44 1865 407333

2. Hazards identification

GHS-classification : The product is not classified according to GHS.

GHS label elements : None.

Precautionary statement : None.

National/local information : See section 15 for regulatory information.

3. Composition/information on ingredients

Substance or Mixture : Substance

Components	CAS #	Gazette notification		
		ENCS no.	ISHL no.	Concentration (%)
Polycarbonate resin	25971-63-5	(7)-738	(7)-738	95 – 100
Chemical formula	: (C15H16O2.CCl2O)x (25971-63-5)			

4. First aid measures

If inhaled : In case of inhalation of dusts or fumes from heated product: Move injured person into fresh air and keep person calm under observation. Get medical attention if any discomfort continues.

If on skin : Rinse with water. Get medical attention promptly if symptoms persist or occur after washing. If burned by contact with hot material, cool molten material adhering to skin as quickly as possible with water, and see a physician for removal of adhering material and treatment of burn.

If in eyes : Dust in the eyes: Do not rub eyes. Flush thoroughly with water. If irritation occurs, get medical assistance.

If swallowed : Rinse mouth thoroughly. Large quantities: Get medical attention if symptoms occur.

Expected acute and delayed Symptoms : None.

Protection of first-aid responders : First aid personnel must be aware of own risk during rescue.

Notes to physician : Treat symptomatically.

5. Fire-fighting measures

Extinguishing media : Extinguish with foam, carbon dioxide, dry powder or water fog.

Extinguishing media to avoid : None.

Specific hazards	: During fire, gases hazardous to health may be formed.
Special fire fighting procedures	: Use standard firefighting procedures and consider the hazards of other involved materials.
Protection of fire-fighters	: Selection of respiratory protection for fire fighting: follow the general fire precautions indicated in the workplace.

6. Accidental release measures

Personal precautions, protective equipment and emergency measures	: Avoid inhalation of dust. See Section 8 of the SDS for Personal Protective Equipment.#
Environmental precautions	: Do not allow to enter drains, sewers or watercourses.
Clean-up methods and materials and containment measures	: Collect and dispose of spillage as indicated in Section 13 of the SDS.

7. Handling and storage

Handling

Technical measures	: Use explosion-proof electrical equipment if airborne dust levels are high.
Local and general ventilation	: Provide adequate ventilation.
Precautions	: Use work methods which minimize dust production. Wear appropriate personal protective equipment.
Safe handling advice	: Avoid inhalation of dust. Avoid prolonged or repeated contact with skin. Avoid vapors from heated materials to prevent exposure to potentially toxic/irritating fumes.

Storage

Technical measures	: Avoid dust formation.
Suitable storage conditions	: Store in closed original container in a dry place.
Safe packaging materials	: Keep in original container.

8. Exposure controls/personal protection

Engineering measures	: Provide adequate ventilation. Japan Society of Occupational Health, class 3 dust (limestone, other inorganic and organic dusts): respirable dust 2 mg/m ³ , total dust 8 mg/m ³ .
----------------------	---

Personal protective equipment

Respiratory protection	: Wear respirator if there is dust formation. When the product is heated, use suitable respiratory equipment with gas filter for organic gas.
Hand protection	: For prolonged or repeated skin contact use suitable protective gloves. When material is heated, wear gloves to protect against thermal burns.
Eye protection	: Use tight fitting goggles if dust is generated. If contact with hot material may occur, safety glasses and face shield are recommended.
Skin and body protection	: No protection is ordinarily required under normal conditions of use
Hygiene measures	: Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state	: Solid.
Form	: Pellets.
Color	: Natural.
Odor	: None.
pH	: Not applicable.
Melting point/Freezing point	: > 464°F (> 240°C)
Boiling point, initial boiling point, and boiling range	: Not applicable.
Flash point	: > 971.6°F (> 522°C)
Auto-ignition temperature	: > 1022°F (> 550°C)
Combustion characteristics (solid, gas)	: Not available.
Flammability limit - lower (%)	: Not available.
Flammability limit - upper (%)	: Not available.
Vapor pressure	: Not applicable.
Vapor density	: Not applicable.
Specific gravity	: 1.2
Solubility	: Insoluble in water
Partition coefficient (n-octanol/water)	: Not available.
Decomposition temperature	: Not available.

10. Stability and reactivity

Stability	: Stable under normal temperature conditions.
Possibility of hazardous reactions	: Will not occur.
Conditions to avoid	: None known.
Incompatible materials	: Incompatible materials
Hazardous decomposition products	: During combustion: Carbon monoxide. Carbon Dioxide.

11. Toxicological information

Acute toxicity	: May cause discomfort if swallowed.
Skin corrosion/irritation	: Dust may irritate skin.
Serious eye damage/eye irritation	: Dust in the eyes will cause irritation. May cause redness and pain.
Respiratory sensitizer	: None known.
Skin sensitizer	: None known.
Germ cell mutagenicity	: None known.
Carcinogenicity	: None known.
Toxic to reproduction	: None known.
Specific target organ toxicity - single exposure	: None known.
Specific target organ toxicity - repeated exposure	: None known.

12. Ecological information

Ecotoxicity	: The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
Persistence/degradability	: None known.
Bioaccumulation	: None known.
Mobility in soil	: The product is insoluble in water and will sediment in water systems.
Other hazardous effects	: None known.

13. Disposal considerations

Residual waste	: Dispose of waste at a facility with special permission to dispose industrial wastes. Waste should be accompanied by a manifest for the industrial waste. Dispose of in accordance with local regulations. Do not discharge into rivers, lakes, mountains, etc. because the product may affect the environment.
Contaminated packaging	: Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

International regulations	: Not regulated as dangerous under UN transport regulation.
IATA	: Not regulated as dangerous goods.
IMDG	: Not regulated as dangerous goods.

15. Regulatory information

Industrial Safety and Health Act

Specified substances regulation	: Not regulated.
Organic solvents regulation	: Not regulated.
Notifiable substances	: Not regulated.
Labeling substances	: Not regulated.
Poisonous and Deleterious Substances Control Act	: Not regulated.
Act on the Evaluation of Chemical Substances and Regulation of Their Manufacture, etc.	
Class I specified chemical substances	: Not regulated.
Class II specified chemical substances	: Not regulated.
Monitoring chemical substances	: Not regulated.
Law concerning Pollutant Release and Transfer Register	
Specified class 1 substances (substance name, ordinance number and content)	
Not regulated.	
Class 1 substances (substance name, ordinance number and content)	
Not regulated.	
Class 2 substances (substance name, ordinance number and content)	
Not regulated.	
Fire Service Act	: Not dangerous goods under Fire Service Law
Ship Safety Law, Dangerous Goods Marine Transport and Storage Rule	
Not regulated.	
Air Law, Enforcement Rule	: Not regulated.

Safety Data Sheet

multicomp^{PRO}

Explosives Control Act : Not regulated.
High Pressure Gas Safety Act : Not regulated.
Act on Prevention of Marine Pollution and Maritime Disaster
Not regulated.

16. Other information

NA

Part Number
7001-6P4C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}