

SPECIFICATION - 12 LT DEHUMIDIFIER

Model Number	OL12-BD023AF
---------------------	---------------------

1. 12 Liter Per Day;
2. Eco-Friendly R290 Refrigerant;
3. Low Noise $\leq 38\text{dB(A)}$;
4. Large water tank up to 2.0 Liter;
5. High Efficient Dehumidifying capacity and famous brand compressor;
6. 24-hour timer; Water-full indicator;



Dehumidifying Capacity (Liter/Day)	12 Liter/Day(30°C, 80%RH)
Dehumidifying Capacity (Liter/Day)	7 Liter/Day(27°C, 60%RH)
Power Supply	AC220-240V/50Hz
Rated Input Power & Current Amps	185W/1.0A(30°C, 80%RH)
Rated Input Power & Current Amps	160W/0.9A(27°C, 60%RH)
Refrigerant/Charge	R290(55g)
Water Tank Capacity(Liter)	2L
Air Circulation	100m ³ /h
Noise	$\leq 38\text{dB(A)}$
Body Size (mm)	255x220x470
Carton Size (mm)	305x265x520
Net Weight	11kg
Gross Weight	12kg
Application Area	8-12m ²
Loading Quantity (20'/40'/40' HQ)	624/1312/1638
Control Type	Electronic Control Type
Accessories	Manual+water hose
Certificate	CE, GS, UKCA, ERP, RoHS