

SPECIFICATION - 20 LT DEHUMIDIFIER

Model Number	OL20-BD068CF
---------------------	---------------------

1. 16Liter Per Day;
2. Eco-Friendly R290 Refrigerant;
3. Low Noise≤38dB(A);
4. Large water tank up to 4.5Liter;
5. High Effificent Dehumidifying capacity and famous brand compressor;
6. 24-hour timer;Water-full indicatoer;



Dehumidifying Capacity (Liter/Day)	20 Liter/Day(30°C, 80%RH)
Dehumidifying Capacity (Liter/Day)	10Liter/Day(27°C, 60%RH)
Power Supply	AC220-240V/50Hz
Rated Input Power &Current Amps	330W/1.2A(30°C, 80%RH)
Rated Input Power &Current Amps	280W/1.0A(27°C, 60%RH)
Refrigerant/Charge	R290(54g)
Water Tank Ccapacity(Liter)	4.5L
Air Circulation	120m ³ /h
Noise	≤38dB(A)
Body Size (mm)	305x235x495
Carton Size (mm)	347x277x535
Net Weight	13kg
Gross Weight	15kg
Application Area	15-25m ²
Loading Quantity (20'/40'/40' HQ)	520/1080/1350
Control Type	Electronic Control Type
Accessories	Manual+water hose
Certificate	CE, GS,UKCA, ERP, RoHS