

## Product Specification

**Model:** BHN1903R-1 **Product Name** Smart Heater

### Product Picture



### Packing

product dimension	180*180*369mm
qty per unit packing	1pc
unit packing: (LxWxH)	220*220*413mm
unit packing (G.W.)	2.6Kg
qty per export carton	4PCS
export carton (WxHxL)	46*46*42.8cm
export carton (G.W.)	11.40KG
units per 20"/40"/40" HQ	

### additional packing information

### Mechanical Specification

- ◆ Material 材质 ABS
- ◆ Flame Retardance 防火等级 750°C FIRE-RETARDANT
- ◆ Ingress Protection(IP) 防水等级 No

### Electrical Specification 电气参数

- ◆ Power 功率 1500W
- ◆ Input Voltage 输入电压 AC 220V-240V
- ◆ Frequency 输入电压频率 50Hz
- ◆ MAX LOAD NC NA  
最大负载 NO 7A 220-240V 1500W 请根据实际参数填写
- ◆ WiFi Standard WiFi 标准
- ◆ WiFi Frequency Range WiFi频率范围 2.4GHz 802.11a/b/g/n
- ◆ WiFi range (open area) WiFi接收范围 2.4-2.483GHz
- ◆ Net weight 净重 2.4-2.483GHz
- ◆ Operating Temperature 使用温度 -14°F-113°F (-10°C-45°C)
- ◆ Storage Temperature 存储温度 -14°F-113°F (-10°C-45°C)
- ◆ Max Humidity 最大湿度 80%

### Protection 保护功能

- ◆ Overload protection 过载保护 Yes
- ◆ Lightning protection 防雷保护 No
- ◆ Surge protection 浪涌保护 Yes
- ◆ Child safety shutter protection Yes
- ◆ 过零保护 Yes
- ◆ Housing 外壳 White
- ◆ Button 按键 Touch
- ◆ Power LED 电源灯 Blue
- ◆ WiFi 指示灯 Blue

### Others

- ◆ Approved Certification 认证 CE ROHS
- ◆ Warranty period 质保时间 2 Years

### Accessories

- ◆ Instruction manual 说明书 Yes