

DMX-CONTROLLED RGBW STROBE







HYPNOTIC

FEATURES

- 4/6/13/16/32 DMX channels
- 1024x 4-in-1 RGBW LEDs
- DMX, auto, master-slave and sound-controlled operation
- 55 preset effects with speed adjustment
- Dimmer 0-100%
- Strobe adjustable from 0 - 25 flashes/sec
- Forced air-cooling

Power supply	110-240V~, 50/60Hz
Consumption	400W
LED	1024x 5050 4-in-1 RGBW LEDs
LED lifespan	approx. 50.000 hours
Beam angle	135°
Strobe	0 - 25 flashes/sec
Dimensions	300 x 300 x 100mm
Weight	3,5kg



CODE: **16-2105**
 EAN: **5420047142054**



LOGISTIC VALUES / VALEURS LOGISTIQUES

Height / Hauteur	15,0cm
Width / Largeur	40,5cm
Depth / Profondeur	38,0cm
Volume	0,023m ³
Net weight / Poids net	3,5kg
Gross weight / Poids brut	4,0kg
Carton qty / Colisage	6 pcs.

STROBOSCOPE RGBW CONTROLE PAR DMX







HYPNOTIC

FEATURES

- 4/6/13/16/32 canaux DMX
- 1024 LED RGBW 4-en-1
- Fonctionnement DMX, automatique, maître-esclave et contrôlé par le son
- 55 effets automatiques à vitesse variable
- Dimmer 0-100%
- Stroboscope réglable de 0 - 25 flashes/s
- Refroidissement par air pulsé

Alimentation.....	110-240V~, 50/60Hz
Consommation.....	400W
Type de LED	1024x 5050 4-in-1 RGBW LEDs
Durée de vie des led	approx. 50.000 hours
Angle du faisceau.....	135°
Stroboscope.....	0 - 25 flashes/sec
Dimensions	300 x 300 x 100mm
Poids.....	3,5kg



CODE: **16-2105**
EAN: **5420047142054**



LOGISTIC VALUES / VALEURS LOGISTIQUES

Height / Hauteur	15,0cm
Width / Largeur.....	40,5cm
Depth / Profondeur.....	38,0cm
Volume	0,023m ³
Net weight / Poids net.....	3,5kg
Gross weight / Poids brut	4,0kg
Carton qty / Colisage	6 pcs.

ESTROBOSCOPIO RGBW CONTROLADO POR DMX







HYPNOTIC

FEATURES

- 4/6/13/16/32 canales DMX
- 1024 LED RGBW 4-en-1
- Funcionamiento DMX, automático, maestro-esclavo y controlado por el sonido
- 55 efectos automáticos de velocidad variable
- Dimmer 0-100%
- Estroboscopio ajustable de 0 - 25 flashes/s
- Refrigeración por aire forzado

Alimentación	110-240V~, 50/60Hz
Consumo	400W
Tipo de LED	1024x 5050 4-en-1 RGBW LEDs
Duración de la vida de los LEDs.....	alred. 50.000 horas
Angulo del haz.....	135°
Estrobo	0 - 25 flashes/sec
Dimensiones	300 x 300 x 100mm
Peso	3,5kg



CODE: **16-2105**
 EAN: **5420047142054**



LOGISTIC VALUES / VALEURS LOGISTIQUES

Height / Hauteur	15,0cm
Width / Largeur.....	40,5cm
Depth / Profondeur.....	38,0cm
Volume	0,023m ³
Net weight / Poids net.....	3,5kg
Gross weight / Poids brut	4,0kg
Carton qty / Colisage	6 pcs.