

PRODUCT DATASHEET

LED R63 60 36° DIM S 4.9W 927 E27

LED R63 | Dimmable LED reflector lamps R63 with screw base, natural daylight



SUPERIOR
CLASS

Areas of application

- Shops and exhibition rooms
- Domestic applications
- Commercial applications
- Accent lighting
- Outdoor use in suitable outdoor luminaires only

Product benefits

- Quick, simple and safe replacement without rewiring
- Design, dimensions, luminous flux comparable to a halogen lamp
- Natural light spectrum with outstanding color rendering of CRI>90
- Greatly reduced blue component
- Improved visual comfort and reduced eye strain
- Low maintenance costs and cost savings thanks to long lifetime
- Low flickering

Product features

- LED alternative to conventional low voltage lamps
- Dimmable
- Base: E27
- Color rendering index $R_a: \geq 90$
- Lamp made of glass



TECHNICAL DATA**Electrical data**

| | |
|--|-------------|
| Nominal wattage | 4.9 W |
| Construction wattage | 4.90 W |
| Nominal voltage | 220...240 V |
| Operating mode | AC Mains |
| Claimed equiv. conventional lamp power | 60 W |
| Nominal current | 30 mA |
| Type of current | AC |
| Inrush current | 0.027 A |
| Operating frequency | 50/60 Hz |
| Mains frequency | 50/60 Hz |
| Max. lamp no. on circuit break. 10 A (B) | 266 |
| Max. lamp no. on circuit break. 16 A (B) | 426 |
| Power factor λ | ≥ 0.70 |

Photometrical data

| | |
|---|---------------|
| Luminous intensity | 550 cd |
| Luminous flux | 345 lm |
| Nominal useful luminous flux 90° | 345 lm |
| Luminous efficacy | 70 lm/W |
| Lumen main.fact.at end of nom.life time | 0.70 |
| Light color (designation) | Warm White |
| Color temperature | 2700 K |
| Color rendering index Ra | 90 |
| Light color | 927 |
| Standard deviation of color matching | ≤ 5 sdcn |
| Rated peak intensity | 550 cd |
| Rated LLMF at 6,000 h | 0.80 |
| Flickering metric (Pst LM) | 1.0 |
| Stroboscope effect metric (SVM) | 0.4 |



Light technical data

| | |
|---------------------|----------|
| Beam angle | 36 ° |
| Warm-up time (60 %) | < 0.50 s |
| Starting time | < 0.5 s |

Dimensions & Weight

| | |
|------------------|----------|
| Overall length | 98.00 mm |
| Diameter | 62.90 mm |
| Maximum diameter | 63 mm |
| Product weight | 76.00 g |

Temperatures & operating conditions

| | |
|--------------------------------------|--------------|
| Ambient temperature range | -20...+40 °C |
| Maximum temperature at tc test point | 72.3 °C |

Lifespan

| | |
|--|---------|
| Lifespan L70/B50 at 25 °C | 25000 h |
| Number of switching cycles | 100000 |
| Lumen maintenance at end of service lifetime | 0.70 |
| Rated lamp survival factor at 6,000 h | ≥ 0.90 |

Additional product data

| | |
|-----------------------------|--------|
| Base (standard designation) | E27 |
| Mercury content | 0.0 mg |
| Mercury-free | Yes |

| | |
|----------------|--|
| Product remark | All technical parameters apply to the entire lamp / Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value |
|----------------|--|

Capabilities

| | |
|----------|-------------------|
| Dimmable | Yes ¹⁾ |
|----------|-------------------|

¹⁾ Check dimmer compatibility at [ledvance.com/compatibility](https://www.ledvance.com/compatibility)

Certificates & Standards

| | |
|--|-----------------|
| Energy efficiency class | G ¹⁾ |
| Energy consumption | 5.00 kWh/1000h |
| Type of protection | IP20 |
| Standards | CE / UKCA / EAC |
| Photobiological safety group acc. to EN62778 | RG1 |

¹⁾ Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

Country-specific categorizations

| | |
|-----------------|-----------------|
| Order reference | LED R636036 DIM |
|-----------------|-----------------|

LOGISTICAL DATA

| | |
|------------------------------|--------------|
| Temperature range at storage | -20...+80 °C |
|------------------------------|--------------|

Energy labelling regulation data acc EU 2019/2015

| | |
|---|--------------|
| Lighting technology used | LED |
| Non-directional or directional | DLS |
| Mains or non-mains | MLS |
| Light source cap-type (or other electric interface) | E27 |
| Connected light source (CLS) | No |
| Color-tuneable light source | No |
| Envelope | No |
| High luminance light source | No |
| Anti-glare shield | No |
| Correlated colour temperature type | SINGLE_VALUE |
| Standby power | 0 W |
| Networked standby power for CLS | 0 W |
| Claim of equivalent power | Yes |

| | |
|--|----------------|
| Length | 98.00 mm |
| Height | 62.90 mm |
| Width | 62.90 mm |
| Chromaticity coordinate x | 0,458 |
| Chromaticity coordinate y | 0,410 |
| R9 Colour rendering index | 1 |
| Beam angle correspondence | NARROW_CONE_90 |
| Survival factor | 0.9 |
| Displacement factor | / |
| LED light source replaces a fluorescent light source | No |
| EPREL ID | 1368254 |
| Model number | AC45641 |

DOWNLOAD DATA

Documents and certificates



Declarations Of Conformity CE

Photometric and lighting design files



IES file (IES)



LDT file (Eulumdat)



LDC typ polar



Spectral power distribution

LOGISTICAL DATA

| Product code | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Gross weight | Volume |
|---------------|------------------------------|--------------------------------------|--------------|----------------------|
| 4099854048456 | Folding box 1 | 65 mm x 65 mm x 107 mm | 93.00 g | 0.45 dm ³ |
| 4099854048463 | Shipping box 10 | 357 mm x 147 mm x 125 mm | 1063.00 g | 6.56 dm ³ |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

- For dimming conformity see www.ledvance.com/dim
 - For Guarantee see www.ledvance.com/guarantee
-

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.