



## IPS MONITOR

### Vero B7 series- B247Y D3

- FHD resolution with ZeroFrame design
- 85% PCR, 5% OBP and 100% recyclable paper packaging
- AI Noise Cancellation for cancelling environmental noise, ensuring that a user's voice comes through loud and clear
- 5M-IR webcam, supports Windows Hello
- TUV/Eyesafe™ certified; protect eyes by reducing harmful blue light while maintaining high color accuracy
- 100Hz refresh rate, flicker-free
- Delta E<1
- 4ms (G to G)
- ErgoStand-Tilt, swivel, pivot and height adjust with flexibility
- TCO Edge/ENERGY STAR/EPEAT Gold certified



# Specifications

Panel	Display Size	23.8" H
	Color	Black
	Maximum Resolution and Refresh Rate	1920x1080 @100Hz
	Glare	No
	Panel	IPS
	Response Time	4ms (G to G)
	Contrast Ratio	100 million:1 max (ACM)
	Brightness	250 nits (cd/m <sup>2</sup> )
	Viewing Angle	178° (H), 178° (V)
	Colors	16.7M
System	Bits/Color Gamut	6Bit+FRC/sRGB 99%
	Input Signal	1H(1.4)+1DP(1.2)+1DP out+1USB C (90W)+SPK+Audio out+USB 3.2x3+USB-B (2up 3down)+Adj. Webcam 5M IR/Mic array
	VESA Wall Mounting	100 x 100 mm
	Speaker	5W x 2
	Power Supply (100 - 240 V)	Internal
	Tilt / Height adjustment	-5° - 35° / 150mm
Swivel/Pivot	+/- 45° / +/-90°	

## Feature Highlights

### Professional Performance

- 23.8" Full HD resolution
- AI Noise Cancellation
- 5M-IR webcam
- Type-C 90W PD
- Delta E<1
- AMD FreeSync™ technology
- HDR10 support
- 4ms (G to G)

### Ergonomic design

- Flexible adjustment with tilt, swivel, height and pivot.
- Robust stand design with strong stability
- VESA supportive

### Comfort and protection

- TUV/Eyesafe™ certified; protect eyes by reducing harmful blue light while maintaining high color accuracy
- 100Hz refresh rate, flicker-free
- BlueLightShield Pro
- 85% PCR, 5% OBP
- 100% recyclable paper packaging
- TCO/ENERGY STAR/EPEAT Gold Certified



### Full HD LED monitor



Clearer, sharper images in full high-definition color. Acer monitors brings users into a perfect colorful world in FHD 1920 x 1080, and provides the finest natural and sharp original quality 100,000,000:1 contrast ratio.



### 100Hz Refresh Rate

The 100Hz refresh rate speeds up the frames per second, lowering input lag, delivering ultra-smooth 2D motion scenes, and providing a strain-free viewing experience.



### Ergostand

The Acer monitor allows user to tilt, swivel, height adjust, and pivot with flexibility to meet every using environment, finding the best viewing angle..



### Eco-Display

As part of our commitment to sustainable operations and corporate social responsibility, Acer uses methods to carry out product design and material management distinctly meant to reduce environmental impact.

## About Acer

Established in 1976, Acer is an information and communication technology company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's green supply chain delivers environmentally friendly PCs, displays, projectors, servers, tablets and smartphones — tools our customers need to explore beyond limits and experience more. Ranked No. 3 for notebooks globally (IDC 2012), Acer employs 8,000 people, and 2011 revenues reached US\$15.7 billion. Please visit [www.acer.com](http://www.acer.com) for more information.

