

Liebert® itON 400 VA - 2000 VA



Reliable Power Protection for Desktop Workstations

Features

- Automatic voltage regulator (AVR)
- Compact size
- Light weight
- Easy operation.

Higher Availability

- Overload protection and alarm
- Auto re-start with AC recovery
- Fast charging
- Cold start function.

Flexibility

- Available in ratings from 400 VA up to 2000 VA
- USB port (for 1000 VA, 1500 VA, 2000 VA)

Liebert® itON is a reliable line-interactive UPS designed for the protection of desktop computers and standalone IT equipment

Liebert itON comes complete with an automatic voltage regulator (AVR) allowing flexibility and reliability for PCs and other sensitive electronic equipment. With its compact design and easy to use controls, Liebert itON also provides sufficient back up time, allowing work in progress to be saved safely before proceeding with the system shutdown. Liebert itON also comes complete with automatic restart and cold start functions for increased continuity and availability.

Ideally Suited for:

- Desktop PCs
- Professional workstations
- Small routers, bridges and hubs
- Point-of-sale terminals
- PBXs
- Other sensitive electronics.



Liebert itON 600 VA

Liebert itON 1000 VA

Liebert itON 2000 VA

Liebert® itON VA Specifications

Model Number	LI32101CT01	LI32111CT01	LI32121CT01
Power Rating	400VA / 240W	600VA / 360W	800VA / 360W
Dimensions, W x D x H - mm			
Unit		101 x 279 x 142	
Shipping		330x145x225	
Weight - kg			
Unit	7.83 (3.55)	9.37 (4.2)	10.8 (4.9)
Shipping	3.82kg	4.51kg	5.2kg
Input AC Parameters			
Line Input Nominal Voltage		220 - 240 VAC	
Line Frequency		50Hz / 60Hz (auto-sensing)	
Input Socket		IEC 320-C14	
Output Sockets		(4) IEC 320-C13	
Output Voltage		230 V AC	
Waveform (Battery Operation)		Stepped sinewave	
Battery Parameters			
Type		Valve-regulated, non-spillable, lead acid	
Quantity x Voltage x Rating	12V x 4.5 Ah x 1	12V x 7 Ah x 1	12V x 9 Ah x 1
Recharge Time		4 - 6 hours to 90%	
Environmental			
Operating Temperature		32 to 104 (0 to 40)	
Relative Humidity		0 - 90% non-condensing	
Operating Altitude		0 - 2000 m	
Standards and Certifications			
Safety		EN62040-1:2008	
EMC		EN62040-2:2006 class C2	
Compliance		CE	

Model Number	LI32131CT21	LI32141CT21	LI32151CT21
Power Rating	1000VA / 600W	1500VA / 900W	2000VA / 1200W
Dimensions, W x D x H - mm			
Unit		130 x 320 x 182	
Shipping		395x197x280	
Weight - kg			
Unit	18.1 (8.2)	22.9 (10.4)	24.1 (11)
Shipping	9.2kg	10.9kg	11.01kg
Input AC Parameters			
Line Input Nominal Voltage		220 - 240 V AC	
Line Frequency		50 / 60 Hz; Auto Sensing	
Input Socket		IEC 320-C14	
Output Socket	(4) IEC 320-C13	(6) IEC 320-C13	(6) IEC 320-C13
Output Voltage		230 V AC	
Waveform (Battery Operation)		Stepped sinewave	
Battery Parameters			
Type		Valve-regulated, non-spillable, lead acid	
Quantity x Voltage x Rating	12V x 7 Ah x 2	12V x 9 Ah x 2	12V x 9 Ah x 2
Recharge Time		4 - 6 hours to 90%	
Environmental			
Operating Temperature		32 to 104 (0 to 40)	
Relative Humidity		0 - 90% non-condensing	
Operating Altitude		0 - 2000 m	
Standards and Certifications			
Safety		EN62040-1:2008	
EMC		EN62040-2:2006 class C2	
Compliance		CE	

Note: External battery cabinets are not permitted. Internal batteries only.

Tech Support

Always On! Our Commitment to your daily Business, provided by multi language Tech Support.

Toll-free 0080011554499 **Toll** +39 02 98250222 **Email** eoc@Vertiv.com

Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2023 Vertiv Co. All rights reserved. Vertiv, and the Vertiv logo trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.