

207473-1 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit

TE Internal #: 207473-1

Cable Clamp Kit, Thermoplastic, Black, Shell Size 4, 37 Position,
AMPLIMITE Kit

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Thermoplastic**

Primary Product Color: **Black**

Compatible With Connector Shell Size: **4**

Shielded: **No**

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
Sealable	No

Configuration Features

Number of Positions	37
---------------------	----

Body Features

Cable Exit Angle	180°
Primary Product Material	Thermoplastic
Primary Product Color	Black

Mechanical Attachment

Thread Size	None
-------------	------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Dimensions



Compatible Insulation Diameter Range	10.29 mm, 16.26 mm [.405 in][.64 in]
--------------------------------------	--------------------------------------

Operation/Application

Compatible With Connector Shell Size	4
Shielded	No

Packaging Features

Packaging Method	Individual
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | AMPLIMITE Kit



Customers Also Bought



Documents

[Product Drawings](#)
[CABLE CLAMP KIT,SZ 4](#)

English

[CAD Files](#)
[Customer View Model](#)
[ENG_CVM_CVM_207473-1_D.2d_dxf.zip](#)



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_207473-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207473-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English