

# Capacitance Meter



**RoHS  
Compliant**

## Description

The digital capacitance meter is a 3½ digits with steady operations, fashionable design and highly reliable hand-held measuring instrument. The meter can also measure resistance, transistor, diode and continuity buzzer. the meter has a broad capacitance measurement range and precise accuracy. It can be used in measuring the circuit designed capacitance of cable, switch and PCB layout.

## Features

- Display Count : 1,999
- Manual Range
- Diode Test
- Transistor Test
- Continuity Buzzer
- Low Battery Indication
- Data Hold

## Specifications

	Range	Best Accuracy
Resistance (Ω)	20Ω/200Ω/2kΩ/20kΩ/200kΩ/2MΩ/20MΩ/200MΩ/2000MΩ	±(0.8%+1)
Capacitance (C)	200pF/2nF/20nF/200nF/2μF/20μF/200μF/2mF/20mF	±(0.5%+10)

## General Characteristic

Power	9V Battery (6F22)
LCD Size	61mm × 32mm
Product Colour	Orange and Grey
Product Net Weight	310g
Product Size	172mm × 83mm × 38mm

Accessories	Qty.	Note
Operating Manual	1 Piece	-
Alligator clip short test leads	1 Pair	Core: 19/20 Length: 110-130mm
Battery	1 Piece	9V Alkaline Battery(6F22), non-rechargeable, replaceable

## Part Number Table

Description	Part Number
Capacitance Meter, 20000μF, 1999	72-8150

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
Farnell.com/exclusive-brands  
Element14.com/exclusive-brands

