

MODIFICATION

PRODUCT CHANGE NOTIFICATION

PRODUCT
CHANGE.

ID-No.:000750620

Ladies and Gentlemen,

we would like to inform you about the change of our PCB-Transformers:

DESCRIPTION OF THE CHANGE

As part of restructuring in the production processes of our PCB transformers, technical features change in addition to the visual appearance. You will find the changes in the following overview. There may also be small differences in the no-load voltages and efficiency. The pinning is identical to the previous version.

PARTS:

The following product series are affected by this change:

- VB 0,35/...
- VB 0,5/...
- VB 1,0/...
- VB 1,2/...
- VB 1,5/...
- VB 2,0/...
- VB 2,3/...

(... = followed by any suffixes)

Date of announcement	July 2024
Scheduled date of change	After sale of the respective stock (starting from Q1/2025)
Productgroup	Transformer
Existing inventory can still be used	<input checked="" type="checkbox"/> yes <input type="checkbox"/> no
Mixing of inventory approved	<input type="checkbox"/> yes <input checked="" type="checkbox"/> no
Issued by	Andreas Reinhardt Head of Transformer Development

BLOCK Transformatoren-Elektronik GmbH













Max-Planck-Straße 36-46
27283 Verden • Germany
Phone: +49 4231 678-0 • Fax: +49 4231 678-177
info@block.eu • www.block.eu

BLOCK 
perfecting power

MODIFICATION

PRODUCT CHANGE NOTIFICATION

PRODUCT
CHANGE.

	Current transformers	Future transformers
Color of the housing:		
Color of the potting compound:		
Approvals:	  File E103521	  File E103521
Ambient temperature: <ul style="list-style-type: none"> - VB 0,35/... - VB 0,5/... - VB 1,0/... - VB 1,2/... - VB 1,5/... - VB 2,0/... - VB 2,3/... 	  max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C max. 70°C max.70°C	  max. 50°C max.40°C max. 70°C max.40°C max. 70°C max.40°C max. 70°C max.40°C max. 70°C max.40°C max. 70°C max.40°C max. 70°C max.40°C max. 60°C max.40°C
Dimensions: <ul style="list-style-type: none"> - VB 0,35/... - VB 0,5/... - VB 1,0/... - VB 1,2/... - VB 1,5/... - VB 2,0/... - VB 2,3/... 	<u>Wide x Depth x Height</u> 22,7mm x 22,0mm x 15,0mm 22,7mm x 22,0mm x 19,0mm 32,3mm x 27,3mm x 21,8mm 32,3mm x 27,3mm x 23,8mm 32,3mm x 27,3mm x 23,8mm 32,3mm x 27,3mm x 26,8mm 32,3mm x 27,3mm x 29,0mm	<u>Wide x Depth x Height</u> 24,0mm x 23,0mm x 16,0mm 24,0mm x 23,0mm x 20,0mm 32,8mm x 27,8mm x 22,3mm 32,8mm x 27,8mm x 22,3mm 32,8mm x 27,8mm x 24,4mm 32,8mm x 27,8mm x 27,4mm 32,8mm x 27,8mm x 29,8mm
Country of origin:	Germany	China

BLOCK Transformatoren-Elektronik GmbH

Max-Planck-Straße 36-46
 27283 Verden • Germany
 Phone: +49 4231 678-0 • Fax: +49 4231 678-177
 info@block.eu • www.block.eu