

D-Sub F AWG 22-26 contact cat7 module



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 5476
Specification	D-Sub F AWG 22-26 contact cat7 module
HARTING eCatalogue	https://b2b.harting.com/09930005476

Identification

Category	Contacts
Series	D-Sub
Type of contact	Crimp contact

Version

Gender	Female
--------	--------

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Transmission characteristics	Cat. 7 _A
Contact resistance	≤10 mΩ
Mating cycles	≥500

Material properties

Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	100
Net weight	0.304 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229228
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors