

## Final datasheet

### EasyBRIDGE module with CoolSiC™ Schottky diode and PressFIT / NTC

#### Features

- Electrical features
  - $V_R = 650\text{ V}$
  - $I_F = 60\text{ A}$ ,  $I_{FRM} = 120\text{ A}$
  - CoolSiC™ Schottky diode gen 5
  - High dynamic robustness
  - Suitable Infineon gate drivers can be found under <https://www.infineon.com/gdfinder>
- Mechanical features
  - Compact design
  - Rugged mounting due to integrated mounting clamps
  - PressFIT contact technology
  - Integrated NTC temperature sensor
  - $\text{Al}_2\text{O}_3$  substrate with low thermal resistance



Typical appearance


#### Potential applications

- DC charger for EV

#### Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

#### Description



## Table of contents

	<b>Description</b> .....	1
	<b>Features</b> .....	1
	<b>Potential applications</b> .....	1
	<b>Product validation</b> .....	1
	<b>Table of contents</b> .....	2
<b>1</b>	<b>Package</b> .....	3
<b>2</b>	<b>Diode, Rectifier</b> .....	3
<b>3</b>	<b>MOSFET</b> .....	4
<b>4</b>	<b>Body diode (MOSFET)</b> .....	6
<b>5</b>	<b>NTC-Thermistor</b> .....	6
<b>6</b>	<b>Characteristics diagrams</b> .....	7
<b>7</b>	<b>Circuit diagram</b> .....	11
<b>8</b>	<b>Package outlines</b> .....	12
<b>9</b>	<b>Module label code</b> .....	13
	<b>Revision history</b> .....	14
	<b>Disclaimer</b> .....	15

## 1 Package

**Table 1** Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	$V_{ISOL}$	RMS, $f = 50$ Hz, $t = 1$ min	3.0	kV
Internal isolation		basic insulation (class 1, IEC 61140)	$Al_2O_3$	
Comparative tracking index	$CTI$		> 200	
Relative thermal index (electrical)	$RTI$	housing	140	°C

**Table 2** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	$L_{sCE}$			15		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_H = 25$ °C, per switch		2.2		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25$ °C, per switch		3.8		mΩ
Storage temperature	$T_{stg}$		-40		125	°C
Mounting force per clamp	$F$		20		50	N
Weight	$G$			24		g

Note: The current under continuous operation is limited to 25 A rms per connector pin.

## 2 Diode, Rectifier

**Table 3** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Repetitive peak reverse voltage	$V_{RRM}$	$T_{vj} = 25$ °C	650	V	
Maximum RMS forward current per chip	$I_{FRMSM}$	$T_H = 30$ °C	50	A	
Maximum RMS current at rectifier output	$I_{RMSM}$	$T_H = 30$ °C	70	A	
Surge forward current	$I_{FSM}$	$t_p = 10$ ms	$T_{vj} = 25$ °C	341	A
			$T_{vj} = 150$ °C	295	
$I^2t$ - value	$I^2t$	$t_p = 10$ ms	$T_{vj} = 25$ °C	581	A <sup>2</sup> s
			$T_{vj} = 150$ °C	434	

**Table 4** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	$V_F$	$I_F = 60 \text{ A}$	$T_{vj} = 25 \text{ °C}$	1.45		V
			$T_{vj} = 150 \text{ °C}$	1.65		
Reverse current	$I_r$	$T_{vj} = 150 \text{ °C}, V_R = 650 \text{ V}$		3.39		mA
Thermal resistance, junction to heat sink	$R_{thJH}$	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$		1.25		K/W
Temperature under switching conditions	$T_{vj, op}$		-40		150	°C

### 3 MOSFET

**Table 5** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Drain-source voltage	$V_{DSS}$	$T_{vj} = 25 \text{ °C}$	1200	V
Continuous DC drain current	$I_{DDC}$	$T_{vj} = 175 \text{ °C}, V_{GS} = 18 \text{ V}$ $T_H = 95 \text{ °C}$	15	A
Repetitive peak drain current	$I_{DRM}$	verified by design, $t_p$ limited by $T_{vjmax}$	30	A
Gate-source voltage, max. transient voltage	$V_{GS}$	$D < 0.01$	-10/23	V
Gate-source voltage, max. static voltage	$V_{GS}$		-7/20	V

**Table 6** Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
On-state gate voltage	$V_{GS(on)}$		15...18	V
Off-state gate voltage	$V_{GS(off)}$		-5...0	V

**Table 7** Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-resistance	$R_{DS(on)}$	$I_D = 15\text{ A}$	$V_{GS} = 18\text{ V}, T_{vj} = 25\text{ °C}$		52.9	79	mΩ
					85.5		
					114		
					63.5		
Gate threshold voltage	$V_{GS(th)}$	$I_D = 6\text{ mA}, V_{DS} = V_{GS}, T_{vj} = 25\text{ °C},$ (tested after 1ms pulse at $V_{GS} = +20\text{ V}$ )		3.45	4.3	5.15	V
Total gate charge	$Q_G$	$V_{DD} = 800\text{ V}, V_{GS} = -3/18\text{ V}$			0.045		μC
Internal gate resistor	$R_{Gint}$	$T_{vj} = 25\text{ °C}$			7.5		Ω
Input capacitance	$C_{ISS}$	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		1.35		nF
Output capacitance	$C_{OSS}$	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.064		nF
Reverse transfer capacitance	$C_{rSS}$	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.005		nF
$C_{OSS}$ stored energy	$E_{OSS}$	$V_{DS} = 800\text{ V}, V_{GS} = -3/18\text{ V}, T_{vj} = 25\text{ °C}$			26.2		μJ
Drain-source leakage current	$I_{DSS}$	$V_{DS} = 1200\text{ V}, V_{GS} = -3\text{ V}$	$T_{vj} = 25\text{ °C}$		0.01	111	μA
Gate-source leakage current	$I_{GSS}$	$V_{DS} = 0\text{ V}, T_{vj} = 25\text{ °C}$	$V_{GS} = 20\text{ V}$			400	nA
Thermal resistance, junction to heat sink	$R_{thJH}$	per MOSFET, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot\text{K})$			2.02		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$			-40		175	°C

**Note:** The selection of positive and negative gate-source voltages impacts losses and the long-term behavior of the MOSFET and body diode. The design guidelines described in Application Notes AN 2018-09 and AN 2021-13 must be considered to ensure sound operation of the device over the planned lifetime.

$T_{vj,op} > 150\text{ °C}$  is allowed for operation at overload conditions for MOSFET and body diode. For detailed specifications, please refer to AN 2021-13.

## 4 Body diode (MOSFET)

**Table 8** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
DC body diode forward current	$I_{SD}$	$T_{vj} = 175\text{ °C}$ , $V_{GS} = -3\text{ V}$ $T_H = 105\text{ °C}$	7	A

**Table 9** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	$V_{SD}$	$I_{SD} = 15\text{ A}$ , $V_{GS} = -3\text{ V}$	$T_{vj} = 25\text{ °C}$	4.2	5.35	V
			$T_{vj} = 125\text{ °C}$	3.9		
			$T_{vj} = 175\text{ °C}$	3.8		

## 5 NTC-Thermistor

**Table 10** Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	$R_{25}$	$T_{NTC} = 25\text{ °C}$		5		k $\Omega$
Deviation of $R_{100}$	$\Delta R/R$	$T_{NTC} = 100\text{ °C}$ , $R_{100} = 493\text{ }\Omega$	-5		5	%
Power dissipation	$P_{25}$	$T_{NTC} = 25\text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15\text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15\text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15\text{ K}))]$		3433		K

Note: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4.

## 6 Characteristics diagrams


**Forward characteristic (typical), Diode, Rectifier**

$$I_F = f(V_F)$$



**Transient thermal impedance, Diode, Rectifier**


$$Z_{th} = f(t)$$



**Output characteristic (typical), MOSFET**

$$I_D = f(V_{DS})$$


$$V_{GS} = 15\text{ V}$$



**Output characteristic (typical), MOSFET**


$$I_D = f(V_{DS})$$

$$V_{GS} = 18\text{ V}$$




**Output characteristic field (typical), MOSFET**

$I_D = f(V_{DS})$   
 $T_{vj} = 175\text{ °C}$




**Drain source on-resistance (typical), MOSFET**

$R_{DS(on)} = f(I_D)$   
 $V_{GS} = 18\text{ V}$




**Drain source on-resistance (typical), MOSFET**

$R_{DS(on)} = f(T_{vj})$   
 $I_D = 15\text{ A}$



**Transfer characteristic (typical), MOSFET**

$I_D = f(V_{GS})$   
 $V_{DS} = 20\text{ V}$






6 Characteristics diagrams

**Gate-source threshold voltage (typical), MOSFET**

$$V_{GS(th)} = f(T_{vj})$$


$$V_{GS} = V_{DS}$$



**Gate charge characteristic (typical), MOSFET**

$$V_{GS} = f(Q_G)$$


$$I_D = 15 \text{ A}, T_{vj} = 25 \text{ °C}$$



**Capacity characteristic (typical), MOSFET**

$$C = f(V_{DS})$$


$$f = 100 \text{ kHz}, T_{vj} = 25 \text{ °C}, V_{GS} = 0 \text{ V}$$



**Reverse bias safe operating area (RBSOA), MOSFET**

$$I_D = f(V_{DS})$$


$$R_{Goff} = 1.6 \text{ } \Omega, T_{vj} = 175 \text{ °C}, V_{GS} = -3/18 \text{ V}$$



6 Characteristics diagrams

**Transient thermal impedance, MOSFET**


$Z_{th} = f(t)$



**Forward characteristic body diode (typical), MOSFET**

$I_{SD} = f(V_{SD})$


$T_{vj} = 25\text{ }^\circ\text{C}$



**Forward voltage of body diode (typical), MOSFET**


$V_{SD} = f(T_{vj})$

$I_{SD} = 15\text{ A}$



**Temperature characteristic (typical), NTC-Thermistor**

$R = f(T_{NTC})$



## 7 Circuit diagram




Figure 1

## 8 Package outlines




Figure 2

## 9 Module label code

Module label code			
Code format	Data Matrix	Barcode Code128	
Encoding	ASCII text	Code Set A	
Symbol size	16x16	23 digits	
Standard	IEC24720 and IEC16022	IEC8859-1	
Code content	Content	Digit	Example
	Module serial number	1 - 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 - 21	15
	Date code (production week)	22 - 23	30
Example	 		
	71549142846550549911530		71549142846550549911530

Figure 3

## Revision history

Document revision	Date of release	Description of changes
0.10	2023-06-14	Initial version
1.00	2023-08-24	Final datasheet

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2023-08-24**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2023 Infineon Technologies AG**

**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**IFX-ABD824-002**

## Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

## Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.