

## HLPT-B3x0-00000

### Silicon NPN Phototransistor

---

#### Description

The HLPT-B3x0-00000 is a robust and efficient phototransistor that is available in an industry-standard 3-mm through-hole lamp package.

This product comes with black epoxy, which filters undesired visible light. It is available in an angle of half sensitivity of  $\pm 12$  and  $\pm 25$  degrees.

It has a wide spectral range of sensitivity from 720 nm to 1100 nm. Coupled with its high photosensitivity, this product is a suitable candidate for a variety of applications in consumer and industrial segments, such as office automation, light curtains, and machine control.

This product is easy to use and is a cost-effective solution that offers superior performance.


#### Features

- Silicon NPN phototransistor
- 3-mm radial package
- Black epoxy package
- High photosensitivity
- Angle of half sensitivity of  $\pm 12$  and 25 degrees
- Wide spectral sensitivity from 720 nm to 1100 nm

#### Applications

- Office automation
- Home appliances
- Light curtains
- Machine control

Figure 1: Package Drawing



**NOTE:**

- All dimensions are in millimeters (mm).
- Tolerance is  $\pm 0.25$  mm unless otherwise specified.
- Lead spacing is measured at where the leads emerge from the body.
- The epoxy meniscus may extend up to a maximum of 1.00 mm down the leads.

## Device Selection Guide ( $T_J = 25^\circ\text{C}$ )

Part Number	Collector Light Current, $I_{ca}$ (mA) @ $E_e = 1 \text{ mW/cm}^2$ , $\lambda = 940 \text{ nm}$ , $V_{CE} = 5\text{V}$			Angle of Sensitivity, $\phi$
	Min.	Typ.	Max.	
HLPT-B3D0-00000	8.0	14.6	23.0	$\pm 12$
HLPT-B3G0-00000	4.3	8.2	11.0	$\pm 25$

## Absolute Maximum Ratings

Parameter	Symbol	Rating	Unit
Collector-Emitter Voltage	$V_{CEO}$	30	V
Emitter-Collector Voltage	$V_{ECO}$	5	V
Collector Current	$I_C$	30	mA
Power Dissipation <sup>a</sup>	$P_d$	150	mW
Operating Temperature Range	—	-40 to +85	$^\circ\text{C}$
Storage Temperature Range	—	-40 to +100	$^\circ\text{C}$

a. Derate linearly as shown in [Figure 10](#).

## Optical and Electrical Characteristics ( $T_J = 25^\circ\text{C}$ )

Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Spectral Range of Sensitivity	$\lambda$	720	—	1100	nm	—
Wavelength of Peak Sensitivity	$\lambda_{max}$	—	920	—	nm	—
Dark Current	$I_{CEO}$	—	—	100	nA	$V_{CE} = 20\text{V}$ , $E_e = 0 \text{ mW/cm}^2$
Collector-Emitter Saturation Voltage	$V_{CEsat}$	—	—	0.4	V	$I_C = 0.1 \text{ mA}$ , $E_e = 1 \text{ mW/cm}^2$ , $\lambda = 940 \text{ nm}$
Collector-Emitter Capacitance	$C_{CEO}$	—	5.7	—	pF	$V_{CE} = 0\text{V}$ , $f = 1 \text{ MHz}$ , $E_e = 0 \text{ mW/cm}^2$

Figure 2: Relative Sensitivity vs. Wavelength




Figure 3: Relative Sensitivity vs. Angular Displacement




Figure 4: Relative Collector Current vs. Irradiance




Figure 5: Collector-Emitter Capacitance vs. Collector-Emitter Voltage




Figure 6: Collector Current vs. Collector-Emitter Voltage for HLPT-B3D0




Figure 7: Collector Current vs. Collector-Emitter Voltage for HLPT-B3G0




Figure 8: Relative Collector Current vs. Ambient Temperature




Figure 9: Dark Current vs. Ambient Temperature





Figure 10: Power Dissipation vs. Ambient Temperature



## Precautionary Notes

### Soldering and Handling Precautions

- Set and maintain the wave soldering parameters according to the recommended temperature and dwell time. Perform a daily check on the profile to ensure that it always conforms to the recommended conditions. Exceeding these conditions will overstress the package and cause premature failures.
- Use only bottom preheaters to reduce the thermal stress experienced by the package.
- Recalibrate the soldering profile before loading a new type of PCB. A PCB with a different size and design (component density) will have a different heat capacity and might cause a change in the temperature experienced by the PCB if the same wave soldering setting is used.
- Do not perform wave soldering more than once.
- Any alignment fixture used during wave soldering must be loosely fitted and must not apply stress on the package. Use a nonmetal material because it will absorb less heat during the wave soldering process.
- At elevated temperatures, the package is more susceptible to mechanical stress. Allow the package to sufficiently cool to room temperature before handling. Do not apply stress to the package when it is hot.
- Use wave soldering to solder the package. Use hand soldering only for rework or touch-up if unavoidable, but it must be strictly controlled to following conditions:
  - Soldering iron tip temperature = 315°C maximum
  - Soldering duration = 2-second maximum
  - Number of cycles = 1 only
  - Power of soldering iron = 50W maximum
- Do not touch the package body with the soldering iron except for the soldering terminals as it might damage the package.
- Confirm beforehand whether the functionality and performance of the package are affected by hand soldering.
- Keep the heat source at least 1.6 mm away from the package body during soldering.

Figure 11: Recommended PCB Through-Hole Size





Figure 12: Recommended Wave Soldering Profile



**NOTE:** Refers to measurements with a thermocouple mounted at the bottom of the PCB.

### Lead Forming

- To pre-form or cut the leads before insertion and soldering onto PCB, use a proper tool instead of doing it manually.
- Do not bend the leads at a location that is less than 3 mm from the package body.
- Do not use the base of the package body as a fulcrum for lead bending. Secure the leads properly before bending.
- If manual lead cutting is unavoidable, cut the leads after soldering to reduce stress to the package body.

### Application Precautions

- Avoid rapid changes in ambient temperatures, especially in high-humidity environments, because they cause condensation on the package.
- If the package is intended to be used in harsh or outdoor environments, protect the package against damages caused by rain water, water, dust, oil, corrosive gases, external mechanical stresses, and so on.

## Disclaimer

Broadcom's products and software are not specifically designed, manufactured, or authorized for sale as parts, components, or assemblies for the planning, construction, maintenance, or direct operation of a nuclear facility or for use in medical devices or applications. The customer is solely responsible, and waives all rights to make claims against Broadcom or its suppliers, for all loss, damage, expense, or liability in connection with such use.

Copyright © 2024 Broadcom. All Rights Reserved. The term "Broadcom" refers to Broadcom Inc. and/or its subsidiaries. For more information, go to [www.broadcom.com](http://www.broadcom.com). All trademarks, trade names, service marks, and logos referenced herein belong to their respective companies.

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.



Lead (Pb) Free  
RoHS Compliant