



TE Internal #: 2480655-2
 MCX Cable Assembly, .305 m [1.01 ft], Brown Cable, 0 – 6 GHz
 Operating Frequency, 50 ohm, FEP, 26 – 25 AWG, 1.53 mm [.06 in]
 Diameter, MCX Plug End A

[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Cable Assembly Type: **MCX**
 Cable Assembly Length: **.305 m [1.01 ft]**
 Cable Color: **Brown**
 Operating Frequency: **0 – 6 GHz**
 Impedance: **50 Ω**

Features

Configuration Features

Number of Positions	1
---------------------	---

Contact Features

Contact Underplating Material	Nickel
Ferrule Plating Material	Gold
Ferrule Material	Brass
Contact Mating Area Plating Material	Gold
Contact Base Material	Brass
Center Contact Plating	Gold

Operation/Application

Shielded	Yes
Operating Frequency	0 – 6 GHz

Body Features

Body Plating Material	Gold
Conductor Material	Beryllium Copper



Conductor Plating Material	Gold
Shield Material	Brass
Cable Color	Brown
Jacket Material	FEP

Product Type Features

Cable Assembly Type	MCX
Cable Assembly (End A)	MCX Plug
Cable Assembly (End B)	MCX Plug
Coax Cable Type	RG 316

Other

Cable Assembly Length	.305 m[1.01 ft]
EU RoHS Compliance	Compliant with Exemptions

Electrical Characteristics

Impedance	50 Ω
-----------	-------------

Dimensions

Wire Size	26 – 25 AWG
Outside Cable Diameter	1.53 mm[.06 in]

Usage Conditions

Operating Temperature Range	-45 – 125 °C[-49 – 257 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4.75% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR

/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1337581-0
MCX Str PCB Skt 50Ohm Gold Pltd



TE Part # 829558-4
MCX GE KU LEI



TE Part # CONMCX001-SMD-T
MCX Jack 50 Ohm PCB Surface Mount



TE Part # CONMCX002-SMD-T
MCX Jack 50 Ohm PCB Surface Mount



TE Part # L9000245-01
MCX Jack 50 Ohm .031 PCB Edge Mount



TE Part # CONMCX001
MCX Jack 50 Ohm PCB Through Hole



TE Part # 1-1337582-0
MCX SMT Skt 50Ohm Gold Pltd

Documents

Product Drawings

[MCX Plug to MCX Plug RA RG316 50 Ohm 12"](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_2480655-2_1.3d_stp.zip](#)

English



Customer View Model

[ENG_CVM_CVM_2480655-2_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2480655-2_1.2d_dxf.zip](#)

English

[3D PDF](#)

[3D](#)

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[dnd-fly-RF-cable-assemblies-product-expansion](#)

English