



EN-24

Order No.: 0210200

PRODUCTINFOS

Stereo magnetic phono cartridge system,

(moving magnet).

- Diamond stylus and 1.3 cm (½") fixing
- Matching turntables of our programme (DJP-...) and as a replacement for other hi-fi turntables
- Stylus pressure: approx. 1.5 g

Manufacturer information:

MONACOR INTERNATIONAL GmbH & Co. KG
Zum Falsch 36
28307 Bremen
Germany
info@monacor.com

TECHNICAL SPECIFICATIONS

EN-24

Frequency range	20-20,000 Hz
Output voltage	5 mV/1 kHz, 5 cm/s
Terminal impedance	47 k Ω /200 pF
Impedance	1.2 k Ω
DC resistance	300 Ω
Channel balance	< 2.5 dB/1 kHz
Channel separation	> 24 dB/1 kHz
Dyn. compliance	5 μ m/mN
Recom. stylus pressure	1.5 g
Stylus tip	conical 0.6 μ m
Weight	4.5 g

EN-24

EAN code	4007754098761
Net weight	0.005 kg