



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 10

LOCTITE SUPERLUBE known as SUPERLUBE GREASE 12X85GM

SDS No. : 168446
V003.2

Revision: 05.05.2023

printing date: 05.02.2025

Replaces version from: 27.03.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SUPERLUBE known as SUPERLUBE GREASE 12X85GM

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Lubricant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Adhesives
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.3. Other hazards

None if used properly.

Following substances are present in a concentration \geq the concentration limit for depiction in Section 3 and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in a concentration \geq the concentration limit for depiction in Section 3 that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.
Ensure adequate ventilation.
Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.

Vapours should be extracted to avoid inhalation.

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Keep away from heat and direct sunlight.

Refer to Technical Data Sheet

7.3. Specific end use(s)

Lubricant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

| Ingredient [Regulated substance] | ppm | mg/m ³ | Value type | Short term exposure limit category / Remarks | Regulatory list |
|--|-----|-------------------|------------------------------|--|-----------------|
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, RESPIRABLE DUST] | | 2,4 | Time Weighted Average (TWA): | | EH40 WEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, INHALABLE DUST] | | 6 | Time Weighted Average (TWA): | | EH40 WEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [Dust, inhalable dust] | | 10 | Time Weighted Average (TWA): | | EH40 WEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [Dust, respirable dust] | | 4 | Time Weighted Average (TWA): | | EH40 WEL |

Occupational Exposure Limits

Valid for
Ireland

| Ingredient [Regulated substance] | ppm | mg/m ³ | Value type | Short term exposure limit category / Remarks | Regulatory list |
|---|-----|-------------------|------------------------------|--|-----------------|
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [DUSTS NON-SPECIFIC] | | 10 | Time Weighted Average (TWA): | | IR_OEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS] | | 2,4 | Time Weighted Average (TWA): | | IR_OEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS] | | 6 | Time Weighted Average (TWA): | | IR_OEL |
| Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [DUSTS NON-SPECIFIC] | | 4 | Time Weighted Average (TWA): | | IR_OEL |
| White mineral oil (petroleum) 8042-47-5 [MINERAL OILS THAT HAVE BEEN USED BEFORE IN INTERNAL COMBUSTION ENGINES TO LUBRICATE AND COOL THE MOVING PARTS WITHIN THE ENGINE] | | | Skin designation: | Can be absorbed through the skin. | IR_OEL |
| White mineral oil (petroleum) 8042-47-5 [MINERAL OILS THAT HAVE BEEN USED BEFORE IN INTERNAL COMBUSTION ENGINES TO LUBRICATE AND COOL THE MOVING PARTS WITHIN THE ENGINE] | | | | Included in the regulation but with no data values. See regulation for further details | IR_OEL |
| White mineral oil (petroleum) 8042-47-5 [MINERAL OIL PURE, HIGHLY & SEVERELY REFINED] | | 5 | Time Weighted Average (TWA): | | IR_OEL |

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

| | |
|--|---|
| Delivery form | paste |
| Colour | white |
| Odor | None |
| Physical state | liquid |
| Melting point | Not applicable, Product is a liquid |
| Initial boiling point | Not available. |
| Flammability | The product is not flammable. |
| Explosive limits | Not applicable, The product is not flammable. |
| Flash point | > 93 °C (> 199.4 °F); Tagliabue closed cup |
| Auto-ignition temperature | Not applicable, The product is not flammable. |
| Decomposition temperature | Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use |
| pH | Not available. |
| Viscosity (kinematic) | Currently under determination |
| Solubility (qualitative) | Insoluble |
| (20 °C (68 °F); Solvent: Water) | |
| Partition coefficient: n-octanol/water | Not applicable |
| | Mixture |
| Vapour pressure | Currently under determination |

| | |
|----------------------------|---------------------------------------|
| Density (20 °C (68 °F)) | 0,89 g/cm ³ None |
| Relative vapour density: | Currently under determination |
| Particle characteristics | Not applicable Product is a liquid |

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information

General toxicological information:

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

No data available.

Acute dermal toxicity:

No data available.

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

No data available.

Serious eye damage/irritation:

No data available.

Respiratory or skin sensitization:

No data available.

Germ cell mutagenicity:

No data available.

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure:

No data available.

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains / surface water / ground water.

12.1. Toxicity**Toxicity (Fish):**

No data available.

Toxicity (aquatic invertebrates):

No data available.

Chronic toxicity (aquatic invertebrates):

No data available.

Toxicity (Algae):

No data available.

Toxicity (microorganisms):

No data available.

12.2. Persistence and degradability

The product is not biodegradable.

No substance data available.

12.3. Bioaccumulative potential

No data available.

No substance data available.

12.4. Mobility in soil

Cured adhesives are immobile.

No substance data available.

12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Do not empty into drains / surface water / ground water.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

14 06 03 Other solvents and solvent mixtures

SECTION 14: Transport information

- 14.1. UN number or ID number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Maritime transport in bulk according to IMO instruments**
not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

| | |
|---|----------------|
| Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009): | Not applicable |
| Prior Informed Consent (PIC) (Regulation (EU) No 649/2012): | Not applicable |
| Persistent organic pollutants (Regulation (EU) 2019/1021): | Not applicable |
| VOC content (2010/75/EC) | 0 % |

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

| | |
|-------------|---|
| ED: | Substance identified as having endocrine disrupting properties |
| EU OEL: | Substance with a Union workplace exposure limit |
| EU EXPLD 1: | Substance listed in Annex I, Reg (EC) No. 2019/1148 |
| EU EXPLD 2 | Substance listed in Annex II, Reg (EC) No. 2019/1148 |
| SVHC: | Substance of very high concern (REACH Candidate List) |
| PBT: | Substance fulfilling persistent, bioaccumulative and toxic criteria |
| PBT/vPvB: | Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria |
| vPvB: | Substance fulfilling very persistent and very bioaccumulative criteria |

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.