

Metallized Polypropylene Film Capacitor DC-Link Capacitor MKP Type



FEATURES

- Slim line, low building height
- Very long useful life time: Up to 100 000 h at U_{NDC} and 70 °C
- High ripple current capability, low ESR, low ESL
- Temperature range: 105 °C
- Mounting: Radial
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- PV micro inverters
- LED street lighting
- On board chargers (EV/HEV), battery chargers

QUICK REFERENCE DATA	
Rated capacitance range	2 μ F to 100 μ F
Capacitance tolerance	5 %
Rated voltage range, U_{NDC}	500 V to 1000 V
Climatic testing class	40/105/56
Rated temperature	85 °C
Maximum permissible case temperature	105 °C, observing voltage derating
Maximum applicable peak to peak ripple voltage	0.2 x U_{NDC}
Reference standards	IEC 61071, IEC 60068
Dielectric	Polypropylene film
Electrodes	Metallized dielectric capacitor
Construction	Mono construction
Encapsulation	Plastic case sealed with resin; flame retardant
Terminals	Tinned wire
Self inductance (L_s)	< 1 nH per mm of lead spacing
Withstanding DC voltage between terminals ⁽¹⁾	1.5 U_{NDC} for 10 s, cut off current 10 mA, rise time \leq 1000 V/s
Insulation resistance	RC between leads, after 1 min > 10 000 s For $U_{NDC} \leq$ 500 V measuring voltage 100 V For $U_{NDC} >$ 500 V measuring voltage 500 V
Life time expectancy	Useful life time: > 100 000 h at U_{NDC} and 70 °C FIT: < 10 x 10 ⁻⁹ /h (10 per 10 ⁹ component h) at 0.5 x U_{NDC} , 40 °C
Marking	C-value; tolerance; rated voltage; code for dielectric material; code for manufacturing origin; manufacturer's type designation; manufacturer's logo; year and week of manufacture


Notes

- For more detailed data and test requirements, contact dc-film@vishay.com
- For general information like characteristics and definitions used for film capacitors follow the link: www.vishay.com/doc?28147
- ⁽¹⁾ See document "Voltage Proof Test for Metallized Capacitors" (www.vishay.com/doc?28169)

DC VOLTAGE RATINGS			
U_{NDC} at 85 °C	500 V	700 V	1000 V
U_{OPDC} at 70 °C	600 V	800 V	1200 V
U_{OPDC} at 105 °C	350 V	500 V	750 V



COMPOSITION OF CATALOG NUMBER



Notes

- (1) Tabs terminals or customized terminals are available on request
- (2) Product height on request

DIMENSIONS in millimeters	
<p> $P1 \pm 0.5 \text{ mm}$ $lt = 6 \text{ mm} + 0 \text{ mm} / - 1 \text{ mm}$ </p>	
<p> $P1 \text{ and } P2 \pm 0.5 \text{ mm}$ $lt = 6 \text{ mm} + 0 \text{ mm} / - 2 \text{ mm}$ </p>	
<p> $P1 \text{ and } P2 \pm 0.5 \text{ mm}$ $lt = 6 \text{ mm} + 0 \text{ mm} / - 2 \text{ mm}$ </p>	

Notes

- Standard dimension
- $\varnothing dt \pm 10 \%$ of standard diameter specified



ELECTRICAL DATA AND ORDERING CODE																
U _{NDC} (V)	HEIGHT (mm)	CAP. (7) (µF)	DIMENSION (5) (mm)			P1 (mm)	P2 (mm)	dV/dt (V/µs)	I _{PEAK} (A)	I _{RMS} (2) (A)		ESR (3) (mΩ)		tan δ 10 kHz (< 10 ⁻⁴) (4)		ORDERING CODE (1)
			w	h	l					2 PINS	4 PINS	2 PINS	4 PINS	2 PINS	4 PINS	
500	12	5	24	12	31.5	27.5	-	36	180	4	-	17.5	-	85	-	MKP1848S55050JK2A
	15	7	27	15	31.5	27.5	-	36	252	5.5	-	12.5	-	90	-	MKP1848S57050JK2B
		10	27	15	42	37.5	10.2	18	180	5	5.5	17	15.5	170	150	MKP1848S61050JP*B
		15	33	15	42	37.5	10.2	18	270	7	7	12	10	170	150	MKP1848S61550JP*B
		20	33	15	57.5	52.5	20.3	9	180	6.5	6.5	17	15	335	300	MKP1848S62050JY*B
		30	45	15	57.5	52.5	20.3	9	270	8.5	9	11.5	10	335	300	MKP1848S63050JY*B
		50 (6)	62	15	57.5	52.5	20.3	9	450	13	13.5	6.5	6	335	300	MKP1848S65050JY6B
	18	10	24	18	42	37.5	10.2	18	180	5	5.5	17	15.5	170	150	MKP1848S61050JP*C
		15	27	18	42	37.5	10.2	18	270	6.5	7	11.5	10	170	150	MKP1848S61550JP*C
		20	39	18	42	37.5	10.2	18	360	8.5	9	8.5	7.5	170	155	MKP1848S62050JP*C
		30	35	18	57.5	52.5	20.3	9	270	8	8.5	11.5	10	335	300	MKP1848S63050JY*C
		50 (6)	50	18	57.5	52.5	20.3	9	450	12	13	6.5	6	335	300	MKP1848S65050JY6C
	24	20	30	24	42	37.5	10.2	18	360	8.5	9	8.5	7.5	170	155	MKP1848S62050JP*F
		30	39	24	42	37.5	10.2	18	540	11.5	12	5.5	5	170	155	MKP1848S63050JP*F
		50	39	24	57.5	52.5	20.3	9	450	12	12.5	6.5	6	335	300	MKP1848S65050JY*F
		100 (6)	70	24	57.5	52.5	20.3	9	900	-	22	-	3	-	305	MKP1848S71050JY6F
700	12	3	24	12	31.5	27.5	-	51	153	3.5	-	22.5	-	65	-	MKP1848S53070JK2A
	15	5	27	15	31.5	27.5	-	51	255	5	-	13.5	-	65	-	MKP1848S55070JK2B
		7	27	15	42	37.5	10.2	25	175	5	5	19.5	17	130	120	MKP1848S57070JP*B
		10	33	15	42	37.5	10.2	25	250	6	6.5	14	12	135	120	MKP1848S61070JP*B
		15	33	15	57.5	52.5	20.3	12	180	6	6.5	18	16	265	235	MKP1848S61570JY*B
		20	45	15	57.5	52.5	20.3	12	240	8	8.5	13.5	12	265	235	MKP1848S62070JY*B
		30 (6)	62	15	57.5	52.5	20.3	12	360	11	12	9	8	265	240	MKP1848S63070JY6B
	18	7	24	18	42	37.5	10.2	25	175	5	5	19.5	17	130	120	MKP1848S57070JP*C
		10	27	18	42	37.5	10.2	25	250	6	6.5	13.5	12	135	120	MKP1848S61070JP*C
		15	39	18	42	37.5	10.2	25	375	8.5	9	9	8	135	120	MKP1848S61570JP*C
		20	35	18	57.5	52.5	20.3	12	240	7.5	8	13.5	12	265	235	MKP1848S62070JY*C
		30 (6)	50	18	57.5	52.5	20.3	12	360	10.5	11	9	8	265	240	MKP1848S63070JY6C
	24	15	30	24	42	37.5	10.2	25	375	8.5	9	9	8	135	120	MKP1848S61570JP*F
		20	39	24	42	37.5	10.2	25	500	10.5	11	6.5	6	135	120	MKP1848S62070JP*F
		30	39	24	57.5	52.5	20.3	12	360	10.5	11	9	8	265	240	MKP1848S63070JY*F
		50 (6)	70	24	57.5	52.5	20.3	12	600	-	17.5	-	4.5	-	240	MKP1848S65070 JY6F



ELECTRICAL DATA AND ORDERING CODE																
U _{NDC} (V)	HEIGHT (mm)	CAP. ⁽⁷⁾ (μF)	DIMENSION ⁽⁵⁾ (mm)			P1 (mm)	P2 (mm)	dV/dt (V/μs)	I _{PEAK} (A)	I _{RMS} ⁽²⁾ (A)		ESR ⁽³⁾ (mΩ)		tan δ 10 kHz (< 10 ⁻⁴) ⁽⁴⁾		ORDERING CODE ⁽¹⁾
			w	h	l					2 PINS	4 PINS	2 PINS	4 PINS	2 PINS	4 PINS	
1000	12	2	24	12	31.5	27.5	-	80	160	3	-	27	-	55	-	MKP1848S52010JK2A
	15	5	27	15	42	37.5	10.2	40	200	4.5	5	21	19	105	95	MKP1848S55010JP*B
		7	33	15	42	37.5	10.2	40	280	6	6	15	13.5	105	95	MKP1848S57010JP*B
		10	33	15	57.5	52.5	20.3	20	200	5.5	6	21	19	205	185	MKP1848S61010JY*B
		15	45	15	57.5	52.5	20.3	20	300	8	8.5	14	12.5	205	185	MKP1848S61510JY*B
		20 ⁽⁶⁾	62	15	57.5	52.5	20.3	20	400	10.5	11	10.5	9.5	205	185	MKP1848S62010JY6B
	18	3	24	18	42	37.5	10.2	40	120	3.5	3.5	35.5	31.5	105	95	MKP1848S53010JP*C
		5	27	18	42	37.5	10.2	40	200	5	5	21	19	105	95	MKP1848S55010JP*C
		7	39	18	42	37.5	10.2	40	280	6.5	7	15	13.5	105	95	MKP1848S57010JP*C
		10	39	18	42	37.5	10.2	40	400	8	8.5	10.5	9.5	105	95	MKP1848S61010JP*C
		15	50	18	57.5	52.5	20.3	20	300	8.5	9	14	12.5	205	185	MKP1848S61510JY*C
		20 ⁽⁶⁾	50	18	57.5	52.5	20.3	20	400	10	10.5	10.5	9.5	205	185	MKP1848S62010JY6C
	24	7	30	24	42	37.5	10.2	40	280	6.5	7	15	13.5	105	95	MKP1848S57010JP*F
		10	39	24	42	37.5	10.2	40	400	8.5	9	10.5	9.5	105	95	MKP1848S61010JP*F
		15	39	24	57.5	52.5	20.3	20	300	8	8.5	14	12.5	205	185	MKP1848S61510JY*F
		20	39	24	57.5	52.5	20.3	20	400	9.5	10	10.5	9.5	205	185	MKP1848S62010JY*F
		30 ⁽⁶⁾	70	24	57.5	52.5	20.3	20	600	-	15.5	-	6	-	185	MKP1848S63010JY6F

Notes

- (1) Change the * symbol with special code for the terminals
- (2) Maximum RMS current at 10 kHz, + 85 °C, Δt = + 15 °C, capacitance tolerance ≤ ± 5 %
- (3) Equivalent series resistance typical values at 10 kHz
- (4) Maximum tan δ values
- (5) Standard dimension
- (6) 6 pins
- (7) Intermediate capacitance values available on request

PACKAGING INFORMATION						
U _{NDC} (V)	HEIGHT (mm)	CAP. ⁽¹⁾ (μF)	Ø dt	ORDERING CODE ⁽¹⁾	MASS (g)	SPQ ⁽³⁾ (pcs)
500	12	5	0.8	MKP1848S55050JK2A	9.5	99
	15	7	0.8	MKP1848S57050JK2B	13.5	90
		10	1.0	MKP1848S61050JP*B	18.5	70
		15	1.0	MKP1848S61550JP*B	21.5	56
		20	1.2	MKP1848S62050JY*B	29	40
		30	1.2	MKP1848S63050JY*B	40	30
		50 ⁽²⁾	1.2	MKP1848S65050JY6B	52.5	20
	18	10	1.0	MKP1848S61050JP*C	20	77
		15	1.0	MKP1848S61550JP*C	20.5	70
		20	1.0	MKP1848S62050JP*C	32	49
		30	1.2	MKP1848S63050JY*C	35	35
		50 ⁽²⁾	1.2	MKP1848S65050JY6C	49	10
	24	20	1.0	MKP1848S62050JP*F	32	63
		30	1.0	MKP1848S63050JP*F	38	49
		50	1.2	MKP1848S65050JY*F	48.5	35
		100 ⁽²⁾	1.2	MKP1848S71050JY6F	91.5	20



PACKAGING INFORMATION						
U _{NDC} (V)	HEIGHT (mm)	CAP. ⁽¹⁾ (μ F)	\emptyset dt	ORDERING CODE ⁽¹⁾	MASS (g)	SPQ ⁽³⁾ (pcs)
700	12	3	0.8	MKP1848S53070JK2A	9.5	99
	15	5	0.8	MKP1848S55070JK2B	13	90
		7	1.0	MKP1848S57070JP*B	18.5	70
		10	1.0	MKP1848S61070JP*B	21.5	56
		15	1.2	MKP1848S61570JY*B	27.5	16
		20	1.2	MKP1848S62070JY*B	40	30
		30 ⁽²⁾	1.2	MKP1848S63070JY6B	55	20
	18	7	1.0	MKP1848S57070JP*C	19.5	77
		10	1.0	MKP1848S61070JP*C	20.5	70
		15	1.0	MKP1848S61570JP*C	30.5	49
		20	1.2	MKP1848S62070JY*C	35	35
		30 ⁽²⁾	1.2	MKP1848S63070JY6C	51	10
	24	15	1.0	MKP1848S61570JP*F	29	63
		20	1.0	MKP1848S62070JP*F	37.5	49
		30	1.2	MKP1848S63070JY*F	51	35
		50 ⁽²⁾	1.2	MKP1848S65070JY6F	104	20
1000	12	2	0.8	MKP1848S52010JK2A	9.5	99
	15	5	1.0	MKP1848S55010JP*B	17	70
		7	1.0	MKP1848S57010JP*B	20	32
		10	1.2	MKP1848S61010JY*B	26.5	40
		15	1.2	MKP1848S61510JY*B	36.5	12
		20 ⁽²⁾	1.2	MKP1848S62010JY6B	52.5	20
	18	3	1.0	MKP1848S53010JP*C	21.5	77
		5	1.0	MKP1848S55010JP*C	22	70
		7	1.0	MKP1848S57010JP*C	33.5	49
		10	1.0	MKP1848S61010JP*C	29.5	49
		15	1.2	MKP1848S61510JY*C	55.5	25
		20 ⁽²⁾	1.2	MKP1848S62010JY6C	48.5	10
	24	7	1.0	MKP1848S57010JP*F	32.5	63
		10	1.0	MKP1848S61010JP*F	42.5	49
		15	1.2	MKP1848S61510JY*F	56	35
		20	1.2	MKP1848S62010JY*F	48	35
30 ⁽²⁾		1.2	MKP1848S63010JY6F	104.5	20	

Notes

(1) Intermediate capacitance values available on request

(2) 6 pins

(3) SPQ = Standard Packing Quantity

CONSTRUCTION DESCRIPTION

Low inductive wound cell elements of metallized polypropylene film, potted with resin in a flame retardant case.

SPECIFIC METHOD OF MOUNTING TO WITHSTAND VIBRATION AND SHOCK

The capacitor unit is designed for mounting on a printed circuit board. In order to withstand vibration and shock tests, it must be insured that the stand-off pips are in good contact with the printed circuit board. The capacitors shall be mechanically fixed by the leads and the body clamped.


SPACE REQUIREMENTS ON PRINTED-CIRCUIT BOARD FOR 2 PINS PRODUCTS

The maximum space for length ($l_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) of film capacitors to take in account on the printed circuit board is shown in the drawings.

For products with pitch = 37.5 mm, $\Delta = 0.7$ mm for l and w , and $\Delta = 0$ mm for h

For products with pitch = 52.5 mm, $\Delta = 1.0$ mm for l and w , and $\Delta = 0$ mm for h

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.


SPACE REQUIREMENTS ON PRINTED-CIRCUIT BOARD FOR MULTIPLE PINS PRODUCTS

The product height with seating plane as given by "IEC 60717" as reference: $h_{max.} = h$. The maximum length and width of film capacitors is shown in the figure.

DIMENSIONS in millimeters				
P1	L _{max.}	W _{max.}	Ø D	H
37.5	$l + 1.5$	$w + 1.8$	1.5	$h + 0.5$
52.5	$l + 1.8$	$w + 2.0$	1.7	$h + 0.5$

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile we refer to the document "Soldering Conditions Vishay Film Capacitors": www.vishay.com/doc?28171

STORAGE TEMPERATURE

Storage temperature: $T_{stg} = -25\text{ °C to }+35\text{ °C}$ with RH maximum 75 % without condensation


RATINGS AND CHARACTERISTICS REFERENCE CONDITIONS

Unless otherwise specified, all electrical values apply to an ambient temperature of $23\text{ °C} \pm 1\text{ °C}$, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of $50\% \pm 2\%$.


For reference testing, a conditioning period shall be applied over $96\text{ h} \pm 4\text{ h}$ by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.




CHARACTERISTICS




Capacitance as a function of ambient temperature (typical)




Insulation resistance as a function of ambient temperature (typical)




Lifetime expectancy (typical)



Maximum I_{RMS} current in function of ambient temperature



Impedance vs. Frequency (typical)



Impedance vs. Frequency (typical)

HEAT CONDUCTIVITY			
DIMENSION (mm)			HEAT CONDUCTIVITY (mW/°C)
w	h	l	
24	12	31.5	21.5
27	15	31.5	26
27	15	42	33
33	15	42	38
24	18	42	33.5
27	18	42	36
39	18	42	47
30	24	42	45.5
39	24	42	54.5
33	15	57.5	48.5
45	15	57.5	61.5
62	15	57.5	80
35	18	57.5	55
50	18	57.5	72
39	24	57.5	68
70	24	57.5	106


POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free air ambient temperature.

The component temperature rise (ΔT) can be measured or calculated by $\Delta T = P/G$:

- $\Delta T = T_{\text{case}} - T_{\text{ambient}} =$ Case temperature rise ($^{\circ}\text{C}$) with a maximum of 15°C at rated temperature.
- $P = I_{\text{RMS}}^2 \times \text{ESR} =$ Power dissipation of the component (mW)
- $G =$ Heat conductivity of the component (mW/ $^{\circ}\text{C}$)

MEASURING THE COMPONENT TEMPERATURE



The case temperature is measured in unloaded condition (T_{amb}) and loaded condition (T_{C}).


To avoid external thermal radiation or convection, the capacitor must be tested in a closed area, free from air circulation.

APPLICATION NOTES AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

To select the capacitor for a certain application, the following conditions must be checked:

1. The continuous peak voltage (U_{p+}) shall not exceed the DC voltage rating (U_{NDC})
2. The peak-to-peak ripple voltage (U_{pp}) shall not be greater than $0.2 \times U_{NDC}$



3. For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact dc-film@vishay.com.
4. The voltage peak slope (dU/dt) shall not exceed the pulse slope at the DC voltage rating.
If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by U_{NDC} and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_0^T \left(\frac{dU}{dt} \right)^2 \times dt < U_{NDC} \times \left(\frac{dU}{dt} \right)_{\text{rated}}$$

T is the pulse duration

MAXIMUM REPETITIVE PEAK VOLTAGES	
REPETITIVE SURGE VOLTAGE	MAXIMUM DURATION PER DAY
$1.1 \times U_{NDC}$	30 % of on load duration
$1.15 \times U_{NDC}$	30 min
$1.2 \times U_{NDC}$	5 min
$1.3 \times U_{NDC}$	1 min
$1.5 \times U_{NDC}$	110 ms

Note

- The capacitor unit may be subjected to the following surge without any significant reduction of lifetime expectancy



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
ROUTINE TEST - FINAL INSPECTION		
5.14.2-1 External inspection, visual examination		Legible marking as specified
5.14.2-2 Dimensions		See specification drawing
5.3-1 Capacitance	1 kHz at room temperature	See specific reference data
5.3-2 tan δ	1 kHz at room temperature 10 kHz at room temperature	See specific reference data
5.5.1-2 Voltage test between terminals	1.5 x U _{NDC} at T _{amb} Duration: 10 s	No visible damage or puncture No flashover
5.7 Insulation resistance	U _{NDC} ≤ 500 V measuring voltage 100 V at room temperature U _{NDC} > 500 V measuring voltage 500 V at room temperature Duration: 1 min	See specific reference data
TYPE TESTS		
5.14.2 External inspection	Check for finish, marking and overall dimensions	Legible marking and finish as specified Dimensions: See specification drawing
5.14.0 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz	
5.14.1-1/4 Robustness of terminations IEC 60068-2-21	Tensile U _{a1} Wire diameter Section modulus Load ≤ 0.8 mm ≤ 0.5 mm ² 10 N ≤ 1.25 mm ≤ 1.2 mm ² 20 N Duration: 10 s ± 1 s Bending, U _b method 1 Wire diameter Section modulus Load ≤ 0.8 mm ≤ 0.5 mm ² 10 N ≤ 1.25 mm ≤ 1.2 mm ² 20 N 4 x 90°, duration: 2 s to 3 s/bend	
5.14.1-6 Resistance to soldering heat IEC 60068-2-20	No pre-drying, method 1A Solder bath: 260 °C ± 5 °C Duration: 10 s ± 1 s	
5.14.4 Final measurements	Capacitance tan δ	\Delta C/C ≤ 0.5 % Increase of tan δ ≤ 0.0050 compared to the values measured in 5.14.0
5.14.0 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz	
5.14.3-1 Vibration IEC 60068-2-6	10 Hz to 55 Hz; amplitude ± 0.35 mm or acceleration 98 m/s ² Test duration: 10 frequency cycles 3 axes offset from each other by 90° 1 octave/min Visual examination	No visible damage



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
5.14.3-2 Shock or impact IEC 60068-2-6 5.14.4 Final measurements	Pulse shape: half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms Visual examination Capacitance tan δ	No visible damage $ \Delta C/C \leq 0.5\%$ Increase of tan δ ≤ 0.0050 compared to the values measured in 5.14.0
5.5.3-1 Initial measurements 5.5.3-2 Voltage test between terminals 5.5.3-3 Final measurements	Capacitance at 1 kHz tan δ at 10 kHz R insulation 1.5 x U _{NDC} at T _{amb} Duration: 60 s Capacitance tan δ R insulation	$ \Delta C/C \leq 0.5\%$ Increase of tan δ ≤ 0.0050 R insulation ≤ 50 % of specified values
5.9-1 Initial measurements 5.9-2 Surge discharge test 5.9-2 Voltage test between terminals 5.9-3 Final measurements	Capacitance at 1 kHz tan δ at 10 kHz 1.1 x U _{NDC} Number of discharges: 5 Time lapse: every 2 min (10 min total) Within 5 min after the surge discharge test Duration: 60 s 1.5 x U _{NDC} at T _{amb} Capacitance tan δ at 10 kHz	$ \Delta C/C \leq 1.0\%$ tan δ ≤ 1.2 x initial tan δ + 0.0001 compared to the values measured in 5.9-1
5.11-1 Initial measurements 5.11-2 Self healing test 5.11-3 Final measurements	Capacitance at 1 kHz tan δ at 10 kHz 1.5 x U _{NDC} Duration: 10 s Number of clearings ≤ 5 Clearing = Voltage drop of 5 % increase the voltage at 100 V/s till 5 clearings occur with a max. of 2.5 x U _{NDC} for a duration of 10 s Capacitance tan δ	$ \Delta C/C \leq 0.5\%$ tan δ ≤ 1.2 x initial tan δ + 0.0001 compared to the values measured in 5.11-1



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
<p>5.13-0 Initial measurements</p> <p>5.13-1 Change of temperature according to IEC 60682-2-14</p> <p>5.13-2 Damp heat steady state according to IEC 60682-2-78</p> <p>5.5.3-2 Voltage test between terminals</p> <p>5.13-3 Final measurements</p>	<p>Capacitance at 1 kHz tan δ at 10 kHz</p> <p>Test Nb $T_{max.} = 85\text{ }^{\circ}\text{C}$ $T_{min.} = -40\text{ }^{\circ}\text{C}$ Transition time: 1 h, equivalent to 1 $^{\circ}\text{C}/\text{min}$ 5 cycles</p> <p>Test Ca $T_{max.} = 40\text{ }^{\circ}\text{C} + 2\text{ }^{\circ}\text{C}$ RH = 93 % \pm 3 % Duration: 56 days</p> <p>1.5 x U_{NDC} at ambient temperature Duration: 60 s</p> <p>Visual examination</p> <p>Capacitance tan δ at 1 V_{RMS} 10 kHz</p>	<p>No puncturing or flashover Self healing punctures are permitted</p> <p>$\Delta C/C \leq 2.0\text{ }%$ Increase of tan $\delta \leq 0.0150$ compared to the values measured in 5.13-0</p>
<p>5.10.0 Initial measurements</p> <p>5.10-1 Thermal stability test under overload conditions</p> <p>5.10-2 Final measurements</p>	<p>Capacitance at 1 kHz tan δ at 10 kHz</p> <p>Natural cooling $T_{amb} \pm 5\text{ }^{\circ}\text{C}$ $1.21 \times P_{max.} = (U_2/2) \times W_2 \times C \times \tan \delta =$ $1.21 \times (I_{max.}^2/W_2 \times C) \times \tan \delta$ with $W_2 = 2 \times p \times f_2$ for $I_{max.}$ (see specific reference data) $f_2 = 10\text{ kHz}$ Duration: 48 h</p> <p>Measure the temperature every 1.5 h during the last 6 h</p>	<p>Temperature rise $\leq 1\text{ }^{\circ}\text{C}$ $\Delta C/C \leq 2.0\text{ }%$ Increase of tan $\delta \leq 1.2 \times \text{initial } \delta + 0.0150$</p>
<p>5.12 Resonance frequency measurement</p>	<p>Impedance analyser at T_{amb}</p>	<p>< 0.9 times the value as specified in typical curve "Resonant frequency" of this specification</p>



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
5.15-0 Initial measurements 5.15-1 Endurance test between terminals 5.15-2 Final measurement	Capacitance at 1 kHz tan δ at 10 kHz Sequence: 1.3 x U _{NDC} at 85 °C 1.3 x U _{OPDC} at 105 °C Duration: 500 h 1000 x discharge at 1.4 x I _{peak} (maximum respective peak current in continuous operation) 1.3 x U _{NDC} at 85 °C 1.3 x U _{OPDC} at 105 °C Duration: 500 h	 $ \Delta C/C \leq 3.0 \%$ Increase of tan $\delta \leq 0.0150$ compared to the values measured in 5.15-0
5.16.3-0 Initial measurements 5.16.3-1 Destruction test sequence High DC voltage test High AC voltage test 5.16.3-2 Final measurements	Capacitance at 1 kHz T _{max.} = 85 °C Product enveloped with cheese cloth 3 x U _{NDC} for DC voltage until repetitive product healings occur Duration = 15 min AC RMS voltage = U _{NDC} /2 $\sqrt{2}$ with minimum of 250 V _{AC} Duration = 5 min Repeat destruction sequence 3 x	 Audible healings or check healings with oscilloscope No puncturing, flashover or burning of the cheese cloth Self healing punctures are permitted

Note

- Sub-clause numbers of tests and performance requirements refer to the “Sectional Specification, IEC-publication 61071”



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[MKP1848S53070JK2A](#) [MKP1848S55010JP2C](#) [MKP1848S55050JK2A](#) [MKP1848S57070JP2C](#)
[MKP1848S61010JY2B](#) [MKP1848S61050JP2C](#) [MKP1848S61070JP2C](#) [MKP1848S61570JP2C](#) [MKP1848S62010JY5F](#)
[MKP1848S62050JY2B](#) [MKP1848S62070JP2F](#) [MKP1848S62070JY5B](#) [MKP1848S63050JY5C](#)
[MKP1848S63070JY5F](#)