

C4AQ, Radial, 2 or 4 Leads, 500 - 1,500 VDC, for DC Link (Automotive Grade)

Overview

C4AQ capacitors are polypropylene metallized film with rectangular plastic box type filled with resin (white and grey color) and 2 or 4 tinned copper wires.


Automotive grade devices meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.

Applications

Typical applications include DC filtering and energy storage.

Benefits


- Self-healing
- Low losses
- High ripple current
- High capacitance density
- High contact reliability
- Suitable for high frequency applications
- Automotive (AEC-Q200) grades



Part Number System

C4	A	Q	U	B	W	5270	1	3	N	J
Series	Type	Application	Rated Voltage (VDC)	Case	Terminals Code	Capacitance Code (pF)	C-Spec	Lead Diameter (mm)	Size Code: B x H x L (mm)	Tolerance
C4 = MKP Power Capacitors	A = Box, wire terminals	Q = DC Link Automotive Grade	L = 500 C = 650 I = 800 Q = 1,100 U = 1,300 S = 1,500	B = Box, plastic case E = Extended box, plastic case	U = 2 pins W = 4 pins	Digits two - four indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	A = Standard B - Z = Special	1 = 0.8 2 = 1.0 3 = 1.2	Digit 6 = B W = 11 x 20 x 31.5 X = 13 x 25 x 31.5 Y = 14 x 28 x 31.5 1 = 19 x 29 x 31.5 2 = 22 x 37 x 31.5 F = 20 x 40 x 42 J = 28 x 37 x 42 L = 30 x 45 x 42 O = 35 x 50 x 42 M = 30 x 45 x 57.5 N = 35 x 50 x 57.5 Digit 6 = E A = 45 x 56 x 57.5 N = 45 x 65 x 57.5	J = 5% K = 10%

Dimensions – Millimeters



Size Code		p		p1		B		H		L		LL		d	
Digit 6	Digit 14	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
B	W	27.5	±0.4	-	-	11.0	+0.3	20.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
B	X	27.5	±0.4	-	-	13.0	+0.3	25.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
B	Y	27.5	±0.4	-	-	14.0	+0.3	28.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
B	1	27.5	±0.4	-	-	19.0	+0.3	29.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
B	2	27.5	±0.4	-	-	22.0	+0.3	37.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
B	F	37.5	±0.4	5.1/10.2	±0.4	20.0	+0.4	40.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
B	J	37.5	±0.4	10.2	±0.4	28.0	+0.4	37.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
B	L	37.5	±0.4	20.3	±0.4	30.0	+0.4	45.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
B	O	37.5	±0.4	20.3	±0.4	35.0	+0.4	50.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
B	M	52.5	±0.4	20.3	±0.4	30.0	+0.5	45.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
B	N	52.5	±0.4	20.3	±0.4	35.0	+0.5	50.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
E	A	52.5	±0.4	20.3	±0.4	45.0	+0.5	56.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
E	B	52.5	±0.4	20.3	±0.4	45.0	+0.5	65.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05

Qualification

Reference Standards	IEC 61071, EN61071, VDE0560
Climatic Category	55/105/56 according to IEC 60068-1

Automotive Grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.

General Technical Data

Dielectric	Polypropylene metallized film, non-inductive type, self-healing property
Application	DC filtering, DC link
Special Features	AEC-Q200 qualified
Climatic Category	55/105/56 IEC 60068-1
Maximum Operating Temperature	+105°C
Endurance Test	500h + 500h at $1.3 \times V_{NDC}$ at 70°C
	500h + 500h at $1.0 \times V_{OP85}$ at 85°C
	500h + 500h at $1.0 \times V_{OP105}$ at 105°C
Standard	IEC 61071, EN61071, VDE0560, AEC-Q200
Protection	Solvent resistant plastic case UL94 V-0 compliant Thermosetting resin sealing UL94 V-0 compliant
Installation	Any position
Leads	Tinned copper wires - standard lead wire length 6 (+0/-2) mm
Packaging	Packed in cardboard trays with protection for the terminals
RoHS Compliance	Compliant with the restricted substance requirements of Directive 2011/65/EU

Electrical Characteristics

Rated Capacitance Range	1 to 210 μ F
Rated Voltage (V_{NDC}) Range	500 to 1,500 VDC
Capacitance Tolerance	$\pm 5\%$ (J) or $\pm 10\%$ (K) measured at $T = +25^\circ\text{C} \pm 5^\circ\text{C}$
Dissipation Factor PP Typical (tg δ)	≤ 0.0002 at 10 kHz with $T = 25^\circ\text{C} \pm 5^\circ\text{C}$
Surge Voltage	$1.5 * V_{NDC}$ for maximum 10 times in lifetime at $25^\circ\text{C} \pm 5^\circ\text{C}$
Overvoltage (IEC 61071)	$1.15 * V_{NDC}$ for maximum 30 minutes, once per day
	$1.3 * V_{NDC}$ for maximum 1 minute, once per day
Peak Non-Repetitive Current	$1.5 * I_{PKR}$ for maximum 1,000 times in lifetime
Insulation Resistance	$IR \times C \geq 30.000$ seconds at 100 VDC 1 minute at $T = +25^\circ\text{C} \pm 5^\circ\text{C}$
Capacitance Deviation in Operation	$\pm 2.0\%$ max. on capacitance value measured at $T = +25^\circ\text{C} \pm 5^\circ\text{C}$
Temperature Storage	-40 to +80°C
Storage time	≤ 36 months from the date marked on the label glued to the package
Permissible Relative Humidity - Storage	Annual average $\leq 70\%$, 85% on 30 days/year randomly distributed throughout year. Dewing not admissible.

Life Expectancy

Life Expectancy	100,000 hours at V_{NDC} at hot spot temperature $T_{HS} = +70^{\circ}C$
	100,000 hours at V_{OP85} at hot spot temperature $T_{HS} = +85^{\circ}C$
	10,000 hours at V_{OP105} at hot spot temperature $T_{HS} = +105^{\circ}C$
Capacitance Drop at End of Life	-5% (typical)
Failure Rate IEC 61709	≤ 300 FIT at V_{OP85} at hot spot temperature $T_{HS} = +85^{\circ}C$
	≤ 200 FIT at V_{NDC} at hot spot temperature $T_{HS} = +70^{\circ}C$

Test Method


Test Voltage Between Terminals	$1.5 * V_{NDC}$ for 10 seconds or $1.65 * V_{NDC}$ for 2 seconds, at $T = +25^{\circ}C \pm 5^{\circ}C$
Test Voltage Between Terminals and Case	3.2 kVAC 50 Hz for 2 seconds
Damp Heat	IEC 60068-2-78
Change of Temperature	IEC 60068-2-14
Biased Humidity test 40°C/93% R.H. at V_{NDC} - 1,000 hours	$ \Delta C/C_0 \leq 5\%$ $ \Delta DF/DF_0 \leq 200\%$ (at 10 kHz) $IR \geq 50\%$ of initial limit"
Biased Humidity test 60°C/95% R.H. at V_{NDC} - 1,000 hours	$ \Delta C/C_0 \leq 5\%$ $ \Delta DF/DF_0 \leq 200\%$ (at 10 kHz) $IR \geq 100 M\Omega$

Operative Voltage Derating


	Symbol	Voltage (VDC)						Life Expectancy (Hours)
		500	650	800	1,100	1,300	1,500	
Rated Voltage at 70°C (T_{HS})	U_{NDC}	500	650	800	1,100	1,300	1,500	100,000
Operating Voltage at 85°C (T_{HS})	U_{OP85}	450	600	700	900	1,100	1,200	100,000
Operating Voltage at 105°C (T_{HS})	U_{OP105}	350	450	550	700	850	900	10,000

Life Expectancy/Failure Quota Graphs

Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 500$ VDC



Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 650$ VDC



Notes:


$$T_{HS} = T_{AMB} + \Delta T$$

$$\Delta T = ESR * I_{rms}^2 * Rth$$


I_{rms} should be limited to values granting $\Delta T \leq 30^\circ C$

Life Expectancy/Failure Quota Graphs cont'd.

Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 800$ VDC



Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 1,100$ VDC



Notes:

$$T_{HS} = T_{AMB} + \Delta T$$

$$\Delta T = ESR * I_{rms}^2 * Rth$$


I_{rms} should be limited

to values granting


$$\Delta T \leq 30^{\circ}C$$

Life Expectancy/Failure Quota Graphs cont'd.

Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 1,300$ VDC



Lifetime Curve & FIT at Hot Spot Temperature - $U_{NDC} = 1,500$ VDC



Notes:

$$T_{HS} = T_{AMB} + \Delta T$$

$$\Delta T = ESR * I_{rms}^2 * Rth$$

I_{rms} should be limited

to values granting

$$\Delta T \leq 30^{\circ}C$$

Environmental Compliance

As an environmentally conscious company, KEMET is working continuously to improve the environmental effects of both our capacitors and their production.

In Europe, due to the RoHS Directive, and in some other geographical areas such as China, legislation has been put in place to prevent the use of some hazardous materials, including lead (Pb) in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products to fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material.

KEMET will closely follow any changes in legislation on a global basis and make any necessary changes to its products whenever needed.

Some customer segments including medical, defense and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products, the following symbols are used on the packaging labels for RoHS compliant and Pb-free capacitors.

Because of customer requirements, additional markings such as "LF" for lead-free or "LFW" for lead-free wires may appear on the packaging label.

Materials & Environment

The selection of materials used by KEMET for the production of capacitors is the result of extensive experience and constant attention to environmental protection. KEMET selects its suppliers according to ISO 9001 standards and carries out statistical analysis on the materials purchased before acceptance. All materials are, to the company's present knowledge, non-toxic and free from cadmium, mercury, chrome and compounds, polychlorine triphenyl (PCB), bromide and chlorine dioxins bromurate chlorurate, CFC and HCFC, and asbestos.

Green Products

All KEMET power film products are ROHS Compliant.

Insulation Resistance

When the capacitor temperature increases, the insulation resistance decreases. This is due to increased electron activity. Low insulation resistance can also be the result of moisture trapped in the windings, caused by a prolonged exposure to excessive humidity.

Dissipation Factor

Dissipation factor is a complex function involved with the inefficiency of the capacitor. The $\tan\delta$ may change up and down with increased temperature. For more information, please refer to Performance Characteristics.

Sealing

Hermetically Sealed Capacitors

When the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor which can result in leakage, impregnation, filling fluid or moisture susceptibility.

Resin Encased/Wrap & Fill Capacitors

The resin seals on resin encased and wrap and fill capacitors will withstand short-term exposure to high humidity environments without degradation. Resins and plastic tapes will form a pseudo-impervious barrier to humidity and chemicals. These case materials are somewhat porous and through osmosis can cause contaminants to enter the capacitor. The second area of contaminated absorption is the lead-wire/resin interface. Since resins cannot bond 100% to tinned wires, there can be a path formed up to the lead wire into the capacitor section. Aqueous cleaning of circuit boards can aggravate this condition.

Barometric Pressure

The altitude at which hermetically sealed capacitors are operated controls the voltage rating of the capacitor. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. This can be in the form of capacitance changes or dielectric arc-over as well as low insulation resistance. Heat transfer can also be affected by altitude operation. Heat generated in operation cannot be dissipated properly and can result in high RI2 losses and eventual failure.

Radiation

Radiation capabilities of capacitors must be taken into consideration. Electrical degradation in the form of dielectric embitterment can take place causing shorts or opens.

Table 1 – Ratings & Part Number Reference

Cap Value (µF)	VDC	Dimensions (mm)					dV/dt V/µs	Ipkr Apk	ESL nH	ESR 70°C at 10 kHz mΩ	Irms* 70°C at 10 kHz Arms	Rth (HS/Amb) (°C/W)	Packaging Quantity	PART NUMBER
		B	H	L	P	P1								
U_{NDC} at 70°C = 500 VDC; U_{OP85} at 85°C = 450 VDC; U_{OP105} at 105°C = 350 VDC														
5.6	500	11	20	31.5	27.5	\	10	54	25	13.1	4.5	44	256	C4AQLBU4560A1WK
10	500	13	25	31.5	27.5	\	10	96	25	8.1	6.5	36	234	C4AQLBU5100A1XK
12.5	500	14	28	31.5	27.5	\	10	122	26	6.8	7.5	33	96	C4AQLBU5125A1YK
15	500	19	29	31.5	27.5	\	10	147	26	6	8.5	29	72	C4AQLBU5150A11K
25	500	22	37	31.5	27.5	\	10	245	28	4.5	11.5	23	64	C4AQLBU5250A12K
40	500	20	40	42	37.5	10.2	7	262	30	3.5	13.5	20	58	C4AQLBW5400A3FK
50	500	28	37	42	37.5	10.2	7	332	30	2.8	16	18	36	C4AQLBW5500A3JK
70	500	30	45	42	37.5	20.3	7	464	30	2.1	20.5	15	36	C4AQLBW5700A3LK
90	500	35	50	42	37.5	20.3	7	585	35	1.5	26	13	30	C4AQLBW5900A30K
100	500	30	45	57.5	52.5	20.3	4	442	35	3	19	12	27	C4AQLBW6100A3MK
130	500	35	50	57.5	52.5	20.3	4	581	35	2.4	23	10	23	C4AQLBW6130A3NK
170 ¹	500	45	56	57.5	52.5	20.3	4	780	41	1.8	29.5	8	18	C4AQLBW6170A3AK
210 ¹	500	45	65	57.5	52.5	20.3	4	840	45	1.4	35.5	7	18	C4AQLBW6210A3BK
U_{NDC} at 70°C = 650 VDC; U_{OP85} at 85°C = 600 VDC; U_{OP105} at 105°C = 450 VDC														
3.3	650	11	20	31.5	27.5	\	13	41	25	17	4	44	256	C4AQCUBU4330A1WJ
5.6	650	13	25	31.5	27.5	\	13	71	25	10.7	6	36	234	C4AQCUBU4560A1XJ
7	650	14	28	31.5	27.5	\	13	88	26	9	7	33	96	C4AQCUBU4700A1YJ
10	650	19	29	31.5	27.5	\	13	127	26	6.8	8.5	29	72	C4AQCUBU5100A11J
15	650	22	37	31.5	27.5	\	13	190	28	5.3	10.5	23	64	C4AQCUBU5150A12J
20	650	20	40	42	37.5	10.2	9	172	30	5.3	11	20	58	C4AQCUBW5200A3FJ
30	650	28	37	42	37.5	10.2	9	255	30	3.6	14	18	36	C4AQCUBW5300A3JJ
40	650	30	45	42	37.5	20.3	9	344	30	2.8	18	15	36	C4AQCUBW5400A3LJ
50	650	35	50	42	37.5	20.3	9	430	35	2	22.5	13	30	C4AQCUBW5500A30J
55	650	30	45	57.5	52.5	20.3	6	319	35	4.1	16.5	12	27	C4AQCUBW5550A3MJ
75	650	35	50	57.5	52.5	20.3	6	435	35	3.1	20.5	10	23	C4AQCUBW5750A3NJ
110 ¹	650	45	56	57.5	52.5	20.3	6	625	41	2.2	27	8	18	C4AQCUBW6110A3AJ
130 ¹	650	45	65	57.5	52.5	20.3	6	754	45	1.7	32	7	18	C4AQCUBW6130A3BJ
U_{NDC} at 70°C = 800 VDC; U_{OP85} at 85°C = 700 VDC; U_{OP105} at 105°C = 550 VDC														
2.7	800	11	20	31.5	27.5	\	19	51	25	18.3	4	44	256	C4AQIBU4270A1WJ
4	800	13	25	31.5	27.5	\	19	77	25	12.9	5.5	36	234	C4AQIBU4400A1XJ
5	800	14	28	31.5	27.5	\	19	96	26	10.7	6	33	96	C4AQIBU4500A1YJ
8	800	19	29	31.5	27.5	\	19	154	26	7.3	8	29	72	C4AQIBU4800A11J
12.5	800	22	37	31.5	27.5	\	19	241	28	5.5	10	23	64	C4AQIBU5125A12J
15	800	20	40	42	37.5	5.1	13	196	30	6.2	10	20	58	C4AQIBW5150A3FJ
15	800	20	40	42	37.5	10.2	13	196	30	6.2	10	20	58	C4AQIBW5150B3FJ
20	800	28	37	42	37.5	10.2	13	262	30	4.7	12.5	18	36	C4AQIBW5200A3JJ
30	800	30	45	42	37.5	20.3	13	389	30	3.2	16.5	15	36	C4AQIBW5300A3LJ
40	800	35	50	42	37.5	20.3	13	524	35	2.2	21.5	13	30	C4AQIBW5400A30J
45	800	30	45	57.5	52.5	20.3	9	389	35	4.4	16	12	27	C4AQIBW5450A3MJ
55	800	35	50	57.5	52.5	20.3	9	485	35	3.6	19	10	23	C4AQIBW5550A3NJ
60	800	35	50	57.5	52.5	20.3	9	530	35	3.4	19.5	10	23	C4AQIBW5600A3NJ
85 ¹	800	45	56	57.5	52.5	20.3	9	728	41	2.5	25.5	8	18	C4AQIEW5850A3AJ
100 ¹	800	45	65	57.5	52.5	20.3	9	883	45	1.9	30.5	7	18	C4AQIEW6100A3BJ
Cap Value (µF)	VDC	B	H	L	P	P1	dV/dt V/µs	Ipkr Apk	ESL nH	ESR 70°C at 10 kHz mΩ	Irms* 70°C at 10 kHz Arms	Rth (HS/Amb) (°C/W)	Packaging Quantity	PART NUMBER
		Dimensions (mm)												

¹ Items available for sample.

(*) Irms value that leads to a ΔT of ≈ 15°C in the Hot Spot > T_{HS} = T_{AMB} + ΔT = 70°C + 15°C = 85°C

Table 1 – Ratings & Part Number Reference cont'd.

Cap Value (µF)	VDC	Dimensions (mm)					dV/dt V/µs	lpkr Apk	ESL nH	ESR 70°C at 10 kHz	Irms* 70°C at 10 kHz	Rth (HS/Amb) °C/W	Packaging Quantity	PART NUMBER	
		B	H	L	P	P1				mΩ	Arms	(°C/W)			
U_{NDC} at 70°C = 1,100 VDC; U_{OP85} at 85°C = 900 VDC; U_{OP105} at 105°C = 700 VDC															
1.5	1100	11	20	31.5	27.5	\	24	36	25	26.3	3.5	44	256	C4AQQBU4150A1WJ	
2.7	1100	13	25	31.5	27.5	\	24	65	25	15.3	5	36	234	C4AQQBU4270A1XJ	
3.3	1100	14	28	31.5	27.5	\	24	79	26	12.9	5.5	33	96	C4AQQBU4330A1YJ	
5	1100	19	29	31.5	27.5	\	24	120	26	9.1	7	29	72	C4AQQBU4500A11J	
8	1100	22	37	31.5	27.5	\	24	193	28	6.6	9.5	23	64	C4AQQBU4800A12J	
12	1100	20	40	42	37.5	10.2	16	190	30	6.3	10	20	58	C4AQQBW5120A3FJ	
14	1100	28	37	42	37.5	10.2	16	229	30	5.4	11.5	18	36	C4AQQBW5140A3JJ	
20	1100	30	45	42	37.5	20.3	16	321	30	3.9	15	15	36	C4AQQBW5200A3LJ	
25	1100	35	50	42	37.5	20.3	16	409	35	2.8	19	13	30	C4AQQBW5250A3OJ	
30	1100	30	45	57.5	52.5	20.3	11	324	35	5.2	15	12	27	C4AQQBW5300A3MJ	
40	1100	35	50	57.5	52.5	20.3	11	428	35	4	18	10	23	C4AQQBW5400A3NJ	
55 ¹	1100	45	56	57.5	52.5	20.3	11	595	41	2.6	24.5	8	18	C4AQQEW5550A3AJ	
65 ¹	1100	45	65	57.5	52.5	20.3	11	717	45	2.3	28	7	18	C4AQQEW5650A3BJ	
U_{NDC} at 70°C = 1,300 VDC; U_{OP85} at 85°C = 1,100 VDC; U_{OP105} at 105°C = 850 VDC															
1	1300	11	20	31.5	27.5	\	28	28	25	33.1	3	44	256	C4AQBUB4100A1WJ	
1.8	1300	13	25	31.5	27.5	\	29	52	25	19.1	4.5	36	234	C4AQBUB4180A1XJ	
2.2	1300	14	28	31.5	27.5	\	29	63	26	16	5	33	96	C4AQBUB4220A1YJ	
3.3	1300	19	29	31.5	27.5	\	29	95	26	11.2	6.5	29	72	C4AQBUB4330A11J	
5	1300	22	37	31.5	27.5	\	29	145	28	8.2	8.5	23	64	C4AQBUB4500A12J	
8	1300	20	40	42	37.5	10.2	20	157	30	7.9	9	20	58	C4AQBWB4800A3FJ	
10	1300	28	37	42	37.5	10.2	20	196	30	6.3	11	18	36	C4AQBWB5100A3JJ	
12	1300	30	45	42	37.5	20.3	20	235	30	5.3	13	15	36	C4AQBWB5120A3LJ	
18	1300	35	50	42	37.5	20.3	19	350	35	3.2	18	13	30	C4AQBWB5180A3OJ	
20	1300	30	45	57.5	52.5	20.3	13	262	35	6.5	13	12	27	C4AQBWB5200A3MJ	
25	1300	35	50	57.5	52.5	20.3	13	331	35	5.2	16	10	23	C4AQBWB5250A3NJ	
27	1300	35	50	57.5	52.5	20.3	13	354	35	4.9	16.5	10	23	C4AQBWB5270A3NJ	
38 ¹	1300	45	56	57.5	52.5	20.3	13	498	41	3.1	22.5	8	18	C4AQUEW5380A3AJ	
45 ¹	1300	45	65	57.5	52.5	20.3	13	596	45	2.7	26	7	18	C4AQUEW5450A3BJ	
U_{NDC} at 70°C = 1,500 VDC; U_{OP85} at 85°C = 1,200 VDC; U_{OP105} at 105°C = 900 VDC															
1.0	1500	11	20	31.5	27.5	\	31	31	24	25.7	3.5	44	256	C4AQSBUB4100A1WJ	
1.5	1500	13	25	31.5	27.5	\	31	49	25	17.7	4.5	36	234	C4AQSBUB4150A1XJ	
2.0	1500	14	28	31.5	27.5	\	32	65	26	14.1	5.5	33	96	C4AQSBUB4200A1YJ	
3.0	1500	19	29	31.5	27.5	\	32	95	26	9.7	7	29	72	C4AQSBUB4300A11J	
4.5	1500	22	37	31.5	27.5	\	33	148	28	7.3	9	23	64	C4AQSBUB4450A12J	
6.0	1500	20	40	42	37.5	10.2	22	132	30	8	9	20	58	C4AQSBWB4600A3FJ	
8.0	1500	28	37	42	37.5	10.2	22	176	30	6	11	18	36	C4AQSBWB4800A3JJ	
12	1500	30	45	42	37.5	20.3	22	256	33	4.1	14.5	15	36	C4AQSBWB5120A3LJ	
15	1500	35	50	42	37.5	20.3	22	326	35	3.5	17.5	13	30	C4AQSBWB5150A3OJ	
17	1500	30	45	57.5	52.5	20.3	14	236	35	5.9	13.5	12	27	C4AQSBWB5170A3MJ	
22	1500	35	50	57.5	52.5	20.3	14	308	38	4.6	17	10	23	C4AQSBWB5220A3NJ	
32 ¹	1500	45	56	57.5	52.5	20.3	14	460	41	3.4	22	8	18	C4AQSEW5320A3AJ	
40 ¹	1500	45	65	57.5	52.5	20.3	14	562	45	2.8	25	7	18	C4AQSEW5400A3BJ	
Cap Value (µF)	VDC	B	H	L	P	P1	V/µs	Apk	nH	mΩ	Arms	(°C/W)	Packaging Quantity	PART NUMBER	
		Dimensions (mm)					dV/dt	lpkr	ESL	ESR 70°C at 10 kHz	Irms* 70°C at 10 kHz	Rth (HS/Amb)			

¹ Items available for sample.

(*) Irms value that leads to a ΔT of ≈ 15°C in the Hot Spot > T_{HS} = T_{AMB} + ΔT = 70°C + 15°C = 85°C

Soldering Process


The implementation of the RoHS directive has resulted in the selection of SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 mm to 15 mm), and great care has to be taken during soldering. The recommended solder profiles from KEMET should be used. Please consult KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760-1 Edition 2 serves as a solid guideline for successful soldering. Please see Figure 1.

Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the above the recommended limits may result to degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after the curing of surface mount parts. Consult KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Please allow time for the capacitor surface temperature to return to a normal temperature before the second soldering cycle.


Manual Soldering Recommendations

Following is the recommendation for manual soldering with a soldering iron.



The soldering iron tip temperature should be set at 350°C (+10°C maximum) with the soldering duration not to exceed more than 3 seconds.

Wave Soldering Recommendations



Soldering Process cont'd

Wave Soldering Recommendations cont'd


1. The table indicates the maximum set-up temperature of the soldering process
 Figure 1

Dielectric Film Material	Maximum Preheat Temperature			Maximum Peak Soldering Temperature	
	Capacitor Pitch ≤ 10 mm	Capacitor Pitch = 15 mm	Capacitor Pitch > 15 mm	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm
Polyester	130°C	130°C	130°C	270°C	270°C
Polypropylene	100°C	110°C	130°C	260°C	270°C
Paper	130°C	130°C	140°C	270°C	270°C
Polyphenylene Sulphide	150°C	150°C	160°C	270°C	270°C

2. The maximum temperature measured inside the capacitor:

Set the temperature so that inside the element the maximum temperature is below the limit:

Dielectric Film Material	Maximum temperature measured inside the element
Polyester	160°C
Polypropylene	110°C
Paper	160°C
Polyphenylene Sulphide	160°C




Temperature monitored inside the capacitor.

Selective Soldering Recommendations


Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is preheated and transported over the solder bath as in normal flow soldering without touching the solder. When the board is over the bath, it is stopped and pre-designed solder pots are lifted from the bath with molten solder only at the places of the selected components, and pressed against the lower surface of the board to solder the components.

The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document, **however, instead of two baths, there is only one bath with a time from 3 to 10 seconds.** In selective soldering, the risk of overheating is greater than in double wave flow soldering, and great care must be taken so that the parts are not overheated.


Construction



Winding Scheme



Marking



Manufacturing Date Code (IEC-60062)

Y = Year, Z = Month

Year	Code	Month	Code
2010	A	January	1
2011	B	February	2
2012	C	March	3
2013	D	April	4
2014	E	May	5
2015	F	June	6
2016	H	July	7
2017	J	August	8
2018	K	September	9
2019	L	October	0
2020	M	November	N
2021	N	December	D
2022	P		
2023	R		
2024	S		
2025	T		
2026	U		
2027	V		
2028	W		
2029	X		
2030	A		

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.