

NPN/PNP high power double bipolar transistor 14 October 2014 P

Product data sheet

1. General description

NPN/PNP high power double bipolar transistor in a SOT1205 (LFPAK56D) Surface-Mounted Device (SMD) power plastic package.

NPN/NPN complement: PHPT610030NK.

PNP/PNP complement: PHPT610030PK.

2. Features and benefits

- High thermal power dissipation capability
- Suitable for high temperature applications up to 175 °C
- Reduced Printed-Circuit Board (PCB) requirements comparing to transistors in DPAK
- High energy efficiency due to less heat generation
- AEC-Q101 qualified

3. Applications

- Motor control
- Power management
- Load switch
- Linear mode voltage regulator
- Backlighting applications
- Relay replacement

4. Quick reference data

Table 1. Qui	ck reference data							
Symbol	Parameter	Conditions		Min	Тур	Max	Unit	
Per transistor;	Per transistor; for the PNP transistor with negative polarity							
V _{CEO}	collector-emitter voltage	open base		-	-	100	V	
I _C	collector current			-	-	3	А	
TR1 (NPN)								
R _{CEsat}	collector-emitter saturation resistance	I_{C} = 3 A; I_{B} = 300 mA; pulsed; $t_{p} \le$ 300 μs; δ ≤ 0.02; T_{amb} = 25 °C		-	75	110	mΩ	





PHPT610030NPK

NPN/PNP high power double bipolar transistor

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
TR2 (PNP)							
R _{CEsat}	collector-emitter saturation resistance	I_{C} = -2 A; I_{B} = -200 mA; pulsed; $t_{p} \le 300$ μs; δ ≤ 0.02; T_{amb} = 25 °C		-	110	180	mΩ

5. Pinning information

Table 2.	Pinning	information		
Pin	Symbol	Description	Simplified outline	Graphic symbol
1	E1	emitter TR1	8 7 6 5	C1 B2 E2
2	B1	base TR1		
3	E2	emitter TR2		
4	B2	base TR2		
5	C2	collector TR2		E1 B1 C2
6	C2	collector TR2		sym139
7	C1	collector TR1	1 2 3 4 LFPAK56D (SOT1205)	
8	C1	collector TR1	(0011200)	

6. Ordering information

Table 3. Ordering information						
Type number	Package	•				
	Name	Description	Version			
PHPT610030NPK	LFPAK56D	Plastic single ended surface mounted package (LFPAK56D); 8 leads	SOT1205			

7. Marking

Table 4. Marking codes	
Type number	Marking code
PHPT610030NPK	1003NPK

NPN/PNP high power double bipolar transistor

8. Limiting values

Table 5.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
Per transis	tor; for the PNP transistor with	negative polarity	·			
V _{CBO}	collector-base voltage	open emitter		-	100	V
V _{CEO}	collector-emitter voltage	open base		-	100	V
V _{EBO}	emitter-base voltage	open collector		-	7	V
I _C	collector current			-	3	Α
I _{CM}	peak collector current	single pulse; t _p ≤ 1 ms		-	8	А
I _B	base current			-	0.5	А
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[1]	-	1	W
		T _{amb} ≤ 25 °C	[2]	-	2.4	W
			[3]	-	25	W
Per device						
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[1]	-	1.25	W
			[2]	-	3	W
			[4]	-	5	W
Tj	junction temperature			-	175	°C
T _{amb}	ambient temperature			-55	175	°C
T _{stg}	storage temperature			-65	175	°C

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.


^[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 6 cm².

[3] Power dissipation from junction to mounting base.

[4] Device mounted on a ceramic PCB, Al₂O₃, standard footprint.

PHPT610030NPK

NPN/PNP high power double bipolar transistor



9. Thermal characteristics

Table 6.Thermal characteristics

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Per transist	tor						
R _{th(j-a)}	thermal resistance	in free air	[1]	-	-	150	K/W
	from junction to ambient		[2]	-	-	62.5	K/W
R _{th(j-sp)}	thermal resistance from junction to solder point			-	-	6	K/W
Per device		·	·				
R _{th(j-a)}	thermal resistance	in free air	[1]	-	-	120	K/W
	from junction to ambient		[2]	-	-	50	K/W
	ampiciti		[3]	-	-	30	K/W


[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

^[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 6 cm².

[3] Device mounted on a ceramic PCB, Al₂O₃, standard footprint.

PHPT610030NPK

NPN/PNP high power double bipolar transistor



NPN/PNP high power double bipolar transistor

10. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
TR1 (NPN)		I				_
I _{CBO} collector-base cut-off		V_{CB} = 80 V; I _E = 0 A; T _{amb} = 25 °C	-	-	100	nA
	current	V _{CB} = 80 V; I _E = 0 A; T _j = 150 °C	-	-	50	μA
I _{CES}	collector-emitter cut-off current	V _{CE} = 80 V; V _{BE} = 0 V	-	-	100	nA
I _{EBO}	emitter-base cut-off current	V_{EB} = 7 V; I _C = 0 A; T _{amb} = 25 °C	-	-	100	nA
h _{FE}	DC current gain	$\begin{split} V_{CE} &= 10 \text{ V}; \text{ I}_{C} = 500 \text{ mA}; \text{ pulsed}; \\ t_{p} &\leq 300 \mu\text{s}; \delta \leq 0.02; T_{amb} = 25 ^{\circ}\text{C} \end{split}$	150	250	-	
		V_{CE} = 10 V; I _C = 1 A; pulsed; t _p ≤ 300 µs; δ ≤ 0.02; T _{amb} = 25 °C	80	250	-	
		$V_{CE} = 10 \text{ V}; \text{ I}_{C} = 2 \text{ A}; \text{ pulsed};$ $t_{p} \leq 300 \mu\text{s}; \delta \leq 0.02; T_{amb} = 25 ^{\circ}\text{C}$	20	100	-	
		$V_{CE} = 10 \text{ V}; \text{ I}_{C} = 3 \text{ A}; \text{ pulsed};$ $t_{p} \leq 300 \mu\text{s}; \delta \leq 0.02; T_{amb} = 25 ^{\circ}\text{C}$	10	40	-	
olout	collector-emitter saturation voltage	I_{C} = 1 A; I_{B} = 50 mA; pulsed; $t_{p} \le 300 \ \mu$ s; δ ≤ 0.02; T_{amb} = 25 °C	-	90	150	mV
		$\begin{split} I_C = 3 \text{ A}; \ I_B = 0.3 \text{ A}; \ \text{pulsed}; \ t_p \leq 300 \ \mu\text{s}; \\ \delta \leq 0.02; \ T_{\text{amb}} = 25 \ ^\circ\text{C} \end{split}$	-	225	330	mV
R _{CEsat}	collector-emitter saturation resistance	$\begin{split} I_{C} &= 3 \text{ A}; \ I_{B} = 300 \text{ mA}; \text{ pulsed}; \\ t_{p} &\leq 300 \mu\text{s}; \ \delta &\leq 0.02; \ T_{amb} = 25 \ ^{\circ}\text{C} \end{split}$	-	75	110	mΩ
V _{BEsat}	base-emitter saturation voltage	$\begin{split} I_{C} &= 1 \text{ A}; I_{B} = 50 \text{ mA}; \text{ pulsed}; \\ t_{p} &\leq 300 \mu\text{s}; \delta \leq 0.02; T_{amb} = 25 ^{\circ}\text{C} \end{split}$	-	0.86	1	V
		I_C = 2 A; I_B = 200 mA; pulsed; $t_p \le 300 \ \mu$ s; δ ≤ 0.02; T_{amb} = 25 °C	-	1	1.2	V
V_{BEon}	base-emitter turn-on voltage	V_{CE} = 2 V; I _C = 100 mA; pulsed; t _p ≤ 300 µs; δ ≤ 0.02; T _{amb} = 25 °C	-	0.67	0.85	V
t _d	delay time	V_{CC} = 12.5 V; I _C = 1 A; I _{Bon} = 50 mA;	-	20	-	ns
t _r	rise time	I _{Boff} = -50 mA; T _{amb} = 25 °C	-	300	-	ns
t _{on}	turn-on time		-	320	-	ns
t _s	storage time		-	830	-	ns
t _f	fall time		-	470	-	ns
t _{off}	turn-off time		-	1300	-	ns
f _T	transition frequency	V_{CE} = 10 V; I _C = 100 mA; f = 100 MHz; T _{amb} = 25 °C	-	140	-	MHz

PHPT610030NPK


PHPT610030NPK

NPN/PNP high power double bipolar transistor

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
C _c	collector capacitance	V _{CB} = 10 V; I _E = 0 A; i _e = 0 A; f = 1 MHz; T _{amb} = 25 °C	-	11	-	pF
TR2 (PNP)		· · · · · · · · · · · · · · · · · · ·				
I _{CBO}	collector-base cut-off	V _{CB} = -80 V; I _E = 0 A	-	-	-100	nA
	current	V_{CB} = -80 V; I _E = 0 A; T _j = 150 °C	-	-	-50	μA
I _{CES}	collector-emitter cut-off current	V _{CE} = -80 V; V _{BE} = 0 V	-	-	-100	nA
I _{EBO}	emitter-base cut-off current	V _{EB} = -7 V; I _C = 0 A	-	-	-100	nA
h _{FE}	DC current gain	V_{CE} = -10 V; I _C = -500 mA; T _{amb} = 25 °C	150	200	-	
		V_{CE} = -10 V; I _C = -1 A; pulsed; t _p ≤ 300 µs; δ ≤ 0.02; T _{amb} = 25 °C	80	210	-	
		$V_{CE} = -10 \text{ V}; \text{ I}_{C} = -2 \text{ A}; \text{ pulsed};$ $t_{p} \leq 300 \mu\text{s}; \delta \leq 0.02; T_{amb} = 25 ^{\circ}\text{C}$	20	100	-	
		$\label{eq:VcE} \begin{array}{l} V_{CE} \texttt{=} -10 \; V; \; I_{C} \texttt{=} -3 \; A; \; pulsed; \\ t_{p} \texttt{\leq} 300 \; \mu \texttt{s}; \; \delta \texttt{\leq} 0.02; \; T_{amb} \texttt{=} 25 \; ^{\circ} C \end{array}$	10	40	-	
OLOUI	collector-emitter saturation voltage	I _C = -500 mA; I _B = -50 mA; T _{amb} = 25 °C	-	-70	-110	mV
		$\begin{split} &I_{C}=\text{-2 A};I_{B}=\text{-0.2 A};pulsed;\\ &t_{p}\leq300\;\mu s;\delta\leq0.02;T_{amb}=25\;^{\circ}\mathrm{C} \end{split}$	-	-220	-360	mV
R _{CEsat}	collector-emitter saturation resistance	I_{C} = -2 A; I_{B} = -200 mA; pulsed; $t_{p} \le 300 \ \mu$ s; δ ≤ 0.02; T_{amb} = 25 °C	-	110	180	mΩ
V _{BEsat}	base-emitter saturation voltage	I_{C} = -1 A; I_{B} = -50 mA; pulsed; $t_{p} \le 300 \ \mu$ s; δ ≤ 0.02 ; T_{amb} = 25 °C	-	-0.91	-1	V
		I_{C} = -2 A; I_{B} = -200 mA; pulsed; $t_{p} \le 300 \ \mu$ s; δ ≤ 0.02; T_{amb} = 25 °C	-	-1.02	-1.2	V
V _{BEon}	base-emitter turn-on voltage	$V_{CE} = -2 \text{ V; } I_C = -100 \text{ mA; pulsed;}$ $t_p \le 300 \mu\text{s; } \delta \le 0.02; T_{amb} = 25 ^\circ\text{C}$	-	-0.68	-0.9	V
t _d	delay time	V_{CC} = -12.5 V; I _C = -1 A; I _{Bon} = -50 mA;	-	20	-	ns
t _r	rise time	I_{Boff} = 50 mA; T_{amb} = 25 °C	-	180	-	ns
t _{on}	turn-on time		-	200	-	ns
t _s	storage time		-	350	-	ns
t _f	fall time	-	-	220	-	ns
t _{off}	turn-off time	-	-	570	-	ns
f _T	transition frequency	V _{CE} = -10 V; I _C = -100 mA; f = 100 MHz; T _{amb} = 25 °C	-	125	-	MHz


PHPT610030NPK

NPN/PNP high power double bipolar transistor



PHPT610030NPK

NPN/PNP high power double bipolar transistor




PHPT610030NPK

All information provided in this document is subject to legal disclaimers.

PHPT610030NPK


NPN/PNP high power double bipolar transistor



PHPT610030NPK

All information provided in this document is subject to legal disclaimers.


NPN/PNP high power double bipolar transistor



PHPT610030NPK

All information provided in this document is subject to legal disclaimers.


NPN/PNP high power double bipolar transistor



11. Test information

PHPT610030NPK

NPN/PNP high power double bipolar transistor




11.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101* - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

NPN/PNP high power double bipolar transistor

12. Package outline




PHPT610030NPK

All information provided in this document is subject to legal disclaimers.

NPN/PNP high power double bipolar transistor

13. Soldering



NPN/PNP high power double bipolar transistor

14. Revision history

Table 8. Revision history							
Data sheet ID	Release date	Data sheet status	Change notice	Supersedes			
PHPT610030NPK v.1	20141014	Product data sheet	-	-			

PHPT610030NPK

All information provided in this document is subject to legal disclaimers.

NPN/PNP high power double bipolar transistor

15. Legal information

15.1 Data sheet status

Document status [1][2]	Product status [<u>3]</u>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <u>http://www.nxp.com</u>.

15.2 Definitions

Preview — The document is a preview version only. The document is still subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

PHPT610030NPK

NPN/PNP high power double bipolar transistor

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Bitsound, CoolFlux, CoReUse, DESFire, FabKey, GreenChip, HiPerSmart, HITAG, I²C-bus logo, ICODE, I-CODE, ITEC, MIFARE, MIFARE Plus, MIFARE Ultralight, SmartXA, STARplug, TOPFET, TrenchMOS, TriMedia and UCODE — are trademarks of NXP Semiconductors N.V.

HD Radio and **HD Radio** logo — are trademarks of iBiquity Digital Corporation.

NPN/PNP high power double bipolar transistor

16. Contents

1
1
1
1
2
2
2
3
4
6
2
3
4
5
6
7
7
7
7
8

© NXP Semiconductors N.V. 2014. All rights reserved

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com Date of release: 14 October 2014