



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 15

LOCTITE EA 9450 DC50ML EN

SDS No. : 178446
V003.0

Revision: 25.03.2022

printing date: 16.01.2024

Replaces version from: 03.07.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE EA 9450 DC50ML EN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

2-Component epoxy adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Chronic hazards to the aquatic environment	Category 2
H411 Toxic to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Contains**

reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700)

Bisphenol-F epichlorhydrin resin; MW<700

Signal word:

Warning

Hazard statement:

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

**Precautionary statement:
Prevention**

P273 Avoid release to the environment.

P280 Wear protective gloves.

**Precautionary statement:
Response**

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration \geq 0,1% and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration \geq the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	50- 100 %	Skin Irrit. 2, H315 Skin Sens. 1, H317 Aquatic Chronic 2, H411 Eye Irrit. 2, H319	Eye Irrit. 2; H319; C \geq 5 % Skin Irrit. 2; H315; C \geq 5 %	
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5 01-2119454392-40	20- 40 %	Skin Irrit. 2, Dermal, H315 Skin Sens. 1, H317 Aquatic Chronic 2, H411		

**For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.**

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

SKIN: Rash, Urticaria.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Dispose of contaminated material as waste according to Section 13.

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.
Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.
Refer to Technical Data Sheet

7.3. Specific end use(s)

2-Component epoxy adhesive

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	aqua (freshwater)		0,003 mg/l				
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	aqua (marine water)		0,0003 mg/l				
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	sewage treatment plant (STP)		10 mg/l				
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	sediment (freshwater)				0,294 mg/kg		
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	sediment (marine water)				0,0294 mg/kg		
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Soil				0,237 mg/kg		
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	aqua (intermittent releases)		0,0254 mg/l				
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Air						no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Predator						no potential for bioaccumulation

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Workers	Inhalation	Long term exposure - systemic effects		29,39 mg/m ³	no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Workers	dermal	Long term exposure - systemic effects		104,15 mg/kg	no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	Workers	dermal	Acute/short term exposure - local effects		0,0083 mg/cm ²	no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	General population	Inhalation	Long term exposure - systemic effects		8,7 mg/m ³	no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	General population	dermal	Long term exposure - systemic effects		62,5 mg/kg	no hazard identified
Reaction product: bisphenol-F-(epichlorhydrin); epoxy resin (number average molecular weight ≤ 700) (old) 9003-36-5	General population	oral	Long term exposure - systemic effects		6,25 mg/kg	no hazard identified

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Filter type: A (EN 14387)

Hand protection:
Chemical-resistant protective gloves (EN 374).
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	liquid
Delivery form	white
Colour	
Odor	None
Initial boiling point	> 148 °C (> 298.4 °F)
Flash point	> 93 °C (> 199.4 °F)
pH	Not available., Product is non-soluble (in water).
Solubility (qualitative) (Solvent: Water)	Insoluble
Vapour pressure (50 °C (122 °F))	< 700 mbar;no method
Density ()	1,2 g/cm3 None

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with strong oxidants.
Reaction with strong acids.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information

Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 420 (Acute Oral Toxicity)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	LD50	> 5.000 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	LD50	> 2.000 mg/kg	rat	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not irritating	4 h	rabbit	not specified
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	irritating	4 h	rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 472 (Genetic Toxicology: Escherichia coli, Reverse Mutation Assay)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	positive	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	negative	oral: gavage		mouse	not specified
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	negative	oral: gavage		mouse	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	negative	oral: gavage		rat	OECD Guideline 486 (Unscheduled DNA Synthesis (UDS) Test with Mammalian Liver Cells in vivo)

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not carcinogenic	dermal	2 y daily	mouse	male	OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	not carcinogenic	oral: gavage	2 y daily	rat	male/female	OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight≤700) 25068-38-6	NOAEL P >= 50 mg/kg NOAEL F1 >= 750 mg/kg NOAEL F2 >= 750 mg/kg	Two generation study	oral: gavage	rat	OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	NOAEL P > 750 mg/kg NOAEL F1 750 mg/kg NOAEL F2 750 mg/kg	two-generation study	oral: gavage	rat	OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	NOAEL 50 mg/kg	oral: gavage	14 w daily	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	NOAEL 250 mg/kg	oral: gavage	13 w daily	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	LC50	1,75 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	LC50	5,7 mg/l	96 h	Leuciscus idus	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	EC50	1,7 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	EC50	2,55 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	NOEC	0,3 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	NOEC	0,3 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	EC50	> 11 mg/l	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	NOEC	4,2 mg/l	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	EC50	1,8 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	IC50	> 100 mg/l	3 h	activated sludge, industrial	other guideline:
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	IC50	> 100 mg/l	3 h	activated sludge, industrial	other guideline:

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	not readily biodegradable.	aerobic	5 %	28 d	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	not readily biodegradable.	aerobic	0 %	28 d	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)

12.3. Bioaccumulative potential

No substance data available.
No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700) 25068-38-6	3,242	25 °C	EU Method A.8 (Partition Coefficient)
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	2,7 - 3,6		OECD Guideline 117 (Partition Coefficient (n-octanol / water), HPLC Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Bisphenol-F epichlorhydrin resin; MW<700 9003-36-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09* waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information
--

14.1. UN number

ADR	3082
RID	3082
ADN	3082
IMDG	3082
IATA	3082

14.2. UN proper shipping name

ADR	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
RID	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
ADN	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
IMDG	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
IATA	Environmentally hazardous substance, liquid, n.o.s. (Bisphenol-A Epichlorhydrin resin)

14.3. Transport hazard class(es)

ADR	9
RID	9
ADN	9
IMDG	9
IATA	9

14.4. Packing group

ADR	III
RID	III
ADN	III
IMDG	III
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	Marine pollutant
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode:
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

The transport classifications in this section apply generally to packed and bulk goods alike. For containers with a net volume of no more than 5 L for liquid substances or a net mass of no more than 5 kg for solid substances per individual or inner package, the exemptions SP 375 (ADR), A197 (IATA), 2.10.2.7 (IMDG) may be applied, which can result in a deviation from the transport classification for packed goods.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable
VOC content (2010/75/EC)	< 3,00 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.



Safety Data Sheet according to (EC) No 1907/2006 as amended Page 1 of 16

LOCTITE EA 9450 DC50ML EN

SDS No. : 152802
V003.0
Revision: 25.03.2022
printing date: 16.01.2024
Replaces version from: 03.07.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE EA 9450 DC50ML EN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Epoxy Hardener

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Adhesives
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin corrosion	Sub-category 1B
H314 Causes severe skin burns and eye damage.	
Serious eye damage	Category 1
H318 Causes serious eye damage.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Chronic hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:

Contains

Pentaerythritol-PO-mercaptoglycerol

Benzyltrimethylamine

2-aminoethanol

Signal word:	Danger
Hazard statement:	H314 Causes severe skin burns and eye damage. H317 May cause an allergic skin reaction. H412 Harmful to aquatic life with long lasting effects.
Precautionary statement:	P280 Wear protective gloves/protective clothing/eye protection/face protection.
Prevention	P273 Avoid release to the environment.
Precautionary statement:	P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
Response	P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P310 Immediately call a POISON CENTER or doctor.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration $\geq 0,1\%$ and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration \geq the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
Pentaerythritol-PO-mercaptoglycerol 72244-98-5 701-196-7 01-2120118957-46	50- 100 %	Skin Sens. 1B, H317 Aquatic Chronic 3, H412		
Benzyltrimethylamine 103-83-3 203-149-1 01-2119529232-48	5- < 10 %	Acute Tox. 4, Dermal, H312 Skin Corr. 1B, H314 Flam. Liq. 3, H226 Aquatic Chronic 2, H411 Acute Tox. 4, Oral, H302 Acute Tox. 3, Inhalation, H331		
2-aminoethanol 141-43-5 205-483-3 01-2119486455-28	1- < 5 %	Acute Tox. 4, Oral, H302 Acute Tox. 4, Dermal, H312 Eye Dam. 1, H318 Skin Corr. 1B, H314 Acute Tox. 4, Inhalation, H332 STOT SE 3, H335 Aquatic Chronic 3, H412	STOT SE 3; H335; C $\geq 5\%$ ===== inhalation:ATE = 1,5 mg/l;dust/mist	EU OEL

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Causes burns.

SKIN: Rash, Urticaria.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

None

carbon oxides.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation.

Avoid skin and eye contact.

Wear protective equipment.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.
Use only in well-ventilated areas.
Gloves and safety glasses should be worn
Do not inhale vapors and fumes.
See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.
Good industrial hygiene practices should be observed.
Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.
Store in a cool, well-ventilated place.

7.3. Specific end use(s)

Epoxy Hardener

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]			Skin designation:	Can be absorbed through the skin.	EH40 WEL
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	1	2,5	Time Weighted Average (TWA):		EH40 WEL
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	3	7,6	Short Term Exposure Limit (STEL):	Indicative	ECLTV
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	1	2,5	Time Weighted Average (TWA):	Indicative	ECLTV
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	3	7,6	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	1	2,5	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	3	7,6	Short Term Exposure Limit (STEL):	Indicative	ECLTV
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	1	2,5	Time Weighted Average (TWA):	Indicative	ECLTV
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]			Skin designation:	Can be absorbed through the skin.	IR_OEL
2-Aminoethanol 141-43-5 [2-AMINOETHANOL]	3	7,6	Short Term Exposure Limit (STEL):	15 minutes Indicative OELV	IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	aqua (freshwater)		0,07 mg/l				
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	Freshwater - intermittent		0,12 mg/l				
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	aqua (marine water)		0,007 mg/l				
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	sediment (freshwater)				0,322 mg/kg		
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	sediment (marine water)				0,032 mg/kg		
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro- w-hydroxy-, ether with 2,2- bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	sewage treatment plant (STP)		10 mg/l				
Benzyl dimethylamine 103-83-3	aqua (freshwater)		0,0048 mg/l				
Benzyl dimethylamine 103-83-3	aqua (marine water)		0,00048 mg/l				
Benzyl dimethylamine 103-83-3	aqua (intermittent releases)		0,0134 mg/l				
Benzyl dimethylamine 103-83-3	sewage treatment plant (STP)		534 mg/l				
Benzyl dimethylamine 103-83-3	sediment (freshwater)				0,071 mg/kg		
Benzyl dimethylamine 103-83-3	sediment (marine water)				0,0071 mg/kg		
Benzyl dimethylamine 103-83-3	Soil				0,0114 mg/kg		
2-Aminoethanol 141-43-5	aqua (freshwater)		0,07 mg/l				
2-Aminoethanol 141-43-5	aqua (marine water)		0,007 mg/l				
2-Aminoethanol 141-43-5	aqua (intermittent releases)		0,028 mg/l				
2-Aminoethanol 141-43-5	sediment (freshwater)				0,357 mg/kg		
2-Aminoethanol 141-43-5	sediment (marine water)				0,036 mg/kg		
2-Aminoethanol 141-43-5	Soil				1,29 mg/kg		
2-Aminoethanol 141-43-5	sewage treatment plant (STP)		100 mg/l				

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	Workers	inhalation	Long term exposure - systemic effects		22 mg/m ³	
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	Workers	dermal	Long term exposure - systemic effects		2,7 mg/kg	
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	General population	inhalation	Long term exposure - systemic effects		6,52 mg/m ³	
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	General population	dermal	Long term exposure - systemic effects		1,61 mg/kg	
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptop 72244-98-5	General population	oral	Long term exposure - systemic effects		1,9 mg/kg	
Benzyl dimethylamine 103-83-3	Workers	dermal	Long term exposure - systemic effects		2,3 mg/kg	
Benzyl dimethylamine 103-83-3	Workers	inhalation	Long term exposure - systemic effects		14,6 mg/m ³	
Benzyl dimethylamine 103-83-3	Workers	inhalation	Long term exposure - local effects		1 mg/m ³	
Benzyl dimethylamine 103-83-3	General population	dermal	Long term exposure - systemic effects		1,25 mg/kg	
Benzyl dimethylamine 103-83-3	General population	oral	Long term exposure - systemic effects		1,25 mg/kg	
Benzyl dimethylamine 103-83-3	General population	inhalation	Long term exposure - systemic effects		43,75 mg/m ³	
2-Aminoethanol 141-43-5	Workers	inhalation	Long term exposure - systemic effects		1 mg/m ³	
2-Aminoethanol 141-43-5	Workers	inhalation	Long term exposure - local effects		0,51 mg/m ³	
2-Aminoethanol 141-43-5	Workers	dermal	Long term exposure - systemic effects		3 mg/kg	
2-Aminoethanol 141-43-5	General population	dermal	Long term exposure - systemic effects		1,5 mg/kg	
2-Aminoethanol 141-43-5	General population	oral	Long term exposure - systemic effects		1,5 mg/kg	
2-Aminoethanol 141-43-5	General population	inhalation	Long term exposure - systemic effects		0,18 mg/m ³	
2-Aminoethanol 141-43-5	General population	inhalation	Long term exposure - local effects		0,28 mg/m ³	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Filter type: A (EN 14387)

Hand protection:
Chemical-resistant protective gloves (EN 374).
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):
nitrile rubber (NBR; ≥ 0.4 mm thickness)
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	liquid
Delivery form	light yellow
Colour	
Odor	of amine
Initial boiling point	> 180 °C (> 356 °F)no method
Flash point	75 °C (167 °F)
pH	Not applicable, Product is non-soluble (in water).
Vapour pressure (50 °C (122 °F))	< 700 mbar;no method
Density ()	1,16 g/cm ³ None

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

No data available.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information

Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Pentaerythritol-PO- mercaptoglycerol 72244-98-5	LD50	2.600 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)
Benzylidimethylamine 103-83-3	LD50	353 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)
2-aminoethanol 141-43-5	LD50	1.515 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Pentaerythritol-PO- mercaptoglycerol 72244-98-5	LD50	> 10.200 mg/kg	rabbit	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)
Benzylidimethylamine 103-83-3	LD50	1.477 mg/kg	rabbit	not specified
2-aminoethanol 141-43-5	LD50	1.025 mg/kg	rabbit	not specified

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Benzyltrimethylamine 103-83-3	LC50	2,052 mg/l	vapour	4 h	rat	not specified
2-aminoethanol 141-43-5	Acute toxicity estimate (ATE)	1,5 mg/l	dust/mist			Expert judgement
2-aminoethanol 141-43-5	LC50	1 - 5 mg/l		4 h	rat	not specified

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Pentaerythritol-PO- mercaptoglycerol 72244-98-5	not irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
2-aminoethanol 141-43-5	corrosive	4 h	rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Pentaerythritol-PO- mercaptoglycerol 72244-98-5	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)
2-aminoethanol 141-43-5	corrosive		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Pentaerythritol-PO- mercaptoglycerol 72244-98-5	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)
2-aminoethanol 141-43-5	not sensitising	Guinea pig maximisation test	guinea pig	not specified

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
2-aminoethanol 141-43-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		equivalent or similar to OECD Guideline 471 (Bacterial Reverse Mutation Assay)
2-aminoethanol 141-43-5	negative	in vitro mammalian chromosome aberration test	without		equivalent or similar to OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
2-aminoethanol 141-43-5	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
2-aminoethanol 141-43-5	negative	oral: gavage		mouse	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)

Carcinogenicity

No data available.

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
2-aminoethanol 141-43-5	NOAEL P 300 mg/kg NOAEL F1 1.000 mg/kg NOAEL F2 1.000 mg/kg	Two generation study	oral: feed	rat	OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
2-aminoethanol 141-43-5	NOAEL 300 mg/kg	oral: feed	> 75 d daily	rat	other guideline:

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	LC50	87 mg/l	96 h	Danio rerio	OECD Guideline 203 (Fish, Acute Toxicity Test)
Benzylidimethylamine 103-83-3	LC50	37,8 mg/l	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
2-aminoethanol 141-43-5	LC50	349 mg/l	96 h	Cyprinus carpio	EU Method C.1 (Acute Toxicity for Fish)
2-aminoethanol 141-43-5	NOEC	1,24 mg/l	41 d	Oryzias latipes	OECD Guideline 210 (fish early lite stage toxicity test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	EC50	12 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Benzylidimethylamine 103-83-3	EC50	> 100 mg/l	48 h	Daphnia magna	EU Method C.2 (Acute Toxicity for Daphnia)
2-aminoethanol 141-43-5	EC50	27,04 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	NOEC	3,5 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Benzylidimethylamine 103-83-3	NOEC	0,789 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
2-aminoethanol 141-43-5	NOEC	0,85 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	EC50	> 733 mg/l	72 h	Desmodesmus subspicatus	OECD Guideline 201 (Alga, Growth Inhibition Test)
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	NOEC	338 mg/l	72 h	Desmodesmus subspicatus	OECD Guideline 201 (Alga, Growth Inhibition Test)
Benzyl dimethylamine 103-83-3	EC50	1,34 mg/l	72 h	Desmodesmus subspicatus (reported as Scenedesmus subspicatus)	EU Method C.3 (Algal Inhibition test)
Benzyl dimethylamine 103-83-3	NOEC	0,24 mg/l	72 h	Desmodesmus subspicatus (reported as Scenedesmus subspicatus)	EU Method C.3 (Algal Inhibition test)
2-aminoethanol 141-43-5	EC50	2,8 mg/l	72 h	Pseudokirchneriella subcapitata (reported as Raphidocelis subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
2-aminoethanol 141-43-5	EC10	0,7 mg/l	72 h	Pseudokirchneriella subcapitata (reported as Raphidocelis subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	EC50	> 1.000 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Benzyl dimethylamine 103-83-3	EC10	534 mg/l	17 h	Pseudomonas putida	DIN 38412, part 8 (Pseudomonas Zellvermehrungshemm-Test)
2-aminoethanol 141-43-5	EC 50	> 1.000 mg/l	3 h		OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

12.2. Persistence and degradability

The product is not biodegradable.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	not readily biodegradable.	aerobic	5 %	28 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
Benzyl dimethylamine 103-83-3	not readily biodegradable.	aerobic	0 - 2 %	28 d	OECD Guideline 301 C (Ready Biodegradability: Modified MITI Test (I))
2-aminoethanol 141-43-5	readily biodegradable	aerobic	> 80 %	19 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)

12.3. Bioaccumulative potential

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
Benzyl dimethylamine 103-83-3	> 2,1 - 22	42 d		Cyprinus carpio	OECD Guideline 305 C (Bioaccumulation: Test for the Degree of Bioconcentration in Fish)

12.4. Mobility in soil

Cured adhesives are immobile.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	1,2	20 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)
Benzyltrimethylamine 103-83-3	1,98		EU Method A.8 (Partition Coefficient)
2-aminoethanol 141-43-5	-1,91	25 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Pentaerythritol-PO-mercaptoglycerol 72244-98-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Benzyltrimethylamine 103-83-3	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
2-aminoethanol 141-43-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09* waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

14.1. UN number

ADR	2735
RID	2735
ADN	2735
IMDG	2735
IATA	2735

14.2. UN proper shipping name

ADR	AMINES, LIQUID, CORROSIVE, N.O.S. (Benzyldimethylamine,Ethanolamine)
RID	AMINES, LIQUID, CORROSIVE, N.O.S. (Benzyldimethylamine,Ethanolamine)
ADN	AMINES, LIQUID, CORROSIVE, N.O.S. (Benzyldimethylamine,Ethanolamine)
IMDG	AMINES, LIQUID, CORROSIVE, N.O.S. (Benzyldimethylamine,Ethanolamine)
IATA	Amines, liquid, corrosive, n.o.s. (Benzyldimethylamine,Ethanolamine)

14.3. Transport hazard class(es)

ADR	8
RID	8
ADN	8
IMDG	8
IATA	8

14.4. Packing group

ADR	III
RID	III
ADN	III
IMDG	III
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable
VOC content	< 3,00 % Combined A/B

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H226 Flammable liquid and vapor.
 H302 Harmful if swallowed.
 H312 Harmful in contact with skin.
 H314 Causes severe skin burns and eye damage.
 H317 May cause an allergic skin reaction.
 H318 Causes serious eye damage.
 H331 Toxic if inhaled.
 H332 Harmful if inhaled.
 H335 May cause respiratory irritation.
 H411 Toxic to aquatic life with long lasting effects.
 H412 Harmful to aquatic life with long lasting effects.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.