Data sheet Cisco public



Cisco Catalyst IW9167 Heavy Duty Series

Contents

| Product overview | 3 |
|------------------------------------------------------------------|----|
| Cisco Catalyst IW9167E Heavy Duty Access Point | 3 |
| Cisco Catalyst IW9167I Heavy Duty Access Point | 4 |
| Catalyst IW9167E Heavy Duty Access Point for Hazardous Locations | 4 |
| Secure infrastructure | 4 |
| Features and benefits | 5 |
| Prominent features | 7 |
| Licensing | 8 |
| Product sustainability | 8 |
| Product specifications | 9 |
| IW9167I antenna patterns | 28 |
| Ordering information | 31 |
| Warranty information | 31 |
| Cisco and partner services | 31 |
| Smart Account | 32 |
| Cisco Capital | 32 |
| Learn more | 32 |
| Document history | 32 |

The Cisco® Catalyst® IW9167 Series provides reliable wireless connectivity for mission-critical applications in a state-of-the art platform. It can operate in Wi-Fi 6, Workgroup Bridge (WGB), or Ultra-Reliable Wireless Backhaul (URWB) mode.

Product overview

The Catalyst IW9167 Series addresses the growing need to provide reliable wireless connectivity for mission-critical applications as organizations automate processes and operations. It comes with three 4x4 radios in a heavy-duty design that is IP67 rated and packed with advanced features.

The Catalyst IW9167 Series is designed to take advantage of the 6 GHz band expansion to deliver a network that is more reliable and secure, with higher throughput, more capacity, and less device interference. The 6 GHz band support will be available with a future software upgrade and is subject to approvals and regulations by each countries' regulatory agencies for the use of the 6 GHz spectrum for outdoor standard power devices. Please refer to the Wi-Fi 6E white paper for more details on 6 GHz.

Cisco Catalyst IW9167E Heavy Duty Access Point

The Catalyst IW9167E is designed with external antenna ports and provides flexibility to choose the right antenna based on the use case. It offers unmatched flexibility, as it can operate in one of three different modes: Wi-Fi 6, WGB, or URWB:

- All the <u>benefits of Wi-Fi 6</u> in industrial or outdoor spaces: Higher density, higher throughput, more channels, power efficiency, and improved security.
- WGB mode provides an arsenal of features and capabilities to help ensure continuous connectivity for static and mobile industrial applications in a Wi-Fi deployment.
- <u>URWB</u> provides ultra-reliable wireless connectivity for moving assets or to extend the network where
 running fiber isn't feasible or is too costly. It provides up to 99.995% availability, <10 ms latency, and
 zero packet loss with seamless handoffs. URWB is a proven technology that has been used by many
 customers, operates on unlicensed spectrum, deploys like Wi-Fi, and gives you full control of your
 network.



Figure 1.
Catalyst IW9167E Heavy Duty Access Point

Cisco Catalyst IW9167I Heavy Duty Access Point

The Catalyst IW9167I is designed to make wireless deployments simple in outdoor and industrial environments. It is built with a cast-aluminum case that can handle water, dust, and extreme temperatures. It comes with a built-in antenna that enables high-throughput connectivity for high-density Wi-Fi clients.

The IW9167I supports Wi-Fi 6, and it comes with 6-GHz hardware support. That way organizations can deploy Wi-Fi 6E and get up to 1.2 GHz more spectrum to boost capacity and mitigate interference.



Figure 2.
Catalyst IW9167I Heavy Duty Access Point

Catalyst IW9167E Heavy Duty Access Point for Hazardous Locations

The Catalyst IW9167E-HZ has all the capabilities, benefits, and features of the IW9167E Heavy Duty Access Point with the additional capability to deploy in Hazardous Locations (HAZLOC) around the world. Equipped with hardened ports and certified by UL, ATEX, and IECEx, the Catalyst IW9167E Heavy Duty Access Point for Hazardous Locations brings Wi-Fi 6, Wi-Fi 6E, and URWB into regulated explosive environments for the first time.

Note: IW9167E-HZ shares all specifications listed for IW9167E unless otherwise noted

Secure infrastructure

Trustworthy systems built with Cisco Trust Anchor technologies provide a highly secure foundation for Cisco products. With the Cisco Catalyst IW9167 Series, these technologies enable assurance of hardware and software authenticity for supply chain trust and strong defense against man-in-the-middle attacks that compromise software and firmware. Trust Anchor capabilities include:

- Image signing
- Secure Boot
- Cisco Trust Anchor module

Features and benefits

 Table 1.
 Catalyst IW9167 Series features and benefits

| Feature | Benefit | | | |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|--|--|
| Wi-Fi 6 (802.11ax)/Wi-Fi 6E- ready | The IEEE 802.11ax standard, also known as High-Efficiency Wireless or Wi-Fi 6, builds on 802.11ac. IW9167 series can support 4x4 MIMO and up to four spatial streams. | | | |
| | Wi-Fi 6E is Wi-Fi 6 "extended" into the 6 GH additional channels. IW9167 is Wi-Fi 6E reactive use of the 6 GHz spectrum by each countries. | dy, subject to approvals and regulations for | | |
| Flexible multitechnology support | Two different technologies (Wi-Fi and URWE on the use case. Ability to swap images in the URWB operating modes without changing the | ie field helps you select Wi-Fi, WGB, or | | |
| Tri-radio architecture | IW9167E • 2.4 GHz 4x4 radio: 20-MHz channels | IW9167I • 2.4 GHz 4x4 radio: 20-MHz channels | | |
| | 5 GHz 4x4 radio: 20, 40, 80 MHz channels 5/6* GHz 4x4 radio: 20, 40, 80, and 160 MHz channels | 5 GHz 4x4 radio: 20, 40, 80 MHz channels 6° GHz 4x4 radio: 20, 40, 80, and 160 MHz channels | | |
| Multigigabit Ethernet | Dual Multigigabit Ethernet supports speeds u | up to 5 Gbps. | | |
| Smart AP+¥ | Smart AP causes the access point to change its power consumption to reflect its current client load. An access point will typically operate on the radios provided to it regardless of how many clients are connected. With Smart AP, if the number of clients is small enough, the access point will automatically reduce the radio stream count, saving power. | | | |
| Band steering ^{¥†} | Enhanced to help clients that are 6 GHz capable to leave the 5 GHz radio and connect to the 6 GHz one. Wi-Fi 6E clients are automatically directed to connect to the 6 GHz radio to take advantage of the benefits that the radio offers and free up the 2.4- and 5 GHz radios for legacy clients. IW9167 is Wi-Fi 6E ready, subject to approvals and regulations for the use of the 6 GHz spectrum by each countries' regulatory agencies | | | |
| Uplink/downlink OFDMA¥ | Orthogonal Frequency-Division Multiple Access (OFDMA)-based scheduling splits the bandwidth into smaller frequency allocations called Resource Units (RUs), which can be assigned to individual clients in both the downlink and uplink directions to reduce overhead and latency. | | | |
| Uplink/downlink MU-MIMO technology [¥] | Supporting four spatial streams, Multiuser Multiple Input, Multiple Output (MU-MIMO) enables access points to split spatial streams between client devices to maximize throughput. | | | |
| BSS coloring [¥] | Spatial reuse (also known as Basic Service Set [BSS] coloring) allows the access points and their clients to differentiate between BSSs, thus permitting more simultaneous transmissions. | | | |
| Target Wake Time¥ | Target Wake Time (TWT) allows the client to stay asleep and to wake up only at prescheduled (target) times to exchange data with the access point. This offers significant energy savings for battery-operated devices, up to three to four times the savings achieved by 802.11n and 802.11ac. | | | |
| Intelligent Capture¥ | Intelligent Capture probes the network and provides Cisco DNA Center with deep analysis. The software can track more than 240 anomalies and instantaneously review all packets on demand, emulating the onsite network administrator. Intelligent Capture allows for more informed decisions on your wireless networks. | | | |

| Feature | Benefit |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Bluetooth 5 [†] | The integrated Bluetooth Low Energy (BLE) 5 radio enables location-based use cases such as asset tracking, wayfinding, and analytics. |
| Scanning radio [†] | Dedicated radio for monitoring air space to perform advanced RF spectrum analysis and deliver features such as Cisco CleanAir®, Wireless Intrusion Prevention System (WIPS), etc. |
| GNSS | A built-in GNSS (Global Navigation Satellite System) receiver provides coordinates to track the location of the access point. |
| M12 adapter | M12 adapter accessories give the flexibility to convert Ethernet and power interfaces on the base unit into M12 interfaces while retaining all the certifications. |
| Multipath operations†¢ | Multipath Operations (MPO) can enhance reliability by sending duplicate copies of packets across multiple wireless paths. |
| WorkGroup Bridge (WGB) | Provides wireless connectivity to a lightweight access point infrastructure on behalf of wired clients that are connected via Ethernet behind the WGB access point. |

[†] Available with a future software upgrade.

[¥] Available only in Wi-Fi mode.

[¢] Available only in URWB mode.

 $[\]ensuremath{^{^{*}}}$ 6 GHz subject to approval by country's regulatory agency.

Prominent features

Get reliable wireless connectivity for your mission-critical applications

As you automate your processes and operations to increase safety and productivity, you also need to improve your situational awareness to control your systems. Moving assets involved in mission-critical applications, such as Automated Guided Vehicles (AGVs), Autonomous Mobile Robots (AMRs), and teleremote devices, require reliable wireless connectivity. And sometimes you need to extend your network where running fiber isn't feasible or is too costly.

The Catalyst IW9167 Series gives you flexibility and reliability so you can extend reliable wireless connectivity to more places and applications, with features such as:

- One hardware device, three different technologies: Protect your investment and evolve your wireless networks without the added cost of purchasing a new device. Simply update the software to run Wi-Fi 6, WGB, or URWB.
- MultiPath Operations (MPO): Patented technology that duplicates your high-priority traffic and works alongside hardware failures to increase availability, lower latency, and lower the effects of interference and hardware failures.
- WorkGroup Bridge (WGB): In workgroup bridge mode, the device associates to another access point as a client and provides a network connection for the equipment connected to its Ethernet port.
- Heavy-duty design: IP67-rated, hardened to withstand shock, vibration, and extreme temperatures.
 Supports industrial protocols and industrial certifications (e.g., the EN 50155 rail standard on the Catalyst IW9167E).
- Class I, Division 2, ATEX, and IECEx rated²: extend cutting edge wireless connectivity to explosive environments worldwide with the Catalyst IW9167E-HZ.

¹ In URWB mode.

² Available on IW9167EH-x-HZ only; please work with your account team to ensure local requirements and regulations are met.

Licensing

Table 2.Wi-Fi licensing

| Item | Description |
|----------|------------------------------------------|
| IW-DNA-E | Industrial Wireless Cisco DNA Essentials |
| IW-DNA-A | Industrial Wireless Cisco DNA Advantage |

Table 3.URWB licensing

| Item | Description |
|------------------|--------------------------------------|
| IW9167-URWB-NW-E | IW9167 Cisco URWB Network Essentials |
| IW9167-URWB-NW-A | IW9167 Cisco URWB Network Advantage |
| IW9167-URWB-NW-P | IW9167 Cisco URWB Network Premier |
| IOTOD-IW-E | IoT-OD Essentials for Cisco URWB |
| IOTOD-IW-A | IoT-OD Advantage for Cisco URWB |

Product sustainability

Information about Cisco's Environmental, Social, and Governance (ESG) initiatives and performance is provided in Cisco's CSR and sustainability <u>reporting</u>.

 Table 4.
 Cisco environmental sustainability information

| Sustainab | ility topic | Reference |
|-----------|--------------------------------------------------------------------------------------------------------|----------------------------------|
| General | Information on product-material-content laws and regulations | <u>Materials</u> |
| | Information on electronic waste laws and regulations, including our products, batteries, and packaging | WEEE Compliance |
| | Information on product takeback and reuse program | Cisco Takeback and Reuse Program |
| | Sustainability Inquiries | Contact: csr_inquiries@cisco.com |
| | Environmental operating temperature range | Table 5. Product Specifications |
| Power | Power input | Table 5. Product Specifications |
| | Power consumption | Table 5. Product Specifications |
| Material | Product packaging weight and materials | Contact: environment@cisco.com |
| | Physical dimensions and weight | Table 5. Product Specifications |

Product specifications

 Table 5.
 IW9167 Series product specifications

| Item | Specification |
|----------|-----------------------------------------------------------------------------------------------------|
| Hardware | Cisco Catalyst IW9167E Heavy Duty Access Point |
| | • IW9167EH-x: Catalyst IW9167E for x domains |
| | • IW9167EH-ROW: Catalyst IW9167E for 'Rest of the World' |
| | Cisco Catalyst IW9167I Heavy Duty Access Point |
| | • IW9167IH-x: Catalyst IW9167I for x domains |
| | • IW9167IH-ROW: Catalyst IW9167I for 'Rest of the World' |
| | Catalyst IW9167E Heavy Duty Access Point for Hazardous Locations |
| | • IW9167EH-x-HZ: Catalyst IW9167E-HZ for x domains |
| | • IW9167EH-ROW-HZ: Catalyst IW9167E-HZ for 'Rest of the World' |
| | Regulatory domains: (x = A, B, E, F, Q, or Z) |
| | ROW is for 'rest of the world' that is not covered as part of above-mentioned specific domain list. |
| | Customers are responsible for verifying approval for use in their individual countries. To verify |
| | approval and to identify the regulatory domain that corresponds to a particular country, visit |
| | https://www.cisco.com/go/aironet/compliance. |
| | Not all regulatory domains have been approved. As they are approved, the part numbers will be |
| | available on the Global Price List and/or regional price lists. |
| | See the ordering information section for actual orderable part numbers. |
| Software | IW9167EH-AP |
| | Cisco IOS® XE Software Release 17.9.4 or later |
| | IW9167EH-URWB |
| | Cisco Unified Industrial Wireless Software 17.11.1 or later |

| Item | Specification | | | | |
|---------------------------------------|-----------------------------------------------------------------------------------------------------|--|--|--|--|
| | IW9167EH-WGB | | | | |
| | Cisco Unified Industrial Wireless Software 17.11.1 or later | | | | |
| | | | | | |
| | IW9167IH-AP | | | | |
| | Cisco IOS XE Software Release 17.12.1 or later | | | | |
| Supported wireless LAN controllers | Cisco Catalyst 9800 Series Wireless Controllers (physical or virtual) | | | | |
| 802.11n version 2.0 (and related) | • 4x4 MIMO with four spatial streams in one 2.4 GHz radio and two 5 GHz radios | | | | |
| capabilities | Maximal Ratio Combining (MRC) | | | | |
| | • 802.11n and 802.11a/g | | | | |
| | • 20- and 40-MHz channels | | | | |
| | • PHY data rates up to 1.5 Gbps (with 40 MHz on both 5 GHz radios and 20 MHz on the 2.4 GHz radio) | | | | |
| | Packet aggregation: Aggregate MAC Protocol Data Unit (A-MPDU) (transmit and receive), Aggregate MAC | | | | |
| | Service Data Unit (A-MSDU) (transmit and receive) | | | | |
| | • 802.11 Dynamic Frequency Selection (DFS) | | | | |
| | Cyclic Shift Diversity (CSD) support | | | | |
| 802.11ac | 4x4 downlink MU-MIMO with four spatial streams on both 5 GHz radios | | | | |
| | Maximal Ratio Combining (MRC) | | | | |
| | • 802.11ac beamforming | | | | |
| | • 20, 40, and 80 MHz channels | | | | |
| | PHY data rates up to 3.4 Gbps (dual 4x4:4SS 80 MHz) | | | | |
| | Packet aggregation: A-MPDU (transmit and receive), A-MSDU (transmit and receive) | | | | |
| | • 802.11 DFS | | | | |
| | CSD support | | | | |
| | Wi-Fi Protected Access (WPA) 3 support | | | | |
| | | | | | |

| Item | Specification | |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 802.11ax | 4x4 uplink/downlink MU-MIMO with four spatial stree Uplink/downlink OFDMA Target Wake Time (TWT) BSS coloring Maximal Ratio Combining (MRC) 802.11ax beamforming 20, 40, 80, and 160 MHz channels (IW9167E 5/6 GRee) 20, 40, 80 channels (5 GHz radio) 20 MHz channels (2.4 GHz radio) PHY data rates up to 7.8 Gbps (4x4 160 MHz on 6 GRee) Packet aggregation: A-MPDU (transmit and receive) 802.11 DFS CSD support WPA3 support | Hz radio, IW9167I 6 GHz radio) GHz, 4x4 80 MHz on 5 GHz, and 4x4 20 MHz on 2.4 GHz) |
| Antennas | • 8x N-type antenna ports • 1x TNC GNSS antenna port • Cisco offers the industry's broadest selection of antennas, delivering optimal coverage for a variety of deployment scenarios. • Supports Self-Identifiable Antennas (SIA) | IW9167I 2.4 GHz: Peak gain 3.95 dBi, internal antennas, cross-polarized, omnidirectional 5 GHz: Peak gain 4.78 dBi, internal antennas, cross-polarized, omnidirectional 6 GHz: Peak gain 5.81 dBi, internal antennas, cross-polarized, omnidirectional BLE: Peak gain 3.05 dBi, internal antenna, vertical polarization, omnidirectional |
| Interfaces | • 1x 100M/1000M/2.5G/5G Multigigabit Ethernet (RJ in | -45)/M12 X-code autosensing PoE+ in (802.3at/bt), UPOE |

| Item | Specification | | | | |
|--------------|---------------------------------------------------------------------------------------------|-------------------------------------------------|--|--|--|
| | • 1x SFP (copper) 100M/1000M/10G Multigigabit Ethernet /M12 X-code OR 1x SFP (fiber) 1G/10G | | | | |
| | Management console port (RJ-45) | | | | |
| | Multicolor system LED | | | | |
| | DC power input (micro-fit/M12 A-code) | | | | |
| | Reset button | | | | |
| | Note: PG 13.5 glands or M12 adapters shall be u | used with Ethernet and power interfaces to meet | | | |
| | IP67 rating. | | | | |
| | Note: Catalyst IW9167E-HZ has permanent PG2 | 5 ports. M12 adapters are not compatible. See | | | |
| | Installation Guide for gland requirements. | | | | |
| Dimensions | IMO147F/IMO147F 117 | IMO1471 | | | |
| (W x L x H) | IW9167E/IW9167E-HZ | IW9167I | | | |
| | • 11.5 x 10.5 x 2.8 in (29.2 x 26.7 x 7.1 cm) | • 11.5 x 10.5 x 3.0 in (29.2 x 26.7 x 7.6 cm) | | | |
| | Note: IW9167E-HZ has permanent PG25 ports | | | | |
| | extending. 35" on bottom of Access Points but | | | | |
| | do not exceed overall dimensions listed | | | | |
| Weight | IW9167E | IW9167I | | | |
| | • 9.2 lb. (4.2 kg) | • 8 lb. (3.6 kg) | | | |
| | IW9167E-HZ | | | | |
| | • 9.4 lb. (4.3 kg) | | | | |
| Input power | • 802.3at (PoE+), 802.3bt (PoE++), Cisco Universal PoE (Cisco UPOE®) | | | | |
| requirements | • DC power source: 24 to 48 VDC (maximum voltage range: 18 to 60 VDC) | | | | |
| | • Cisco power AC-DC power adapter, IW-PWRADPT-MFIT4P= | | | | |
| | • Cisco power injector, IW-PWRINJ-60RGDMG= | | | | |
| | | | | | |

| Item | Specification | | | | | | | |
|---------------|------------------------------------------------------------------------------------|------------------|------------------|----------------------------------------------------------------------------------------------------------|----------------|-----------------------|-----------------|---------------|
| Power draw | Power input type | 2.4 GHz radio | 5 GHz radio | 5/6 GHz radio | | RJ45 | SFP/SFP+ | Power |
| | 24-48 VDC | 4x4 | 4x4 | 4x4 | | 5Gbps | Yes | 48W |
| | 802.3bt (UPOE) | 4x4 | 4x4 | 4x4 | | 5Gbps | Yes | 48W |
| | 802.3at (PoE+) | 2x2 | 2x2 | 2x2 | | 1Gbps | Yes/1G | 25W |
| | Note: Power req | | | e Equip | ment (PS | SE) will depend on | the cable le | ngth and |
| Surge | IW9167E | | | | IW9167 | I | | |
| | DC power input | | | | DC power input | | | |
| | EN50121-4, ± 2 kV (line-earth) and ± 1 kV (line-line) | | | CISPR35, ± 0.5 kV (line-earth) Surge protection to ± 2 kV on Ethernet ports | | | | |
| | AREMA, ± 1 kV (line-earth) and ± 1 kV (line-line) | | | Surge protection to ± 1 kV on SFP copper port with shielded cable | | | | |
| | ∘ CISPR35, ± 0 |).5 kV (line-e | earth) | | | | | |
| | Surge protection | n to ± 2 kV c | on Ethernet port | 5 | | | | |
| | Surge protection to ± 1 kV on SFP copper port with shielded cable | | | ort | | | | |
| Environmental | IW9167E | | IW9167I | | | | | |
| | • Nonoperating (s +185°F (-40° to | | perature: -40° t | ro | | perating (storage) te | mperature: -4 | .0° to +185°F |
| | Nonoperating (s 17,000 ft. | torage) altitu | ude test: +25°C | (77°F), | • Nonop | oerating (storage) al | titude test: +2 | 5°C (77°F), |

| Item | Specification | | |
|-----------------------|-----------------------------------------------------|--------------------------------------------------------|--|
| | | | |
| | Operating temperature: -40° to +149°F (-40° to | Operating temperature: -40° to +131°F (-40° to | |
| | +65°C) with solar load and still air | +55°C) with solar load and still air | |
| | Extended operating temperature (DC powered): - | • Extended operating temperature (DC powered): -58° | |
| | 58° to +158°F (-50° to +70°C) without solar | to +149°F (-50° to +65°C) without solar loading, still | |
| | loading, still air, and cold start limited to -40°C | air, and cold start limited to -40° C | |
| | Operating type test: +85°C for 16 hours | Operating type test: +85°C for 16 hours | |
| | Operating humidity: 0% to 100% (condensing) | Operating humidity: 0% to 100% (condensing) | |
| | • Operating altitude: 15,000 ft. (4,500 m) | • Operating altitude: 15,000 ft. (4,500 m) | |
| | Wind resistance: Up to 160 mph (257 km/h) | Wind resistance: Up to 160 mph (257 km/h) sustained | |
| | sustained winds | winds | |
| Environmental ratings | • EN/IEC 60529 (IP66 and IP67) | | |
| System memory | • 2048 MB DRAM | | |
| | • 1024 MB flash | | |
| Data rates supported | 2.4 GHz radio: | | |
| | 802.11b: 1, 2, 5.5, 11 Mbps | | |
| | 802.11g: 6, 9, 12, 18, 24, 36, 48, 54 Mbps | | |
| | 802.11n: HT20 MCS0 - 31 | | |
| | 802.11ax: HE20 MCS0 - 11, 1 to 4 spatial streams | | |
| | 5 GHz radio: | | |
| | 802.11a: 6, 9, 12, 18, 24, 36, 48, 54 Mbps | | |
| | 802.11n: HT20 and HT40, MCS0 to 31 | | |
| | 802.11ac: | | |
| | VHT20 MCS0 to 8, 1 to 4 spatial streams | | |

| Item | Specification |
|------|--------------------------------------------------------------------------|
| | VHT40 and VHT80 MCS0 to 9, 1 to 4 spatial streams |
| | 802.11ax: |
| | • HE20, HT40, and HE80 MCS0 to 11, 1 to 4 spatial streams |
| | IW9167E 5/6 GHz radio: |
| | 802.11a (5 GHz band only): 6, 9, 12, 18, 24, 36, 48, 54 Mbps |
| | 802.11n (5 GHz band only): HT20 and HT40, MCS0 to 31 |
| | 802.11ac (5 GHz band only): |
| | VHT20 MCS0 to 8, 1 to 4 spatial streams |
| | VHT80, VHT160 MCS0 to 9, 1 to 4 spatial streams |
| | 802.11ax: HE20, HT40, HE80, and HE160 MCS0 to 11, 1 to 4 spatial streams |
| | IW9167I 6 GHz radio: |
| | 802.11ax: HE20, HE40, HE80, and HE160 MCS0 to 11,1 to 4 spatial streams |

| Item | Specification |
|---------------------------|----------------------------------------------------------------|
| | |
| Frequency band and 20-MHz | A (A regulatory domain): |
| operating channels | • 2.412 to 2.462 GHz; 11 channels |
| | • 5.260 to 5.320 GHz; 4 channels |
| | • 5.500 to 5.700 GHz; 8 channels (excludes 5.600 to 5.640 GHz) |
| | • 5.745 to 5.825 GHz; 5 channels |
| | B (B regulatory domain): |
| | • 2.412 to 2.462 GHz; 11 channels |
| | • 5.180 to 5.320 GHz; 8 channels |
| | • 5.500 to 5.720 GHz; 12 channels |
| | • 5.745 to 5.825 GHz; 5 channels |
| | E (E regulatory domain, outdoor): |
| | • 2.412 to 2.472 GHz; 13 channels |
| | • 5.500 to 5.700 GHz; 11 channels |
| | E (E regulatory domain, indoor): |
| | • 2.412 to 2.472 GHz; 13 channels |
| | • 5.180 to 5.320 GHz; 8 channels |
| | • 5.500 to 5.700 GHz; 11 channels |
| | F (F regulatory domain): |
| | • 2.412 to 2.472 GHz; 13 channels |
| | • 5.745 to 5.805 GHz; 4 channels |
| | Q (Q regulatory domain): |
| | • 2.412 to 2.472 GHz; 13 channels |
| | • 5.500 to 5.720 GHz; 12 channels |

Item Specification

Z (Z regulatory domain):

• 2.412 to 2.462 GHz; 11 channels

• 5.500 to 5.700 GHz; 8 channels (excludes 5.600 to 5.640 GHz)

• 5.745 to 5.825 GHz; 5 channels

Note: This varies by regulatory domain. Customers are responsible for verifying approval for use in their individual countries. To verify approval and to determine availability of the regulatory domain that corresponds to a particular country, visit

https://www.cisco.com/c/dam/assets/prod/wireless/wireless-compliance-tool/index.html.

Maximum number of nonoverlapping channels

| 2.4 GHz | 5 GHz | 6 GHz [*] |
|---------------|--------------|--------------------|
| • 802.11b/g: | • 802.11a: | • 802.11ax: |
| 。 20 MHz: 3 | 。 20 MHz: 25 | ∘ 20 MHz: 41 |
| • 802.11n/ax: | • 802.11n: | 。 40 MHz: 20 |
| 。 20 MHz: 3 | 。 20 MHz: 25 | 。 80 MHz: 9 |
| | 。 40 MHz: 12 | ∘ 160 MHz: 4 |

| Item | Specificat | tion | | | | | | | | | | | | |
|-----------------------------------------------------|------------|--------------|--------|-------------------|----------|----------|--------|-------|---------------|----------|----------|---------|------------|------|
| | 40.14 | L 1 /h h | | . 00 | 2.11ac/a | 244 | | | | | | | | |
| | | Hz: 1 (hardw | are | • 80. | 2.11aC/a | ax: | | | | | | | | |
| | capal | oie) | | 0 | 20 MHz | : 25 | | | | | | | | |
| | | | | 0 | 40 MHz | : 12 | | | | | | | | |
| | | | | 0 | 80 MHz | : 6 | | | | | | | | |
| | | | | | | | | | | | | | | |
| | Note: This | varies by r | egulat | ory do | main. F | Refer to | the pr | oduc | t docum | entatic | n for sp | ecific | details fo | or |
| | each regu | latory doma | ain. | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| Available conducted transmit | 2.4 GHz | | 5 GH | Z | | | | | IW9167 | E 5/6 G | SHZ | | | |
| power settings (max/min), all antennas active | • 24 dBm | (250 mW) | • 30 | dBm (1 | 1 W) | | | | • 23 dB | m (200 | mW) | | | |
| antennas active | • -4 dBm | (0.4 mW) | • -4 | dBm (0 |).4 mW) | | | | • -4 dBı | m (0.4 r | mW) | | | |
| | | | | | | | | | IW9167I 6 GHz | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | | | | m (630 | mW) | | | |
| | | | | • -4 dBm (0.4 mW) | | | | | | | | | | |
| Conducted transmit | | | 2.4 0 | iHz rac | dio | | 5 GH | z rad | lio | | 5/6 G | Hz rad | io (E) | |
| power and receive sensitivity | | | | | | | | | | | | | | |
| | | | | | | | | | | | 6 GH | z radio | (I) | |
| | | Spatial | Total | Тх | Rx | | Tota | l Tx | Rx | | Total | Tx | Rx | |
| | | streams | powe | | sensit | tivity | pow | | sensi | tivity | powe | | sensit | ivit |
| | | Streams | | | | | | | | | | | | |
| | | | (dBm | IJ | (dBm) | | (dBm | IJ | (dBm |) | (dBm |) | y (dBn | 11) |
| | | | E | ı | E | ı | E | ı | E | 1 | E | 1 | E | ı |
| | | | | | | | | | | | | | | |
| | 802.11/11 | b | | | | | | | | | | | | |
| | 1 Mbps | 1 | 30 | 30 | -99 | -100 | _ | _ | - | _ | _ | _ | _ | _ |
| | | · | | | . , | . 55 | | | | | | | | |
| | 11 Mbps | 1 | 30 | 30 | -90 | -91 | - | - | - | - | - | - | - | - |
| | | | | | | | | | | | | | | |

| Item | Specificat | tion | | | | | | | | | | | | |
|------|------------|------|----|----|-----|-----|----|----|-----|-----|----|---|-----|---|
| | 802.11a/g | 1 | | | | | | | | | | | | |
| | 6 Mbps | 1 | 30 | 30 | -93 | -94 | 30 | 30 | -96 | -94 | 23 | - | -96 | - |
| | 24 Mbps | 1 | 30 | 30 | -84 | -85 | 30 | 30 | -87 | -86 | 23 | - | -86 | - |
| | 54 Mbps | 1 | 27 | 27 | -77 | -78 | 27 | 27 | -79 | -78 | 21 | - | -79 | - |
| | 802.11n H | T20 | | | | | | | | | | | | |
| | MCS0 | 1 | 30 | 30 | -94 | -95 | 30 | 30 | -96 | -94 | 23 | - | -95 | - |
| | MCS7 | 1 | 26 | 26 | -77 | -77 | 25 | 25 | -79 | -77 | 20 | - | -79 | - |
| | MCS8 | 2 | 30 | 30 | -92 | -92 | 30 | 30 | -93 | -92 | 23 | - | -91 | - |
| | MCS15 | 2 | 26 | 26 | -74 | -74 | 25 | 25 | -76 | -74 | 20 | - | -76 | - |
| | MCS24 | 4 | 30 | 30 | -89 | -89 | 30 | 30 | -90 | -89 | 23 | - | -89 | - |
| | MCS31 | 4 | 26 | 26 | -71 | -71 | 25 | 25 | -73 | -71 | 20 | - | -73 | - |
| | 802.11n H | T40 | | | | | | | | | | | | |
| | MCS0 | 1 | - | - | - | - | 28 | 28 | -94 | -91 | 23 | - | -92 | - |
| | MCS7 | 1 | - | - | - | - | 25 | 25 | -76 | -74 | 20 | - | -76 | - |
| | MCS8 | 2 | - | - | - | - | 28 | 28 | -91 | -88 | 23 | - | -89 | - |
| | MCS15 | 2 | - | - | - | - | 25 | 25 | -73 | -71 | 20 | - | -73 | - |
| | MCS24 | 4 | - | - | - | - | 28 | 28 | -88 | -85 | 23 | - | -86 | _ |

| Item | Specification | tion | | | | | | | | | | | | |
|------|---------------|-------|---|---|---|---|----|----|-----|-----|----|---|-----|---|
| | MCS31 | 4 | - | - | - | - | 25 | 25 | -70 | -68 | 20 | - | -70 | - |
| | 802.11ac | VHT20 | | | | | | | | | | | | |
| | MCS0 | 1 | - | - | - | - | 30 | 30 | -96 | -94 | 23 | - | -95 | - |
| | MCS8 | 1 | - | - | - | - | 24 | 24 | -74 | -72 | 19 | - | -75 | _ |
| | MCS0 | 2 | - | - | - | - | 30 | 30 | -93 | -92 | 23 | - | -92 | - |
| | MCS8 | 2 | - | - | - | - | 24 | 24 | -71 | -69 | 19 | - | -72 | - |
| | MCS0 | 4 | - | - | - | - | 30 | 30 | -90 | -89 | 23 | - | -89 | - |
| | MCS8 | 4 | - | - | - | - | 24 | 24 | -68 | -66 | 19 | - | -69 | - |
| | 802.11ac | VHT40 | | | | | | | | | | | | |
| | MCS0 | 1 | - | - | - | - | 28 | 28 | -94 | -91 | 23 | - | -92 | - |
| | MCS9 | 1 | - | - | - | - | 24 | 24 | -70 | -69 | 19 | - | -71 | - |
| | MCS0 | 2 | - | - | - | - | 28 | 28 | -91 | -88 | 23 | - | -89 | - |
| | MCS9 | 2 | - | - | - | - | 24 | 24 | -67 | -66 | 19 | - | -68 | - |
| | MCS0 | 4 | - | - | - | - | 28 | 28 | -88 | -85 | 23 | - | -86 | - |
| | MCS9 | 4 | - | - | - | - | 24 | 24 | -64 | -63 | 19 | - | -65 | - |
| | 802.11ac | VHT80 | | | | | | | | | | | | |
| | MCS0 | 1 | - | - | - | - | 28 | 28 | -91 | -89 | 23 | - | -89 | - |

| Item | Specifica | tion | | | | | | | | | | | | |
|------|-----------|------|----|------|-----|-----|----|------|-----|-----|----|----|-----|-----|
| | MCS9 | 1 | - | - | - | - | 23 | 24 | -67 | -66 | 19 | - | -67 | - |
| | MCS0 | 2 | - | - | - | - | 28 | 28 | -88 | -86 | 23 | - | -86 | - |
| | MCS9 | 2 | - | - | - | - | 23 | 24 | -64 | -63 | 19 | - | -64 | - |
| | MCS0 | 4 | - | - | - | - | 28 | 28 | -85 | -83 | 23 | - | -83 | - |
| | MCS9 | 4 | _ | - | - | - | 23 | 24 | -61 | -60 | 19 | - | -61 | - |
| | 802.11ax | HT20 | | | | | | | | | | | | |
| | MCS0 | 1 | 30 | 30 | -94 | -95 | 30 | 30 | -96 | -94 | 23 | 28 | -95 | -96 |
| | MCS11 | 1 | 23 | 23 | -65 | -66 | 23 | 23 | -67 | -65 | 16 | 23 | -68 | -69 |
| | MCS0 | 2 | 30 | 30 | -92 | -92 | 30 | 30 | -93 | -92 | 23 | 28 | -92 | -93 |
| | MCS11 | 2 | 23 | 23 | -62 | -63 | 23 | 23 | -64 | -62 | 16 | 23 | -65 | -66 |
| | MCS0 | 4 | 30 | 30 | -89 | -89 | 30 | 30 | -90 | -89 | 23 | 28 | -89 | -90 |
| | MCS11 | 4 | 23 | 23 - | 59 | -60 | | 3 23 | -61 | -59 | 16 | 23 | -62 | -63 |
| | 802.11ax | HE40 | | | | | | | | | | | | |
| | MCS0 | 1 | - | - | - | - | 28 | 28 | -94 | -92 | 23 | 28 | -92 | -93 |
| | MCS11 | 1 | - | - | - | - | 23 | 23 | -64 | -62 | 16 | 23 | -64 | -66 |
| | MCS0 | 2 | - | - | - | - | 28 | 28 | -91 | -89 | 23 | 28 | -89 | -90 |
| | MCS11 | 2 | - | - | - | - | 23 | 23 | -61 | -59 | 16 | 23 | -61 | -63 |

| Specific | ation | | | | | | | | | | | | | |
|----------|---------|---|---|---|---|---|----|----|-----|-----|----|----|-----|-----|
| MCS0 | 4 | - | - | | - | - | 28 | 28 | -88 | -86 | 23 | 28 | -84 | -87 |
| MCS11 | 4 | - | - | | - | _ | 23 | 23 | -58 | -56 | 16 | 23 | -58 | -60 |
| 802.11a | x HE80 | | | | | | | | | | | | | |
| MCS0 | 1 | - | - | - | - | | 28 | 28 | -91 | -89 | 23 | 27 | -89 | -90 |
| MCS11 | 1 | - | - | - | - | - | 22 | 23 | -61 | -60 | 16 | 23 | -62 | -63 |
| MCS0 | 2 | - | - | - | - | - | 28 | 28 | -88 | -86 | 23 | 27 | -86 | -8 |
| MCS11 | 2 | - | - | - | _ | - | 22 | 23 | -58 | -57 | 16 | 23 | -59 | -60 |
| MCS0 | 4 | - | - | - | _ | - | 28 | 28 | -85 | -83 | 23 | 27 | -83 | -8 |
| MCS11 | 4 | - | - | - | _ | - | 22 | 23 | -55 | -54 | 16 | 23 | -56 | -5 |
| 802.11a | x HE160 | | | | | | | | | | | | | |
| MCS0 | 1 | - | - | - | - | | - | - | - | - | 23 | 26 | -86 | -87 |
| MCS11 | 1 | - | - | - | - | - | - | - | - | - | 16 | 23 | -58 | -60 |
| MCS0 | 2 | - | - | - | - | - | _ | - | - | - | 23 | 26 | -83 | -84 |
| MCS11 | 2 | - | - | - | - | - | _ | - | - | - | 16 | 23 | -55 | -57 |
| MCS0 | 4 | - | - | - | - | - | - | - | - | - | 23 | 26 | -80 | -81 |
| MCS11 | 4 | - | _ | - | - | - | _ | - | - | - | 16 | 23 | -52 | -54 |

| Item | Specification | |
|----------------------|----------------------------------------|-------------------------------|
| Compliance standards | IW9167E | IW9167I |
| | Environmental | Environmental |
| | EN 60529 IP67 | EN 60529 IP67 |
| | UL50E Type 4X | UL50E Type 4X |
| | IEC 60068-2-1 (Cold) | Electromagnetic compatibility |
| | IEC 60068-2-2 (Dry Heat) | FCC 47 CFR Part 15 Class A |
| | IEC 60068-2-14 (Change of Temperature) | EN 55032 Class A |
| | IEC 60068-2-30 (Damp Heat) | VCCI Class A |
| | IEC 60068-2-6 (Vibration) | AS/NZ CISPR 32 Class A |
| | IEC 60068-2-27 (Shock) | CISPR 32 Class A |
| | IEC 60068-2-30 (Humidity) | ICES 003 Class A |
| | IEC 60068-2-32 (Freefall) | CNS13438 Class A |
| | IEC 60068-3-3 (Seismic) | EN 300 386 |
| | Electromagnetic compatibility | KS C 9832:2019 |
| | FCC 47 CFR Part 15 Class A | EN 301 489-1 v2.1.1 |
| | EN 55032 Class A | EN 301 489-17 v2.1.1 |
| | VCCI Class A | EN 301 489 - 19 |
| | AS/NZ CISPR 32 Class A | EN 55035 |
| | CISPR 32 Class A | CISPR35 |
| | ICES 003 Class A | KS C 9835:2019 |
| | CNS13438 Class A | KS X 3124 |

| Item | Specification | |
|------|--------------------------------------------|---------------------------------------------|
| | EN 300 386 | KS X 3126 |
| | KS C 9832:2019 | IEC/EN 61000-4-2 - Electrostatic Discharge |
| | EN 301 489-1 v2.1.1 | IEC/EN 61000-4-3 - Radiated RF Immunity |
| | EN 301 489-17 v2.1.1 | IEC/EN 61000-4-5 - Surge |
| | EN 301 489 - 19 | IEC/EN 61000-4-6 - Conducted RF Immunity |
| | EN 55035 | IEC/EN 61000-4-8 - Power Frequency Magnetic |
| | CISPR35 | Field |
| | KS C 9835:2019 | IEC 61000-4-11 - AC Voltage Dips |
| | KS X 3124 | EN-61000-4-29 - DC Voltage Dips |
| | KS X 3126 | Safety |
| | IEC/EN 61000-4-2 - Electrostatic Discharge | IEC 62368-1 |
| | IEC/EN 61000-4-3 - Radiated RF Immunity | EN 62368-1 |
| | IEC/EN 61000-4-5 - Surge | EN 62311 |
| | IEC/EN 61000-4-6 - Conducted RF Immunity | Industrial |
| | IEC/EN 61000-4-8 - Power Frequency | EN 61000-6-2 - Industrial |
| | Magnetic Field | EN 61000-6-4 - Industrial |
| | IEC 61000-4-9 - Pulsed Magnetic Field | EN 61000-6-1 - Light Industrial |
| | IEC 61000-4-11 - AC Voltage Dips | |
| | IEC 61000-4-18 - Damped Oscillatory Wave | |
| | EN-61000-4-29 - DC Voltage Dips | |
| | Safety | |
| | | |


| Item | Specification | |
|------|---------------------------------------------|--|
| | IEC 62368-1 | |
| | EN 62368-1 | |
| | EN 62311 | |
| | Flammability | |
| | EN 45545-3 | |
| | DIN 5510-2 | |
| | Industrial | |
| | EN 61000-6-2 - Industrial | |
| | EN 61000-6-4 - Industrial | |
| | EN 61000-6-1 - Light Industrial | |
| | Rail | |
| | AREMA C&S Manual Section 11.5.1 | |
| | AAR S9401 Rail - Rolling stock cab, wayside | |
| | outside | |
| | EN 50155 Rail - Electronic Equipment on | |
| | Rolling Stock Class TX (EMC, Environmental) | |
| | EN 61373 Rail - Environmental | |
| | EN 50121-4 Rail - Signaling and | |
| | Telecommunications Apparatus | |
| | EN 50121-3-2 Rail - Apparatus for Rolling | |
| | Stock | |
| | EN 61373 - Shock and Vibration | |


| Item | Specification |
|------------------------|---------------------------------------|
| | Hazardous Locations (IW9167E-HZ only) |
| | Class I Division 2 (C1D2) |
| | UL/cUL C1D2 |
| | Zone 2/Zone 22 (ec+ic+tc) |
| | UL 121201 |
| | CSA C22.2 No 213 |
| | ANSI/UL 60079-0, -7, -11, -31 |
| | IECEx |
| | ATEX |
| | UKEx |
| | IEC/EN 60079-0 |
| | IEC/EN 60079-7 |
| | IEC/EN 60079-11 |
| | IEC/EN 60079-31 |
| Wireless communication | Radio approvals |
| standards | • FCC Part 15.247, 15.407 |
| | • RSS 247 |
| | • EN 300 328 v2.2.2 (EU) |
| | • EN 301 893 v2.1.1 (EU) |
| | • EN 303 413 |
| | • ARIB-STD 66 (Japan) |
| | ARIB-STD T71 (Japan) |


| Item | Specification | | | |
|---------------------------|---------------------------------------------------------------------------------------------------------|--|--|--|
| | EMI and susceptibility (Class B) | | | |
| | IEEE Wi-Fi and security standards | | | |
| | • IEEE 802.11a/b/g/n/ac/ax, 802.11h, 802.11d, 802.11v, 802.11u, 802.11k, 802.11r | | | |
| | • IEEE 802.11i, Wi-Fi Protected Access 3 (WPA3), WPA2, WPA | | | |
| | • IEEE 802.1X | | | |
| | Advanced Encryption Standards (AES), Temporal Key Integrity Protocol (TKIP) | | | |
| | Extensible Authentication Protocol (EAP) types | | | |
| | • EAP-Transport Layer Security (TLS) | | | |
| | • EAP-Tunneled TLS (TTLS) or Microsoft Challenge Handshake Authentication Protocol Version 2 (MSCHAPv2) | | | |
| | Protected EAP (PEAP) v0 or EAP-MSCHAPv2 | | | |
| | EAP-Flexible Authentication via Secure Tunneling (FAST) | | | |
| | PEAP v1 or EAP-Generic Token Card (GTC) | | | |
| | • EAP-Subscriber Identity Module (SIM) | | | |
| | Multimedia | | | |
| | Wi-Fi Multimedia (WMM) | | | |
| | Other | | | |
| | • FCC Bulletin OET-65C | | | |
| | • RSS-102 | | | |
| *6 GHz usage subject to a | approvals by country's regulatory agency. | | | |


^{*6} GHz usage subject to approvals by country's regulatory agency.


IW9167I antenna patterns






































Ordering information

Table 6.Ordering information

| Part # | Product description |
|-----------------|--------------------------------------------------------------------------------------|
| IW9167EH-x-AP | Industrial Wireless 9167E, 11ax 6E AP, 8 RF ports, x domain, Wi-Fi software |
| IW9167EH-x-URWB | Industrial Wireless 9167E, 11ax 6E AP, 8 RF ports, x domain, URWB software |
| IW9167EH-x-WGB | Industrial Wireless 9167E, 11ax 6E AP, 8 RF ports, x domain, WGB software |
| IW9167IH-x-AP | Industrial Wireless 9167I, 11ax 6E AP, internal antenna, x domain, Wi-Fi software |
| IW9167EH-x-HZ | Industrial Wireless 9167EH-HZ, 11ax 6E AP, 8 RF ports, x domain, Hazardous Locations |

x = regulatory domain

Warranty information

The Catalyst IW9167 Series comes with a 1-year limited warranty. The warranty includes 10-day advance hardware replacement and ensures that software media are defect-free for 90 days. For more details, visit Product Warranties.

Cisco and partner services

Realize the full business value of your technology investments faster with intelligent, customized services from Cisco and our partners. Backed by deep networking expertise and a broad ecosystem of partners, Cisco Services enable you to deploy a sound, scalable mobility network that enables rich media collaboration while improving the operational efficiency gained from a converged wired and wireless network infrastructure. Together with our partners, we offer expert plan, build, and run services to accelerate your transition to advanced mobility services while continuously optimizing the performance, reliability, and security of that architecture after it is deployed. For more details, visit Services for Wireless.

Smart Account

Creating a Smart Account by using the Cisco Smart Software Manager (SSM) enables you to order devices and licensing packages and also manage your software licenses from a centralized website. For more information on Smart Accounts, refer to https://www.cisco.com/go/smartaccounts.

Cisco Capital

Flexible payment solutions to help you achieve your objectives

Cisco Capital® makes it easier to get the right technology to achieve your objectives, enable business transformation and help you stay competitive. We can help you reduce the total cost of ownership, conserve capital, and accelerate growth. In more than 100 countries, our flexible payment solutions can help you acquire hardware, software, services, and complementary third-party equipment in easy, predictable payments. Learn more.

Learn more

Get reliable wireless connectivity for any application, anywhere

Need to connect your mission-critical time-sensitive applications wirelessly with more bandwidth, higher reliability, and seamless handoffs? Take advantage of the 6 GHz band expansion and the flexibility to run one of two wireless technologies (Wi-Fi 6 or URWB) in a state-of-the-art hardware platform with the Cisco Catalyst IW9167 Series.

Learn more:

- Cisco.com/go/iw9167
- Cisco.com/go/iw

Document history

| New or Revised Topic | Described In | Date |
|-------------------------------------|----------------------------------------|------------------|
| Product overview and specifications | Updated details about IW9167I platform | May 31, 2023 |
| Multiple Sections | IW9167E-HZ variant information added | January 10, 2024 |

Americas Headquarters Cisco Systems, Inc. San Jose, CA Asia Pacific Headquarters Cisco Systems (USA) Pte. Ltd. Singapore

Europe Headquarters Cisco Systems International BV Amsterdam, The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at https://www.cisco.com/go/offices.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: https://www.cisco.com/go/trademarks. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)

Printed in USA C11-2982402-04 04/24