OSRAM SFH 2201 Datasheet

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved






TOPLED® D5140

SFH 2201

Silicon PIN Photodiode with Enhanced Blue Sensitivity





Applications

- Digital Diagnostic Devices

- Vital Sign Monitoring

Features

- Package: clear silicone
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Especially suitable for applications from 300 nm to 1100 nm
- Small outline dimensions
- Solder control structure
- Suitable for reflow soldering



Ordering Information

Туре	Photocurrent ¹⁾	Photocurrent typ.	Ordering Code
	E_v = 1000 lx; white LED; V_R = 5 V I_P	$E_v = 1000 \text{ lx}; \text{ white LED}; V_R = 5 \text{ V}$ I_P	
SFH 2201	≥ 11 µA	13 µA	Q65112A3981



Maximum Ratings $T = 25 \degree C$

T _A = 25 °C			
Parameter	Symbol		Values
Operating Temperature	T _{op}	min.	-40 °C
	- r	max.	85 °C
Storage temperature	T _{stg}	min.	-40 °C
	3	max.	85 °C
Reverse voltage	V _R	max.	16 V
Total power dissipation	P _{tot}	max.	150 mW
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	max.	2 kV




Characteristics

T _A = 25 °C			
Parameter	Symbol		Values
Spectral sensitivity V _R = 5 V; Std. Light A, T = 2856 K	S	typ.	76 nA/lx
Wavelength of max sensitivity	$\lambda_{_{ m Smax}}$	typ.	950 nm
Spectral range of sensitivity	$\lambda_{_{10\%}}$	typ.	300 1100 nm
Radiant sensitive area	А	typ.	8.12 mm ²
Dimensions of active chip area	L x W	typ.	2.85 x 2.85 mm x mm
Half angle	φ	typ.	60 °
Dark current V _R = 10 V	I _R	typ. max.	1 nA 25 nA
Spectral sensitivity of the chip $\lambda = 400 \text{ nm}$	S_{λ}	typ.	0.2 A / W
Spectral sensitivity of the chip $\lambda = 550 \text{ nm}$	S _λ	typ.	0.45 A / W
Open-circuit voltage E _v = 1000 lx; Std. Light A	V _o	min. typ.	300 mV 350 mV
Short-circuit current E _v = 1000 lx; Std. Light A	I _{sc}	typ.	76 µA
Rise time V _R = 5 V; R _L = 50 Ω; λ = 950 nm; I _P = 800 μA	t _r	typ.	1.6 µs
Rise time V _R = 5 V; R _L = 50 Ω; λ = 450 nm; I _P = 800 μA	t _r	typ.	0.07 µs
Fall time V _R = 5 V; R _L = 50 Ω; λ = 950 nm; I _P = 800 μA	t _f	typ.	1.2 µs
Fall time V _R = 5 V; R _L = 50 Ω; λ = 450 nm; I _P = 800 μA	t _r	typ.	0.065 µs
Forward voltage I _F = 100 mA; E = 0	V _F	typ.	1.2 V
Capacitance $V_R = 0 V$; f = 1 MHz; E = 0	C _o	typ.	65 pF
Temperature coefficient of voltage	TC _v	typ.	-2.6 mV / K




Relative Spectral Sensitivity ^{2), 3)}

 $S_{rel} = f(\lambda)$



Directional Characteristics ^{2), 3)}


 $S_{rel} = f(\phi)$



SFH 2201 DATASHEET




Dark Current ^{2), 3)}




Capacitance ^{2), 3)}

C = f (V_R); f = 1MHz; E = 0; T_A = 25°C





Dimensional Drawing ⁴⁾



general tolerance ± 0.1 lead finish Au

C63062-A4306-A6-02


Further Information:


Approximate Weight:46.0 mg


Package marking: Cathode



Recommended Solder Pad⁴⁾







solder stencil

0.6


E062.3010.210-01

Handling Indication: The package is casted with silicone. Mechanical stress at the silicone surface of the unit should be avoided. Pickup the device at the plastic frame.



Reflow Soldering Profile





Profile Feature	Symbol	Pb	-Free (SnAgCu) Ass	embly	Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat [•]) 25 °C to 150 °C			2	3	K/s
Time t _s T _{Smin} to T _{Smax}	t _s	60	100	120	S
Ramp-up rate to peak ^{*)} T_{smax} to T_{p}			2	3	K/s
Liquidus temperature	TL		217		°C
Time above liquidus temperature	t		80	100	S
Peak temperature	Τ _Ρ		245	260	°C
Time within 5 °C of the specified peak temperature T_{p} - 5 K	t _P	10	20	30	S
Ramp-down rate* T _P to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S


All temperatures refer to the center of the package, measured on the top of the component

* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

SFH 2201 DATASHEET




Taping 4)



C63062-A4306-B1-01



Tape and Reel ⁵⁾




Reel Dimensions


А	W	N _{min}	W ₁	$W_{2 \max}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	1500



Barcode-Product-Label (BPL)



Dry Packing Process and Materials⁴⁾



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Notes

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.



Glossary

- ¹⁾ **Photocurrent:** The photocurrent values are measured (by irradiating the devices with a homogenous light source and applying a voltage to the device) with a tolerance of ±11 %.
- ²⁾ Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ³⁾ **Testing temperature:** TA = 25°C (unless otherwise specified)
- ⁴⁾ **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁵⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Revision History

Version	Date	Change
1.2	2019-12-02	Characteristics
1.3	2021-06-09	Schematic Transportation Box Dimensions of Transportation Box
1.4	2021-11-23	Characteristics
1.5	2023-03-20	New Layout Applications



EU RoHS and China RoHS compliant product 此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准, 不含有毒有害物质或元素。

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved

