

Features

- 3GPP release 13 compliant
- LTE CAT M1 – 23 dBm (nominal)
- LTE NB1 – 23 dBm (nominal) (dual module only)
- 16 MByte of flash
- Dimension: 11.1x11.4x1.4 mm (typ), 1.5mm(max)
- Package: LGA
- Antenna configurations: external
- SIM configuration: external
- 3GPP Rel. 13 eDRX and PSM modes
- Power Consumption: enables up to 10 year battery life
 - Hibernation current: 1.5 μ A(avg)
 - eDRX current: <45 uA (avg) @ 8 Hyperframes
 - PSM current: dormant window configurable
- Moisture control: MSL4
- Operating temperature range: -40°C to 85°C
- OTA firmware upgrade
- Regulatory certificate: FCC/IC, ETSI, TELEC
- Global Certification: PTCRB, GCF
- Control via AT commands according to 3GPP TS27.005, 27.007 and customized AT commands
- IPv4/IPv6 stack with TCP and UDP protocol
- SSL/TLS

Benefits

- 4G LTE technology capability
- Dedicated LTE half-duplex operation (HD-FDD) for CatM1
- Cellular transceiver designed to meet 3GPP Rel-13 specifications
- LTE universal modem supports (low-band and mid-band):
 - Low-band B5/B8/B12/B13/B17/B18/B19/B20/B26/B28
 - Mid-band B1/B2/B3/B4/B25
- Optimized for Class 3 LTE output power (+23 dBm)

Applications

- Wearables
- Smart Meter
- Medical/Healthcare
- Asset Tracking

LBAD0XX1SC

**LTE CAT M1&NB1
Module**



RoHS Compliance

This component is compliant with RoHS directive.

This component was always RoHS compliant from the first date of manufacture.

Table of Contents

| | |
|--|-----------|
| REVISION HISTORY | 2 |
| TABLE OF CONTENTS | 3 |
| 1 INTRODUCTION | 6 |
| 1.1 Scope | 6 |
| 1.2 Block Diagram | 6 |
| 1.3 Acronyms | 6 |
| 1.4 References | 6 |
| 2 MECHANICAL SPECIFICATION | 7 |
| 2.1 Dimension | 7 |
| 2.2 Pin Configuration | 8 |
| 3 RF SPECIFICATION | 12 |
| 3.1 Tx Output Power | 12 |
| 3.2 Rx Sensitivity | 12 |
| 3.3 Power Consumption for CAT M1 | 12 |
| 3.4 Power Consumption for NB1 (for dual mode only) | 12 |
| 4 ENVIRONMENTAL SPECIFICATION | 13 |
| 4.1 Absolute Maximum Rating | 13 |
| 4.2 Recommended Operating Condition | 13 |
| 4.3 Interface Voltage specifications | 13 |
| 4.4 Digital I/O Pin's specifications | 13 |
| 4.5 Analog I/O Pin's specifications | 14 |
| 5 POWER SEQUENCE | 15 |
| 5.1 Power Sequence for power up | 15 |
| 5.2 Power Sequence for power down | 15 |
| 5.3 Power Sequence for reset | 15 |
| 6 UART INTERFACE | 16 |
| 7 HOST PCB LANDING PATTERN (TOP VIEW) | 16 |
| 8 REFERENCE CIRCUIT | 17 |
| 9 ASSEMBLY INFORMATION | 17 |
| 10 PACKAGING AND MARKING INFORMATION | 18 |
| 10.1 Dimensions of Tape (Plastic tape) | 18 |
| 10.2 Dimensions of Reel | 19 |
| 10.3 Taping Diagrams | 19 |
| 10.4 Module Marking Information | 21 |
| 10.5 Moisture Sensitivity Level | 21 |
| 11 REGULATORY INFORMATION | 22 |
| 12 ROHS INFORMATION | 23 |
| 13 ORDERING INFORMATION | 23 |
| 14 NOTICE | 23 |
| 14.1 Storage Conditions | 23 |
| 14.2 Handling Conditions | 23 |
| 14.3 Standard PCB Design (Land Pattern and Dimensions) | 23 |
| 14.4 Notice for Chip Placer | 24 |

| | |
|--|-----------|
| 14.5 Operational Environment Conditions | 24 |
| 14.6 Input Power Capacity | 24 |
| 15 PRECONDITIONS TO USE MURATA PRODUCTS | 25 |

LIST OF FIGURES

| | |
|---|----|
| Figure 1.1 Block Diagram..... | 6 |
| Figure 2.1 Module Top and Side View..... | 7 |
| Figure 2.2 Module Footprint Bottom View..... | 7 |
| Figure 2.3 Pinout Diagram Top View..... | 8 |
| Figure 5.1 Power Sequence Diagram – Power Up..... | 15 |
| Figure 5.2 Power Sequence Diagram – Power Up..... | 15 |
| Figure 5.3 Power Sequence Diagram – Power Up..... | 15 |
| Figure 7.1 Recommended PCB Landing Pattern..... | 16 |
| Figure 9.1 Reflow Profile..... | 17 |
| Figure 10.1 Tape Dimensions (Unit: mm)..... | 18 |
| Figure 10.2 Reel Dimensions (Unit: mm)..... | 19 |
| Figure 10.3 Tape Diagram..... | 20 |
| Figure 10.4 Type 1SC Module Marking Diagram..... | 21 |
| Figure 10.5 Type 1SC DM Module Marking Diagram..... | 21 |

LIST OF TABLES

| | |
|--|----|
| Table 2.1 Dimension..... | 8 |
| Table 2.2 Pinouts..... | 9 |
| Table 3.1 Rx Sensitivity..... | 12 |
| Table 3.2 Power Consumption for CAT M1..... | 12 |
| Table 3.3 Power Consumption for NB1..... | 12 |
| Table 4.1 Absolute Maximum Rating..... | 13 |
| Table 4.2 Recommended Operating Condition..... | 13 |
| Table 4.3 Interface Voltage Condition..... | 13 |
| Table 4.4 Digital IO Pin's Specifications..... | 13 |
| Table 4.5 Digital IO Absolute Maximum Rating..... | 13 |
| Table 4.6 Analog IO Pin's specifications..... | 14 |
| Table 4.7 Analog IO Absolute Maximum Rating..... | 14 |
| Table 6.1 UART Interface..... | 16 |
| Table 11.1 Regulatory Standards Conformance for 1SC single mode..... | 22 |

1 Introduction

1.1 Scope

This product is designed to meet 3GPP Rel-13 specifications

- Host Interface : UART
- Reference Clock : Reference clock embedded
- Size : 11.1 x 11.4 x 1.5 mm (max)
- Weight : 0.45g (typ)
- RoHS : This component can meet with RoHS compliance
- MSL :Level 4
- *This product is moisture sensitive. Please check the detail in 14.1 Storage Condition section.

1.2 Block Diagram




Figure 1.1 Block Diagram

1.3 Acronyms

- LTE Long Term Evolution
- UART Universal Asynchronous Receiver Transmitter
- eUICC Embedded Universal Integrated Circuit Card
- LGA Land Grid Array
- BB Baseband
- RFIC Radio Frequency Integrated Circuit
- GPS Global Positioning System
- LB Low Band (699 MHz to 960 MHz frequency range)
- MB Mid Band (1710 MHz to 2170 MHz frequency range)
- PSM Power Save Mode
- eDRX Extended Discontinuous Reception

1.4 References

- [1] Altair Semiconductor, AL1250 – Datasheet 1.24, August 2020

2 Mechanical Specification

2.1 Dimension




Figure 2.1 Module Top and Side View




Figure 2.2 Module Footprint Bottom View

Table 2.1 Dimension

| Mark | Dimension | Mark | Dimension | Mark | Dimension |
|-----------|--------------|-----------|-------------|------------|-------------|
| L | 11.10 ± 0.20 | W | 11.4 ± 0.20 | T | 1.50 max |
| a1 | 0.30 ± 0.10 | a2 | 0.80 ± 0.10 | b1 | 0.30 ± 0.20 |
| b2 | 1.50 ± 0.20 | b3 | 3.55 ± 0.20 | b4 | 3.85 ± 0.20 |
| b5 | 0.35 ± 0.20 | b6 | 3.70 ± 0.20 | b7 | 0.30 ± 0.20 |
| b8 | 0.60 ± 0.10 | b9 | 1.70 ± 0.20 | b10 | 1.70 ± 0.20 |
| c1 | 0.60 ± 0.10 | c2 | 0.80 ± 0.10 | e1 | 0.35 ± 0.10 |
| e2 | 0.80 ± 0.10 | e3 | 0.80 ± 0.10 | | |

unit [mm]

2.2 Pin Configuration




Figure 2.3 Pinout Diagram Top View

Table 2.2 Pinouts

| 1SC Pin# | Module Pin Name | ALT1250 Pin No | ALT1250 IC Symbol Pin Name | Type | Direction | Reset Value | IO Domain / Supply | Description |
|----------|-----------------|----------------|----------------------------|---------|-----------|-------------|--------------------|--|
| 1 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 2 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 3 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 4 | EJ_TRST | J5 | EJ_TRST/GPIO20 | Digital | I | PD | VDDIO | JTAG Test Reset - require external pull down(10kOhm) |
| 5 | PMU_AT_IN | R3 | PMU_AT_IN | Analog | I | | PMU_VRTC | Anti-tamper input; short to GND if not used |
| 6 | PMU_WAKEUP | P2 | PMU_WAKEUP | Analog | I | | PMU_VRTC | Wakeup active high; Device Wake-Up (HI) |
| 7 | VDD_RF | L1 | PMU_VO_RF | Power | O | | | MIPI RFFE IO (antenna tuning) |
| 8 | VSIM | R1 | PMU_VO_SIM | Power | O | | | SIM LDO output |
| 9 | VDD_AUX | T2 | PMU_VO_AUX_LDO | Power | O | | | SC2 LDO output |
| 10 | NC | | | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 11 | SIMIO | M10 | SC_IO/GPIO14 | Digital | I/O | PD | VDDIO | SIM Data 1.8V |
| 12 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 13 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 14 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 15 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 16 | VBAT_FEM | | | Power | I | | | Input from battery to FEM |
| 17 | VBAT_FEM | | | Power | I | | | Input from battery to FEM |
| 18 | VBAT_FEM | | | Power | I | | | Input from battery to FEM |
| 19 | GND | | | | | | | |
| 20 | UART2_RX | H14 | UART2_RX | Digital | I | PU | VDDIO | Only use for internal test |
| 21 | UART2_CTS | G15 | UART2_CTS | Digital | I | PD | VDDIO | Only use for internal test |
| 22 | UART2_TX | G13 | UART2_TX | Digital | O | PU | VDDIO | Only use for internal test |
| 23 | GND | | | | | | | |
| 24 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 25 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 26 | GND | | | | | | | |
| 27 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 28 | GND | | | | | | | |
| 29 | RF_RXTX | | | RF | | | | CAT-M1 RF in/out signal |
| 30 | GND | | | | | | | |
| 31 | GPIO53 | N13 | GPIO53 | Digital | O | PU | VDDIO | TX Indicator |
| 32 | GPIO50 | P10 | GPIO50 | Digital | O | PD | VDDIO | Device Reset Status (HI) |
| 33 | GPIO5 | H12 | GPIO5 | Digital | O | PD | VDDIO | External DCDC Control |
| 34 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 35 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 36 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 37 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 38 | GND | | | | | | | |
| 39 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 40 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 41 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 42 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |

| 1SC Pin# | Module Pin Name | ALT1250 Pin No | ALT1250 IC Symbol Pin Name | Type | Direction | Reset Value | IO Domain / Supply | Description |
|----------|---------------------|----------------|----------------------------|---------|-----------|-------------|--------------------|---|
| 43 | UART1_RTS | P12 | UART1_RTS | Digital | O | PU | VDDIO | Port 1: UART RTS |
| 44 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 45 | UART1_RX | T12 | UART1_RX | Digital | I | PU | VDDIO | Port 1: UART RX |
| 46 | UART1_TX | U13 | UART1_TX | Digital | O | PU | VDDIO | Port 1: UART TX |
| 47 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 48 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 49 | VDDIO | AA7 Y6 | PMU_VDDIO PMU_VO_IO | Power | O | | | IO Reference |
| 50 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 51 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 52 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 53 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 54 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 55 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 56 | PMU_VBACKUP | W7 | PMU_VBACKUP | Power | I | | | Connect to backup battery or VBAT |
| 57 | PMU_VRTC | W5 | PMU_VRTC | Power | O | | | Use for PMU_SHUTDOWN and PMU_POWERBUTTON pull source |
| 58 | VBAT | U3 | PMU_VBAT_LDO | Power | I | | | Voltage from Battery |
| 59 | VBAT | V2 | PMU_VBAT_DCDC_V2 | Power | I | | | Voltage from Battery |
| 60 | VBAT | W1 | PMU_VBAT_DCDC_W1 | Power | I | | | Voltage from Battery |
| 61 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 62 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 63 | PMU_AT_OUT | N3 | PMU_AT_OUT | Analog | O | | PMU_VRTC | Anti-tamper output; connect to PMU_AT_IN or NC if not used |
| 64 | PMU_SHUTDOWN | M2 | PMU_SHUTDOWN | Analog | I | PU | PMU_VRTC | "Shutdown active low , Pull up with 620kΩ on to PMU_VRTC |
| 65 | PMU_EXT_ALARM | L3 | PMU_EXT_ALARM/ | Analog | O | | VDDIO | Debug monitoring only |
| 66 | PMU_POWER_BUTTON ON | K2 | PMU_POWER_BUTTON ON | Analog | I | PU | PMU_VRTC | Power button active low Pull up with 620kΩ onto PMU_VRTC |
| 67 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 68 | SIMRST | M8 | SC_RST/GPIO13 | Digital | O | PD | VDDIO | SIM Reset 1.8V |
| 69 | SIMCLK | L9 | SC_CLK/GPIO15 | Digital | O | PD | VDDIO | SIM Clock 1.8V |
| 70 | SIM_DETECT | J11 | SC_DET | Digital | I | PD | VDDIO | SIM Detection 1.8V |
| 71 | SC_SWP | J9 | SC_SWP | Digital | O | PD | VDDIO | Host Wake-Up (HI) |
| 72 | UART0_RTS | K8 | UART0_RTS | Digital | O | PU | VDDIO | <ul style="list-style-type: none"> • Default is UART0 Request to Send • Data host interface; UART RTS |
| 73 | UART0_TX | K10 | UART0_TX | Digital | O | PU | VDDIO | <ul style="list-style-type: none"> • Default is UART0 Transmit Data • Data host interface; UART TX |
| 74 | UART2_RTS | K6 | UART2_RTS | Digital | O | PU | VDDIO | Only use for internal test |
| 75 | UART0_RX | G11 | UART0_RX | Digital | I | PU | VDDIO | <ul style="list-style-type: none"> • Default is UART0 Clear to Send • Data host interface; UART |

| 1SC Pin# | Module Pin Name | ALT1250 Pin No | ALT1250 IC Symbol Pin Name | Type | Direction | Reset Value | IO Domain / Supply | Description |
|----------|-----------------|----------------|----------------------------|---------|-----------|-------------|--------------------|---|
| | | | | | | | | RX |
| 76 | UART0_CTS | G9 | UART0_CTS | Digital | I | PU | VDDIO | <ul style="list-style-type: none"> • Default is UART0 Clear to Send • Data host interface; UART CTS |
| 77 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 78 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 79 | GND | | | | | | | |
| 80 | GND | | | | | | | |
| 81 | GND | | | | | | | |
| 82 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 83 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 84 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 85 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 86 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 87 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 88 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 89 | GND | | | | | | | |
| 90 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 91 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 92 | GND | | | | | | | |
| 93 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 94 | UART1_CTS | V12 | UART1_CTS | Digital | I | PU | VDDIO | Port1 : UART CTS |
| 95 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 96 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 97 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 98 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 99 | GND | | | | | | | |
| 100 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 101 | GND | | | | | | | |
| 102 | PMU_VCAP | V6 | PMU_VCAP | Analog | O | | VBAT | Connecting external capacitor as backup for VBAT or NC if not used |
| 103 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 104 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 105 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 106 | NC | | N/A | N/A | N/A | N/A | N/A | Reserved (No Connection) |
| 107-115 | GND | | | | | | | |

3 RF Specification

3.1 Tx Output Power

The module is compliant to the 3GPP spec for release 13 and rated at a Class 3 device (23 dBm) for CATM1 and NB1.

3.2 Rx Sensitivity

Table 3.1 Rx Sensitivity

| Items | | Contents | | | |
|-----------------|----------------------------------|----------|------|------|------|
| | | Min | Typ. | Max | Unit |
| Frequency Range | LB | 699 | - | 960 | MHz |
| | MB | 1710 | - | 2170 | MHz |
| Rx Sensitivity | MCS5, BER<5% All OneSKU bands | - | -103 | - | dBm |

3.3 Power Consumption for CAT M1

Table 3.2 Power Consumption for CAT M1

| Mode | Current (TYP) | Condition |
|-----------------|---------------|---|
| Tx Power @23dBm | 400mA | CAT M1 |
| Rx | 90mA | RRC connected monitoring consecutive sub frames |
| PSM | 1.5uA | Hibernation period when module is asleep |
| eDRX | 45uA | eDRX, 8HF, 81.92s, PTW=1, excluding SIM |

3.4 Power Consumption for NB1 (for dual mode only)

Table 3.3 Power Consumption for NB1

| Mode | Current (TYP) | Condition |
|-----------------|---------------|---|
| Tx Power @23dBm | 800mA | Single Tone (3.75kHz) |
| Rx | 90mA | RRC connected monitoring consecutive sub frames |
| PSM | 1.5uA | Hibernation period when module is asleep |
| eDRX | 45uA | eDRX, 8HF, 81.92s, PTW=1, excluding SIM |

4 Environmental Specification

4.1 Absolute Maximum Rating

Table 4.1 Absolute Maximum Rating

| Parameters | | Min | Typ | Max | Unit |
|---------------------|-------------|------|-----|------|------|
| Storage Temperature | | -40 | - | +85 | degC |
| Supply Voltage | VBAT | -0.3 | - | 4.35 | V |
| | PMU_VBACKUP | -0.3 | - | 4.35 | V |
| | PMU_VCAP | -0.3 | - | 4.35 | V |
| | VBAT_FEM | -0.5 | - | 5.2 | V |

4.2 Recommended Operating Condition

Table 4.2 Recommended Operating Condition

| Parameters | | Min | Typ | Max | Unit |
|-----------------------|-------------|------|-----|------|------|
| Operating Temperature | | -40 | 25 | +85 | degC |
| Supply Voltage | VBAT | 2.2 | - | 4.35 | V |
| | PMU_VBACKUP | 2.2 | - | 4.35 | V |
| | PMU_VCAP | 2.2 | - | 4.35 | V |
| | VBAT_FEM | 2.85 | - | 4.5 | V |

4.3 Interface Voltage specifications

Table 4.3 Interface Voltage Condition

| Parameters | Min | Typ | Max | Unit |
|------------|-----|-----|-----|------|
| VDDIO | 1.7 | 1.8 | 1.9 | V |

For VDDIO, the total current from all IOs combined, and supplied by PMU_VDDIO, should not exceed 50mA.

4.4 Digital I/O Pin's specifications

Table 4.4 Digital IO Pin's Specifications

| Parameters | | Min | typ | Max | Unit |
|-------------------|------------|-----------|-----|-----------|------|
| Input Voltage | High-level | 0.7*VDDIO | - | VDDIO | V |
| | Low-level | VSS | - | 0.3*VDDIO | V |
| Output Voltage | High-level | 0.8*VDDIO | - | - | V |
| | Low-level | - | - | 0.2*VDDIO | V |
| IO Drive Strength | | 2 | - | 12 | mA |

(*)The total current from all IOs combined should not exceed 50mA

Table 4.5 Digital IO Absolute Maximum Rating

| | Min | typ | Max | Unit |
|----------------------|------|-----|-------------|------|
| All digital 1.8V IOs | -0.2 | - | VDDIO + 0.2 | V |

4.5 Analog I/O Pin's specifications

Table 4.6 Analog IO Pin's specifications

| Parameters | | Min | typ | Max | Unit |
|------------------|------------|-----|-----|-----|------|
| PMU_WAKEUP | Low-level | - | - | 0.3 | V |
| | High-level | 1.2 | - | - | V |
| PMU_POWER_BUTTON | Low-level | - | - | 0.3 | V |
| | High-level | 1 | - | - | V |
| PMU_SHUTDOWN | Low-level | - | - | 0.3 | V |
| | High-level | 1.3 | - | - | V |

Table 4.7 Analog IO Absolute Maximum Rating

| | Min | typ | Max | Unit |
|---------------------|------|-----|-------------|------|
| All Analog 1.8V IOs | -0.2 | - | VDDIO + 0.2 | V |

5 POWER SEQUENCE

5.1 Power Sequence for power up




Figure 5.1 Power Sequence Diagram – Power Up

5.2 Power Sequence for power down




Figure 5.2 Power Sequence Diagram – Power Up

5.3 Power Sequence for reset




Figure 5.3 Power Sequence Diagram – Power Up

6 UART Interface

Table 6.1 UART Interface

| Parameters | Setting |
|--------------------|------------|
| Serial wires | Tx and Rx |
| Baud rate | 115200 bps |
| Data bit | 8bit |
| Start bit | 1bit |
| Stop bit | 1bit |
| Flow control | None |
| Parity bit | None |
| Transmission Order | LSB first |

7 Host PCB Landing Pattern (Top View)




Figure 7.1 Recommended PCB Landing Pattern

8 Reference Circuit

Please refer to "Reference Circuit_Type1SC"

9 Assembly Information

Refer to Figure 9.1 for recommended soldering conditions.

Soldering must be done by this method to prevent products from damage. Set up the highest temperature of reflow within 260 °C. If considering other soldering conditions, you must contact Murata before proceeding.

Reflow soldering standard conditions




Figure 9.1 Reflow Profile


Please don't use the reflow method more than twice.

Use rosin type flux or a weakly active flux with a chlorine content of 0.2 wt % or less.

Since this Product is Moisture Sensitive, any cleaning with liquid is NOT permitted.

10 Packaging and Marking Information

10.1 Dimensions of Tape (Plastic tape)



- 1) The corner and ridge radiuses (R) of inside cavity are 0.3mm max.
- 2) Cumulative tolerance of 10 pitches of the sprocket hole is ± 0.2 mm
- 3) Measuring of cavity positioning is based on cavity center in accordance with JIS/IES standard.

Figure 10.1 Tape Dimensions (Unit: mm)

10.2 Dimensions of Reel




Figure 10.2 Reel Dimensions (Unit: mm)

10.3 Taping Diagrams

- [1] Feeding Hole : As specified in (1)
- [2] Hole for chip : As specified in (1)
- [3] Cover tape : 62μm in thickness
- [4] Base tape : As specified in (1)




Figure 10.3 Tape Diagram

10.4 Module Marking Information

Figures below show the module marking. Dimensions are nominal, not absolute.




Figure 10.4 Type 1SC DM Module Marking Diagram

10.5 Moisture Sensitivity Level

The module is rated to MSL 4 (72 hours). Please observe this rating with the utmost importance. For storage condition detail, please refer to 14.1 Storage Conditions.

11 Regulatory Information

The table below shows the regulatory compliance status of the Type 1SC module.

Table 11.1 Regulatory Standards Conformance for 1SC single mode

| Regulatory Body | Country | Certificate ID for Cat M1/NB1 |
|------------------------|------------------------|--------------------------------------|
| FCC | US | HSW-TY1SCDM |
| IC | Canada | 4492A-TY1SCDM |
| ETSI | EU | Compliant |
| TELEC | Japan | 003-180242 |
| RCM/ACMA | Australia, New Zealand | 1102MUR_LBAD0_S042-1 |
| RRA/KC | Korea | R-C-VPY-Type1SC |
| NCC | Taiwan | CCAM20NB0010T3 |
| GCF | Global | Compliant |
| PTCRB | Global | Compliant |

For the details; Please refer to Type1SC Hardware Design Guidelines.

12 RoHS Information

The Type 1SC module conforms to RoHS requirements.

13 Ordering Information

| Product | Model Name | Murata Ordering Part Number |
|-----------------|-------------|-----------------------------|
| Module Sample | Type 1SC | LBAD0XX1SC-151 |
| Development Kit | Type 1SC DK | LBAD0XX1SC-DM-EVK-TEMP |

14 Notice

14.1 Storage Conditions

Please use this product within 6 months after receipt.

- The product shall be stored in original package under with an ambient temperature from 5 to 35°C, and humidity from 20% to 70%RH. (Packing materials, in particular, may become deformed if the temperature exceeds 40°C.)
- If the product is not used for more than 6 months after receipt, confirm the solderability before use.
- Store the product in non-corrosive gas (Cl₂, NH₃, SO₂, NO_x, etc.).
- Avoid mechanical shock, such as dropping or puncturing the product, to preserve integrity of the packing materials.
- After the package is opened, store it at <30°C / <60%RH and use the product within **72** hours.
- If the color of the indicator in the packing changes, bake the product before soldering.

Baking condition: 125 +5/-0 °C, 24hours, 1 time

Bake the product on a heat-resistant tray because other materials (Base Tape, Reel Tape and Cover Tape) are not heat-resistant.

14.2 Handling Conditions

Be careful in handling or transporting products because excessive stress or mechanical shock may break products.

Handle products with care to avoid cracks or damages on the terminals, causing unwarranted changes in the product characteristics. Do not touch products with bare hands to avoid degrading solder ability or damage caused by static electrical charge.

14.3 Standard PCB Design (Land Pattern and Dimensions)

All the ground terminals should be connected to the ground patterns. Furthermore, the ground pattern should be provided between IN and OUT terminals. Please refer to the specifications for the standard land dimensions.

The recommended land pattern and dimensions is in accordance with Murata's standard. The characteristics of products may vary depending on the pattern drawing method, grounding method, land dimensions, land forming method of the NC terminals and the PCB material and thickness. Therefore, be sure to verify the characteristics in the actual set. If using non-standard lands, contact Murata beforehand.

14.4 Notice for Chip Placer

When positioning products on the PCB, be aware that mechanical chucking may damage products. When placing products on the PCB, a worn-out chucking locating claw or a suction nozzle can cause undue stress and uneven force, resulting in damaged products. To prevent products from damage, be sure to follow the specifications for the maintenance of the chip placer in use.

14.5 Operational Environment Conditions

Products are designed to work under normal environmental conditions (ambient temperature, humidity and pressure) as stated above. However, if products are used under the following circumstances, they may be damaged, resulting in leakage of electricity and abnormal temperatures.

- In an atmosphere containing corrosive gas (Cl₂, NH₃, SO_x, NO_x, etc.).
- In an atmosphere containing combustible and volatile gases.
- Dusty environment.
- Direct sunlight.
- Excessive moisture.
- Excessive humidity where water condenses.
- Extreme cold, such as in freezing temperatures.

If products could be exposed to those conditions described above, consult with Murata before actual use.

Static electricity may degrade or destroy products. Avoid static electricity or excessive voltage while assembling and measuring.

14.6 Input Power Capacity

Avoid exceeding the input power capacity as specified in this document.

If operating conditions may exceed parameters as stated in this document, inform Murata before use.

15 PRECONDITIONS TO USE MURATA PRODUCTS

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product when our product is mounted to your product.

All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the products is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The product shall not be used in any application listed below which requires especially high reliability for the prevention of such defect as may directly cause damage to the third party's life, body or property. You acknowledge and agree that, if you use our products in such applications, we will not be responsible for any failure to meet such requirements. Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN SUCH APPLICATIONS.

- Aircraft equipment.
- Aerospace equipment
- Undersea equipment.
- Power plant control equipment
- Medical equipment.
- Transportation equipment (vehicles, trains, ships, elevator, etc.).
- Traffic signal equipment.
- Disaster prevention / crime prevention equipment.
- Burning / explosion control equipment
- Application of similar complexity and/ or reliability requirements to the applications listed in the above.

We expressly prohibit you from analyzing, breaking, reverse-engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use.

Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc. Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

By signing on specification sheet or approval sheet, you acknowledge that you are the legal representative for your company and that you understand and accept the validity of the contents herein. When you are not able to return the signed version of specification sheet or approval sheet within 30 days from receiving date of specification sheet or approval sheet, it shall be deemed to be your consent on the content of specification sheet or approval sheet. Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status. We reject any liability or product warranty for engineering samples. In particular we disclaim liability for damages caused by

- the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the product to be sold by you,
- deviation or lapse in function of engineering sample,
- improper use of engineering samples.

We disclaim any liability for consequential and incidental damages.

If you can't agree the above contents, you should inquire our sales.