



# Product Manual

## **Barracuda 7200.10 Serial ATA**

- |             |             |
|-------------|-------------|
| ST3750640AS | ST3300620AS |
| ST3750840AS | ST3300820AS |
| ST3500630AS | ST3250620AS |
| ST3500830AS | ST3250820AS |
| ST3400620AS | ST3200820AS |
| ST3400820AS |             |
| ST3320620AS |             |
| ST3320820AS |             |







# Product Manual

## **Barracuda 7200.10 Serial ATA**

- ST3750640AS
- ST3750840AS
- ST3500630AS
- ST3500830AS
- ST3400620AS
- ST3400820AS
- ST3320620AS
- ST3320820AS
- ST3300620AS
- ST3300820AS
- ST3250620AS
- ST3250820AS
- ST3200820AS



©2006, Seagate Technology LLC All rights reserved

Publication number: 100402371, Rev. A

May 2006

Seagate, Seagate Technology, and the Seagate logo are registered trademarks of Seagate Technology LLC. SeaTools, SeaFONE, SeaBOARD, and SeaTDD are either registered trademarks or trademarks of Seagate Technology LLC. Other product names are registered trademarks or trademarks of their owners.

Seagate reserves the right to change, without notice, product offerings or specifications. No part of this publication may be reproduced in any form without written permission of Seagate Technology LLC.





# Contents

|            |   |           |
|------------|---|-----------|
| <b>1.0</b> | <b>Introduction</b>                                       | <b>1</b>  |
| 1.1        | About the Serial ATA interface                            | 2         |
| <b>2.0</b> | <b>Drive specifications</b>                               | <b>3</b>  |
| 2.1        | Specification summary tables                              | 3         |
| 2.2        | Formatted capacity  | 18        |
| 2.2.1      | LBA mode  | 18        |
| 2.3        | Default logical geometry                                  | 18        |
| 2.4        | Recording and interface technology                        | 19        |
| 2.5        | Physical characteristics                                  | 19        |
| 2.6        | Seek time   | 20        |
| 2.7        | Start/stop times  | 20        |
| 2.8        | Power specifications                                      | 20        |
| 2.8.1      | Power consumption   | 20        |
| 2.8.2      | Conducted noise   | 22        |
| 2.8.3      | Voltage tolerance   | 22        |
| 2.8.4      | Power-management modes                                    | 22        |
| 2.9        | Environmental specifications                              | 24        |
| 2.9.1      | Ambient temperature                                       | 24        |
| 2.9.2      | Temperature gradient                                      | 24        |
| 2.9.3      | Humidity  | 24        |
| 2.9.4      | Altitude  | 24        |
| 2.9.5      | Shock   | 24        |
| 2.9.6      | Vibration   | 25        |
| 2.10       | Acoustics   | 26        |
| 2.11       | Electromagnetic immunity                                  | 26        |
| 2.12       | Reliability   | 27        |
| 2.13       | Agency certification                                      | 27        |
| 2.13.1     | Safety certification                                      | 27        |
| 2.13.2     | Electromagnetic compatibility                             | 27        |
| 2.13.3     | FCC verification  | 28        |
| 2.14       | Environmental protection                                  | 28        |
| 2.14.1     | European Union Restriction of Hazardous Substances (RoHS) | 28        |
| 2.15       | Corrosive environment                                     | 29        |
| <b>3.0</b> | <b>Configuring and mounting the drive</b>                 | <b>31</b> |
| 3.1        | Handling and static-discharge precautions                 | 31        |
| 3.2        | Configuring the drive                                     | 32        |
| 3.3        | Serial ATA cables and connectors                          | 32        |
| 3.4        | Drive mounting  | 33        |
| <b>4.0</b> | <b>Serial ATA (SATA) interface</b>                        | <b>35</b> |
| 4.1        | Hot-Plug compatibility                                    | 35        |
| 4.2        | Serial ATA device plug connector pin definitions          | 36        |
| 4.3        | Supported ATA commands                                    | 37        |
| 4.3.1      | Identify Device command                                   | 39        |
| 4.3.2      | Set Features command                                      | 43        |
| 4.3.3      | S.M.A.R.T. commands                                       | 44        |
| <b>5.0</b> | <b>Seagate Technology support services</b>                | <b>45</b> |





## List of Figures

|           |   |    |
|-----------|---|----|
| Figure 1. | Typical 5V startup and operation current profile . . . . .  | 21 |
| Figure 2. | Typical 12V startup and operation current profile . . . . . | 22 |
| Figure 3. | Serial ATA connectors . . . . .                             | 32 |
| Figure 4. | Attaching SATA cabling . . . . .                            | 32 |
| Figure 5. | Mounting dimensions—top, side and end view . . . . .        | 33 |



## 1.0 Introduction

---

This manual describes the functional, mechanical and interface specifications for the following Seagate Barracuda® 7200.10 Serial ATA model drives:

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ST3750640AS | ST3400620AS | ST3300620AS | ST3200820AS |
| ST3750840AS | ST3400820AS | ST3300820AS |             |
| ST3500630AS | ST3320620AS | ST3250620AS |             |
| ST3500830AS | ST3320820AS | ST3250820AS |             |

These drives provide the following key features:

- 7,200 RPM spindle speed.
- High instantaneous (burst) data-transfer rates (up to 150 Mbytes per second).
- Tunneling Giant Magnetoresistive (TGMR) recording heads and EPRML technology, provide the drives with increased areal density.
- State-of-the-art cache and on-the-fly error-correction algorithms.
- Native Command Queuing with command ordering to increase performance in demanding applications.
- Full-track multiple-sector transfer capability without local processor intervention.
- Quiet operation.
- SeaTools diagnostic software performs a drive self-test that eliminates unnecessary drive returns.
- Support for S.M.A.R.T. drive monitoring and reporting.
- Supports latching SATA cables and connectors.

## 1.1 About the Serial ATA interface

The Serial ATA interface provides several advantages over the traditional (parallel) ATA interface. The primary advantages include:

- Easy installation and configuration with true plug-and-play connectivity. It is not necessary to set any jumpers or other configuration options.
- Thinner and more flexible cabling for improved enclosure airflow and ease of installation.
- Scalability to higher performance levels.

In addition, Serial ATA makes the transition from parallel ATA easy by providing legacy software support. Serial ATA was designed to allow you to install a Serial ATA host adapter and Serial ATA disc drive in your current system and expect all of your existing applications to work as normal.

The Serial ATA interface connects each disc drive in a point-to-point configuration with the Serial ATA host adapter. There is no master/slave relationship with Serial ATA devices like there is with parallel ATA. If two drives are attached on one Serial ATA host adapter, the host operating system views the two devices as if they were both “masters” on two separate ports. This essentially means both drives behave as if they are Device 0 (master) devices.

**Note.** The host adapter may, optionally, emulate a master/slave environment to host software where two devices on separate Serial ATA ports are represented to host software as a Device 0 (master) and Device 1 (slave) accessed at the same set of host bus addresses. A host adapter that emulates a master/slave environment manages two sets of shadow registers. This is not a typical Serial ATA environment.

The Serial ATA host adapter and drive share the function of emulating parallel ATA device behavior to provide backward compatibility with existing host systems and software. The Command and Control Block registers, PIO and DMA data transfers, resets, and interrupts are all emulated.

The Serial ATA host adapter contains a set of registers that shadow the contents of the traditional device registers, referred to as the Shadow Register Block. All Serial ATA devices behave like Device 0 devices. For additional information about how Serial ATA emulates parallel ATA, refer to the “Serial ATA: High Speed Serialized AT Attachment” specification. The specification can be downloaded from [www.serialata.org](http://www.serialata.org).

## 2.0 Drive specifications

---

Unless otherwise noted, all specifications are measured under ambient conditions, at 25°C, and nominal power. For convenience, the phrases *the drive* and *this drive* are used throughout this manual to indicate the following drive models:

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ST3750640AS | ST3400620AS | ST3300620AS | ST3200820AS |
| ST3750840AS | ST3400820AS | ST3300820AS |             |
| ST3500630AS | ST3320620AS | ST3250620AS |             |
| ST3500830AS | ST3320820AS | ST3250820AS |             |

### 2.1 Specification summary tables

The specifications listed in the following table are for quick reference. For details on specification measurement or definition, see the appropriate section of this manual.

**Table 1: Drive specifications summary for 750 Gbyte models**

| Drive specification                                   | ST3750640AS   | ST3750840AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 750   |             |
| Guaranteed sectors                                    | 1,465,149,168   |             |
| Heads   | 8   | 8           |
| Discs   | 4   | 4           |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 926   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 128.2   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 78  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 720 grams   |             |
| Average latency                                       | 4.16 msec   |             |
| Power-on to ready (sec max)                           | 15 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 read; <1.0 write   |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 300 Gs  |             |

| Drive specification                                    | ST3750640AS  | ST3750840AS |
|--|--|-------------|
| Vibration, operating                                   | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                                | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                    |  |             |
| Idle**   | 2.7 (typical)<br>3.0 (max)   |             |
| Performance seek                                       | 3.0 (typical)<br>3.4 (max)   |             |
| Nonrecoverable read errors                             | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                          | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the “Verify Your Warranty” link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles<br>(25°C, 50% rel. humidity) | 50,000   |             |
| Supports Hotplug operation per SATA II specification   | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 2: Drive specifications summary for 500 Gbyte models**

| Drive specification                                   | ST3500630AS   | ST3500830AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 500   |             |
| Guaranteed sectors                                    | 976,773,168   |             |
| Heads   | 6   |             |
| Discs   | 3   |             |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 813   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 114.4   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 635 grams   |             |
| Average latency (msec)                                | 4.16  |             |
| Power-on to ready (sec max)                           | 15 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 300 Gs  |             |



| Drive specification                                    | ST3500630AS  | ST3500830AS |
|--|--|-------------|
| Vibration, operating                                   | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                                | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                    |  |             |
| Idle**   | 2.7 (typical)<br>3.0 (max)   |             |
| Performance seek                                       | 3.0 (typical)<br>3.4 (max)   |             |
| Nonrecoverable read errors                             | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                          | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the "Verify Your Warranty" link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles<br>(25°C, 50% rel. humidity) | 50,000   |             |
| Supports Hotplug operation per SATA II specification   | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 3: Drive specifications summary for 400 Gbyte models**

| Drive specification                                   | ST3400620AS   | ST3400820AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 400   |             |
| Guaranteed sectors                                    | 781,422,768   |             |
| Heads   | 5   |             |
| Doscs   | 3   |             |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 781   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 128.2   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 635 grams   |             |
| Average latency (msec)                                | 4.16  |             |
| Power-on to ready (sec max)                           | 15 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 300 Gs  |             |

| Drive specification                                    | ST3400620AS  | ST3400820AS |
|--|--|-------------|
| Vibration, operating                                   | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                                | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                    |  |             |
| Idle**   | 2.8 (typical)<br>3.0 (max)   |             |
| Performance seek                                       | 3.2 (typical)<br>3.4 (max)   |             |
| Nonrecoverable read errors                             | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                          | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the “Verify Your Warranty” link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles<br>(25°C, 50% rel. humidity) | 50,000   |             |
| Supports Hotplug operation per SATA II specification   | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 4: Drive specifications summary for 320 Gbyte models**

| Drive specification                                   | ST3320620AS   | ST3320820AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 320   |             |
| Guaranteed sectors                                    | 625,142,448   |             |
| Heads   | 4   |             |
| Discs   | 2   |             |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 781   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 114.4   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 635 grams   |             |
| Average latency (msec)                                | 4.16  |             |
| Power-on to ready (sec max)                           | 15 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 350 Gs  |             |

| Drive specification                                  | ST3320620AS  | ST3320820AS |
|--|--|-------------|
| Vibration, operating                                 | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                              | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                  |  |             |
| Idle**   | 2.8 (typical)<br>3.0 (max)   |             |
| Performance seek                                     | 3.2 (typical)<br>3.4 (max)   |             |
| Nonrecoverable read errors                           | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                        | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the "Verify Your Warranty" link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles (25°C, 50% rel. humidity)  | 50,000   |             |
| Supports Hotplug operation per SATA II specification | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 5: Drive specifications summary for 300 Gbyte models**

| Drive specification                                   | ST3300620AS   | ST3300820AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 300   |             |
| Guaranteed sectors                                    | 586,072,368   |             |
| Heads   | 3   |             |
| Discs   | 2   |             |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 781   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 114.4   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 580 grams (1.28 lb.)  |             |
| Average latency (msec)                                | 4.16  |             |
| Power-on to ready (sec max)                           | 11 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 350 Gs  |             |

| Drive specification                                  | ST3300620AS  | ST3300820AS |
|--|--|-------------|
| Vibration, operating                                 | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                              | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                  |  |             |
| Idle**   | 2.5 (typical)<br>2.8 (max)   |             |
| Performance seek                                     | 3.0 (typical)<br>3.1 (max)   |             |
| Nonrecoverable read errors                           | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                        | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the “Verify Your Warranty” link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles (25°C, 50% rel. humidity)  | 50,000   |             |
| Supports Hotplug operation per SATA II specification | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 6: Drive specifications summary for 250 Gbyte models**

| Drive specification                                   | ST3250620AS   | ST3250820AS |
|---|---|-------------|
| Formatted Gbytes (512 bytes/sector)*                  | 250   |             |
| Guaranteed sectors                                    | 488,397,168   |             |
| Heads   | 3   |             |
| Discs   | 2   |             |
| Bytes per sector                                      | 512   |             |
| Default sectors per track                             | 63  |             |
| Default read/write heads                              | 16  |             |
| Default cylinders                                     | 16,383  |             |
| Recording density, KBPI (kbits/in max)                | 813   |             |
| Track density, KTPI (ktracks/in avg.)                 | 145   |             |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 114.4   |             |
| Spindle speed (RPM)                                   | 7,200   |             |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |             |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |             |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |             |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |             |
| Cache buffer  | 16 Mbytes   | 8 Mbytes    |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |             |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |             |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |             |
| Weight (max)  | 580 grams (1.28 lb.)  |             |
| Average latency (msec)                                | 4.16  |             |
| Power-on to ready (sec max)                           | 11 sec  |             |
| Standby to ready (sec max)                            | 15 sec  |             |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |             |
| Average seek, read (msec typical)                     | <8.5  |             |
| Average seek, write (msec typical)                    | <10.0   |             |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |             |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |             |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |             |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |             |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |             |
| Relative humidity gradient                            | 30% per hour max  |             |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |             |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |             |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |             |
| Operational Shock (max at 2 msec)                     | 68 Gs   |             |
| Non-Operational Shock (max at 2 msec)                 | 350 Gs  |             |



| Drive specification                                  | ST3250620AS  | ST3250820AS |
|--|--|-------------|
| Vibration, operating                                 | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.50 Gs<br>350–500 Hz:: 0.25 Gs   |             |
| Vibration, nonoperating                              | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |             |
| Drive acoustics, sound power (bels)                  |  |             |
| Idle**   | 2.5 (typical)<br>2.8 (max)   |             |
| Performance seek                                     | 3.0 (typical)<br>3.1 (max)   |             |
| Nonrecoverable read errors                           | 1 per 10 <sup>14</sup> bits read   |             |
| Annualized Failure Rate (AFR)                        | 0.34%  |             |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the “Verify Your Warranty” link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |             |
| Contact start-stop cycles (25°C, 50% rel. humidity)  | 50,000   |             |
| Supports Hotplug operation per SATA II specification | Yes  |             |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

**Table 7: Drive specifications summary for 200 Gbyte models**

| Drive specification                                   | ST3200820AS   |
|---|---|
| Formatted Gbytes (512 bytes/sector)*                  | 80  |
| Guaranteed sectors                                    | 390,721,968   |
| Heads   | 3   |
| Discs   | 2   |
| Bytes per sector                                      | 512   |
| Default sectors per track                             | 63  |
| Default read/write heads                              | 16  |
| Default cylinders                                     | 16,383  |
| Recording density, KBPI (kbits/in max)                | 813   |
| Track density, KTPI (ktracks/in avg.)                 | 145   |
| Areal density, (Gbits/in <sup>2</sup> avg)            | 114.4   |
| Spindle speed (RPM)                                   | 7,200   |
| Internal data transfer rate (Mbits/sec max)           | 1,030   |
| Sustained data transfer rate OD (Mbytes/sec max)      | 72  |
| I/O data-transfer rate (Mbytes/sec max)               | 300   |
| ATA data-transfer modes supported                     | PIO modes 0–4<br>Multiword DMA modes 0–2<br>Ultra DMA modes 0–6 |
| Cache buffer  | 8 Mbytes  |
| Height (mm max)                                       | 26.1 mm (1.028 inches)  |
| Width (mm max)  | 101.6 mm (4.000 inches) +/- 0.010 inches                        |
| Length (mm max)                                       | 146.99 mm (5.787 inches)  |
| Weight (max)  | 580 grams (1.28 lb.)  |
| Average latency (msec)                                | 4.16  |
| Power-on to ready (sec max)                           | 11 sec  |
| Standby to ready (sec max)                            | 15 sec  |
| Track-to-track seek time (msec typical)               | <0.8 (read), <1.0 (write)                                       |
| Average seek, read (msec typical)                     | <8.5  |
| Average seek, write (msec typical)                    | <10.0   |
| Startup current (typical) 12V (peak)                  | 2.8 amps  |
| Voltage tolerance (including noise)                   | 5V ± 5%<br>12V ± 10%  |
| Ambient temperature                                   | 0° to 60°C (operating)<br>–40° to 70°C (nonoperating)           |
| Temperature gradient (°C per hour max)                | 20°C (operating)<br>30°C (nonoperating)                         |
| Relative humidity                                     | 5% to 90% (operating)<br>5% to 95% (nonoperating)               |
| Relative humidity gradient                            | 30% per hour max  |
| Wet bulb temperature (°C max)                         | 37.7 (operating)<br>37.7 (nonoperating)                         |
| Altitude, operating                                   | –60.96 m to 3,048 m<br>(–200 ft. to 10,000+ ft.)                |
| Altitude, nonoperating<br>(below mean sea level, max) | –60.96 m to 12,192 m<br>(–200 ft. to 40,000+ ft.)               |
| Operational Shock (max at 2 msec)                     | 68 Gs   |
| Non-Operational Shock (max at 2 msec)                 | 350 Gs  |

| <b>Drive specification</b>                             | <b>ST3200820AS</b>   |
|--|--|
| Vibration, operating                                   | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 0.5 Gs<br>350–500 Hz:: 0.25 Gs  |
| Vibration, nonoperating                                | 5–22 Hz: 0.25 Gs, Limited displacement<br>22–350 Hz: 5.0 Gs<br>350–500 Hz:: 1.0 Gs   |
| Drive acoustics, sound power (bels)                    |  |
| Idle**   | 2.5 (typical)<br>2.8 (max)   |
| Performance seek                                       | 3.0 (typical)<br>3.1 (max)   |
| Nonrecoverable read errors                             | 1 per 10 <sup>14</sup> bits read   |
| Annualized Failure Rate (AFR)                          | 0.34%  |
| Warranty   | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the “Verify Your Warranty” link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |
| Contact start-stop cycles<br>(25°C, 50% rel. humidity) | 50,000   |
| Supports Hotplug operation per SATA II specification   | Yes  |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

\*\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

## 2.2 Formatted capacity

| Model       | Formatted capacity* | Guaranteed sectors | Bytes per sector |
|-------------|---------------------|--------------------|------------------|
| ST3750640AS | 750 Gbytes          | 1,465,149,168      | 512              |
| ST3750840AS | 750 Gbytes          | 1,465,149,168      | 512              |
| ST3500630AS | 500 Gbytes          | 976,773,168        | 512              |
| ST3500830AS | 500 Gbytes          | 976,773,168        | 512              |
| ST3400620AS | 400 Gbytes          | 781,422,768        | 512              |
| ST3400820AS | 400 Gbytes          | 781,422,768        | 512              |
| ST3320620AS | 320 Gbytes          | 625,142,448        | 512              |
| ST3320820AS | 320 Gbytes          | 625,142,448        | 512              |
| ST3300620AS | 300 Gbytes          | 586,072,368        | 512              |
| ST3300820AS | 300 Gbytes          | 586,072,368        | 512              |
| ST3250620AS | 250 Gbytes          | 488,397,168        | 512              |
| ST3250820AS | 250 Gbytes          | 488,397,168        | 512              |
| ST3200820AS | 200 Gbytes          | 390,721,968        | 512              |

\*One Gbyte equals one billion bytes when referring to hard drive capacity. Accessible capacity may vary depending on operating environment and formatting.

### 2.2.1 LBA mode

When addressing these drives in LBA mode, all blocks (sectors) are consecutively numbered from 0 to  $n-1$ , where  $n$  is the number of guaranteed sectors as defined above.

See Section 4.3.1, "Identify Device command" (words 60-61 and 100-103) for additional information about 48-bit addressing support of drives with capacities over 137 Gbytes.

## 2.3 Default logical geometry

| Cylinders | Read/write heads | Sectors per track |
|-----------|------------------|-------------------|
| 16,383    | 16               | 63                |

### LBA mode

When addressing these drives in LBA mode, all blocks (sectors) are consecutively numbered from 0 to  $n-1$ , where  $n$  is the number of guaranteed sectors as defined above.

## 2.4 Recording and interface technology

|   | 750GB                  | 500GB | 400GB | 320GB | 300GB | 250GB | 200GB |
|---|------------------------|-------|-------|-------|-------|-------|-------|
| Interface                                     | Serial ATA (SATA)      |       |       |       |       |       |       |
| Recording method                              | Perpendicular          |       |       |       |       |       |       |
| Recording density, KBPI (kbits/inch max)      | 926                    | 813   | 781   |       |       | 813   |       |
| Track density, KTPI (ktracks/inch avg)        | 145                    |       |       |       |       |       |       |
| Areal density (Gbits/inch <sup>2</sup> avg)   | 128.2                  | 114.4 |       |       |       |       |       |
| Spindle speed (RPM) (± 0.2%)                  | 7,200                  |       |       |       |       |       |       |
| Internal data transfer rate (Mbits/sec max)   | 1,030                  |       |       |       |       |       |       |
| Sustained data transfer rate (Mbytes/sec max) | 78                     | 72    |       |       |       |       |       |
| I/O data-transfer rate (Mbytes/sec max)       | 300 (Ultra DMA mode 5) |       |       |       |       |       |       |

## 2.5 Physical characteristics

|   |                                   |
|---|-----------------------------------|
| Maximum height  | 26.1 mm (1.028 inches)            |
| Maximum width   | 101.6 mm (4.000 +/- 0.010 inches) |
| Maximum length  | 146.99 mm (5.787 inches)          |
| Max weight  |                                   |
| ST3750640AS and ST3750840AS   | 720 grams (1.59 lbs)              |
| ST3500630AS and ST3500830AS   | 635 grams (1.4 lbs)               |
| ST3400620AS and ST3400820AS   | 635 grams (1.4 lbs)               |
| ST3320620AS and ST3320820AS   | 635 grams (1.4 lbs)               |
| ST3300620AS and ST3300820AS   | 580 grams (1.28 lbs)              |
| ST3250620AS, ST3250820AS and ST3200820AS  | 580 grams (1.28 lbs)              |
| Cache buffer  |                                   |
| ST3750640AS<br>ST3500630AS<br>ST3400620AS<br>ST3320620AS<br>ST3300620AS<br>ST3250620AS                | 16 Mbytes (16,384 kbytes)         |
| ST3750840AS<br>ST3500830AS<br>ST3400820AS<br>ST3320820AS<br>ST3300820AS<br>ST3250820AS<br>ST3200820AS | 8 Mbytes (8,192 kbytes)           |

## 2.6 Seek time

Seek measurements are taken with nominal power at 25°C ambient temperature. All times are measured using drive diagnostics. The specifications in the table below are defined as follows:

- Track-to-track seek time is an average of all possible single-track seeks in both directions.
- Average seek time is a true statistical random average of at least 5,000 measurements of seeks between random tracks, less overhead.

| *Typical seek times (msec) | Read | Write |
|----------------------------|------|-------|
| Track-to-track             | <0.8 | <1.0  |
| Average                    | <8.5 | <10.0 |
| Average latency:           | 4.16 | 4.16  |

\*Measured in performance mode.

**Note.** These drives are designed to consistently meet the seek times represented in this manual. Physical seeks, regardless of mode (such as track-to-track and average), are expected to meet the noted values. However, due to the manner in which these drives are formatted, benchmark tests that include command overhead or measure logical seeks may produce results that vary from these specifications.

## 2.7 Start/stop times

|                             |          |
|-----------------------------|----------|
| Power-on to Ready (sec)     | 15 (max) |
| Standby to Ready (sec)      | 15 (max) |
| Ready to spindle stop (sec) | 10 (max) |

## 2.8 Power specifications

The drive receives DC power (+5V or +12V) through a native SATA power connector. See Figure 4 on page 32.

### 2.8.1 Power consumption

Power requirements for the drives are listed in the table on page 9. Typical power measurements are based on an average of drives tested, under nominal conditions, using 5.0V and 12.0V input voltage at 25°C ambient temperature.

- **Spinup power**

Spinup power is measured from the time of power-on to the time that the drive spindle reaches operating speed.

- **Seek mode**

During seek mode, the read/write actuator arm moves toward a specific position on the disc surface and does not execute a read or write operation. Servo electronics are active. Seek mode power represents the worst-case power consumption, using only random seeks with read or write latency time. This mode is not typical and is provided for worst-case information.

- **Read/write power and current**

Read/write power is measured with the heads on track, based on a 16-sector write followed by a 32-msec delay, then a 16-sector read followed by a 32-msec delay.

- **Operating power and current**

Operating power is measured using 40 percent random seeks, 40 percent read/write mode (1 write for each 10 reads) and 20 percent drive idle mode.

- **Idle mode power**

Idle mode power is measured with the drive up to speed, with servo electronics active and with the heads in a random track location.

- **Standby mode**


During Standby mode, the drive accepts commands, but the drive is not spinning, and the servo and read/write electronics are in power-down mode.

**Table 8: DC power requirements**


| Power dissipation (4-disc values shown)  | Avg (watts 25° C) | Avg 5V typ amps | Avg 12V typ amps |
|--|-------------------|-----------------|------------------|
| Spinup                                   | —                 | —               | 2.80 (peak)      |
| Idle*                                    | 9.30              | 0.611           | 0.520            |
| Idle* (with offline activity)            | 10.40             | 0.719           | 0.567            |
| Operating (40% r/w, 40% seek, 20% inop.) | 13.00             | 0.772           | 0.762            |
| Seeking (random, 20% idle)               | 12.60             | 0.613           | 0.795            |
| Standby                                  | 0.80              | 0.106           | 0.023            |
| Sleep                                    | 0.80              | 0.106           | 0.023            |

\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

### 2.8.1.1 Typical current profiles



**Figure 1. Typical 5V startup and operation current profile**



**Figure 2. Typical 12V startup and operation current profile**

### 2.8.2 Conducted noise

Input noise ripple is measured at the host system power supply across an equivalent 80-ohm resistive load on the +12 volt line or an equivalent 15-ohm resistive load on the +5 volt line.

- Using 12-volt power, the drive is expected to operate with a maximum of 120 mV peak-to-peak square-wave injected noise at up to 10 MHz.
- Using 5-volt power, the drive is expected to operate with a maximum of 100 mV peak-to-peak square-wave injected noise at up to 10 MHz.

**Note.** Equivalent resistance is calculated by dividing the nominal voltage by the typical RMS read/write current.

### 2.8.3 Voltage tolerance

Voltage tolerance (including noise):

- 5V  $\pm$  5%
- 12V  $\pm$  10%

### 2.8.4 Power-management modes

The drive provides programmable power management to provide greater energy efficiency. In most systems, you can control power management through the system setup program. The drive features the following power-management modes:

| Power modes | Heads    | Spindle  | Buffer   |
|-------------|----------|----------|----------|
| Active      | Tracking | Rotating | Enabled  |
| Idle        | Tracking | Rotating | Enabled  |
| Standby     | Parked   | Stopped  | Enabled  |
| Sleep       | Parked   | Stopped  | Disabled |

- **Active mode**

The drive is in Active mode during the read/write and seek operations.



- **Idle mode**

The buffer remains enabled, and the drive accepts all commands and returns to Active mode any time disc access is necessary.

- **Standby mode**

The drive enters Standby mode when the host sends a Standby Immediate command. If the host has set the standby timer, the drive can also enter Standby mode automatically after the drive has been inactive for a specifiable length of time. The standby timer delay is established using a Standby or Idle command. In Standby mode, the drive buffer is enabled, the heads are parked and the spindle is at rest. The drive accepts all commands and returns to Active mode any time disc access is necessary.

- **Sleep mode**

The drive enters Sleep mode after receiving a Sleep command from the host. In Sleep mode, the drive buffer is disabled, the heads are parked and the spindle is at rest. The drive leaves Sleep mode after it receives a Hard Reset or Soft Reset from the host. After receiving a reset, the drive exits Sleep mode and enters Standby mode with all current translation parameters intact.

- **Idle and Standby timers**

Each time the drive performs an Active function (read, write or seek), the standby timer is reinitialized and begins counting down from its specified delay times to zero. If the standby timer reaches zero before any drive activity is required, the drive makes a transition to Standby mode. In both Idle and Standby mode, the drive accepts all commands and returns to Active mode when disc access is necessary.

## 2.9 Environmental specifications

### 2.9.1 Ambient temperature

Ambient temperature is defined as the temperature of the environment immediately surrounding the drive. Actual drive case temperature should not exceed 69°C (156°F) within the operating ambient conditions.

Above 1,000 feet (305 meters), the maximum temperature is derated linearly to 112°F (44°C) at 10,000 feet (3,048 meters).

|               |                              |
|---------------|------------------------------|
| Operating:    | 0° to 60°C (32° to 140°F)    |
| Nonoperating: | -40° to 70°C (-40° to 158°F) |

### 2.9.2 Temperature gradient

|               |   |
|---------------|---|
| Operating:    | 20°C per hour (68°F per hour max), without condensation |
| Nonoperating: | 30°C per hour (86°F per hour max)                       |

### 2.9.3 Humidity

#### 2.9.3.1 Relative humidity

|               |  |
|---------------|--|
| Operating:    | 5% to 90% noncondensing (30% per hour max) |
| Nonoperating: | 5% to 95% noncondensing (30% per hour max) |

#### 2.9.3.2 Wet bulb temperature

|               |                     |
|---------------|---------------------|
| Operating:    | 37.7°C (99.9°F max) |
| Nonoperating: | 37.7°C (99.9°F max) |

### 2.9.4 Altitude

|               |  |
|---------------|--|
| Operating:    | -60.96 m to 3,048 m (-200 ft. to 10,000+ ft.)  |
| Nonoperating: | -60.96 m to 12,192 m (-200 ft. to 40,000+ ft.) |

### 2.9.5 Shock

All shock specifications assume that the drive is mounted securely with the input shock applied at the drive mounting screws. Shock may be applied in the X, Y or Z axis.

#### 2.9.5.1 Operating shock

These drives comply with the performance levels specified in this document when subjected to a maximum operating shock of 68 Gs based on half-sine shock pulses of 2 msec. Shocks should not be repeated more than two times per second.

## 2.9.5.2 Nonoperating shock

### 2 Disc models

The nonoperating shock level that the drive can experience without incurring physical damage or degradation in performance when subsequently put into operation is 350 Gs based on a nonrepetitive half-sine shock pulse of 2 msec duration.

### 3 and 4 Disc models

The nonoperating shock level that the drive can experience without incurring physical damage or degradation in performance when subsequently put into operation is 300 Gs based on a nonrepetitive half-sine shock pulse of 2 msec duration.

## 2.9.6 Vibration

All vibration specifications assume that the drive is mounted securely with the input vibration applied at the drive mounting screws. Vibration may be applied in the X, Y or Z axis.

### 2.9.6.1 Operating vibration

The maximum vibration levels that the drive may experience while meeting the performance standards specified in this document are specified below.

|            |                                |
|------------|--------------------------------|
| 5–22 Hz    | 0.25 Gs (Limited displacement) |
| 22–350 Hz  | 0.50 Gs                        |
| 350–500 Hz | 0.25 Gs                        |

### 2.9.6.2 Nonoperating vibration

The maximum nonoperating vibration levels that the drive may experience without incurring physical damage or degradation in performance when subsequently put into operation are specified below.

|            |                                |
|------------|--------------------------------|
| 5–22 Hz    | 0.25 Gs (limited displacement) |
| 22–350 Hz  | 5.0 Gs                         |
| 350–500 Hz | 1.0 Gs                         |

## 2.10 Acoustics

Drive acoustics are measured as overall A-weighted acoustic sound power levels (no pure tones). All measurements are consistent with ISO document 7779. Sound power measurements are taken under essentially free-field conditions over a reflecting plane. For all tests, the drive is oriented with the cover facing upward.

**Note.** For seek mode tests, the drive is placed in seek mode only. The number of seeks per second is defined by the following equation:

$$(\text{Number of seeks per second} = 0.4 / (\text{average latency} + \text{average access time}))$$

**Table 9: Fluid Dynamic Bearing (FDB) motor acoustics**

|  | Idle*                            | Performance seek                 |
|--|----------------------------------|----------------------------------|
| ST3750640AS, ST3750840AS   | 2.5 bels (typ)<br>2.7 bels (max) | 3.0 bels (typ)<br>3.2 bels (max) |
| ST3500630AS, ST3500830AS   | 2.5 bels (typ)<br>2.7 bels (max) | 3.3 bels (typ)<br>3.5 bels (max) |
| ST3400620AS, ST3400820AS   | 2.7 bels (typ)<br>2.9 bels (max) | 3.4 bels (typ)<br>3.6 bels (max) |
| ST3320620AS, ST3320820AS, ST3300620AS, ST3300820AS,<br>ST3250620AS, ST3250820AS, ST3200820AS | 2.8 bels (typ)<br>3.0 bels (max) | 3.7 bels (typ)<br>3.9 bels (max) |

\*During periods of drive idle, some offline activity may occur according to the S.M.A.R.T. specification, which may increase acoustic and power to operational levels.

## 2.11 Electromagnetic immunity

When properly installed in a representative host system, the drive operates without errors or degradation in performance when subjected to the radio frequency (RF) environments defined in the following table:

**Table 10: Radio frequency environments**

| Test                      | Description  | Performance level | Reference standard                |
|---------------------------|--|-------------------|-----------------------------------|
| Electrostatic discharge   | Contact, HCP, VCP: ± 4 kV; Air: ± 8 kV   | B                 | EN 61000-4-2: 95                  |
| Radiated RF immunity      | 80 to 1,000 MHz, 3 V/m,<br>80% AM with 1 kHz sine<br>900 MHz, 3 V/m, 50% pulse modulation @ 200 Hz | A                 | EN 61000-4-3: 96<br>ENV 50204: 95 |
| Electrical fast transient | ± 1 kV on AC mains, ± 0.5 kV on external I/O   | B                 | EN 61000-4-4: 95                  |
| Surge immunity            | ± 1 kV differential, ± 2 kV common, AC mains   | B                 | EN 61000-4-5: 95                  |
| Conducted RF immunity     | 150 kHz to 80 MHz, 3 Vrms, 80% AM with 1 kHz sine  | A                 | EN 61000-4-6: 97                  |
| Voltage dips, interrupts  | 0% open, 5 seconds<br>0% short, 5 seconds<br>40%, 0.10 seconds<br>70%, 0.01 seconds                | C<br>C<br>C<br>B  | EN 61000-4-11: 94                 |

## 2.12 Reliability

|                               |  |
|-------------------------------|--|
| Nonrecoverable read errors    | 1 per 10 <sup>14</sup> bits read, max  |
| Annualized Failure Rate (AFR) | 0.34% (nominal power, 25°C ambient temperature)  |
| Contact start-stop cycles     | 50,000 cycles<br>(at nominal voltage and temperature, with 60 cycles per hour and a 50% duty cycle)  |
| Warranty                      | 5 years on distribution units.<br>To determine the warranty for a specific drive, use a web browser to access the following web page:<br><a href="http://www.seagate.com/support/service/">www.seagate.com/support/service/</a><br>From this page, click on the "Verify Your Warranty" link. You will be asked to provide the drive serial number, model number (or part number) and country of purchase. The system will display the warranty information for your drive. |
| Preventive maintenance        | None required.   |

## 2.13 Agency certification

### 2.13.1 Safety certification

The drives are recognized in accordance with UL 1950 and CSA C22.2 (950) and meet all applicable sections of IEC950 and EN 60950 as tested by TUV North America.

### 2.13.2 Electromagnetic compatibility

Hard drives that display the CE mark comply with the European Union (EU) requirements specified in the Electromagnetic Compatibility Directive (89/336/EEC). Testing is performed to the levels specified by the product standards for Information Technology Equipment (ITE). Emission levels are defined by EN 55022, Class B and the immunity levels are defined by EN 55024.

Seagate uses an independent laboratory to confirm compliance with the EC directives specified in the previous paragraph. Drives are tested in representative end-user systems. Although CE-marked Seagate drives comply with the directives when used in the test systems, we cannot guarantee that all systems will comply with the directives. The drive is designed for operation inside a properly designed enclosure, with properly shielded I/O cable (if necessary) and terminators on all unused I/O ports. Computer manufacturers and system integrators should confirm EMC compliance and provide CE marking for their products.

#### Korean RRL

If these drives have the Korea Ministry of Information and Communication (MIC) logo, they comply with paragraph 1 of Article 11 of the Electromagnetic Compatibility control Regulation and meet the Electromagnetic Compatibility (EMC) Framework requirements of the Radio Research Laboratory (RRL) Ministry of Information and Communication Republic of Korea.

These drives have been tested and comply with the Electromagnetic Interference/Electromagnetic Susceptibility (EMI/EMS) for Class B products. Drives are tested in a representative, end-user system by a Korean-recognized lab.

- EUT name (model numbers): ST3750640AS, ST3750840AS, ST3500630AS, ST3500830AS, ST3400620AS, ST3400820AS, ST3320620AS, ST3320820AS, ST3300620AS, ST3300820AS, ST3250620AS, ST3250820AS, and ST3200820AS.
- Certificate number: STX-L3510 (B)
- Trade name or applicant: Seagate Technology
- Manufacturing date: March 2006
- Manufacturer/nationality: Singapore and China

## Australian C-Tick (N176)

If these models have the C-Tick marking, they comply with the Australia/New Zealand Standard AS/NZS3548 1995 and meet the Electromagnetic Compatibility (EMC) Framework requirements of the Australian Communication Authority (ACA).

### 2.13.3 FCC verification

These drives are intended to be contained solely within a personal computer or similar enclosure (not attached as an external device). As such, each drive is considered to be a subassembly even when it is individually marketed to the customer. As a subassembly, no Federal Communications Commission verification or certification of the device is required.

Seagate Technology LLC has tested this device in enclosures as described above to ensure that the total assembly (enclosure, disc drive, motherboard, power supply, etc.) does comply with the limits for a Class B computing device, pursuant to Subpart J, Part 15 of the FCC rules. Operation with noncertified assemblies is likely to result in interference to radio and television reception.

**Radio and television interference.** This equipment generates and uses radio frequency energy and if not installed and used in strict accordance with the manufacturer's instructions, may cause interference to radio and television reception.

This equipment is designed to provide reasonable protection against such interference in a residential installation. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause interference to radio or television, which can be determined by turning the equipment on and off, you are encouraged to try one or more of the following corrective measures:

- Reorient the receiving antenna.
- Move the device to one side or the other of the radio or TV.
- Move the device farther away from the radio or TV.
- Plug the computer into a different outlet so that the receiver and computer are on different branch outlets.

If necessary, you should consult your dealer or an experienced radio/television technician for additional suggestions. You may find helpful the following booklet prepared by the Federal Communications Commission: *How to Identify and Resolve Radio-Television Interference Problems*. This booklet is available from the Superintendent of Documents, U.S. Government Printing Office, Washington, DC 20402. Refer to publication number 004-000-00345-4.

## 2.14 Environmental protection

Seagate designs its products to meet environmental protection requirements worldwide, including regulations restricting certain chemical substances.

### 2.14.1 European Union Restriction of Hazardous Substances (RoHS)

The European Union Restriction of Hazardous Substances (RoHS) Directive restricts the presence of chemical substances, including Lead (Pb), in electronic products effective July 2006. Although amendments to the European Union's Restriction of Hazardous Substances (RoHS) Directive have not been finalized, to the best of our knowledge the disc drives documented in this publication will comply with the final RoHS Directive requirements.

A number of parts and materials in Seagate products are procured from external suppliers. We rely on the representations of our suppliers regarding the presence of RoHS substances in these parts and materials. Our supplier contracts require compliance with our chemical substance restrictions, and our suppliers document their compliance with our requirements by providing material content declarations for all parts and materials for the disc drives documented in this publication. Current supplier declarations include disclosure of the inclusion of any RoHS-regulated substance in such parts or materials.

Seagate also has internal systems in place to ensure ongoing compliance with the RoHS Directive and all laws and regulations which restrict chemical content in electronic products. These systems include standard operating procedures that ensure that restricted substances are not utilized in our manufacturing operations, laboratory analytical validation testing, and an internal auditing process to ensure that all standard operating procedures are complied with.

## **2.15 Corrosive environment**

Seagate electronic drive components pass accelerated corrosion testing equivalent to 10 years exposure to light industrial environments containing sulfurous gases, chlorine and nitric oxide, classes G and H per ASTM B845. However, this accelerated testing cannot duplicate every potential application environment. Users should use caution exposing any electronic components to uncontrolled chemical pollutants and corrosive chemicals as electronic drive component reliability can be affected by the installation environment. The silver, copper, nickel and gold films used in Seagate products are especially sensitive to the presence of sulfide, chloride, and nitrate contaminants. Sulfur is found to be the most damaging. In addition, electronic components should never be exposed to condensing water on the surface of the printed circuit board assembly (PCBA) or exposed to an ambient relative humidity greater than 95%. Materials used in cabinet fabrication, such as vulcanized rubber, that can outgas corrosive compounds should be minimized or eliminated. The useful life of any electronic equipment may be extended by replacing materials near circuitry with sulfide-free alternatives.





## 3.0 Configuring and mounting the drive

---

This section contains the specifications and instructions for configuring and mounting the drive.

### 3.1 Handling and static-discharge precautions

After unpacking, and before installation, the drive may be exposed to potential handling and electrostatic discharge (ESD) hazards. Observe the following standard handling and static-discharge precautions:

**Caution:**

- Before handling the drive, put on a grounded wrist strap, or ground yourself frequently by touching the metal chassis of a computer that is plugged into a grounded outlet. Wear a grounded wrist strap throughout the entire installation procedure.
- Handle the drive by its edges or frame *only*.
- The drive is extremely fragile—handle it with care. Do not press down on the drive top cover.
- Always rest the drive on a padded, antistatic surface until you mount it in the computer.
- Do not touch the connector pins or the printed circuit board.
- Do not remove the factory-installed labels from the drive or cover them with additional labels. Removal voids the warranty. Some factory-installed labels contain information needed to service the drive. Other labels are used to seal out dirt and contamination.

### 3.2 Configuring the drive

Each drive on the Serial ATA interface connects point-to-point with the Serial ATA host adapter. There is no master/slave relationship because each drive is considered a master in a point-to-point relationship. If two drives are attached on one Serial ATA host adapter, the host operating system views the two devices as if they were both “masters” on two separate ports. Both drives behave as if they are Device 0 (master) devices.

Serial ATA drives are designed for easy installation. It is usually not necessary to set any jumpers on the drive for proper operation; however, if you connect the drive and receive a “drive not detected” error, your SATA-equipped motherboard or host adapter may use a chipset that does not support SATA speed autonegotiation. If you have a motherboard or host adapter that does not support autonegotiation:

- Install a jumper as shown in Figure 3 below to limit the data transfer rate to 1.5 Gbits per second (and leave the drive connected to the SATA-equipped motherboard or host adapter that doesn't support autonegotiation) or
- Install a SATA host adapter that supports autonegotiation, leave the drive jumper block set to “Normal operation” (see Figure 3 below), and connect the drive to that adapter. This option has the benefit of not limiting the drive to a 1.5 Gbits/sec transfer rate.




Figure 3. Serial ATA connectors

### 3.3 Serial ATA cables and connectors

The Serial ATA interface cable consists of four conductors in two differential pairs, plus three ground connections. The cable size may be 30 to 26 AWG with a maximum length of one meter (39.37 inches). See Table 11 for connector pin definitions. Either end of the SATA signal cable can be attached to the drive or host.

For direct backplane connection, the drive connectors are inserted directly into the host receptacle. The drive and the host receptacle incorporate features that enable the direct connection to be hot pluggable and blind mateable.

For installations which require cables, you can connect the drive as illustrated in Figure 4.




Figure 4. Attaching SATA cabling

Each cable is keyed to ensure correct orientation. Barracuda 7200.10 Serial ATA drives support latching SATA connectors.

### 3.4 Drive mounting

You can mount the drive in any orientation using four screws in the side-mounting holes or four screws in the bottom-mounting holes. See Figure 5 on page 33 for drive mounting dimensions. Follow these important mounting precautions when mounting the drive:

- Allow a minimum clearance of 0.030 inches (0.76 mm) around the entire perimeter of the drive for cooling.
- Use only 6-32 UNC mounting screws.
- The screws should be inserted no more than 0.150 inch (3.81 mm) into the bottom or side mounting holes.
- Do not overtighten the mounting screws (maximum torque: 6 inch-lb).




Figure 5. Mounting dimensions—top, side and end view



## **4.0 Serial ATA (SATA) interface**

---

These drives use the industry-standard Serial ATA interface that supports FIS data transfers. It supports ATA programmed input/output (PIO) modes 0–4; multiword DMA modes 0–2, and Ultra DMA modes 0–6.

For detailed information about the Serial ATA interface, refer to the “Serial ATA: High Speed Serialized AT Attachment” specification.

### **4.1 Hot-Plug compatibility**

Barracuda 7200.10 Serial ATA drives incorporate connectors which enable you to hot plug these drives in accordance with the Serial ATA II: Extension to Serial ATA 1.0a specification. This specification can be downloaded from [www.serialata.org](http://www.serialata.org).

## 4.2 Serial ATA device plug connector pin definitions

Table 11 summarizes the signals on the Serial ATA interface and power connectors..

**Table 11: Serial ATA connector pin definitions**

| Segment       | Pin | Function | Definition                          |
|---------------|-----|----------|-------------------------------------|
| <b>Signal</b> | S1  | Ground   | 2nd mate                            |
|               | S2  | A+       | Differential signal pair A from Phy |
|               | S3  | A-       |                                     |
|               | S4  | Ground   | 2nd mate                            |
|               | S5  | B-       | Differential signal pair B from Phy |
|               | S6  | B+       |                                     |
|               | S7  | Ground   | 2nd mate                            |

Key and spacing separate signal and power segments

|              |     |                      |   |
|--------------|-----|----------------------|---|
| <b>Power</b> | P1  | V <sub>33</sub>      | 3.3V power                                    |
|              | P2  | V <sub>33</sub>      | 3.3V power                                    |
|              | P3  | V <sub>33</sub>      | 3.3V power, pre-charge, 2nd mate              |
|              | P4  | Ground               | 1st mate                                      |
|              | P5  | Ground               | 2nd mate                                      |
|              | P6  | Ground               | 2nd mate                                      |
|              | P7  | V <sub>5</sub>       | 5V power, pre-charge, 2nd mate                |
|              | P8  | V <sub>5</sub>       | 5V power                                      |
|              | P9  | V <sub>5</sub>       | 5V power                                      |
|              | P10 | Ground               | 2nd mate                                      |
|              | P11 | Ground or LED signal | If grounded, drive does not use deferred spin |
|              | P12 | Ground               | 1st mate.                                     |
|              | P13 | V <sub>12</sub>      | 12V power, pre-charge, 2nd mate               |
|              | P14 | V <sub>12</sub>      | 12V power                                     |
|              | P15 | V <sub>12</sub>      | 12V power                                     |

### Notes:

- All pins are in a single row, with a 1.27 mm (0.050") pitch.
- The comments on the mating sequence apply to the case of backplane blindmate connector only. In this case, the mating sequences are:
  - the ground pins P4 and P12.
  - the pre-charge power pins and the other ground pins.
  - the signal pins and the rest of the power pins.
- There are three power pins for each voltage. One pin from each voltage is used for pre-charge when installed in a blind-mate backplane configuration.
- All used voltage pins (V<sub>x</sub>) must be terminated.

### 4.3 Supported ATA commands

The following table lists Serial ATA standard commands that the drive supports. For a detailed description of the ATA commands, refer to the Serial ATA: High Speed Serialized AT Attachment specification. See “S.M.A.R.T. commands” on page 44 for details and subcommands used in the S.M.A.R.T. implementation.

**Table 12: Supported ATA commands**

| Command name                        | Command code (in hex)              |
|-------------------------------------|------------------------------------|
| Check Power Mode                    | 98 <sub>H</sub> or E5 <sub>H</sub> |
| Device Configuration Freeze Lock    | B1 <sub>H</sub> / C1 <sub>H</sub>  |
| Device Configuration Identify       | B1 <sub>H</sub> / C2 <sub>H</sub>  |
| Device Configuration Restore        | B1 <sub>H</sub> / C0 <sub>H</sub>  |
| Device Configuration Set            | B1 <sub>H</sub> / C3 <sub>H</sub>  |
| Device Reset                        | 08 <sub>H</sub>                    |
| Download Microcode                  | 92 <sub>H</sub>                    |
| Execute Device Diagnostics          | 90 <sub>H</sub>                    |
| Flush Cache                         | E7 <sub>H</sub>                    |
| Flush Cache Extended                | EA <sub>H</sub>                    |
| Format Track                        | 50 <sub>H</sub>                    |
| Identify Device                     | EC <sub>H</sub>                    |
| Idle                                | 97 <sub>H</sub> or E3 <sub>H</sub> |
| Idle Immediate                      | 95 <sub>H</sub> or E1 <sub>H</sub> |
| Initialize Device Parameters        | 91 <sub>H</sub>                    |
| Read Buffer                         | E4 <sub>H</sub>                    |
| Read DMA                            | C8 <sub>H</sub>                    |
| Read DMA Extended                   | 25 <sub>H</sub>                    |
| Read DMA Without Retries            | C9 <sub>H</sub>                    |
| Read Log Ext                        | 2F <sub>H</sub>                    |
| Read Multiple                       | C4 <sub>H</sub>                    |
| Read Multiple Extended              | 29 <sub>H</sub>                    |
| Read Native Max Address             | F8 <sub>H</sub>                    |
| Read Native Max Address Extended    | 27 <sub>H</sub>                    |
| Read Sectors                        | 20 <sub>H</sub>                    |
| Read Sectors Extended               | 24 <sub>H</sub>                    |
| Read Sectors Without Retries        | 21 <sub>H</sub>                    |
| Read Verify Sectors                 | 40 <sub>H</sub>                    |
| Read Verify Sectors Extended        | 42 <sub>H</sub>                    |
| Read Verify Sectors Without Retries | 41 <sub>H</sub>                    |
| Recalibrate                         | 10 <sub>H</sub>                    |
| Security Disable Password           | F6 <sub>H</sub>                    |
| Security Erase Prepare              | F3 <sub>H</sub>                    |

| Command name  | Command code (in hex)  |
|---|--|
| Security Erase Unit   | F4 <sub>H</sub>  |
| Security Freeze   | F5 <sub>H</sub>  |
| Security Set Password   | F1 <sub>H</sub>  |
| Security Unlock   | F2 <sub>H</sub>  |
| Seek  | 70 <sub>H</sub>  |
| Set Features  | EF <sub>H</sub>  |
| Set Max Address<br>Note: Individual Set Max Address commands are identified by the value placed in the Set Max Features register as defined to the right. | F9 <sub>H</sub><br>Address: 00 <sub>H</sub><br>Password: 01 <sub>H</sub><br>Lock: 02 <sub>H</sub><br>Unlock: 03 <sub>H</sub><br>Freeze Lock: 04 <sub>H</sub> |
| Set Max Address Extended  | 37 <sub>H</sub>  |
| Set Multiple Mode   | C6 <sub>H</sub>  |
| Sleep   | 99 <sub>H</sub> or E6 <sub>H</sub>   |
| S.M.A.R.T. Disable Operations   | B0 <sub>H</sub> / D9 <sub>H</sub>  |
| S.M.A.R.T. Enable/Disable Autosave  | B0 <sub>H</sub> / D2 <sub>H</sub>  |
| S.M.A.R.T. Enable Operations  | B0 <sub>H</sub> / D8 <sub>H</sub>  |
| S.M.A.R.T. Execute Offline  | B0 <sub>H</sub> / D4 <sub>H</sub>  |
| S.M.A.R.T. Read Attribute Thresholds  | B0 <sub>H</sub> / D1 <sub>H</sub>  |
| S.M.A.R.T. Read Data  | B0 <sub>H</sub> / D0 <sub>H</sub>  |
| S.M.A.R.T. Read Log Sector  | B0 <sub>H</sub> / D5 <sub>H</sub>  |
| S.M.A.R.T. Return Status  | B0 <sub>H</sub> / DA <sub>H</sub>  |
| S.M.A.R.T. Save Attribute Values  | B0 <sub>H</sub> / D3 <sub>H</sub>  |
| S.M.A.R.T. Write Log Sector   | B0 <sub>H</sub> / D6 <sub>H</sub>  |
| Standby   | 96 <sub>H</sub> or E2 <sub>H</sub>   |
| Standby Immediate   | 94 <sub>H</sub> or E0 <sub>H</sub>   |
| Write Buffer  | E8 <sub>H</sub>  |
| Write DMA   | CA <sub>H</sub>  |
| Write DMA Extended  | 35 <sub>H</sub>  |
| Write DMA FUA Extended  | CD <sub>H</sub>  |
| Write DMA Without Retries   | CB <sub>H</sub>  |
| Write Log Extended  | 3F <sub>H</sub>  |
| Write Multiple  | C5 <sub>H</sub>  |
| Write Multiple Extended   | 39 <sub>H</sub>  |
| Write Multiple FUA Extended   | CE <sub>H</sub>  |
| Write Sectors   | 30 <sub>H</sub>  |
| Write Sectors Without Retries   | 31 <sub>H</sub>  |
| Write Sectors Extended  | 34 <sub>H</sub>  |



### 4.3.1 Identify Device command

The Identify Device command (command code EC<sub>H</sub>) transfers information about the drive to the host following power up. The data is organized as a single 512-byte block of data, whose contents are shown in Table 12 on page 37. All reserved bits or words should be set to zero. Parameters listed with an “x” are drive-specific or vary with the state of the drive. See Section 2.0 on page 3 for default parameter settings.

The following commands contain drive-specific features that may not be included in the Serial ATA specification.

| Word  | Description  | Value             |
|-------|--|-------------------|
| 0     | Configuration information:<br>• Bit 15: 0 = ATA; 1 = ATAPI<br>• Bit 7: removable media<br>• Bit 6: removable controller<br>• Bit 0: reserved | 0C5A <sub>H</sub> |
| 1     | Number of logical cylinders  | 16,383            |
| 2     | ATA-reserved   | 0000 <sub>H</sub> |
| 3     | Number of logical heads  | 16                |
| 4     | Retired  | 0000 <sub>H</sub> |
| 5     | Retired  | 0000 <sub>H</sub> |
| 6     | Number of logical sectors per logical track: 63  | 003F <sub>H</sub> |
| 7–9   | Retired  | 0000 <sub>H</sub> |
| 10–19 | Serial number: (20 ASCII characters, 0000 <sub>H</sub> = none)   | ASCII             |
| 20    | Retired  | 0000 <sub>H</sub> |
| 21    | Retired  | 0400 <sub>H</sub> |
| 22    | Obsolete   | 0000 <sub>H</sub> |
| 23–26 | Firmware revision (8 ASCII character string, padded with blanks to end of string)  | x.xx              |
| 27–46 | Drive model number: (40 ASCII characters, padded with blanks to end of string)   |                   |
| 47    | (Bits 7–0) Maximum sectors per interrupt on Read multiple and Write multiple (16)  | 8010 <sub>H</sub> |
| 48    | Reserved   | 0000 <sub>H</sub> |
| 49    | Standard Standby timer, IORDY supported and may be disabled  | 2F00 <sub>H</sub> |
| 50    | ATA-reserved   | 0000 <sub>H</sub> |
| 51    | PIO data-transfer cycle timing mode  | 0200 <sub>H</sub> |
| 52    | Retired  | 0200 <sub>H</sub> |
| 53    | Words 54–58, 64–70 and 88 are valid  | 0007 <sub>H</sub> |
| 54    | Number of current logical cylinders  | xxxx <sub>H</sub> |
| 55    | Number of current logical heads  | xxxx <sub>H</sub> |
| 56    | Number of current logical sectors per logical track  | xxxx <sub>H</sub> |
| 57–58 | Current capacity in sectors  | xxxx <sub>H</sub> |
| 59    | Number of sectors transferred during a Read Multiple or Write Multiple command   | xxxx <sub>H</sub> |

| Word  | Description   | Value             |
|-------|---|-------------------|
| 60–61 | Total number of user-addressable LBA sectors available (see Section 2.2 for related information)<br>*Note: The maximum value allowed in this field is: 0FFFFFFFh (268,435,455 sectors, 137 Gbytes). Drives with capacities over 137 Gbytes will have 0FFFFFFFh in this field and the actual number of user-addressable LBAs specified in words 100-103. This is required for drives that support the 48-bit addressing feature. | 0FFFFFFFh*        |
| 62    | Retired   | 0000 <sub>H</sub> |
| 63    | Multiword DMA active and modes supported (see note following this table)  | xx07 <sub>H</sub> |
| 64    | Advanced PIO modes supported (modes 3 and 4 supported)  | 0003 <sub>H</sub> |
| 65    | Minimum multiword DMA transfer cycle time per word (120 nsec)   | 0078 <sub>H</sub> |
| 66    | Recommended multiword DMA transfer cycle time per word (120 nsec)   | 0078 <sub>H</sub> |
| 67    | Minimum PIO cycle time without IORDY flow control (240 nsec)  | 00F0 <sub>H</sub> |
| 68    | Minimum PIO cycle time with IORDY flow control (120 nsec)   | 0078 <sub>H</sub> |
| 69–74 | ATA-reserved  | 0000 <sub>H</sub> |
| 75    | Queue depth   | 0000 <sub>H</sub> |
| 76    | Serial ATA capabilities   | xxxx <sub>H</sub> |
| 77    | Reserved for future Serial ATA definition   | xxxx <sub>H</sub> |
| 78    | Serial ATA features supported   | xxxx <sub>H</sub> |
| 79    | Serial ATA features enabled   | xxxx <sub>H</sub> |
| 80    | Major version number  | 003E <sub>H</sub> |
| 81    | Minor version number  | 0000 <sub>H</sub> |
| 82    | Command sets supported  | 364B <sub>H</sub> |
| 83    | Command sets supported  | 7C03 <sub>H</sub> |
| 84    | Command sets support extension  | 4003 <sub>H</sub> |
| 85    | Command sets enabled  | 30xx <sub>H</sub> |
| 86    | Command sets enabled  | 0001 <sub>H</sub> |
| 87    | Command sets enable extension   | 4000 <sub>H</sub> |
| 88    | Ultra DMA support and current mode (see note following this table)  | xx3F <sub>H</sub> |
| 89    | Security erase time   | 0000 <sub>H</sub> |
| 90    | Enhanced security erase time  | 0000 <sub>H</sub> |
| 92    | Master password revision code   | FFFE <sub>H</sub> |
| 93    | Hardware reset value (see description following this table)   | xxxx <sub>H</sub> |
| 95–99 | ATA-reserved  | 0000 <sub>H</sub> |

| Word    | Description  | Value   |
|---------|--|---|
| 100–103 | Total number of user-addressable LBA sectors available (see Section 2.2 for related information). These words are required for drives that support the 48-bit addressing feature. Maximum value: 0000FFFFFFFFFh. | ST3750640AS = 1,465,149,168<br>ST3750840AS = 1,465,149,168<br>ST3500630AS = 976,773,168<br>ST3500830AS = 976,773,168<br>ST3400620AS = 781,422,768<br>ST3400820AS = 781,422,768<br>ST3320620AS = 625,142,448<br>ST3320820AS = 625,142,448<br>ST3300620AS = 586,072,368<br>ST3300820AS = 586,072,368<br>ST3250620AS = 488,397,168<br>ST3250820AS = 488,397,168<br>ST3200820AS = 390,721,968 |
| 104–127 | ATA-reserved   | 0000 <sub>H</sub>   |
| 128     | Security status  | 0001 <sub>H</sub>   |
| 129–159 | Seagate-reserved   | xxxx <sub>H</sub>   |
| 160–254 | ATA-reserved   | 0000 <sub>H</sub>   |
| 255     | Integrity word   | xxA5 <sub>H</sub>   |

**Note.** Advanced Power Management (APM) and Automatic Acoustic Management (AAM) features are not supported

**Note.** See the bit descriptions below for words 63, 88, and 93 of the Identify Drive data.

| <b>Description (if bit is set to 1)</b> |            |   |
|---|------------|---|
|   | <b>Bit</b> | <b>Word 63</b>                            |
|   | 0          | Multiword DMA mode 0 is supported.        |
|   | 1          | Multiword DMA mode 1 is supported.        |
|   | 2          | Multiword DMA mode 2 is supported.        |
|   | 8          | Multiword DMA mode 0 is currently active. |
|   | 9          | Multiword DMA mode 1 is currently active. |
|   | 10         | Multiword DMA mode 2 is currently active. |
|   | <b>Bit</b> | <b>Word 88</b>                            |
|   | 0          | Ultra DMA mode 0 is supported.            |
|   | 1          | Ultra DMA mode 1 is supported.            |
|   | 2          | Ultra DMA mode 2 is supported.            |
|   | 3          | Ultra DMA mode 3 is supported.            |
|   | 4          | Ultra DMA mode 4 is supported.            |
|   | 5          | Ultra DMA mode 5 is supported.            |
|   | 6          | Ultra DMA mode 6 is supported.            |
|   | 8          | Ultra DMA mode 0 is currently active.     |
|   | 9          | Ultra DMA mode 1 is currently active.     |
|   | 10         | Ultra DMA mode 2 is currently active.     |
|   | 11         | Ultra DMA mode 3 is currently active.     |
|   | 12         | Ultra DMA mode 4 is currently active.     |
|   | 13         | Ultra DMA mode 5 is currently active.     |
|   | 14         | Ultra DMA mode 6 is currently active.     |

### 4.3.2 Set Features command

This command controls the implementation of various features that the drive supports. When the drive receives this command, it sets BSY, checks the contents of the Features register, clears BSY and generates an interrupt. If the value in the register does not represent a feature that the drive supports, the command is aborted. Power-on default has the read look-ahead and write caching features enabled. The acceptable values for the Features register are defined as follows:

**Table 13: Set Features command values**

|                 |   |
|-----------------|---|
| 02 <sub>H</sub> | Enable write cache ( <i>default</i> ).  |
| 03 <sub>H</sub> | Set transfer mode (based on value in Sector Count register).<br>Sector Count register values: |
| 00 <sub>H</sub> | Set PIO mode to default (PIO mode 2).   |
| 01 <sub>H</sub> | Set PIO mode to default and disable IORDY (PIO mode 2).                                       |
| 08 <sub>H</sub> | PIO mode 0  |
| 09 <sub>H</sub> | PIO mode 1  |
| 0A <sub>H</sub> | PIO mode 2  |
| 0B <sub>H</sub> | PIO mode 3  |
| 0C <sub>H</sub> | PIO mode 4 ( <i>default</i> )   |
| 20 <sub>H</sub> | Multiword DMA mode 0  |
| 21 <sub>H</sub> | Multiword DMA mode 1  |
| 22 <sub>H</sub> | Multiword DMA mode 2  |
| 40 <sub>H</sub> | Ultra DMA mode 0  |
| 41 <sub>H</sub> | Ultra DMA mode 1  |
| 42 <sub>H</sub> | Ultra DMA mode 2  |
| 43 <sub>H</sub> | Ultra DMA mode 3  |
| 44 <sub>H</sub> | Ultra DMA mode 4  |
| 45 <sub>H</sub> | Ultra DMA mode 5  |
| 46 <sub>H</sub> | Ultra DMA mode 6  |
| 10 <sub>H</sub> | Enable use of SATA features   |
| 55 <sub>H</sub> | Disable read look-ahead (read cache) feature.   |
| 82 <sub>H</sub> | Disable write cache   |
| 90 <sub>H</sub> | Disable use of SATA features  |
| AA <sub>H</sub> | Enable read look-ahead (read cache) feature ( <i>default</i> ).                               |
| F1 <sub>H</sub> | Report full capacity available  |

**Note.** At power-on, or after a hardware or software reset, the default values of the features are as indicated above.

### 4.3.3 S.M.A.R.T. commands

S.M.A.R.T. provides near-term failure prediction for disc drives. When S.M.A.R.T. is enabled, the drive monitors predetermined drive attributes that are susceptible to degradation over time. If self-monitoring determines that a failure is likely, S.M.A.R.T. makes a status report available to the host. Not all failures are predictable. S.M.A.R.T. predictability is limited to the attributes the drive can monitor. For more information on S.M.A.R.T. commands and implementation, see the *Draft ATA-5 Standard*.

SeaTools diagnostic software activates a built-in drive self-test (DST S.M.A.R.T. command for D4<sub>H</sub>) that eliminates unnecessary drive returns. The diagnostic software ships with all new drives and is also available at: <http://seatools.seagate.com>.

This drive is shipped with S.M.A.R.T. features disabled. You must have a recent BIOS or software package that supports S.M.A.R.T. to enable this feature. The table below shows the S.M.A.R.T. command codes that the drive uses.

**Table 14: S.M.A.R.T. commands**

| Code in features register | S.M.A.R.T. command                               |
|---------------------------|--|
| D0 <sub>H</sub>           | S.M.A.R.T. Read Data                             |
| D2 <sub>H</sub>           | S.M.A.R.T. Enable/Disable Attribute Autosave     |
| D3 <sub>H</sub>           | S.M.A.R.T. Save Attribute Values                 |
| D4 <sub>H</sub>           | S.M.A.R.T. Execute Off-line Immediate (runs DST) |
| D5 <sub>H</sub>           | S.M.A.R.T. Read Log Sector                       |
| D6 <sub>H</sub>           | S.M.A.R.T. Write Log Sector                      |
| D8 <sub>H</sub>           | S.M.A.R.T. Enable Operations                     |
| D9 <sub>H</sub>           | S.M.A.R.T. Disable Operations                    |
| DA <sub>H</sub>           | S.M.A.R.T. Return Status                         |

**Note.** If an appropriate code is not written to the Features Register, the command is aborted and 0x04 (abort) is written to the Error register.

## 5.0 Seagate Technology support services

---

### Online services

#### Internet

**www.seagate.com** for information about Seagate products and services. Worldwide support is available 24 hours daily by e-mail for your questions.

*Presales Support:* [www.seagate.com/support/email/email\\_presales.html](http://www.seagate.com/support/email/email_presales.html) or [Presales@Seagate.com](mailto:Presales@Seagate.com)

*Technical Support:* [www.seagate.com/support/email/email\\_disc\\_support.html](http://www.seagate.com/support/email/email_disc_support.html) or [DiscSupport@Seagate.com](mailto:DiscSupport@Seagate.com)

#### mySeagate

[my.seagate.com](http://my.seagate.com) is the industry's first Web portal designed specifically for OEMs and distributors. It provides self-service access to critical applications, personalized content and the tools that allow our partners to manage their Seagate account functions. Submit pricing requests, orders and returns through a single, password-protected Web interface—anytime, anywhere in the world.

#### spp.seagate.com

[spp.seagate.com](http://spp.seagate.com) supports Seagate resellers with product information, program benefits and sales tools. You may register for customized communications that are not available on the web. These communications contain product launch, EOL, pricing, promotions and other channel-related information. To learn more about the benefits or to register, go to [spp.seagate.com](http://spp.seagate.com), any time, from anywhere in the world.

### Seagate Service Centers

#### Presales Support

Our Presales Support staff can help you determine which Seagate products are best suited for your specific application or computer system, as well as drive availability and compatibility.

#### Technical Support

If you need help installing your drive, consult your system's documentation or contact the dealer's support services department for assistance specific to your system. Seagate technical support is also available to assist you online at [support.seagate.com](http://support.seagate.com) or through one of our call centers. Have your system configuration information and your drive's "ST" model number available.

**SeaTDD™ (+1-405-324-3655)** is a telecommunications device for the deaf (TDD). You can send questions or comments 24 hours daily and exchange messages with a technical support specialist during normal business hours for the call center in your region.

## Customer Service Operations

### Warranty Service

Seagate offers worldwide customer support for Seagate drives. Seagate distributors, OEMs and other direct customers should contact their Seagate Customer Service Operations (CSO) representative for warranty-related issues. Resellers or end users of drive products should contact their place of purchase or one of the Seagate CSO warranty centers for assistance. Have your drive's "ST" model number and serial number available.

### Data Recovery Services

Seagate offers data recovery services for all formats and all brands of storage media. Our Data Recovery Services labs are currently located in North America. To get a free quick quote or speak with a case management representative, call 1-800-475-0143. Additional information, including an online request form and data loss prevention resources, is available at [www.datarecovery.seagate.com](http://www.datarecovery.seagate.com).

### Authorized Service Centers

In some locations outside the US, you can contact an Authorized Service Center for service.

## USA/Canada/Latin America support services

### Seagate Service Centers

#### Presales Support

| Call center | Toll-free                   | Direct dial                  | FAX             |
|-------------|-----------------------------|------------------------------|-----------------|
| Americas    | 1-877-271-3285 <sup>1</sup> | +1-405-324-4730 <sup>1</sup> | +1-405-324-4704 |

#### Technical Support

| Call center | Toll-free                  | Direct dial                  | FAX             |
|-------------|----------------------------|------------------------------|-----------------|
| Americas    | 1-800-SEAGATE <sup>2</sup> | +1-405-324-4700 <sup>2</sup> | +1-405-324-3339 |

## Customer Service Operations

### Warranty Service

| Call center   | Toll-free                   | Direct dial      | FAX / E-mail                                |
|---|-----------------------------|------------------|---|
| USA, Canada, Mexico and Latin America                         | 1-800-468-3472 <sup>3</sup> | —                | +1-956-664-4725                             |
| Brazil<br><i>Jabil Industrial Do Brasil LTDA</i> <sup>4</sup> | —                           | +55-11-4191-4761 | +55-11-4191-5084<br>SeagateRMA.br@jabil.com |

### Data Recovery Services

| Call center             | Toll-free       | Direct dial     | FAX                               |
|-------------------------|-----------------|-----------------|-----------------------------------|
| USA, Canada, and Mexico | 1-800-475-01435 | +1-905-474-2162 | 1-800-475-0158<br>+1-905-474-2459 |

<sup>1</sup>Hours of operation are 8:00 A.M. to 6:00 P.M., Monday through Friday (Central time).

<sup>2</sup>Hours of operation are 8:00 A.M. to 8:00 P.M., Monday through Friday (Central time).

<sup>3</sup>Hours of operation are 8:00 A.M. to 5:00 P.M., Monday through Friday (Central time).

<sup>4</sup>Authorized Service Center

<sup>5</sup>Hours of operation are 8:00 A.M. to 8:00 P.M., Monday through Friday, and 9:00 A.M. to 5:00 P.M., Saturday (Eastern time).



## European support services

For presales and technical support in Europe, dial the Seagate Service Center toll-free number for your specific location. If your location is not listed here, dial our presales and technical support call center at +1-405-324-4714 from 8:00 A.M. to 11:45 A.M. and 1:00 P.M. to 5:00 P.M. (Central Europe time) Monday through Friday. The presales and technical support call center is located in Oklahoma City, USA.

For European warranty service, dial the toll-free number for your specific location. If your location is not listed here, dial our European CSO warranty center at +31-20-316-7222 from 8:30 A.M. to 5:00 P.M. (Central Europe time) Monday through Friday. The CSO warranty center is located in Amsterdam, The Netherlands.

## Seagate Service Centers

### Toll-free support numbers

| Call center    | Presales and Technical Support    | Warranty Service   |
|----------------|-----------------------------------|--------------------|
| Austria        | —                                 | 00 800-47324289    |
| Belgium        | 00 800-47324283 (00 800-4SEAGATE) | 00 800-47324289    |
| Denmark        | 00 800-47324283                   | 00 800-47324289    |
| France         | 00 800-47324283                   | 00 800-47324289    |
| Germany        | 00 800-47324283                   | 00 800-47324289    |
| Ireland        | 00 800-47324283                   | 00 800-47324289    |
| Italy          | 00 800-47324283                   | 00 800-47324289    |
| Netherlands    | 00 800-47324283                   | 00 800-47324289    |
| Norway         | 00 800-47324283                   | 00 800-47324289    |
| Poland         | 00 800-311 12 38                  | 00 800-311 12 38   |
| Spain          | 00 800-47324283                   | 00 800-47324289    |
| Sweden         | 00 800-47324283                   | 00 800-47324289    |
| Switzerland    | 00 800-47324283                   | 00 800-47324289    |
| Turkey         | 00 800-31 92 91 40                | 00 800-31 92 91 40 |
| United Kingdom | 00 800-47324283                   | 00 800-47324289    |

### FAX services—All Europe (toll call)

|                   |                 |
|-------------------|-----------------|
| Technical Support | +1-405-324-3339 |
| Warranty Service  | +31-20-653-3513 |

## Africa/Middle East support services

For presales and technical support in Africa and the Middle East, dial our presales and technical support call center at +1-405-324-4714 from 8:00 A.M. to 11:45 A.M. and 1:00 P.M. to 5:00 P.M. (Central Europe time) Monday through Friday. The presales and technical support call center is located in Oklahoma City, USA.

For warranty service in Africa and the Middle East, dial our European CSO warranty center at +31-20-316-7222 from 8:30 A.M. to 5:00 P.M. (Central Europe time) Monday through Friday, or send a FAX to +31-20-653-3513. The CSO warranty center is located in Amsterdam, The Netherlands.

## Asia/Pacific support services

For Asia/Pacific presales and technical support, dial the toll-free number for your specific location. The Asia/Pacific toll-free numbers are available from 6:00 A.M. to 10:45 A.M. and 12:00 P.M. to 6:00 P.M. (Australian Eastern time) Monday through Friday, except as noted. If your location is not listed here, direct dial one of our technical support locations.

Warranty service is available from 9:00 A.M. to 6:00 P.M. April through October, and 10:00 A.M. to 7:00 P.M. November through March (Australian Eastern time) Monday through Friday.

## Seagate Service Centers

| Call center                           | Toll-free          | Direct dial      | FAX           |
|---------------------------------------|--------------------|------------------|---------------|
| Australia                             | 1800-14-7201       | —                | —             |
| China (Mandarin) <sup>1, 4</sup>      | 800-810-9668       | +86-10-6225-5336 | —             |
| Hong Kong                             | 800-90-0474        | —                | —             |
| Hong Kong (Cantonese) <sup>1, 4</sup> | 001-800-0830-1730  | —                | —             |
| India <sup>2, 4</sup>                 | 1-800-180-1104     | —                | —             |
| Indonesia                             | 001-803-1-003-2165 | —                | —             |
| Japan <sup>3, 4</sup>                 | 0034 800 400 554   | —                | —             |
| Korea <sup>3, 4</sup>                 | 007 98 8521 7635   | —                | —             |
| Malaysia                              | 1-800-80-2335      | —                | —             |
| New Zealand                           | 0800-443988        | —                | —             |
| Singapore                             | 800-1101-150       | —                | +65-6488-7525 |
| Taiwan (Mandarin) <sup>1, 4</sup>     | 00-800-0830-1730   | —                | —             |
| Thailand                              | 001-800-11-0032165 | —                | —             |

## Customer Service Operations

### Warranty Service

| Call center        | Toll-free    | Direct dial     | FAX             |
|--------------------|--------------|-----------------|-----------------|
| Asia/Pacific       | —            | +65-6485-3595   | +65-6485-4860   |
| Australia          | 1800-12-9277 | —               | —               |
| India <sup>4</sup> | —            | +91-44-821-6164 | +91-44-827-2461 |

<sup>1</sup>Hours of operation are 8:30 A.M. to 5:30 P.M., Monday through Friday (Australian Western time).

<sup>2</sup>Hours of operation are 9:00 A.M. to 6:00 P.M., Monday through Saturday.

<sup>3</sup>Hours of operation are 9:30 A.M. to 6:30 P.M., Monday through Friday.

<sup>4</sup>Authorized Service Center

# Index

## A

- ACA 28
- acceleration 25
- acoustics 26
- Active 22
- Active mode 22
- actuator arm 20
- Agency certification 27
- altitude 24
- Ambient temperature 24
- ambient temperature 20
- Annualized Failure Rate (AFR) 27
- areal density 1, 19
- ATA commands 37
- Australia/New Zealand Standard AS/NZS3548 1995 28
- Australian Communication Authority (ACA) 28
- Australian C-Tick 28
- Average latency 20
- Average seek time 20

## B

- BPI 19
- buffer 19

## C

- cables and connectors 32
- cache 19
- capacity 18
- case temperature 24
- CE mark 27
- certification 27
- Check Power Mode 37
- Class B computing device 28
- compatibility 27
- Conducted noise 22
- Conducted RF immunity 26
- Configuring the drive 31
- connectors 32
- Corrosive environment 29
- CSA C22.2 (950) 27
- cycles 27
- Cylinders 18

## D

- data-transfer rates 1
- DC power 20
- Default logical geometry 18
- density 19
- Device Configuration Freeze Lock 37
- Device Configuration Identify 37
- Device Configuration Restore 37
- Device Configuration Set 37
- Device Reset 37
- dimensions 33
- disc surface 20
- dissipation 21
- Download Microcode 37

## E

- Electrical fast transient 26
- Electromagnetic compatibility 27
- Electromagnetic Compatibility (EMC) 27
- Electromagnetic Compatibility control Regulation 27
- Electromagnetic Compatibility Directive (89/336/EEC) 27
- Electromagnetic immunity 26
- Electrostatic discharge 26
- electrostatic discharge (ESD) 31
- EN 55022, Class B 27
- EN 55024 27
- EN 60950 27
- Environmental specifications 24
- EPRML 1
- error-correction algorithms 1
- errors 27
- ESD 31
- EU 27
- European Union (EU) requirements 27
- Execute Device Diagnostics 37

## F

- FCC verification 28
- features 1
- Federal Communications Commission 28
- Flush Cache 37
- Flush Cache Extended 37
- Format Track 37
- Formatted capacity 18

## G

- geometry 18
- Gs 25
- guaranteed sectors 18

## H

Handling precautions 31  
heads 18  
height 19  
humidity 24

## I

I/O data-transfer rate 19  
Identify Device 37  
Identify Device command 39  
Idle 22, 37  
Idle Immediate 37  
Idle mode 21, 23  
IEC950 27  
Information Technology Equipment (ITE) 27  
Initialize Device Parameters 37  
Input noise ripple 22  
input voltage 20  
interface 19, 35  
internal data-transfer rate OD 19  
is 20  
ISO document 7779 26  
ITE 27

## K

Korea Ministry of Information and Communication  
(MIC) 27  
Korean RRL 27

## L

latency 20  
latency time 20  
LBA mode 18  
length 19  
logical geometry 18

## M

maintenance 27  
master/slave 2  
maximum temperature 24  
MIC 27  
mounting 33  
mounting screws 24  
mounting the drive 31

## N

noise 22  
nominal power 20  
Nonoperating shock 25  
Nonoperating vibration 25  
Nonrecoverable read errors 27

## O

operating 21  
Operating power 21  
Operating shock 24  
Operating vibration 25

## P

Physical characteristics 19  
point-to-point 2, 32  
Power consumption 20  
power consumption 20  
power dissipation 21  
Power modes 22  
Power specifications 20  
Power-management modes 22  
Power-on to Ready 20  
precautions 31  
printed circuit board 31  
programmable power management 22

## Q

quick reference 3

## R

Radiated RF immunity 26  
Radio and television interference 28  
radio frequency (RF) 26  
random seeks 20, 21  
Read Buffer 37  
Read DMA 37  
Read DMA Extended 37  
Read DMA without Retries 37  
read errors 27  
Read Log Ext 37  
Read Multiple 37  
Read Multiple Extended 37  
Read Native Max Address 37  
Read Native Max Address Extended 37  
Read Sectors 37  
Read Sectors Extended 37  
Read Sectors Without Retries 37  
Read Verify Sectors 37  
Read Verify Sectors Extended 37  
Read Verify Sectors Without Retries 37  
read/write actuator arm 20  
Read/write heads 18  
Read/write power 20  
Recalibrate 37  
recording density 19  
recording method 19  
Recording technology 19  
relative humidity 24  
Reliability 27

RF 26  
RMS read/write current 22  
RoHS 28  
RRL 27

## S

S.M.A.R.T. Disable Operations 38  
S.M.A.R.T. Enable/Disable Autosave 38  
S.M.A.R.T. Enable Operations 38  
S.M.A.R.T. Execute Offline 38  
S.M.A.R.T. implementation 37  
S.M.A.R.T. Read Attribute Thresholds 38  
S.M.A.R.T. Read Data 38  
S.M.A.R.T. Read Log Sector 38  
S.M.A.R.T. Return Status 38  
S.M.A.R.T. Save Attribute Values 38  
S.M.A.R.T. Write Log sector 38  
Safety certification 27  
SATA 35  
screws 24  
sectors 18  
Sectors per track 18  
Security Disable Password 37  
Security Erase Prepare 37  
Security Erase Unit 38  
Security Freeze 38  
Security Set Password 38  
Security Unlock 38  
Seek 38  
seek mode 20  
Seek mode power 20  
Seek time 20  
Seeking 21  
Serial ATA (SATA) interface 35  
serial ATA ports 2  
Servo electronics 20  
servo electronics 21  
Set Features 38  
Set Max Address 38  
Set Max Address Extended 38  
Set Multiple Mode 38  
Shock 24  
single-track seeks 20  
Sleep 21, 22, 38  
Sleep mode 23  
sound 26  
Specification summary table 3  
spindle speed 19  
Spinup 21  
Spinup power 20  
Standby 21, 22, 38  
Standby Immediate 38  
Standby mode 21, 23  
standby timer 23  
Standby to Ready 20

Start/stop times 20  
start-stop cycles 27  
static-discharge 31  
support services 45  
Surge immunity 26

## T

technical support services 45  
temperature 20, 24  
temperature gradient 24  
timer 23  
timers 23  
track density 19  
Track-to-track 20  
Track-to-track seek time 20  
tunneling magnetoresistive (TGMR) recording heads  
1  
TUV North America 27

## U

UL 1950 27

## V

Vibration 25  
voltage 20  
Voltage dips, interrupts 26  
Voltage tolerance 22

## W

weight 19  
wet bulb temperature 24  
width 19  
Write Buffer 38  
Write DMA 38  
Write DMA Extended 38  
Write DMA FUA Extended 38  
Write DMA Without Retries 38  
Write Log Extended 38  
Write Multiple 38  
Write Multiple Extended 38  
Write Multiple FUA Extended 38  
Write Sectors 38  
Write Sectors Extended 38  
Write Sectors Without Retries 38







**Seagate Technology LLC**  
**920 Disc Drive, Scotts Valley, California 95066-4544, USA**  
*Publication Number: 100402371, Rev. A, Printed in USA*