


## High bandwidth 8 MHz, rail-to-rail, 5 V cost-effective op amp



### Features

- Automotive grade version available 
- Gain bandwidth product 8 MHz, unity gain stable
- Rail-to-rail input and output
- Wide supply voltage range: 2.5 V to 5.5 V
- Input offset voltage: 4.5 mV
- Low input bias current: 1 pA typ.
- Extended temperature range: -40 °C to +125 °C

### Applications

- Cost-sensitive applications
- Battery-powered products
- Automotive applications

### Description

The TSL6201, TSL6202 and the TSL6204 are single, dual and quad 8 MHz bandwidth unity-gain-stable amplifiers. The rail-to-rail input stage and the wide supply range from 2.5 V to 5.5 V make the TSL620x ideal for low voltage signal conditioning.

#### Product status link

SOT23-5	<a href="#">TSL6201</a>
MiniSO8	<a href="#">TSL6202</a>
SO14	<a href="#">TSL6204</a>
TSSOP14	<a href="#">TSL6204</a>

#### Related products

For more power savings	<a href="#">TSL6001</a>
------------------------	-------------------------

## 1 Pin description

### 1.1 TSL6201 single operational amplifier

Figure 1. SOT23-5 pin connections (top view)




Table 1. SOT23-5 pin description

Pin	Pin name	Description
1	OUT	Output
2	VCC-	Negative supply voltage
3	IN+	Non-inverting input
4	IN-	Inverting input
5	VCC+	Positive supply voltage

## 1.2 TSL6202 dual operational amplifier

Figure 2. MiniSO8 pin connection (top view)




Table 2. MiniSO8 pin description

Pin	Pin name	Description
1	OUT1	Output channel 1
2	IN1-	Inverting input channel 1
3	IN1+	Non-inverting input channel 1
4	VCC-	Negative supply voltage
5	IN2+	Non-inverting input channel 2
6	IN2-	Inverting input channel 2
7	OUT2	Output channel 2
8	VCC+	Positive supply voltage

### 1.3 TSL6204 quad operational amplifier

Figure 3. SO14 and TSSOP-14 pin connections (top view)





Table 3. SO14 and TSSOP-14 pin description

Pin	Pin name	Description
1	OUT1	Output channel 1
2	IN1-	Inverting input channel 1
3	IN1+	Non-inverting input channel 1
4	V <sub>CC</sub> +	Positive supply voltage
5	IN2+	Non-inverting input channel 2
6	IN2-	Inverting input channel 2
7	OUT2	Output channel 2
8	OUT3	Output channel 3

Pin	Pin name	Description
9	IN3-	Inverting input channel 3
10	IN3+	Non-inverting input channel 3
11	VCC-	Negative supply voltage
12	IN4+	Non-inverting input channel 4
13	IN4-	Inverting input channel 4
14	OUT4	Output channel 4

## 2 Absolute maximum ratings

Table 4. Absolute maximum ratings

Symbol	Parameter	Value	Unit
$V_{CC}^{(1)}$	Supply voltage	6	V
$V_{id}$	Input voltage differential ( $V_{IN+} - V_{IN-}$ )	$\pm V_{CC}$	V
$V_{in}^{(2)}$	Input voltage	$(V_{CC-}) - 0.2$ to $(V_{CC+}) + 0.2$	V
$I_{in}$	Input current	$\pm 10$	mA
$T_{stg}$	Storage temperature	-65 to +150	°C
$R_{th-ja}^{(3)}$	Thermal resistance junction-to-ambient		°C/W
	SOT23-5	250	
	MiniSO8	190	
	SO14	105	
	TSSOP-14	100	
$T_j$	Maximum junction temperature	150	°C
ESD	HBM: human body model <sup>(4)</sup>	2	kV
	CDM: charged device model <sup>(5)</sup>	0.5	kV

1. All voltage values are with respect to the VCC- pin, unless otherwise specified.
2. The maximum input voltage value may be extended to the condition that the input current is limited to  $\pm 10$  mA.
3.  $R_{th-ja}$  is a typical value.
4. Human body model: HBM test according to the standard ESDA/JEDEC JS-001-2017.
5. Charged device model: the test CDM is done in according to the standard ESDA/JEDEC JS-002-2018.

Table 5. Operating conditions

Symbol	Parameter	Value
$V_{CC}$	Supply voltage	2.5 to 5.5 V
$V_{icm}$	Common mode input voltage range (CMR)	$V_{CC-} - 0.1$ V to $V_{CC+} + 0.1$ V
$T_{oper}$	Operating free air temperature range	-40 °C to +125 °C

### 3 Electrical characteristics

**Table 6. Electrical characteristics at  $V_{CC} = 2.5\text{ V to }5.5\text{ V}$ ,  $V_{ICM} = V_{OUT} = V_{CC} / 2$ ,  $T = 25\text{ °C}$  and OUT connected to  $V_{CC} / 2$  through  $R_L = 10\text{ k}\Omega$  (unless otherwise specified)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
<b>DC performance</b>						
$V_{io}$	Input offset voltage	$T = 25\text{ °C}$			$\pm 4.5$	mV
		$-40\text{ °C} \leq T \leq 125\text{ °C}$			$\pm 7.5$	
$DV_{io}/DT$	Input offset voltage temperature drift	$-40\text{ °C} \leq T \leq 125\text{ °C}$		$\pm 5$		$\mu\text{V}/\text{°C}$
$I_{ib}$	Input bias current			$\pm 1$		pA
$I_{io}$	Input offset current			$\pm 1$		pA
$A_{VD}$	Open loop gain	$V_{CC-} + 500\text{ mV} \leq V_{OUT} \leq V_{CC+} - 500\text{ mV}$	80	89		dB
CMR	Common-mode rejection ratio $20 \cdot \log(\Delta V_{io} / \Delta V_{icm})$	$V_{CC-} \leq V_{icm} \leq V_{CC+}$	58	78		dB
$V_{OH}$	High level output voltage drop ( $V_{OH} = V_{CC+} - V_{OUT}$ )				40	mV
$V_{OL}$	Low level output voltage drop ( $V_{OL} = V_{OUT}$ )				40	mV
$I_{OUT}$	Short-circuit	$V_{CC} = 5\text{ V}$		$\pm 30$		mA
$I_{CC}$	Supply current (by operational amplifier)	No load		750	1400	$\mu\text{A}$
<b>AC performance</b>						
GBP	Gain bandwidth product	$R_L = 2\text{ k}\Omega$ , $C_L = 100\text{ pF}$ , $f = 100\text{ kHz}$		8		MHz
SR	Slew rate	$A_V = 1\text{ V/V}$ , 10% to 90%		4.5		$\text{V}/\mu\text{s}$
$\Phi_m$	Phase margin	$R_L = 2\text{ k}\Omega$ , $C_L = 100\text{ pF}$		45		Degrees
en	Input voltage noise density	$f = 10\text{ kHz}$		21		$\text{nV}/\sqrt{\text{Hz}}$

## 4 Typical performance characteristics

Figure 4. Input offset voltage vs. common mode voltage




Figure 5. Positive slew rate vs. supply voltage




Figure 6. Negative slew rate vs. supply voltage




Figure 7. Input equivalent noise vs. frequency






Figure 8. Output current vs. output voltage




Figure 9. Supply current vs. input common voltage




Figure 10. Supply current vs. input common mode voltage





Figure 11. Bode diagram



## 5 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 5.1 SOT23-5 package information

Figure 12. SOT23-5 package outline




Table 7. SOT23-5 package mechanical data

Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.90	1.20	1.45	0.035	0.047	0.057
A1			0.15			0.006
A2	0.90	1.05	1.30	0.035	0.041	0.051
B	0.35	0.40	0.50	0.014	0.016	0.020
C	0.09	0.15	0.20	0.004	0.006	0.020
D	2.80	2.90	3.00	0.110	0.114	0.118
D1		1.90			0.075	
e		0.95			0.037	
E	2.60	2.80	3.00	0.102	0.110	0.118
F	1.50	1.60	1.75	0.059	0.063	0.069
L	0.10	0.35	0.60	0.004	0.014	0.024
K	0°		10°	0°		10°

## 5.2 MiniSO8 package information

Figure 13. MiniSO8 package outline




Table 8. MiniSO8 mechanical data

Dim.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A			1.1			0.043
A1	0		0.15	0		0.006
A2	0.75	0.85	0.95	0.03	0.033	0.037
b	0.22		0.4	0.009		0.016
c	0.08		0.23	0.003		0.009
D	2.8	3	3.2	0.11	0.118	0.126
E	4.65	4.9	5.15	0.183	0.193	0.203
E1	2.8	3	3.1	0.11	0.118	0.122
e		0.65			0.026	
L	0.4	0.6	0.8	0.016	0.024	0.031
L1		0.95			0.037	
L2		0.25			0.01	
k	0°		8°	0°		8°
ccc			0.1			0.004

### 5.3 SO14 package information

Figure 14. SO14 package outline




Table 9. SO14 package mechanical data

Symbol	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
D	8.55		8.75	0.336		0.344
E	5.8		6.2	0.228		0.244
e		1.27			0.050	
e3		7.62			0.300	
F	3.8		4.0	0.149		0.157
G	4.6		5.3	0.181		0.208
L	0.5		1.27	0.019		0.050
M			0.68			0.026
A			1.75			0.068
a1	0.1		0.2	0.003		0.007
a2			1.65			0.064
b	0.35		0.46	0.013		0.018
b1	0.19		0.25	0.007		0.010
C		0.5			0.019	
c1	45° (typ.)					
S	8° (max.)					

## 5.4 TSSOP-14 package information

Figure 15. TSSOP-14 package outline




Table 10. TSSOP-14 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A			1.20
A1	0.05		0.15
A2	0.80	1.00	1.05
b	0.19		0.30
c	0.09		0.20
D	4.90	5.00	5.10
E	6.20	6.40	6.60
E1	4.30	4.40	4.50
e	0.65 BSC		
L	0.45	0.60	0.75
L1		1.00	
k	0		8
aaa			0.10

## 6 Ordering information

**Table 11. Order code**

Order code	Temperature range	Package	Marking
TSL6201ILT	-40 °C to 125 °C	SOT23-5	KD
TSL6201IYLT <sup>(1)</sup>	-40 °C to 125 °C automotive grade		KG
TSL6202IST	-40 °C to 125 °C	MiniSO8	KE
TSL6202IYST <sup>(1)</sup>	-40 °C to 125 °C automotive grade		KJ
TSL6204IDT	-40 °C to 125 °C	SO14	TSL6204I
TSL6204IYDT <sup>(1)</sup>	-40 °C to 125 °C automotive grade		TSL6204Y
TSL6204IPT	-40 °C to 125 °C	TSSOP-14	6204I
TSL6204IYPT <sup>(1)</sup>	-40 °C to 125 °C automotive grade		6204IY

1. Qualified and characterized according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 & Q002 or equivalent. For qualification status detail, check "Maturity status link" on first page ("Quality & Reliability" tab on [www.st.com](http://www.st.com)).

## Revision history

**Table 12. Document revision history**

Date	Version	Changes
01-Dec-2021	1	Initial release.
09-Jan-2023	2	Updated features, applications on the cover page and Section 6: Ordering information.
08-Feb-2024	3	Updated title, features and description on the cover page. Updated GBP value in Table 6.
07-Nov-2024	4	Added new SO14 package and new <a href="#">Section 5.3</a> . Updated <a href="#">Figure 3</a> .

## Contents

<b>1</b>	<b>Pin description</b> .....	<b>2</b>
1.1	TSL6201 single operational amplifier .....	2
1.2	TSL6202 dual operational amplifier .....	3
1.3	TSL6204 quad operational amplifier .....	4
<b>2</b>	<b>Absolute maximum ratings</b> .....	<b>6</b>
<b>3</b>	<b>Electrical characteristics</b> .....	<b>7</b>
<b>4</b>	<b>Typical performance characteristics</b> .....	<b>8</b>
<b>5</b>	<b>Package information</b> .....	<b>10</b>
5.1	SOT23-5 package information .....	10
5.2	MiniSO8 package information .....	11
5.3	SO14 package information .....	12
5.4	TSSOP-14 package information .....	13
<b>6</b>	<b>Ordering information</b> .....	<b>14</b>
	<b>Revision history</b> .....	<b>15</b>





## List of tables

<b>Table 1.</b>	SOT23-5 pin description . . . . .	2
<b>Table 2.</b>	MiniSO8 pin description . . . . .	3
<b>Table 3.</b>	SO14 and TSSOP-14 pin description . . . . .	4
<b>Table 4.</b>	Absolute maximum ratings . . . . .	6
<b>Table 5.</b>	Operating conditions . . . . .	6
<b>Table 6.</b>	Electrical characteristics at $V_{CC} = 2.5\text{ V to }5.5\text{ V}$ , $V_{ICM} = V_{OUT} = V_{CC} / 2$ , $T = 25\text{ }^{\circ}\text{C}$ and OUT connected to $V_{CC} / 2$ through $R_L = 10\text{ k}\Omega$ (unless otherwise specified) . . . . .	7
<b>Table 7.</b>	SOT23-5 package mechanical data . . . . .	10
<b>Table 8.</b>	MiniSO8 mechanical data . . . . .	11
<b>Table 9.</b>	SO14 package mechanical data . . . . .	12
<b>Table 10.</b>	TSSOP-14 mechanical data . . . . .	13
<b>Table 11.</b>	Order code . . . . .	14
<b>Table 12.</b>	Document revision history . . . . .	15

## List of figures

<b>Figure 1.</b>	SOT23-5 pin connections (top view) . . . . .	2
<b>Figure 2.</b>	MiniSO8 pin connection (top view) . . . . .	3
<b>Figure 3.</b>	SO14 and TSSOP-14 pin connections (top view) . . . . .	4
<b>Figure 4.</b>	Input offset voltage vs. common mode voltage . . . . .	8
<b>Figure 5.</b>	Positive slew rate vs. supply voltage . . . . .	8
<b>Figure 6.</b>	Negative slew rate vs. supply voltage . . . . .	8
<b>Figure 7.</b>	Input equivalent noise vs. frequency . . . . .	8
<b>Figure 8.</b>	Output current vs. output voltage . . . . .	9
<b>Figure 9.</b>	Supply current vs. input common voltage . . . . .	9
<b>Figure 10.</b>	Supply current vs. input common mode voltage . . . . .	9
<b>Figure 11.</b>	Bode diagram . . . . .	9
<b>Figure 12.</b>	SOT23-5 package outline . . . . .	10
<b>Figure 13.</b>	MiniSO8 package outline . . . . .	11
<b>Figure 14.</b>	SO14 package outline . . . . .	12
<b>Figure 15.</b>	TSSOP-14 package outline . . . . .	13

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved