LASER DIODE MODULES CUSTOMIZED OR STOCK



WELCOME TO BEA LASERS

The highest quality laser diode modules at a reasonable cost – this is our commitment to you. Our team of applications engineers and sales associates, with many years of experience in the field of optics and photonics, will work closely with you to find a solution – customized or from stock – that meets your needs. BEA Lasers are available nationwide. Our warehouse is in suburban Chicago and ships your components as ordered and on time.

Since 1980, BEA has been committed to offering solutions to industry and research. Many products conform to and surpass the standards of CE and FDA, so your products benefit from the quality that goes into our laser diode modules.



BEA Lasers Corporate Offices

About Laser Diode Modules

Our laser diode modules feature a rugged, compact design that is suitable for industrial or laboratory uses. Heat dissipation is handled by passive radiation through the case and mounting bracket. Integrated electronics protect the diode from reverse wiring and line noise that would otherwise destroy it.

About Lenses

Adjustable focus allows you to project the sharpest beam pattern possible: this is critical for projecting lines and crosshairs. Glass lenses will render a more uniformly focused beam pattern than plastic ones. Plastic lenses, however, are lower in cost and may be sufficient for some applications.

Red and Green Laser Considerations


The human eye perceives the light emitted from a 1mW 670nm laser as bright. Laser light at 650nm is perceived as brighter, and 635nm is seen as the brightest red. Green laser light at 1mW 532nm is clearly perceived as the brightest laser diode module light.

Customization


Other available wavelengths include Blue and Infrared. Caseless construction can save space inside enclosures. Driver electronics can support static protection, beam pulsing, or TTL modulation.

Typical Applications


- Alignment
- Positioning
- Metrology
- Event Detection
- Edge Detection
- Security
- Bar Code Readers
- Vision Systems
- Education
- Leveling
- Robotic Control
- Lab Experimentation



Positioning



Event/Edge



BEA LASERS 800/783-2321 Toll-Free 847/238-1420 Phone 847/238-1423 Fax www.BeaLasers.com info@BeaLasers.com

PRODUCT GUIDE

Style 1

Industry standard design for laser diode modules. Options: emission indicator, static electricity protection.

Style 2

Cooling fins provide extra passive heat dissipation for models with higher power output.

Style 3

Ideal for long distance positioning applications. Set screws in the front of the case allow easy angle adjustment to the single beam. Case also contains a power switch.

Style 4

Green lasers. Features: superior electronic and mechanical ruggedness; excellent heat dissipation.

Style 5

Compatible with 1" mounts. Features: superior ruggedness, beam attenuation shutter, focusing lens, power switch with emission indicator, 2.5mm socket connector for power, and regulated AC adapter.

PART NUMBERING

(Example) 201 H-1-635

Platform:

a unique set of module properties including: optical, mechanical, electrical and environmental

Features:

- H Anti-Static Housing
- P Power Adapter
- **S** Shutter
- C Cross Hair Generator
- L Line Generator

Power: in milliwatts

Wavelength: in nanometers

	Laser Modu		DDE									
						Body Sty	/le 1	Body	Style 2	•		
	Part Number	Class	Beam Diam (mm)	Power (mw)	Body Style	Body Material	Lens Material	Operating Current (mA)	Operating Voltage (DC)	Case Length (mm)	Case Diam (mm)	
Cross Hair Beam Pattern (projected size: 15cm @ 1m), 1-6 milliwatts												
- 1 - E	150C-1-635	П	<1	1	1	Aluminum	Glass	40	4.5-9	50.8	12.7	
	150C-3-635	Illa	<1	3	1	Aluminum	Glass	40	4.5-9	50.8	12.7	
	150C-6-635	IIIb	<1	6	1	Aluminum	Glass	70	4.5-9	50.8	12.7	
	150C-3-650	Illa	<1	3	1	Aluminum	Glass	30	4.5-9	50.8	12.7	
	150C-5-650	Illa	<1	4.5	1	Aluminum	Glass	50	4.5-9	50.8	12.7	
	Line Beam Pa	ttern (p	roiected	d line: 1	17cm (@ 1m 60 deg fan a	angle), 2-3 (milliwatts				
	151L-2-670	Illa	<1	1.6	1	Aluminum	Glass	40	4.5-9	51	13.5	
	151L-3-670	Illa	<1	3	1	Aluminum	Glass	40	4.5-9	51	13.5	
	Green Lasers,	522 nm	1_2 mi	lliwatte								
	622-1-532	332 IIII 	5 1, 1 -3 111	1	4	Aluminum	Glass	<500	3	70	20	
	622-3-532		5	3	4	Aluminum	Glass	<500	3	70	20	
	Red Lasers, 63								-			
	201-1-635	11	4	1	1	Copper	Plastic	45-50	3	32.5	10.5	
	206-1-635		4	1	1	Copper	Glass	<80	3-4.5	45.1	12	
	206H-1-635	11	4	1	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5	
	201H-1-635		4.2	1	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21	
	203-1-635		4.8	1	1	Copper	Plastic	<45	3	37.1	14	
	203H-1-635		4.8	1	1	Brass, Anti-Static	Plastic	<45	3	53.5	22	
	202-1-635		5	1	1	Copper Brace Anti Static	Plastic	<45	3	42.7	12	
	202H-1-635	 	5 5	1 1	1 1	Brass, Anti-Static Aluminum	Plastic Glass	45 60	3 4-6	59 40	20.2 16	
	145-1-635	П	Э	I	I	Aluminum	Glass	60	4-0	40	10	
•	Red Lasers, 63	-				-						
	201-3-635	Illa	4	3	1	Copper	Plastic	45-50	3	32.5	10.5	
	206-3-635	Illa	4	3	1	Copper	Glass	<80	3-4.5	45.1	12	
	206H-3-635	Illa	4	3	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5	
	201H-3-635	Illa	4.2	3	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21	
	203-3-635	Illa	4.8	3	1	Copper	Plastic	<45	3	37.1	14	
	203H-3-635	Illa	4.8	3	1	Brass, Anti-Static	Plastic	<45	3	53.5	22	
	202-3-635 202H-3-635	llla Illa	5 5	3 3	1 1	Copper Brass, Anti-Static	Plastic Plastic	<45 45	3 3	42.7 59	12 20.2	
	20211-3-035	ша	J	J	1	Diass, Anti-Static	Tastic	43	5	59	20.2	
٠	Red Lasers, 63				-	c		45 50	2		46 -	
	201-5-635	IIIb	4	5	1	Copper	Plastic	45-50	3	32.5	10.5	
	206-5-635	IIIb	4	5	1	Copper	Glass	<80	3-4.5	45.1	12	
	206H-5-635	IIIb	4	5	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5	
	201H-5-635	IIIb	4.2	5	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21	
	203-5-635	IIIb	4.8	5	1	Copper	Plastic	<45	3	37.1	14	
	203H-5-635	IIIb	4.8	5	1	Brass, Anti-Static	Plastic	<45	3	53.5	22	
	202-5-635	IIIb	5	5	1	Copper Brace Anti Static	Plastic	<45	3	42.7	12	
	202H-5-635	lllb IIIb	5	5 10	1	Brass, Anti-Static	Plastic	45	3 3	59 53 5	20.2 22	
	203H-10-635	IIIb	4.8	10	1	Brass, Anti-Static	Plastic	<45	č	53.5	22	



Laser Diode Modules





						Body Style 3	Body Style 4		Body St	yle 5	
			Beam					Operatina	Operating	Case	Case
	Part		Diam	Power	Body	Body	Lens	Current	Voltage	Length	Diam
	Number	Class	(mm)	(mw)	Style	Material	Material	(mA)	(DC)	(mm)	(mm)
	Red Lasers, 65	-0 1									
•	201-1-650	90 nm, 1 	4	וננ 1	1	Copper	Plastic	45-50	3	32.5	10.5
	206-1-650	" 	4	1	1	Copper	Glass	<80	3-4.5	45.1	10.5
	206H-1-650	"	4	1	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5
	201H-1-650		4.2	1	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21.5
	203-1-650	"	4.8	1	1	Copper	Plastic	<45	3	37.1	14
	203 H-050	"	4.8	1	1	Brass, Anti-Static	Plastic	<45 <45	3	53.5	22
	202-1-650		5	1	1	Copper	Plastic	<45	3	42.7	12
	202H-1-650		5	1	1	Brass, Anti-Static	Plastic	45	3	59	20.2
	145-1-650		5	1	1	Aluminum	Glass	36	4-6	40	16
•	Red Lasers, 65					c					10 5
	201-3-650	Illa	4	3	1	Copper	Plastic	45-50	3	32.5	10.5
	206-3-650	Illa	4	3	1	Copper	Glass	<80	3-4.5	45.1	12
	206H-3-650	Illa	4	3	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5
	201H-3-650	Illa	4.2	3	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21
	203-3-650	Illa	4.8	3	1	Copper	Plastic	<45	3	37.1	14
	203H-3-650	Illa	4.8	3	1	Brass, Anti-Static	Plastic	<45	3	53.5	22
	202-3-650	Illa	5	3	1	Copper	Plastic	<45	3	42.7	12
	202H-3-650	Illa	5	3	1	Brass, Anti-Static	Plastic	45	3	59	20.2
	218-3-650	Illa	5	3	3 1	Copper	Plastic	<45	3	59	19
	145-3-650	llla	5	3	I	Aluminum	Glass	50	4-6	40	16
	Red Lasers, 65	50 nm, 5	5 milliwa	atts							
	145-5-650	Illa	5	4.5	1	Aluminum	Glass	120	4-6	40	16
	201-5-650	IIIb	4	5	1	Copper	Plastic	45-50	3	32.5	10.5
	206-5-650	IIIb	4	5	1	Copper	Glass	<80	3-4.5	45.1	12
	206H-5-650	IIIb	4	5	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5
	201H-5-650	IIIb	4.2	5	1	Brass, Anti-Static	Plastic	45-50	3	53.5	21
	203-5-650	IIIb	4.8	5	1	Copper	Plastic	<45	3	37.1	14
	203H-5-650	IIIb	4.8	5	1	Brass, Anti-Static	Plastic	<45	3	53.5	22
	202-5-650	IIIb	5	5	1	Copper	Plastic	<45	3	42.7	12
	202H-5-650	IIIb	5	5	1	Brass, Anti-Static	Plastic	45	3	59	20.2
•	Red Lasers, 65	50nm <i>,</i> 1	0-35 mi	lliwatts							
	206-10-650	IIIb	4	10	1	Copper	Glass	<80	3-4.5	45.1	12
	206H-10-650	IIIb	4	10	1	Brass, Anti-Static	Glass	<80	3-4.5	62.5	21.5
	203-10-650	IIIb	4.8	10	1	Copper	Plastic	<45	3	37.1	14
	208-10-650	IIIb	5	10	2	Aluminum	Glass	<180	4.5	51	25
	208H-10-650	IIIb	5	10	1	Brass, Anti-Static	Glass	<180	4.5	67.5	33.2
	208-20-650	IIIb	5	20	2	Aluminum	Glass	<180	4.5	51	25
	208H-20-650	IIIb	5	20	1	Brass, Anti-Static	Glass	<180	4.5	67.5	33.2
	208-30-650	IIIb	5	30	2	Aluminum	Glass	<180	4.5	51	25
	208H-30-650	IIIb	5	30	1	Brass, Anti-Static	Glass	<180	4.5	67.5	33.2
	208-35-650	IIIb	5	35	2	Aluminum	Glass	<180	4.5	51	25
	208H-35-650	IIIb	5	35	1	Brass, Anti-Static	Glass	<180	4.5	67.5	33.2
_	.	-	.								
	Red Lasers, 67						Class	<150	F	E 1	75
	175SP-1-670	 _2	5 x 2	0.9	5	Aluminum	Glass	<150	5	51 51	25
	175SP-3-670	Illa	5 x 2	3	5	Aluminum	Glass	<150	5	51	25

DETECTORS

Designing your own emitter/detector system? These popular components benefit you through superior clean room manufacturing and economies of scale for a most competitive price. Surface-mount versions are available.



DST80036 DST80032 Technical Specifications: Parameter Symbol Test Condition Minimum Maximum Typical DST80032 Active Area 8.1 mm² Spectral Response λ 1200 nm 400 nm Spectral Responsivity R 632 nm 0.36 A/W* Spectral Responsivity R 920 nm 0.62 A/W $V_r = 10V$ Dark Current D 30 nA 5 nA $I_{bd} = 100 \,\mu A$ Reverse Breakdown Voltage VBR 33 V 170 V Rise Time Tr $V_r = 10 V, 100 ohm$ 50 nsec Total Capacitance Ct 1 MHz, 3 V 25 pF

DST80035

Active Area					2.9 mm ²
Spectral Response	λ		400 nm	1100 nm	
Spectral Responsivity	R	632 nm			0.36 A/W
Spectral Responsivity	R	920 nm			0.62 A/W
Reverse Breakdown Voltage	Vbr	lbd = 100 μA			80 V
Rise Time	Tr	Vr = 10 V, 100 ohm			30 nsec

DST80036

				1.7 mm ²
λ		400 nm	1100 nm	
R	632 nm			0.36 A/W
R	920 nm			0.62 A/W
D	$V_r = 10 \text{ mV}$	200 pA	600 pA	
VBR	$I_{bd} = 10 \ \mu A$			80 V
Tr	Vr = 5V, 50 ohm			100 nsec
CJ	10 kHz, 0 V			30 pF
CJ	10 kHz, 10 V			6 pF
	R R ID VBR Tr CJ	$\begin{tabular}{c c c c c c c } \hline R & 632 nm \\ \hline R & 920 nm \\ \hline ID & Vr = 10 mV \\ \hline V_{BR} & I_{bd} = 10 \mu A \\ \hline T_r & Vr = 5V, 50 ohm \\ \hline C_J & 10 kHz, 0 V \\ \hline \end{tabular}$	$\begin{tabular}{c c c c c c c c c c c c c c c c c c c $	$\begin{tabular}{c c c c c c c c c c c c c c c c c c c $

* A/W = Amps per Watt (Electrical current out per optical power in)





POWER SUPPLIES

BEA-220: A convenient 3VDC power supply for use in testing laser diode modules. Powered by 2x1.5 Volt Batteries.



Regulated power supply for laser diode modules. Provides extra power conditioning to protect the laser diode. Converts 120VAC to 5VDC, 300mA. UL Listed, Class 2 Transformer.

BEA-230:

Figure 1: The optical spectrum. Laser light is nonionizing and ranges from the ultra-violet (100 - 400nm), visible (400 - 700nm), and infrared (700nm - 1mm).

X-RAYS		ULTRAVIO	LET		VI	SIBL	E	NEA	R-INI	FRARE	D	MID-INFRARED		FAF	R-INFRARED
1Å 0.1 nm	10Å 1 nm	100 nm 200 0.1 mm nm	300 nm	400 nm	500 nm	600 nm	700 nm	800 nm	900 nm	1000 nm 1 μm	3 μm		30	μm	1000 μm (1mm)
						1	1			. µ				I	I

WHAT IS A LASER?

LASER is an acronym which stands for Light Amplification by Stimulated Emission of Radiation. The energy generated by the laser is in or near the optical portion of the electromagnetic spectrum (see Figure 1). Energy is amplified to extremely high intensity by an atomic process called stimulated emission. The color of laser light is normally expressed in terms of the laser's wavelength. Nanometer (nm) is the most common unit used in expressing a laser's wavelength.

LASER HAZARDS & BEAM HAZARDS

The laser produces an intense, highly directional beam of light. If directed, reflected, or focused upon an object, laser light will be partially absorbed, raising the temperature of the surface and/or the interior of the object, potentially causing an alteration or deformation of the material. Lasers can also cause tissue damage. Today, most high-power lasers are designed to minimize access to laser radiation during normal operation. Lower-power lasers may emit levels of laser light that are not a hazard.

LASER HAZARDS CLASSIFICATION

The Center for Devices and Radiological Health, a division of the Food and Drug Administration regulates the manufacturing and classification of laser products. The laser classes help group lasers by their hazard potential, and identifies these classes based on their optical emission (wavelength, exposure time, output power).

GENERAL GUIDELINES FOR CW LASER CLASSIFICATION

Class I Lasers or laser systems that do not, under normal operating conditions, pose a hazard.

Class lla Low power visible lasers or laser systems that are not intended for prolonged viewing, and under normal operating conditions will not produce a hazard if the beam is viewed directly for periods not exceeding 1000 seconds.

Class II Low power visible lasers or laser systems which, because of the normal human aversion response, do not normally present a hazard, but may present some potential for hazard if viewed directly for extended periods of time (like many conventional light sources).

Class Illa Lasers or laser systems having a CAUTION label that normally would not injure the eye if viewed for only momentary periods (within the aversion response period) with the unaided eye, but may present a greater hazard if viewed using collecting optics. Another group of Class 3a lasers have DANGER labels and are capable of exceeding permissible exposure levels for the eye in 0.25 seconds and still pose a low risk of injury. **Class IIIb** Lasers or laser systems that can produce a hazard if viewed directly. This includes intrabeam viewing of specular reflections. Class 3B lasers will not normally produce a hazardous diffuse reflection.


Class IV Lasers or laser systems that produce a hazard not only from direct or specular reflections, but may also produce hazardous diffuse reflections. Such lasers may produce significant skin hazards as well as fire hazards.

The information mentioned here is intended to be an introduction to lasers and laser safety, and should not be considered to be an authoritarian guide. A better informed user has the knowledge to make safer decisions: learn about safety procedures for your class of laser, and the next class higher.

An excellent source for laser safety is the Laser Institute of America. A very useful resource is their web-based *Safety Bulletin* and printed *Laser Safety Guide*.

LASER DIODE MODULE GLOSSARY

Term	Definition
Angstrom	Metric unit equal to 10 ⁻¹⁰ meter.
Beam Diameter	Calculated distance between two exactly opposed points on a beam at a chosen fraction of peak power.
Beam Divergence	Increase in the diameter of an initially collimated beam as measured in milliradians (mrad) at specified points.
CDRH	Center for Devices and Radiological Health.
CW	Continuous Wave.
LASER	Light Amplification by Stimulated Emission of Radiation.
Laser Diode Module	Small semiconductor laser packaged in a durable housing.
Micron	One-millionth of a meter ($1\mu m = 10^{-6}m$).
Milli	Prefix for one-thousandth (10 ⁻³).
Millimeter	0.001 meter.
MRad	Milli-Radian; 1/1000 of a radian used to specify laser beam divergence.
Nanometer	One-billionth of a meter $(1nm = 10^{-9}m)$.
Watt	Unit of power that produces energy at the rate of 1 joule per second.
Wavelength	Electromagnetic energy transmitted in the form of a sinusoidal wave; the physical distance covered by one cycle of this wave. Wavelength is inversely proportional to frequency.



BEA Lasers is a Corporate Member of the Laser Institute of America.

Note: The data and dimensions contained in this catalog are intended for use as a guide and are subject to change and/or update by BEA Electro Sales, Inc. without notice. Every care has been taken to ensure that the information contained within this catalog is accurate from the date of publication. BEA Electro Sales will not accept responsibility for damage, loss, or expense resulting from any error or omission contained herein. Furthermore, all products are sold with the understanding that users will perform all necessary tests to determine the suitability of these products for their intended use.



2330 Brickvale Drive Elk Grove Village IL 60007 800/783-2321 Toll-Free 847/238-1420 Phone

847/238-1420 Filone 847/238-1423 Fax www.BeaLasers.com info@BeaLasers.com



BirrenDesign.com