

VD56G3 promodules:

Camera module evaluation samples for instant integration of VD56G3 sensor





Order code	Description			
CAM-6G3-073CLR	VD56G3 promodule with 73° FoV lens			
CAM-6G3-084CLR	VD56G3 promodule with 84° FoV lens			
CAM-6G3-152CLR	VD56G3 promodule with 152° FoV lens			

Features

- "Promodules": turnkey camera modules for evaluation:
 - Including VD56G3 image sensor, lens holder, lens, and plug-and-play flex connection.
 - Lens focused, glued, and tested in cleanroom environment using specialized equipment.
 - Small footprint down to 6.5 mm square.
- · Various lens options:
 - Ultra-wide-angle lens for wide scene capture (152° DFOV).
 - Highly compact lens for a thin module (84° DFOV).
 - General purpose lens enabling various system setups (73° DFOV).
- Plug-and-play connector to change promodules at any time:
 - FPC-to-board 30-pin connector.
 - Same connector for all ST promodules.
- Ready for evaluation and integration:
 - On computer with a USB output using the EVK Main hardware tool and the Evaluation GUI free software.
 - On embedded processing platforms with a MIPI CSI-2 output using the P-Board hardware tool and free Linux software tools.
- Promodules also available in color RGB versions (CAM-66GY).

Description

The CAM-56G3 promodules are a full range of sample camera modules made for a seamless evaluation and integration of the VD56G3 1.5-megapixel monochrome image sensor. These ready-to-use vision extensions integrate VD56G3 image sensor, lens holder, lens, and plug-and-play flex connection in a tiny format down to 6.5 mm square.

The CAM-56G3 line leverages the complete toolbox of on-chip features of the VD56G3 image sensor embedded, such as binning, autoexposure, or context management. Multiple GPIOs enable users to synchronize the modules with triggers and illumination. Featuring MIPI CSI-2 output, the promodules are perfectly suited for embedded low-power setups.

Multiple promodule references are available, featuring various lenses to best match the needs of every application in terms of optical setup and mechanical constraints. All camera modules are equipped with the same FPC-to-board connector and pinout. This plug-and-play architecture allows users to change promodule instantly, and reuse the same setup with different lenses, color options and even different image sensors in the ST BrightSense portfolio.

CAM-56G3 promodules can be tested and integrated on computers or embedded processing boards using hardware and software tools from STMicroelectronics. The compatible EVK Main and P-Board hardware kits enable straight connection to PC and embedded processing platforms respectively. Evaluation GUI software and Linux drivers are available for download from the Imaging Software section of the website.

GND -- VANA 2V8 VCORE_1V15 -3 GND XSHUTDOWN — 6 5 VDDIO_1V8 GND -8 7 DATA 1P -10 9 DATA 1N -12 11 GND — 14 13 CLKP -16 15 CLKN — 18 17 02 - NC GND -20 19 NC DATA 2P -22 21 DATA 2N-24 23 GND GND -26 25 - SCL CLKIN -- SDA 28 27 GND GND -30 29

Figure 1. Common connector to all ST promodules

Table 1. Evaluation & development setup with CAM-56G3 promodules



DB5264 - Rev 1 page 2/5



1 Technical specifications

Table 2. Technical specifications

Category	Parameter	Common specifications			
	Sensor featured	VD56G3			
Image characteristics	Resolution	1.53 MP – 1124 x 1364			
	Aspect ratio	5:6			
	Shutter type	Global shutter			
	Color option	Monochrome			
Electrical characteristics	Connector type	FPC-to-board			
	Connector reference	Hirose BM28 B0.6-30DP/2-0.35V			
	Pinout	30 pins			
	Output interface	MIPI CSI-2 1 or 2 lanes			
	Control interface	I ² C			
	Output format	RAW8, RAW10			
	Supply voltages	2.8 V – 1.8 V – 1.15 V			
	External clock frequency	6 to 27 MHz			
Embedded features	Image quality optimization	 Autoexposure Automatic dark calibration Defective pixel correction Analog and digital gains 			
	Power and data optimization	 Cropping Binning Subsampling Context management with up to 4 contexts 			
	Others	 Mirror/Flip Test pattern generation Temperature sensor GPIOs x6 			
Category	Parameter	CAM-6G3-073CLR	CAM-6G3-084CLR	CAM-6G3-152CLR	
	Aperture – f/#	F/2.2	F/2.0	F/2.0	
	Field of view – D H V	73° 51° 60°	84° 60° 69°	152° 97° 118°	
Optical characteristics	EFL	3.03 mm	2.51 mm	1.69 mm	
	Depth of field	40 cm -> ∞	30 cm -> ∞	40 cm -> ∞	
	TV distortion	< 1 %	< 1.5 %	< 27 %	
	Filter	Clear	Clear	Clear	
Mechanical characteristics	Module head dimension – L x W x H	6.5 x 6.5 x 4.68 mm	6.5 x 6.5 x 3.98 mm	9.0 x 9.0 x 7.15 mm	
	Module total dimension – L x W x H	12.4 x 8.0 x 4.68 mm	12.4 x 8.0 x 3.98 mm	13.65 x 9.0 x 7.15 mm	
	Distance from connector to optical center	7.45 mm	7.45 mm	7.45 mm	

DB5264 - Rev 1 page 3/5



Revision history

Table 3. Document revision history

Date	Version	Changes
21-May-2024	1	Initial release

DB5264 - Rev 1 page 4/5



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved

DB5264 - Rev 1 page 5/5